

## PMP11064 REV A Bill of Materials

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
IPCB800	1		PMP11064	Any	Printed Circuit Board	
C500	1	1500pF	DE2E3KY152MN3AM02	MuRata	CAP, CERM, 1500 pF, 250 V, +/- 20%, E, TH, 2- Leads, Body 7x5mm, Pin Spacing 7.5mm	TH, 2- Leads, Body 7x5mm, Pin Spacing 7.5mm
C501, C502	2	47pF	GRM1555C1E470JA01D	MuRata	CAP, CERM, 47pF, 25V, +/-5%, C0G/NP0, 0402	0402
C503, C903	2	0.047uF	GRM32DR72J473KW01L	MuRata	CAP, CERM, 0.047 μF, 630 V, +/- 10%, X7R, 1210	1210
C504, C525	2	DNP	Used in BOM report	Used in BOM report	CAP, CERM, xxxF, xxV, [TempCo], xx%, [PackageReference]	Used in PnP output
C505	1	0.22uF	12065C224KAT2A	AVX	CAP, CERM, 0.22 μF, 50 V, +/- 10%, X7R, 1206	1206
C506, C507, C905	3	1uF	C0603C105K8PACTU	Kemet	CAP, CERM, 1 μF, 10 V, +/- 10%, X5R, 0603	0603
C508, C509	2	1uF	0805YD105KAT2A	AVX	CAP, CERM, 1 μF, 16 V, +/- 10%, X5R, 0805	0805
C510, C511, C513, C516, C517, C518	6	680uF	35ZLH680MEFC10X23	Rubycon	CAP ALUM 680UF 20% 35V RADIAL	10x25
C512, C523	2	0.1uF	08055C104KAT2A	AVX	CAP, CERM, 0.1uF, 50V, +/-10%, X7R, 0805	0805
C514, C515	2	220pF	06031C221KAT2A	AVX	CAP, CERM, 220 pF, 100 V, +/- 10%, X7R, 0603	0603
C519	1	0.033uF	121MPE333J	Rubycon	CAP, Film, 0.033 μF, 1250 V, +/- 5%, TH	18x9.5x18mm
C524	1	0.015uF	121MPE153J	Rubycon	CAP, Film, 0.015 μF, 1250 V, +/- 5%, TH	18x7.5x13mm
C526	1	100pF	GRM31A7U3A101JW31D	MuRata	CAP, CERM, 100pF, 1000V, +/-5%, U2J, 1206	1206
C527	1	0.47uF	C0603C474K4RACTU	Kemet	CAP, CERM, 0.47uF, 16V, +/-10%, X7R, 0603	0603
C528	1	0.01uF	C0603C103K5RACTU	Kemet	CAP, CERM, 0.01uF, 50V, +/-10%, X7R, 0603	0603
C529	1	100pF	C1608C0G1H101J	TDK	CAP, CERM, 100pF, 50V, +/-5%, C0G/NP0, 0603	0603
C530	1	0.01uF	C0603C103J5RACTU	Kemet	CAP, CERM, 0.01 μF, 50 V, +/- 5%, X7R, 0603	0603
C531, C915	2	4.7pF	06035A4R7CAT2A	AVX	CAP, CERM, 4.7 pF, 50 V, +/- 5%, C0G/NP0, 0603	0603
C532	1	0.22uF	08053C224JAT2A	AVX	CAP, CERM, 0.22uF, 25V, +/-5%, X7R, 0805	0805
C533, C907, C908	3	1uF	C0603C105K4PACTU	Kemet	CAP, CERM, 1uF, 16V, +/-10%, X5R, 0603	0603
C534, C535	2	0.1uF	GRM155R61E104KA87D	MuRata	CAP, CERM, 0.1 μF, 25 V, +/- 10%, X5R, 0402	0402
C536	1	1uF	C3216X7R1H105K	TDK	CAP, CERM, 1uF, 50V, +/-10%, X7R, 1206	1206
C800, C806	2	100pF	DE6B3KJ101KN3A	MuRata	CAP CER 100PF 300VAC 10% RADIAL	TH, 2- Leads, Body 8x7mm, Pin Spacing 7.5mm
C801, C807	2	220pF	DE6B3KJ221KN3A	MuRata	CAP, CERM, 220 pF, 300 V, +/- 10%, B, TH, 2- Leads, Body 8x7mm, Pin Spacing 7.5mm	TH, 2- Leads, Body 8x7mm, Pin Spacing 7.5mm
C802	1	1uF	450MPK105J	Rubycon	CAP, Film, 1 μF, 450 V, +/- 5%, TH	18x9.5mm
C804	1	0.22uF	ECQ-U2A224ML	Panasonic	CAP, Film, 0.22uF, 275V, +/-20%, TH	17.5x8x17.5mm
C805	1	0.47uF	ECQ-U2A474ML	Panasonic	CAP, Film, 0.47uF, 275V, +/-20%, TH	Radial 25x8.5x18.5
C808	1	270uF	450VXH270MEFCSN30X30	Rubycon	CAP ALUM 270UF 450V 20% SNAP	D30xL30mm
C810	1	1uF	GRM319R61E105KC36D	MuRata	CAP, CERM, 1uF, 25V, +/-10%, X5R, 1206	1206
C811, C818	2	2.2uF	0805YD225KAT2A	AVX	CAP, CERM, 2.2 μF, 16 V, +/- 10%, X5R, 0805	0805
C812, C813	2	22pF	C0603C220J5GACTU	Kemet	CAP, CERM, 22 pF, 50 V, +/- 5%, C0G/NP0, 0603	0603
C814, C816	2	1000pF	C1608X7R1H102K	TDK	CAP, CERM, 1000 pF, 50 V, +/- 10%, X7R, 0603	0603
C815	1	1uF	GRM188R71E105KA12D	MuRata	CAP, CERM, 1 μF, 25 V, +/- 10%, X7R, 0603	0603
C817	1	820pF	06035A821JAT2A	AVX	CAP, CERM, 820 pF, 50 V, +/- 5%, C0G/NP0, 0603	0603
C819	1	1uF	UMK107AB7105KA-T	Taiyo Yuden	CAP, CERM, 1 μF, 50 V, +/- 10%, X7R, 0603	0603
C820	1	0.1uF	EMK107B7104KA-T	Taiyo Yuden	CAP, CERM, 0.1 μF, 16 V, +/- 10%, X7R, 0603	0603
C821	1	1000pF	06031C102MAT2A	AVX	CAP, CERM, 1000 pF, 100 V, +/- 20%, X7R, 0603	0603
C822	1	680pF	GRM188R71H681KA01D	MuRata	CAP, CERM, 680 pF, 50 V, +/- 10%, X7R, 0603	0603

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
C900, C904	2	100uF	EEU-FR1C101	Panasonic	CAP ALUM 100UF 16V 20% RADIAL	6.3x11.2mm
C901	1	1uF	12063C105KAT2A	AVX	CAP, CERM, 1 µF, 25 V, +/- 10%, X7R, 1206	1206
C902, C906, C913, C914	4	0.1uF	06033C104JAT2A	AVX	CAP, CERM, 0.1 µF, 25 V, +/- 5%, X7R, 0603	0603
C909	1	680pF	VY2681M29Y5US63V7	Vishay	CAP CER 680PF 440VAC 20% RADIAL	10.0x8.0x14.0mm
C910	1	0.01uF	06031C103JAT2A	AVX	CAP, CERM, 0.01 µF, 100 V, +/- 5%, X7R, 0603	0603
C911	1	220uF	EEU-FR1C221	Panasonic	CAP ALUM 220UF 16V 20% RADIAL	6.3x11.2mm
C912	1	1uF	GRM31MR71H105KA88L	MuRata	CAP, CERM, 1 µF, 50 V, +/- 10%, X7R, 1206	1206
C916	1	10uF	GRM31CR61E106KA12L	MuRata	CAP, CERM, 10uF, 25V, +/-10%, X5R, 1206	1206
D500, D501	2	100V	BAS316,115	NXP Semiconductor	Diode, Ultrafast, 100 V, 0.25 A, SOD-323	SOD-323
D502	1	600V	MURA160T3G	ON Semiconductor	Diode, Ultrafast, 600 V, 1 A, SMA	SMA
D503, D504, D801, D805	4	0.35V	BAT54HT1G	ON Semiconductor	Diode, Schottky, 30V, 0.2A, SOD-323	SOD-323
D505, D506	2	0.63V	BAV99WT1G	Fairchild Semiconductor	Diode, P-N, 70V, 0.2A, SOT-323	SOT-323
D507	1	20V	MMSZ5250B-7-F	Diodes Inc.	Diode, Zener, 20 V, 500 mW, SOD-123	SOD-123
D800, D804	2	0.98V	MUR860G	ON Semiconductor	Diode, Ultrafast, 600V, 8A, TH	TO-220AC
D802	1	GBU8J	GBU8J	Vishay	DIODE GPP 8A 600V GPP INLINE GBU	GBU
D803	1	20V	MMSZ5250B-7-F	Diodes Inc.	Diode, Zener, 20V, 500mW, SOD-123	SOD-123
D900, D903, D904	3	100V	SS110-TP	Micro Commercial Component	Diode, Schottky, 100 V, 1 A, SMA	SMA
D901	1	140V	SMCJ140A	AVX	TVS DIODE 140VWM 227VC SMC	SMC
D902	1	1.7V	US1M-13-F	Diodes Inc.	Diode, Ultrafast, 1000V, 1A, SMA	SMA
D905	1		BAS20HT1G		DIODE SWITCH 200V 200MA SOD323	SOD-323
D906	1	100V	MMDL914-TP	Micro Commercial Component	Diode, Switching, 100 V, 0.2 A, SOD-323	SOD-323
F800	1		37216300001	Littelfuse	Fuse, 6.3 A, 250 V, TH	TR5 fuse 8.5mm DIA
H500	1		578622B03200G	Aavid	Twin Channel Style Heat Sink, TO-220, Vertical	Twin Channel Style Heat Sink, TO-220
H501, H800, H802	3		513101B02500G	Aavid	BOARD LEVEL HEAT SINK	12.70x50.80x34.92 mm
H801	1		532602B02500G	Aavid	Heat Sink, TO-220 Vertical	Heat Sink, TO-220 Vertical
H900, H901, H902, H903	4		NY PMS 440 0025 PH	B&F Fastener Supply	Machine Screw, Round, #4-40 x 1/4, Nylon, Philips panhead	Screw
H904, H905, H906, H907	4		1902C	Keystone	Standoff, Hex, 0.5"L #4-40 Nylon	Standoff
J500, J501	2	2x1	1715721	Phoenix Contact	Conn Term Block, 2POS, 5.08mm, TH	2POS Terminal Block
J800	1		1-1318301-3	TE Connectivity	Header, 312mil, 3x1, Tin, TH	19.7x10.7 x8.5 mm
L500	1	40uH	TBD	Delta Electronics Inc.	Inductor, high u, 40 µH, 5.8 A, 0.024 ohm, TH	17.5x16.7mm
L800, L804	2	150 µH	PFC4124QM-151XXX	TDK	Transformer, 160 uH, TH	43x38mm
L802	1	1mH	744824101	Würth Elektronik eiSos	CHOKE TOROID 1.0MH 10A VERT	18.5x33x27.5 mm
L803	1	3.3mH	7448256033	Würth Elektronik eiSos	CHOKE COM MODE 3.3MH 6.0A	30x35x21mm
Q500, Q501	2	100V	BSS123	Fairchild Semiconductor	MOSFET, N-CH, 100 V, 0.17 A, SOT-23	SOT-23
Q502, Q505	2	60V	CSD18532KCS	Texas Instruments	MOSFET, N-CH, 60 V, 100 A,	
Q503, Q504, Q800, Q803	4	500V	IPW50R190CE	Infineon Technologies	MOSFET N-CH 500V 18.5A TO247	TO-247
Q506, Q902	2	60V	2N7002-7-F	Diodes Inc.	MOSFET, N-CH, 60 V, 0.17 A, SOT-23	SOT-23
Q802	1	650V	STB45N65M5	ST Microelectronics	MOSFET N CH 650V 35A D2PAK	DDPAK
Q900, Q901	2	40 V	MMBT4403	Fairchild Semiconductor	Transistor, PNP, 40 V, 0.6 A, SOT-23	SOT-23
R500, R501, R502, R503	4	10.0	RC0603FR-0710RL	Yageo America	RES, 10.0, 1%, 0.1 W, 0603	0603
R504, R522	2	DNP	Used in BOM report	Used in BOM report	RES, xxx ohm, x%, xW, [PackageReference]	Used in PnP output
R505, R506	2	100k	CRCW0603100KFKEA	Vishay-Dale	RES, 100k ohm, 1%, 0.1W, 0603	0603
R507	1	3.3	CRCW12063R30JNEA	Vishay-Dale	RES, 3.3, 5%, 0.25 W, 1206	1206
R508, R509	2	221k	CRCW0603221KFKEA	Vishay-Dale	RES, 221k ohm, 1%, 0.1W, 0603	0603

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
R510, R518, R800, R809	4	3.0	CRCW06033R00JNEA	Vishay-Dale	RES, 3.0 ohm, 5%, 0.1W, 0603	0603
R511, R521	2	20.0k	CRCW080520K0FKEA	Vishay-Dale	RES, 20.0k ohm, 1%, 0.125W, 0805	0805
R512, R516, R540, R822	4	0	CRCW06030000Z0EA	Vishay-Dale	RES, 0, 5%, 0.1 W, 0603	0603
R513, R514, R517, R520	4	0.01	CSRN2010FK10L0	Stackpole Electronics Inc	RES, 0.01, 1%, 1 W, 2010	2010
R523, R538, R544	3	10.0	CRCW060310R0FKEA	Vishay-Dale	RES, 10.0, 1%, 0.1 W, 0603	0603
R524, R527	2	51	CRCW060351R0JNEA	Vishay-Dale	RES, 51, 5%, 0.1 W, 0603	0603
R525	1	1.0Meg	CRCW06031M00JNEA	Vishay-Dale	RES, 1.0 M, 5%, 0.1 W, 0603	0603
R526, R528, R534	3	10.0k	CRCW060310K0FKEA	Vishay-Dale	RES, 10.0k ohm, 1%, 0.1W, 0603	0603
R529	1	15.8k	CRCW060315K8FKEA	Vishay-Dale	RES, 15.8 k, 1%, 0.1 W, 0603	0603
R530, R537	2	15	CRCW060315R0JNEA	Vishay-Dale	RES, 15 ohm, 5%, 0.1W, 0603	0603
R531	1	511	CRCW0603511RFKEA	Vishay-Dale	RES, 511, 1%, 0.1 W, 0603	0603
R532	1	10k	3386P-1-103LF	Bourns	TRIMMER, 10k ohm, 0.5W, TH	375x190x375mil
R533, R906, R909	3	10.0k	CRCW060310K0FKEA	Vishay-Dale	RES, 10.0 k, 1%, 0.1 W, 0603	0603
R535	1	30.1k	CRCW060330K1FKEA	Vishay-Dale	RES, 30.1 k, 1%, 0.1 W, 0603	0603
R536, R546, R547	3	1.00k	CRCW06031K00FKEA	Vishay-Dale	RES, 1.00 k, 1%, 0.1 W, 0603	0603
R539	1	100k	CRCW0402100KFKEA	Vishay-Dale	RES, 100k ohm, 1%, 0.063W, 0402	0402
R541	1	200	CRCW0603200RFKEA	Vishay-Dale	RES, 200, 1%, 0.1 W, 0603	0603
R542	1	20.0k	CRCW060320K0FKEA	Vishay-Dale	RES, 20.0 k, 1%, 0.1 W, 0603	0603
R543	1	3.40k	CRCW06033K40FKEA	Vishay-Dale	RES, 3.40 k, 1%, 0.1 W, 0603	0603
R545	1	2.49k	CRCW06032K49FKEA	Vishay-Dale	RES, 2.49k ohm, 1%, 0.1W, 0603	0603
R801, R810	2	10.0k	CRCW080510K0FKEA	Vishay-Dale	RES, 10.0 k, 1%, 0.125 W, 0805	0805
R802, R803	2	511k	CRCW1206511KFKEA	Vishay-Dale	RES, 511k ohm, 1%, 0.25W, 1206	1206
R804, R805, R806	3	0.033	ERJ-8BWFR033V	Stackpole Electronics Inc	RES SMD 0.033 OHM 1% 1W 1206	1206
R807	1	49.9k	CRCW120649K9FKEA	Vishay-Dale	RES, 49.9k ohm, 1%, 0.25W, 1206	1206
R811	1	3.01Meg	CRCW08053M01FKEA	Vishay-Dale	RES, 3.01 M, 1%, 0.125 W, 0805	0805
R812, R813, R819	3	2.87Meg	CRCW08052M87FKEA	Vishay-Dale	RES, 2.87 M, 1%, 0.125 W, 0805	0805
R814, R815	2	16.5k	CRCW060316K5FKEA	Vishay-Dale	RES, 16.5 k, 1%, 0.1 W, 0603	0603
R817, R820, R825, R826, R827	5	2.74Meg	CRCW08052M74FKEA	Vishay-Dale	RES, 2.74 M, 1%, 0.125 W, 0805	0805
R818	1	100	CRCW0603100RFKEA	Vishay-Dale	RES, 100, 1%, 0.1 W, 0603	0603
R821, R828	2	133k	CRCW0603133KFKEA	Vishay-Dale	RES, 133 k, 1%, 0.1 W, 0603	0603
R823	1	49.9k	CRCW060349K9FKEA	Vishay-Dale	RES, 49.9 k, 1%, 0.1 W, 0603	0603
R824	1	7.50k	CRCW06037K50FKEA	Vishay-Dale	RES, 7.50 k, 1%, 0.1 W, 0603	0603
R829	1	66.5k	CRCW060366K5FKEA	Vishay-Dale	RES, 66.5 k, 1%, 0.1 W, 0603	0603
R830	1	82.5k	CRCW060382K5FKEA	Vishay-Dale	RES, 82.5 k, 1%, 0.1 W, 0603	0603
R900, R901	2	2.0k	CRCW08052K00JNEA	Vishay-Dale	RES, 2.0 k, 5%, 0.125 W, 0805	0805
R902	1	100	CRCW1206100RJNEA	Vishay-Dale	RES, 100, 5%, 0.25 W, 1206	1206
R903	1	15.0	CRCW060315R0FKEA	Vishay-Dale	RES, 15.0 ohm, 1%, 0.1W, 0603	0603
R904	1	2.0k	CRCW06032K00JNEA	Vishay-Dale	RES, 2.0 k, 5%, 0.1 W, 0603	0603
R905	1	54.9k	CRCW060354K9FKEA	Vishay-Dale	RES, 54.9 k, 1%, 0.1 W, 0603	0603
R907	1	4.99k	CR0603-FX-4991ELF	Bourns	RES, 4.99 k, 1%, 0.1 W, 0603	0603
R908, R910	2	1.0k	CRCW06031K00JNEA	Vishay-Dale	RES, 1.0 k, 5%, 0.1 W, 0603	0603
R911	1	330	CRCW1206330RJNEA	Vishay-Dale	RES, 330, 5%, 0.25 W, 1206	1206
R912	1	100k	CRCW0603100KFKEA	Vishay-Dale	RES, 100 k, 1%, 0.1 W, 0603	0603
R914	1	1.15k	CRCW06031K15FKEA	Vishay-Dale	RES, 1.15 k, 1%, 0.1 W, 0603	0603

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
R915	1	21.5k	CRCW060321K5FKEA	Vishay-Dale	RES, 21.5 k, 1%, 0.1 W, 0603	0603
RT800	1	10 ohm	B57236S0100M000	EPCOS Inc	Thermistor NTC, 10 ohm, 20%, Disc 11.5mmx6mm	Disc 11.5mmx6mm
RV800	1		S10K275E2	EPCOS Inc	Varistor 275V RMS 10MM Radial, TH	10mm Radial
S900	1		GT12MV3BE	C&K Components	Toggle Switch, SPST 0.4 VA, 20 V, TH	TH, 7.62x5.46mm
T500	1	210 µH	86H-15059	Delta Electronics Inc.	Transformer, 210 uH, TH	41x36.5mm
T900	1	750 µH	750811438	Würth Elektronik	Transformer, 750 uH, TH	25x22.2mm
TP500, TP504, TP800	3	Red	5000	Keystone	Test Point, Miniature, Red, TH	Red Miniature Testpoint
TP501, TP505, TP506, TP801	4	Black	5001	Keystone	Test Point, Miniature, Black, TH	Black Miniature Testpoint
TP502	1	Orange	5003	Keystone	Test Point, Miniature, Orange, TH	Orange Miniature Testpoint
TP503	1	Yellow	5004	Keystone	Test Point, Miniature, Yellow, TH	Yellow Miniature Testpoint
U500, U501	2		UCC24610D	Texas Instruments	GREEN Rectifier Controller Device, D0008A	D0008A
U502	1		UCC27714D	Texas Instruments	High-Speed,4A, 600V High-side Low-side Gate Driver Device, D0014A	D0014A
U503, U507, U902	3		PC817X4NSZ0F		Opto-Isolator, 1 Channel, TH	DIP-4
U504	1		UCC25600D	Texas Instruments	High-Performance Resonant Mode Controller with Voltage Control, 50 % Duty Cycle, -40 to +125 degC, 8-pin SOIC (D), Green (RoHS & no Sb/Br)	D0008A
U505	1		INA213AIDCK	Texas Instruments	Voltage Output, High or Low Side Measurement, Bi-Directional Zero-Drift Series Current-Shunt Monitor, DCK0006A	DCK0006A
U506	1		TL431BIDBZR	Texas Instruments	Adjustable Precision Shunt Regulator, 34 ppm / degC, 100 mA, -40 to 85 degC, 3-pin SOT-23 (DBZ), Green (RoHS & no Sb/Br)	DBZ0003A
U800	1		UCC27524AD	Texas Instruments	Dual 5-A High-Speed Low-Side Gate Driver, D0008A	D0008A
U801	1		UCC28063DR	Texas Instruments	Natural Interleaving™ Transition-Mode PFC Controller with Improved Audible Noise Immunity, D0016A	D0016A
U900	1		TPS71550DCKR	Texas Instruments	Single Output LDO, 50 mA, Fixed 5 V Output, 3 to 24 V Input, 5-pin SC70 (DCK), -40 to 85 degC, Green (RoHS & no Sb/Br)	DCK0005A
U901	1		UCC28910DR	Texas Instruments	High-Voltage Flyback Switcher with Primary-Side Regulation and Constant-Current Control, D0007A	D0007A
Q801, Q804	0	20V	FMMT718TA	Diodes Inc.	Transistor, PNP, 20V, 1.5A, SOT-23	SOT-23
R808, R816	0	0	CRCW12060000Z0EA	Vishay-Dale	RES, 0, 5%, 0.25 W, 1206	1206

## IMPORTANT NOTICE FOR TI REFERENCE DESIGNS

Texas Instruments Incorporated ("TI") reference designs are solely intended to assist designers ("Buyers") who are developing systems that incorporate TI semiconductor products (also referred to herein as "components"). Buyer understands and agrees that Buyer remains responsible for using its independent analysis, evaluation and judgment in designing Buyer's systems and products.

TI reference designs have been created using standard laboratory conditions and engineering practices. **TI has not conducted any testing other than that specifically described in the published documentation for a particular reference design.** TI may make corrections, enhancements, improvements and other changes to its reference designs.

Buyers are authorized to use TI reference designs with the TI component(s) identified in each particular reference design and to modify the reference design in the development of their end products. HOWEVER, NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY THIRD PARTY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT, IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI REFERENCE DESIGNS ARE PROVIDED "AS IS". TI MAKES NO WARRANTIES OR REPRESENTATIONS WITH REGARD TO THE REFERENCE DESIGNS OR USE OF THE REFERENCE DESIGNS, EXPRESS, IMPLIED OR STATUTORY, INCLUDING ACCURACY OR COMPLETENESS. TI DISCLAIMS ANY WARRANTY OF TITLE AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, QUIET ENJOYMENT, QUIET POSSESSION, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS WITH REGARD TO TI REFERENCE DESIGNS OR USE THEREOF. TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY BUYERS AGAINST ANY THIRD PARTY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON A COMBINATION OF COMPONENTS PROVIDED IN A TI REFERENCE DESIGN. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, SPECIAL, INCIDENTAL, CONSEQUENTIAL OR INDIRECT DAMAGES, HOWEVER CAUSED, ON ANY THEORY OF LIABILITY AND WHETHER OR NOT TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES, ARISING IN ANY WAY OUT OF TI REFERENCE DESIGNS OR BUYER'S USE OF TI REFERENCE DESIGNS.

TI reserves the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques for TI components are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

Reproduction of significant portions of TI information in TI data books, data sheets or reference designs is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards that anticipate dangerous failures, monitor failures and their consequences, lessen the likelihood of dangerous failures and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in Buyer's safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed an agreement specifically governing such use.

Only those TI components that TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components that have **not** been so designated is solely at Buyer's risk, and Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.