

TIDM-TM4C129POE REV A0 Bill of Materials

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
I PCB	1		TIDM-TM4C129POE	Any	Printed Circuit Board	
C1, C3, C4, C5, C6, C7, C8, C9, C10, C11, C12, C13, C14, C19	14	0.1uF	GRM155R71C104KA88D	MuRata	CAP, CERM, 0.1 uF, 16 V, +/- 10%, X7R, 0402	0402
C2, C18	2	1uF	C1005X5R1C105K050BC	TDK	CAP, CERM, 1 uF, 16 V, +/- 10%, X5R, 0402	0402
C15, C16	2	0.01uF	GRM155R71C103KA01D	MuRata	CAP, CERM, 0.01 uF, 16 V, +/- 10%, X7R, 0402	0402
C17	1	2.2uF	GRM155R61C225KE11D	MuRata	CAP, CERM, 2.2 uF, 16 V, +/- 10%, X5R, 0402	0402
C20, C21	2	22pF	C1005C0G1H220J050BA	TDK	CAP, CERM, 22 pF, 50 V, +/- 5%, C0G/NP0, 0402	0402
C22, C23, C24	3	0.1uF	C0603C104J3RAC	Kemet	CAP, CERM, 0.1 uF, 25 V, +/- 5%, X7R, 0603	0603
C25	1	3300pF	C0603X332K5RACTU	Kemet	CAP, CERM, 3300 pF, 50 V, +/- 10%, X7R, 0603	0603
C26, C27, C28, C29	4	0.1uF	GCM155R71C104KA55D	MuRata	CAP, CERM, 0.1 uF, 16 V, +/- 10%, X7R, 0402	0402
C30, C43	2	2200pF	C4532X7R3D222K	TDK	CAP, CERM, 2200 pF, 2000 V, +/- 10%, X7R, 1812	1812
C31	1	4700pF	1812GC472KA1	AVX	CAP, CERM, 4700 pF, 2000 V, +/- 10%, X7R, 1812	1812
C32	1	1000pF	08051C102KAT2A	AVX	CAP, CERM, 1000 pF, 100 V, +/- 10%, X7R, 0805	0805
C33	1	0.1uF	C0805C104K1RACTU	Kemet	CAP, CERM, 0.1 uF, 100 V, +/- 10%, X7R, 0805	0805
C34	1	0.1uF	C1608X7R1H104K	TDK	CAP, CERM, 0.1 uF, 50 V, +/- 10%, X7R, 0603	0603
C35	1	0.022uF	C1608X7R1H223K	TDK	CAP, CERM, 0.022 uF, 50 V, +/- 10%, X7R, 0603	0603
C36	1	330pF	GRM31A5C2J331JW01D	MuRata	CAP, CERM, 330 pF, 630 V, +/- 5%, C0G/NP0, 1206	1206
C37	1	10uF	EMVE160ADA100MD55G	Chemi-Con	CAP, AL, 10 uF, 16 V, +/- 20%, SMD	D55
C38	1	0.22uF	08053C224KAT2A	AVX	CAP, CERM, 0.22 uF, 25 V, +/- 10%, X7R, 0805	0805
C39	1	680pF	C0603C681K5RACTU	Kemet	CAP, CERM, 680 pF, 50 V, +/- 10%, X7R, 0603	0603
C40, C41	2	1uF	C3225X7R2A105K200AA	TDK	CAP, CERM, 1 uF, 100 V, +/- 10%, X7R, 1210	1210
C42	1	22uF	EMVH630ADA220MHA0G	Chemi-Con	CAP, AL, 22 uF, 63 V, +/- 20%, 0.7 ohm, SMD	HA0
C44	1	47uF	EEE-FK0J470R	Panasonic	CAP, AL, 47 uF, 6.3 V, +/- 20%, 0.7 ohm, SMD	SMT Radial C
C45, C46	2	47uF	GRM32ER61A476KE20L	MuRata	CAP, CERM, 47 uF, 10 V, +/- 10%, X5R, 1210	1210
C47	1	1uF	C2012X7R1C105K	TDK	CAP, CERM, 1 uF, 16 V, +/- 10%, X7R, 0805	0805
C48	1	100pF	06035A101JAT2A	AVX	CAP, CERM, 100 pF, 50 V, +/- 5%, C0G/NP0, 0603	0603
C49	1	8200pF	GRM188R71H822KA01D	MuRata	CAP, CERM, 8200 pF, 50 V, +/- 10%, X7R, 0603	0603
C50, C51	2	0.1uF	EMK107B7104KA-T	Taiyo Yuden	CAP, CERM, 0.1 uF, 16 V, +/- 10%, X7R, 0603	0603
C52	1	2.2uF	GRM188R61C225KE15D	MuRata	CAP, CERM, 2.2 uF, 16 V, +/- 10%, X5R, 0603	0603
C53	1	0.01uF	GRM21BR72A103KA01L	MuRata	CAP, CERM, 0.01 uF, 100 V, +/- 10%, X7R, 0805	0805
D1, D2	2	Red	150080SS75000	Würth Elektronik	LED, Red, SMD	LED_0805
D3	1	Green	150060GS75000	Würth Elektronik	LED, Green, SMD	LED_0603
D4	1		SLVU2.8-4.TBT	Semtech	Diode, TVS, Uni, 2.8 V, 400 W, SO-8	SO-8
D5	1	58V	SMAJ58A	Diodes Inc.	Diode, TVS, Uni, 58 V, 400 W, SMA	SMA
D6, D10	2	200V	MURA120T3G	ON Semiconductor	Diode, Ultrafast, 200 V, 1 A, SMA	SMA
D7	1	75V	BAS16-7-F	Diodes Inc.	Diode, Ultrafast, 75 V, 0.3 A, SOT-23	SOT-23
D8	1	40V	MBRS540T3G	ON Semiconductor	Diode, Schottky, 40 V, 5 A, SMC	SMC
D9	1	100V	BAV99,215	NXP Semiconductor	Diode, Switching, 100 V, 0.215 A, SOT-23	SOT-23
FB1, FB2	2	30 ohm	MMZ2012R300A	TDK	Ferrite Bead, 30 ohm @ 100 MHz, 1.5 A, 0805	0805
FID1, FID2, FID3	3		N/A	N/A	Fiducial mark. There is nothing to buy or mount.	Fiducial
J1A, J1B, J2A, J2B	4		TSW-110-07-G-D	Samtec	Header, 100mil, 10x2, Gold, TH	10x2 Header
J3	1		1981568-1	TE Connectivity	Connector, Receptacle, Micro-USB Type B, R/A, Bottom Mount SMT	MICRO USB CONN, R/A
J4	1		FTSH-105-01-F-DV	Samtec	Header, 1.27mm, 5x2, Gold, Black, SMT	Header, 1.27mm, 5x2, SMT

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
J5	1		TSW-103-07-G-S	Samtec	Header, 100mil, 3x1, Gold, TH	3x1 Header
J6	1		ARJP11A-MASA-B-A-EMU2	Abracon Corporation	Connector, RJ-45 with integrated magnetics, Gold, R/A, TH	RJ-45 with integrated magnetics, 14-Leads, TH
J7	1		39357-0002	Molex	Terminal Block, 3.5 mm, 2x1, Tin, TH	Terminal Block, 3.5 mm, 2x1, TH
J8, J9, J10, J11	4		TSW-102-07-G-S	Samtec	Header, 100mil, 2x1, Gold, TH	2x1 Header
L1	1	4.7uH	DO1608C-472MLB	Coilcraft	Inductor, Drum Core, Ferrite, 4.7 uH, 1.5 A, 0.09 ohm, SMD	DO1608C
Q1	1	150V	FDN86246	Fairchild Semiconductor	MOSFET, N-CH, 150 V, 1.6 A, SSOT-3	SSOT-3
R1	1	51	CRCW060351R0JNEA	Vishay-Dale	RES, 51, 5%, 0.1 W, 0603	0603
R2	1	0	ERJ-2GE0R00X	Panasonic	RES, 0, 5%, 0.063 W, 0402	0402
R3	1	4.87k	CRCW06034K87FKEA	Vishay-Dale	RES, 4.87 k, 1%, 0.1 W, 0603	0603
R4, R8, R10	3	100	CRCW0402100RJNED	Vishay-Dale	RES, 100, 5%, 0.063 W, 0402	0402
R5, R9, R11	3	10k	CRCW040210K0JNED	Vishay-Dale	RES, 10 k, 5%, 0.063 W, 0402	0402
R6, R7, R25, R27, R28	5	330	RC0603JR-07330RL	Yageo America	RES, 330, 5%, 0.1 W, 0603	0603
R12	1	100	CRCW0603100RJNEA	Vishay-Dale	RES, 100, 5%, 0.1 W, 0603	0603
R13, R14, R15, R16	4	33	CRCW060333R0JNEA	Vishay-Dale	RES, 33, 5%, 0.1 W, 0603	0603
R17, R18, R19	3	10k	CRCW060310K0JNEA	Vishay-Dale	RES, 10 k, 5%, 0.1 W, 0603	0603
R20	1	1.0Meg	CRCW06031M00JNEA	Vishay-Dale	RES, 1.0 M, 5%, 0.1 W, 0603	0603
R21, R22, R23, R24	4	49.9	CRCW040249R9FKED	Vishay-Dale	RES, 49.9, 1%, 0.063 W, 0402	0402
R26	1	100k	ERJ-2RKF1003X	Panasonic	RES, 100 k, 1%, 0.1 W, 0402	0402
R29	1	1.0Meg	CRCW12061M00JNEA	Vishay-Dale	RES, 1.0 M, 5%, 0.25 W, 1206	1206
R30	1	39.2k	CRCW060339K2FKEA	Vishay-Dale	RES, 39.2 k, 1%, 0.1 W, 0603	0603
R31	1	392k	CRCW0603392KFKEA	Vishay-Dale	RES, 392 k, 1%, 0.1 W, 0603	0603
R32	1	59.0k	CRCW060359K0FKEA	Vishay-Dale	RES, 59.0 k, 1%, 0.1 W, 0603	0603
R33	1	80.6k	CRCW060380K6FKEA	Vishay-Dale	RES, 80.6 k, 1%, 0.1 W, 0603	0603
R34	1	1.27k	CRCW06031K27FKEA	Vishay-Dale	RES, 1.27 k, 1%, 0.1 W, 0603	0603
R35	1	24.9k	CRCW060324K9FKEA	Vishay-Dale	RES, 24.9 k, 1%, 0.1 W, 0603	0603
R36	1	499	CRCW0603499RFKEA	Vishay-Dale	RES, 499, 1%, 0.1 W, 0603	0603
R37	1	2.0k	CRCW06032K00JNEA	Vishay-Dale	RES, 2.0 k, 5%, 0.1 W, 0603	0603
R38, R42	2	49.9	CRCW060349R9FKEA	Vishay-Dale	RES, 49.9, 1%, 0.1 W, 0603	0603
R39, R44	2	0	CRCW06030000Z0EA	Vishay-Dale	RES, 0, 5%, 0.1 W, 0603	0603
R40	1	0.56	ERJ-8RQFR56V	Panasonic	RES, 0.56, 1%, 0.25 W, 1206	1206
R41	1	82	CRCW201082R0JNEF	Vishay-Dale	RES, 82, 5%, 0.75 W, 2010	2010
R43	1	20.0	CRCW120620R0FKEA	Vishay-Dale	RES, 20.0, 1%, 0.25 W, 1206	1206
R45	1	10k	RC0603JR-0710KL	Yageo America	RES, 10 k, 5%, 0.1 W, 0603	0603
R46	1	665	CRCW0603665RFKEA	Vishay-Dale	RES, 665, 1%, 0.1 W, 0603	0603
R47	1	13.3k	CRCW060313K3FKEA	Vishay-Dale	RES, 13.3 k, 1%, 0.1 W, 0603	0603
R48	1	41.2k	CRCW060341K2FKEA	Vishay-Dale	RES, 41.2 k, 1%, 0.1 W, 0603	0603
R49	1	19.1k	CRCW060319K1FKEA	Vishay-Dale	RES, 19.1 k, 1%, 0.1 W, 0603	0603
R50, R51	2	1.0k	CRCW04021K00JNED	Vishay-Dale	RES, 1.0 k, 5%, 0.063 W, 0402	0402
R52	1	49.9k	ERJ-6ENF4992V	Panasonic	RES, 49.9 k, 1%, 0.125 W, 0805	0805
S1, S2, S3	3		SKRKAEE010	Alps	Switch, Push Button, SMD	2.9x2x3.9mm SMD
T1	1	127uH	POE13P-50L	Coilcraft	Flyback Transformer, 13W, SMD	POE13P
TP1, TP2, TP3, TP4, TP5, TP6, TP7, TP8, TP9, TP10, TP11	11		TMS-101-02-T-S	Samtec	Header, 1x1, Tin, TH	Header, 1x1, 50mil, TH
U1	1		TM4C129ENCPDTI3R	Texas Instruments	Tiva C Series Microcontroller, PDT0128A	PDT0128A
U2	1		TPD2E2U06DRLR	Texas Instruments	DUAL CHANNEL HIGH SPEED ESD PROTECTION DEVICE, DRL0005A	DRL0005A

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
U3	1		TPS23753APW	Texas Instruments	IEEE 802.3-2005 PoE Interface and Isolated Converter Controller with Enhanced ESD Ride-Through, -40 to 125 degC, 14-pin SOP (PW14), Green (RoHS & no Sb/Br)	PW0014A
U4	1		FOD817AS	Fairchild Semiconductor	Optocoupler, 5 kV, 80-160% CTR, SMT	DIP-4L Gullwing
U5	1		TLV431ACDBZR	Texas Instruments	Low Voltage Adjustable Precision Shunt Regulator, 39 ppm / degC, 15 mA, 0 to 70 degC, 3-pin SOT-23 (DBZ), Green (RoHS & no Sb/Br)	DBZ0003A
U6	1		TPS73733DCQR	Texas Instruments	Single Output LDO, 1 A, Fixed 3.3 V Output, 2.2 to 5.5 V Input, with Reverse Current Protection, 6-pin SOT-223 (DCQ), -40 to 125 degC, Green (RoHS & no Sb/Br)	DCQ0006A
Y1	1		NX5032GA-25.000M-STD-CSK-4	NDK	Crystal, 25MHz, SMD	5x3.2mm

IMPORTANT NOTICE FOR TI REFERENCE DESIGNS

Texas Instruments Incorporated ("TI") reference designs are solely intended to assist designers ("Designer(s)") who are developing systems that incorporate TI products. TI has not conducted any testing other than that specifically described in the published documentation for a particular reference design.

TI's provision of reference designs and any other technical, applications or design advice, quality characterization, reliability data or other information or services does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such reference designs or other items.

TI reserves the right to make corrections, enhancements, improvements and other changes to its reference designs and other items.

Designer understands and agrees that Designer remains responsible for using its independent analysis, evaluation and judgment in designing Designer's systems and products, and has full and exclusive responsibility to assure the safety of its products and compliance of its products (and of all TI products used in or for such Designer's products) with all applicable regulations, laws and other applicable requirements. Designer represents that, with respect to its applications, it has all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. Designer agrees that prior to using or distributing any systems that include TI products, Designer will thoroughly test such systems and the functionality of such TI products as used in such systems. Designer may not use any TI products in life-critical medical equipment unless authorized officers of the parties have executed a special contract specifically governing such use. Life-critical medical equipment is medical equipment where failure of such equipment would cause serious bodily injury or death (e.g., life support, pacemakers, defibrillators, heart pumps, neurostimulators, and implantables). Such equipment includes, without limitation, all medical devices identified by the U.S. Food and Drug Administration as Class III devices and equivalent classifications outside the U.S.

Designers are authorized to use, copy and modify any individual TI reference design only in connection with the development of end products that include the TI product(s) identified in that reference design. HOWEVER, NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of the reference design or other items described above may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI REFERENCE DESIGNS AND OTHER ITEMS DESCRIBED ABOVE ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING THE REFERENCE DESIGNS OR USE OF THE REFERENCE DESIGNS, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY DESIGNERS AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS AS DESCRIBED IN A TI REFERENCE DESIGN OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF THE REFERENCE DESIGNS OR USE OF THE REFERENCE DESIGNS, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

TI's standard terms of sale for semiconductor products (<http://www.ti.com/sc/docs/stdterms.htm>) apply to the sale of packaged integrated circuit products. Additional terms may apply to the use or sale of other types of TI products and services.

Designer will fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of Designer's non-compliance with the terms and provisions of this Notice.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2016, Texas Instruments Incorporated