

# Bill of Materials

TI DESIGNS TIDA-00285

1kW/36V Power Stage for Brushless Motor in Battery Powered Garden and Power Tools

Qty	Reference	Part Description	Manufacturer	Manufacturer Part Number	PCB Footprint	Note
6	C1, C9, C28, C29, C30, C39	CAP, CERM, 2.2uF, 100V, +/-10%, X7R, 1210	MuRata	GRM32ER72A225KA35L	1210	Fitted
1	C10	CAP, CERM, 22uF, 4V, +/-20%, X5R, 0603	TDK	C1608X5R0G226M080AA	0603	Fitted
1	C11	CAP, CERM, 33pF, 50V, +/-5%, COG/NP0, 0402	Kemet	C0402C330J5GAC	0402	Fitted
1	C12	CAP, CERM, 0.012uF, 16V, +/-10%, X7R, 0402	MuRata	GRM155R71C123KA01D	0402	Fitted
1	C13	CAP, CERM, 0.1uF, 25V, +/-10%, X7R, 0603	MuRata	GRM188R71E104KA01D	0603	Fitted
1	C14	CAP, CERM, 0.1uF, 25V, +/-20%, Y5V, 0603	Kemet	C0603C104M3VACTU	0603	Fitted
2	C16, C17	CAP, CERM, 1uF, 25V, +/-10%, X5R, 0603	MuRata	GRM188R61E105KA12D	0603	Fitted
1	C19	CAP, CERM, 0.1uF, 25V, +/-10%, X7R, 0603	TDK	C1608X7R1E104K	0603	Fitted
2	C2, C22	CAP, CERM, 0.1uF, 100V, +/-10%, X7R, 0603	MuRata	GRM188R72A104KA35D	0603	Fitted
2	C20, C21	CAP 270UF 80V RADIAL	United Chemi-Con	EKYB800ELL271MK20S	Through Hole Radial G	Fitted
5	C23, C34, C35, C36, C37	CAP, CERM, 0.1uF, 16V, +/-5%, X7R, 0603	Kemet	C0603C104J4RACTU	0603	Fitted
1	C24	CAP, CERM, 0.01uF, 100V, +/-10%, X7R, 0603	TDK	C1608X7R2A103K	0603	Fitted
3	C25, C26, C27	CAP, CERM, 2200pF, 16V, +/-10%, X7R, 0603	MuRata	GRM188R71C222KA01D	0603	Fitted
1	C3	CAP, CERM, 0.022uF, 50V, +/-10%, X7R, 0603	TDK	C1608X7R1H223K	0603	Fitted
3	C31, C32, C33	CAP, CERM, 1000pF, 50V, +/-5%, COG/NP0, 0603	Kemet	C0603C102J5GAC	0603	Fitted
1	C38	CAP, CERM, 2.2uF, 10V, +/-20%, X5R, 0603	Kemet	C0603C225M8PACTU	0603	Fitted
2	C4, C15	CAP, CERM, 2.2uF, 25V, +/-10%, X5R, 0805	MuRata	GRM219R61E225KA12D	0805	Fitted
3	C5, C6, C7	CAP, CERM, 0.1uF, 50V, +/-10%, X7R, 0603	TDK	C1608X7R1H104K	0603	Fitted
1	C8	CAP, CERM, 0.01 uF, 25 V, +/- 10%, X7R, 0402	TDK	C1005X7R1E103K	0402	Fitted
1	D1	LED THIN 585NM YEL DIFF 0805 SMD	Lumex Opto/Components Inc	SML-LXT0805YW-TR	0805	Fitted
1	D2	LED THIN660NM SUPRED DIFF0805SMD	Lumex Opto/Components Inc	SML-LXT0805SRW-TR	0805	Fitted
1	D3	Diode, Superfast Rectifier, 400V, 1A, SMA	Littelfuse	1.5SMC56CA	SMA	Fitted
2	D4, D5	LED THIN 565NM GRN DIFF 0805 SMD	Lumex Opto/Components Inc	SML-LXT0805GW-TR	0805	Fitted
1	H1	1/8 BRICK HEATSINK 58X23X2.9MM	Advanced Thermal Solutions Inc	ATS-1181-C1-R0	Rectangular, Angled Fins	Fitted
2	J3, J4	CONN RCPT 20POS .100 DL STR SMD	FCI	89898-310ALF		Fitted
1	L1	Inductor, Drum Core, Ferrite, 120uH, 0.22A, 3.2 ohm, SMD	Bourns	SDR0302-121KL	3x2.5x2.8mm	Fitted
2	Q1, Q2	MOSFET P-CH 8V 5.4A SOT23-3	Vishey Siliconix	SI2325DS-T1-E3	SOT-23-3	Fitted
6	Q3, Q4, Q5, Q6, Q7, Q8	MOSFET, N-CH, 60V, 100A, SON 5x6mm	Texas Instruments	CSD18540Q5B	SON 5x6mm	Fitted
3	R1, R4, R24	RES, 330 ohm, 5%, 0.1W, 0603	Vishay-Dale	CRCW0603330RJNEA	0603	Fitted
1	R10	RES, 34.8 k, 1%, 0.063 W, 0402	Vishay-Dale	CRCW040234K8FKED	0402	Fitted
1	R11	RES, 38.3k ohm, 1%, 0.063W, 0402	Vishay-Dale	CRCW040238K3FKED	0402	Fitted
1	R12	RES, 10.0k ohm, 1%, 0.063W, 0402	Vishay-Dale	CRCW040210K0FKED	0402	Fitted
1	R14	RES, 0 ohm, 5%, 0.1W, 0603	Vishay-Dale	CRCW06030000Z0EA	0603	Fitted
2	R2, R3	RES, 3.3 k, 5%, 0.1 W, 0603	Vishay-Dale	CRCW06033K30JNEA	0603	Fitted
4	R20, R37, R39, R41	RES, 34.8k ohm, 1%, 0.1W, 0603	Vishay-Dale	CRCW060334K8FKEA	0603	Fitted
1	R21	RES, 3.3 ohm, 5%, 0.25W, 1206	Vishay-Dale	CRCW12063R30JNEA	1206	Fitted
4	R22, R38, R40, R42	RES, 2.20k ohm, 1%, 0.1W, 0603	Yageo America	RC0603FR-072K2L	0603	Fitted
1	R23	RES, 12k ohm, 5%, 0.1W, 0603	Vishay-Dale	CRCW060312K0JNEA	0603	Fitted
3	R25, R26, R27	RES, 56 ohm, 5%, 0.1W, 0603	Vishay-Dale	CRCW060356R0JNEA	0603	Fitted
6	R28, R29, R30, R31, R32, R33	RES, 10 ohm, 5%, 0.1W, 0603	Vishay-Dale	CRCW060310R0JNEA	0603	Fitted
3	R34, R35, R36	RES, 0.001 ohm, 1%, 2W, 2512	Panasonic, Panasonic, Stackpole	CSNL2512FT1L00	2512	Fitted
2	R43, R47	RES, 20.0 k, 1%, 0.1 W, 0603	Vishay-Dale	CRCW060320K0FKEA	0603	Fitted
2	R44, R45	RES, 1.00k ohm, 1%, 0.1W, 0603	Vishay-Dale	CRCW06031K00FKEA	0603	Fitted
2	R46, R48	RES, 10.0k ohm, 0.1%, 0.1W, 0603	Susumu Co Ltd	RG1608P-103-B-T5	0603	Fitted
1	R49	RES, 97.6k ohm, 1%, 0.063W, 0402	Vishay-Dale	CRCW040297K6FKED	0402	Fitted
1	R5	RES, 1.0 ohm, 5%, 0.1W, 0603	Vishay-Dale	CRCW06031R00JNEA	0603	Fitted
1	R50	RES, 100, 1%, 0.1 W, 0603	Vishay-Dale	CRCW0603100RFKEA	0603	Fitted
2	R51, R61	RES, 0.0 ohm, 63.2A JUMP, 2512	Panasonic	HCJ2512ZT0R00	2512	Fitted
6	R52, R53, R54, R55, R56, R57	RES, 0, 5%, 0.063 W, 0402	Yageo America	RC0402JR-070RL	0402	Fitted
2	R6, R9	RES, 1.0k ohm, 5%, 0.1W, 0603	Vishay-Dale	CRCW06031K00JNEA	0603	Fitted
1	R7	RES, 30.9k ohm, 1%, 0.063W, 0402	Vishay-Dale	CRCW040230K9FKED	0402	Fitted
1	R8	RES, 909 k, 1%, 0.063 W, 0402	Vishay-Dale	CRCW0402909KFKED	0402	Fitted
2	TP1, TP2	Test Point, 0.040 Hole	STD	STD		Fitted
1	U1	THREE PHASE PRE-DRIVER WITH DUAL CURRENT SHUNT AMPLIFIERS, DCA0048A	Texas Instruments	DRV8303DCA	DCA0048A	Fitted
1	U2	ESD Solution for High-Speed Differential Interface, 4 Channels, 40 to +85 degC, 6-pin SOT-32 (DBV), Green (RoHS & no Sb/Br)	Texas Instruments	TPD4S009DBVR	DBV0006A	Fitted
1	U3	Dual 6.5 MHz, 585 uA, Rail-to-Rail I/O CMOS Operational Amplifier, 2.3 to 5.5 V, -40 to 125 degC, 8-pin SOIC (D0008A), Green (RoHS & no Sb/Br)	Texas Instruments	OPA2374AID	D0008A	Fitted
1	U4	IC, 60V/0.2A Synchronous Buck Regulator	Texas Instruments	TPS54061DRB	QFN	Fitted
1	U5	Analog Temperature Sensors with Class-AB Output, DCK0005A	Texas Instruments	LMT84DCK	DCK0005A	Fitted
1	Thermal Pad	THERMALLY CONDUCTIVE FILLER PAD, 5W/m.K, 0.5MM	AMEC THERMASOL	W8TR500G-0.5	60 mm X 24 mm Rectangular	Fitted
2	Machine Screw	MACHINE SCREW PAN PHILLIPS 6-32	B&F Fastener Supply	PMS 632 0050 PH	6-32 Thread	Fitted
2	Hex Nut	HEX NUT 5/16" 6-32	B&F Fastener Supply	HNZ 632	Hex, 6-32 Thread	Fitted
2	R58, R59	RES, 0, 5%, 0.063 W, 0402	Yageo America	RC0402JR-070RL	0402	Not Fitted

## IMPORTANT NOTICE FOR TI REFERENCE DESIGNS

Texas Instruments Incorporated ("TI") reference designs are solely intended to assist designers ("Buyers") who are developing systems that incorporate TI semiconductor products (also referred to herein as "components"). Buyer understands and agrees that Buyer remains responsible for using its independent analysis, evaluation and judgment in designing Buyer's systems and products.

TI reference designs have been created using standard laboratory conditions and engineering practices. **TI has not conducted any testing other than that specifically described in the published documentation for a particular reference design.** TI may make corrections, enhancements, improvements and other changes to its reference designs.

Buyers are authorized to use TI reference designs with the TI component(s) identified in each particular reference design and to modify the reference design in the development of their end products. HOWEVER, NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY THIRD PARTY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT, IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI REFERENCE DESIGNS ARE PROVIDED "AS IS". TI MAKES NO WARRANTIES OR REPRESENTATIONS WITH REGARD TO THE REFERENCE DESIGNS OR USE OF THE REFERENCE DESIGNS, EXPRESS, IMPLIED OR STATUTORY, INCLUDING ACCURACY OR COMPLETENESS. TI DISCLAIMS ANY WARRANTY OF TITLE AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, QUIET ENJOYMENT, QUIET POSSESSION, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS WITH REGARD TO TI REFERENCE DESIGNS OR USE THEREOF. TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY BUYERS AGAINST ANY THIRD PARTY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON A COMBINATION OF COMPONENTS PROVIDED IN A TI REFERENCE DESIGN. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, SPECIAL, INCIDENTAL, CONSEQUENTIAL OR INDIRECT DAMAGES, HOWEVER CAUSED, ON ANY THEORY OF LIABILITY AND WHETHER OR NOT TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES, ARISING IN ANY WAY OUT OF TI REFERENCE DESIGNS OR BUYER'S USE OF TI REFERENCE DESIGNS.

TI reserves the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques for TI components are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

Reproduction of significant portions of TI information in TI data books, data sheets or reference designs is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards that anticipate dangerous failures, monitor failures and their consequences, lessen the likelihood of dangerous failures and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in Buyer's safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed an agreement specifically governing such use.

Only those TI components that TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components that have **not** been so designated is solely at Buyer's risk, and Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.