

DS9638QML RS-422 Dual High Speed Differential Line Driver

Check for Samples: [DS9638QML](#)

FEATURES

- Single 5V Supply
- Schottky Technology
- TTL and CMOS Compatible Inputs
- Output Short Circuit Protection
- Input Clamp Diodes
- Complementary Outputs
- Minimum Output Skew (<1.0 ns Typical)
- 50 mA Output Drive Capability for 50Ω Transmission Lines
- Meets EIA RS-422 Specifications
- Propagation Delay of Less than 10 ns
- “Glitchless” Differential Output
- Delay Time Stable with V_{CC} and Temperature

Variations (<2.0 ns typical) (Figure 4)

- Extended Temperature Range

DESCRIPTION

The DS9638 is a Schottky, TTL compatible, dual differential line driver designed specifically to meet the EIA Standard RS-422 specifications. It is designed to provide unipolar differential drive to twisted pair or parallel wire transmission lines. The inputs are TTL compatible. The outputs are similar to totem pole TTL outputs, with active pull-up and pull-down. The device features a short circuit protected active pull-up with low output impedance and is specified to drive 50Ω transmission lines at high speed. The mini-CDIP provides high package density.

Connection Diagram




Figure 1. 8-Lead CDIP, Top View



These devices have limited built-in ESD protection. The leads should be shorted together or the device placed in conductive foam during storage or handling to prevent electrostatic damage to the MOS gates.



Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.

All trademarks are the property of their respective owners.

Absolute Maximum Ratings⁽¹⁾

Storage Temperature Range	Ceramic DIP	-65°C to +175°C
Lead Temperature	Ceramic DIP (Soldering, 60 sec.)	300°C
Maximum Power Dissipation at 25°C ⁽²⁾	Cavity Package	1300 mW
V _{CC} Lead Potential to Ground		-5V to 7V
Input Voltage		-0.5V to +7V

- (1) "Absolute Maximum Ratings" are those values beyond which the safety of the device cannot be ensured. They are not meant to imply that the devices should be operated at these limits. The tables of "Electrical Characteristics provide conditions for actual device operation.
- (2) Derate cavity package 8.7 mW/°C above 25°C.

Recommended Operating Conditions

DS9638J/883	Min	Max	Units
Supply Voltage (V _{CC})	4.5	5.5	V
Output Current HIGH (I _{OH})		-50	mA
Output Current LOW (I _{OL})		50	mA
Operating Temperature (T _A)	-55	125	°C

Quality Conformance Inspection

MIL-STD-883, Method 5005 - Group A

Subgroup	Description	Temp (°C)
1	Static tests at	+25°C
2	Static tests at	+125°C
3	Static tests at	-55°C
4	Dynamic tests at	+25°C
5	Dynamic tests at	+125°C
6	Dynamic tests at	-55°C
7	Functional tests at	+25°C
8A	Functional tests at	+125°C
8B	Functional tests at	-55°C
9	Switching tests at	+25°C
10	Switching tests at	+125°C
11	Switching tests at	-55°C
12	Setting time at	+25°C
13	Setting time at	+125°C
14	Setting time at	-55°C

DS9638J/883 Electrical Characteristics DC Parameters

Over recommended operating temperature and supply voltage ranges, unless otherwise specified

Symbol	Parameter	Conditions	Notes	Min	Max	Units	Sub-Groups
V_{OL}	Output Voltage Low	$V_{CC} = 4.5V$, $F_{IOL} = 30mA$ for temp, $F_{IOL} = 35mA$ for room	See (1)		0.5	V	1, 2, 3
V_FCD	Input Clamped Voltage	$V_{CC} = 4.5V$, $F_{IFCD} = -18mA$		-1.2		V	1, 2, 3
V_{OHQVT}	V_T , \bar{V}_T Terminated Output Voltage	$V_{CC} = 5.5V$, $R_O = 100 \Omega$		2		V	1, 2, 3
V_{OH}	Logical "1" Output Voltage	$V_{CC} = 4.5V$, $F_{IOH} = -10mA$		2.5		V	1
				2.0			2, 3
V_{OHQ}	Logical "1" Output Voltage	$V_{CC} = 4.5V$, $F_{IOHQ} = -40mA$		2.0		V	1
				1.0			2, 3
V_{OHQBAL}	V_T , \bar{V}_T Output Balance	$V_{CC} = 5.5V$, $R_O = 100 \Omega$		-0.4	0.4	V	1, 2, 3
I_{IL}	Logical "0" Input Current	$V_{CC} = 5.5V$, $F_{VII} = 0.5V$		-200		μA	1, 2, 3
I_{IH}	Logical "1" Input Current	$V_{CC} = 5.5V$, $F_{VIH} = 2.7V$			25	μA	1, 2, 3
I_{IHQH}	Logical "1" Input Current	$V_{CC} = 5.5V$, $F_{VIHQH} = 5.5V$			50	μA	1, 2, 3
I_{OS}	Output Short Circuit Current	$V_{CC} = 5.5V$, $F_{V_{IOS}} = 0V$		-150	-50	mA	1
				-150	-40		2, 3
I_{CC}	Supply Current	$V_{CC} = 5.5V$, $F_{V_{CCH}} = 5.5V$			65	mA	1
					75		2, 3
I_{OHC}	I_O (off) Output Leakage	$V_{CC} = 5.5V$, $F_{V_{OH}} = 5.5V$			200	μA	1
V_{OS} , \bar{V}_{OS}	Output Offset Voltage		See (2)		3	V	1, 2, 3
V_{OS} , \bar{V}_{OS}	Output Offset Balance		See (3)		.4	V	1, 2, 3
V_{IH}	Input High Voltage		See (4)	2		V	1, 2, 3
V_{IL}	Input Low Voltage		See (4)		0.5	V	1, 2, 3
V_{HB}	I_X Output Leakage	$V_{CC} = 0.0V$, $F_{IOHBQI} = 150 \mu A$		5.55		V	1
I_{CEX}	Output Leakage Current	$V_{CC} = 0.0V$, $F_{V_{CEX}} = 5.5V$			150	μA	2, 3
I_{CEXQI}	Output Leakage Current	$V_{CC} = 0.0V$, $F_{V_{ICEXQ2}} = -0.25V$		-150		μA	2, 3

(1) 35mA is more stringent than 30mA.

(2) Specified by design.

 (3) Specified by V_T - \bar{V}_T test.

 (4) Specified by V_{OH} & V_{OL} tests.

DS9638J/883 Electrical Characteristics AC Parameters

Over recommended operating temperature and supply voltage ranges, unless otherwise specified

Symbol	Parameter	Conditions	Notes	Min	Max	Units	Sub-Groups
t_{PLH}	Propagation Delay to High Level	$V_{CC} = 5V$, $R_O = 100 \Omega$, $C_L = 15pF$			20	nS	9
t_{PHL}	Propagation Delay to Low Level	$V_{CC} = 5V$, $R_O = 100 \Omega$, $C_L = 15pF$			20	nS	9
t_F	Fall Time	$V_{CC} = 5V$, 90% - 10%			20	nS	9
t_R	Rise Time	$V_{CC} = 5V$, 10% - 90%			20	nS	9

Equivalent Circuit




Figure 2.

DC Test Circuit





Figure 3. Terminated Output Voltage and Output Balance



The pulse generator has the following characteristics:
 C_L includes probe and jig capacitance.
 PRR = 500 kHz, $t_{WV} = 100$ ns,
 $t_r \leq 5.0$ ns, $Z_O = 50\Omega$.




Figure 4. AC Test Circuit and Voltage Waveform

Typical Delay Characteristics




Figure 5.




Figure 6.

REVISION HISTORY



Date Released	Revision	Section	Originator	Changes
05/27/08	A	New Release, Corporate Format, Change to DC Electrical Section	Bill Petcher	1 MDS data sheet converted into one Corp. data sheet format. Change made to V_{OH} , V_{OHQ} and I_{OS} . MNDS9638-X, Rev. 0AL data sheet will be Archived.

Changes from Original (April 2013) to Revision A

Page

- Changed layout of National Data Sheet to TI format **5**

PACKAGING INFORMATION

Orderable Device	Status (1)	Package Type	Package Drawing	Pins	Package Qty	Eco Plan (2)	Lead/Ball Finish (6)	MSL Peak Temp (3)	Op Temp (°C)	Device Marking (4/5)	Samples
5962-8754601PA	ACTIVE	CDIP	NAB	8	40	TBD	Call TI	Call TI	-55 to 125	DS9638J/883 5962-87546 01PA Q ACO 01PA Q >T	
DS9638J/883	ACTIVE	CDIP	NAB	8	40	TBD	Call TI	Call TI	-55 to 125	DS9638J/883 5962-87546 01PA Q ACO 01PA Q >T	

(1) The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

OBSOLETE: TI has discontinued the production of the device.

(2) Eco Plan - The planned eco-friendly classification: Pb-Free (RoHS), Pb-Free (RoHS Exempt), or Green (RoHS & no Sb/Br) - please check <http://www.ti.com/productcontent> for the latest availability information and additional product content details.

TBD: The Pb-Free/Green conversion plan has not been defined.

Pb-Free (RoHS): TI's terms "Lead-Free" or "Pb-Free" mean semiconductor products that are compatible with the current RoHS requirements for all 6 substances, including the requirement that lead not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, TI Pb-Free products are suitable for use in specified lead-free processes.

Pb-Free (RoHS Exempt): This component has a RoHS exemption for either 1) lead-based flip-chip solder bumps used between the die and package, or 2) lead-based die adhesive used between the die and leadframe. The component is otherwise considered Pb-Free (RoHS compatible) as defined above.

Green (RoHS & no Sb/Br): TI defines "Green" to mean Pb-Free (RoHS compatible), and free of Bromine (Br) and Antimony (Sb) based flame retardants (Br or Sb do not exceed 0.1% by weight in homogeneous material)

(3) MSL, Peak Temp. - The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

(4) There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.


(5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.

(6) Lead/Ball Finish - Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead/Ball Finish values may wrap to two lines if the finish value exceeds the maximum column width.



Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

NAB0008A



CONTROLLING DIMENSION IS INCH
VALUES IN [] ARE MILLIMETERS



J08A (Rev M)

IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products (also referred to herein as "components") are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of significant portions of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI components or services with statements different from or beyond the parameters stated by TI for that component or service voids all express and any implied warranties for the associated TI component or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards which anticipate dangerous consequences of failures, monitor failures and their consequences, lessen the likelihood of failures that might cause harm and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed a special agreement specifically governing such use.

Only those TI components which TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components which have **not** been so designated is solely at the Buyer's risk, and that Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.

Products

Audio	www.ti.com/audio
Amplifiers	amplifier.ti.com
Data Converters	dataconverter.ti.com
DLP® Products	www.dlp.com
DSP	dsp.ti.com
Clocks and Timers	www.ti.com/clocks
Interface	interface.ti.com
Logic	logic.ti.com
Power Mgmt	power.ti.com
Microcontrollers	microcontroller.ti.com
RFID	www.ti-rfid.com
OMAP Applications Processors	www.ti.com/omap
Wireless Connectivity	www.ti.com/wirelessconnectivity

Applications

Automotive and Transportation	www.ti.com/automotive
Communications and Telecom	www.ti.com/communications
Computers and Peripherals	www.ti.com/computers
Consumer Electronics	www.ti.com/consumer-apps
Energy and Lighting	www.ti.com/energy
Industrial	www.ti.com/industrial
Medical	www.ti.com/medical
Security	www.ti.com/security
Space, Avionics and Defense	www.ti.com/space-avionics-defense
Video and Imaging	www.ti.com/video

TI E2E Community

e2e.ti.com