

Control + Automation MCUs

TM4C12x Family



TM4C12x Overview

TI's TM4C12x MCUs offer the industry's most popular ARM® Cortex®-M4 core with scalable memory and package options, unparalleled connectivity peripherals, and advanced analog integration. From Ethernet connectivity to basic UARTs, the TM4C12x MCUs offer a variety of solutions for networking, displays, sensor hubs, industrial automation, and much more.

Connect

Providing unparalleled point-to-point connectivity features with four SSI/ SPI, up to 10 I2C, eight UARTs, and USB On-The-Go/Host/Device, the TM4C12x provides an excellent baseline for home, building, and industrial applications. TM4C12x MCUs enable customers an opportunity to increase their connectivity integration without sacrificing price, performance, and power consumption.

Communicate

TM4C12x MCUs provide multiple network and communication peripherals, including two CAN controllers, 10/100 Ethernet, and wireless communication libraries. With a variety of examples ready to run on the TM4C12x Evaluation and Development Kits, TI provides everything that customers need to get started networking with Cortex-M.

Control

TM4C12x MCUs include up to 40 PWM outputs and two quadrature encoder inputs tailored to move motors, switches, and actuators. Supported by two fast, accurate, 12-bit ADCs and three on-chip comparators, TM4C12x microcontrollers are a great fit for simple motion control applications.

Customers also have the option to quickly and efficiently implement

Key Features

- 10/100 Ethernet MAC + PHY
- LCD Controller
- Data Protection
- Up to 100,000 write/erase cycles
- Up to 6 KB of Embedded EEPROM
- Low-Power Modes, as low as 1.6uA/t
- USB Full/High Speed (Host/Device/OTG)
- Dual CAN
- Motion Control
- Large, Wide Timer Pool
- Serial Connectivity

advanced graphical user interfaces by leveraging the royalty-free TivaWare™ for C Series Graphics Library. Whether it's graphics, motion, or analog controls, accelerate your design with TM4C12x microcontrollers.

TM4C123x

Temperatures 85°C 105°C

ARM® Cortex™-M4F
Up to 80 MHz

FPU	MPU
NVIC	ETM
SWD/T	

Memory

- Up to 256 KB Flash
- Up to 32 KB SRAM
- 2 KB EEPROM
- ROM

Power & Clocking

- Precision Oscillator
- RTC Battery-Backed Hibernate
- DMA (32 ch)

System Modules

- 6x 32-bit Timer/PWM/CCP
- 6x 64-bit Timer/PWM/CCP
- Systick Timer
- 2x Watchdog Timer

Debug

- Real-time JTAG

Control Peripherals

- 2x Quadrature Encoder Inputs
- 16x PWM Outputs

Comms Peripherals

- 8x UART
- 4x SSI/SPI
- 6x I²C
- 2x CAN
- USB Full Speed (Host/Device/OTG)

Analog

- 12ch, 1 S/H 12-bit 1 MSPS ADC
- 12ch, 1 S/H 12-bit 1 MSPS ADC
- LDO Voltage Regulator
- 3x Analog Comparators
- Temperature Sensor

TM4C129x

Temperatures 85°C 105°C

ARM® Cortex™-M4F
Up to 120 MHz

FPU	MPU
NVIC	ETM
SWD/T	

Memory

- Up to 1 MB Flash
- Up to 256 KB SRAM
- 6 KB EEPROM
- ROM
- DMA (32 ch)

Power & Clocking

- Precision Oscillator
- RTC Battery-Backed Hibernate

System Modules

- 8x 32-bit Timer/PWM/CCP
- EPI
- LCD
- Systick Timer
- 2x Watchdog Timer

System Management

- 1-Wire

Debug

- Real-time JTAG

Control Peripherals

- 8x MC PWM
- Quadrature Encoder Inputs

Comms Peripherals

- 8x UART
- 4x QSSI/SPI
- 10x I²C
- 2x CAN
- 10/100 Ethernet MAC/PHY (IEEE 1588)
- USB Full/High Speed (Host/Device/OTG)

Analog

- 2x 12ch, 12-bit ADCs up to 2 MSPS
- LDO Voltage Regulator
- 3x Analog Comparators

Data Protection

- 4x Tamper Inputs
- CRC Accelerator
- AES, DES, SHA & MD5 Accelerators

Packages


- 212-BGA (ZAD) (10x10x1, 0.5)
- 128-TQFP (PDT) (16x16x1.2, 0.4)

Evaluation Kits

Get started with the TM4C12x product family using the LaunchPad development platform for rapid prototyping from Texas Instruments. These Robust, modular hardware tools offer developers flexibility to launch designs with unique combinations of low-cost TI LaunchPad™ development kits and complementary LaunchPad BoosterPack™ plug-in modules. The award-winning TM4C123 LaunchPad and the new Connected LaunchPad are an ideal introduction to the world of ARM Cortex-M4 microcontrollers.

TM4C129 Connected LaunchPad


The TM4C12x Connected LaunchPad (EK-TM4C1294XL) is the first LaunchPad Development Kit to feature out-of-the-box internet connectivity. The Connected LaunchPad provides a low-cost, feature-rich platform for cloud-enabled



applications. The design highlights the TM4C1294NCPDTI MCU with 120-MHz 32-bit ARM Cortex-M4 MCU with Ethernet MAC+PHY, 1MB Flash, 256KB SRAM and more.

TM4C123 LaunchPad Development Kit

The TM4C123G LaunchPad Development Kit (EK-TM4C123GXL) is a low-cost evaluation platform for ARM® Cortex™-M4F based microcontrollers. The LaunchPad design highlights the TM4C123GH6



microcontroller's USB 2.0 Device interface, Hibernation module, Motion Control PWMs and overall cost effectiveness.

LaunchPad BoosterPack Plug-in Modules

These innovative tools plug into a consistent and standardized connector on the LaunchPad and allow developers to explore different applications enabled by your favorite TI microcontroller.


BoosterPacks are available from Texas Instruments, from third parties and from the community. They include functions such as capacitive touch, wireless communication, sensor readings, LED lighting control, and more. BoosterPacks are available in 20- and 40-pin variants, and multiple BoosterPacks can plug into your LaunchPad to enhance the functionality of your design. www.ti.com/launchpad

Development Kits

TM4C12x Development Kits are designed for the users that want to explore the full features of TM4C12x product family devices. These kits bring out all unused GPIO to pin-headers, displays, and even BoosterPack connections for providing out-of-the-box extensibility. Grab your DK for the TM4C123x or TM4C129x series today!

DK-TM4C129X


The TM4C129X Development Kit is a versatile and feature-rich engineering platform that highlights the 120-MHz TM4C129XNCZAD ARM® Cortex™-M4 based microcontroller,



including integrated 10/100 Ethernet MAC + PHY as well as many other key features.

DK-TM4C123G

The TM4C123G Development Kit is a compact and versatile evaluation platform for the TM4C123G ARM® Cortex™-M4-based microcontroller, highlighting the TM4C123G device with integrated USB 2.0 On-the-



Go/Host/Device interface, CAN, precision analog, sensor hub, and low-power capabilities.

IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products (also referred to herein as "components") are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of significant portions of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI components or services with statements different from or beyond the parameters stated by TI for that component or service voids all express and any implied warranties for the associated TI component or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards which anticipate dangerous consequences of failures, monitor failures and their consequences, lessen the likelihood of failures that might cause harm and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed a special agreement specifically governing such use.

Only those TI components which TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components which have **not** been so designated is solely at the Buyer's risk, and that Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.

Products

Audio	www.ti.com/audio
Amplifiers	amplifier.ti.com
Data Converters	dataconverter.ti.com
DLP® Products	www.dlp.com
DSP	dsp.ti.com
Clocks and Timers	www.ti.com/clocks
Interface	interface.ti.com
Logic	logic.ti.com
Power Mgmt	power.ti.com
Microcontrollers	microcontroller.ti.com
RFID	www.ti-rfid.com
OMAP Applications Processors	www.ti.com/omap
Wireless Connectivity	www.ti.com/wirelessconnectivity

Applications

Automotive and Transportation	www.ti.com/automotive
Communications and Telecom	www.ti.com/communications
Computers and Peripherals	www.ti.com/computers
Consumer Electronics	www.ti.com/consumer-apps
Energy and Lighting	www.ti.com/energy
Industrial	www.ti.com/industrial
Medical	www.ti.com/medical
Security	www.ti.com/security
Space, Avionics and Defense	www.ti.com/space-avionics-defense
Video and Imaging	www.ti.com/video

TI E2E Community

e2e.ti.com