TPS76901-Q1, TPS76912-Q1, TPS76915-Q1, TPS76918-Q1, TPS76925-Q1 TPS76927-Q1, TPS76928-Q1, TPS76930-Q1, TPS76933-Q1, TPS76950-Q1 SGZV004, February 2002

ULTRA LOW POWER 100-mA LOW-DROPOUT LINEAR REGULATORS

HIGHLIGHTS

The TPS769xx-Q1 family of low-dropout (LDO) voltage regulators offers the benefits of low dropout voltage, ultra low-power operation, and miniaturized packaging. These regulators feature low dropout voltages and ultra low quiescent current compared to conventional LDO regulators. Offered in a 5-terminal, small outline integrated-circuit SOT-23 package, the TPS769xx-Q1 series devices are ideal for micropower operations and where board space is at a premium.

A combination of new circuit design and process innovation has enabled the usual PNP pass transistor to be replaced by a PMOS pass element. Because the PMOS pass element behaves as a low-value resistor, the dropout voltage is very low, typically 71 mV at 100 mA of load current (TPS76950-Q1), and is directly proportional to the load current. Since the PMOS pass element is a voltage-driven device, the quiescent current is ultra low (28 uA maximum) and is stable over the entire range of output load current (0 mA to 100 mA). The ultra low-dropout voltage feature and ultra low-power operation result in a significant increase in system battery operating life, making this device suitable for use in automotive applications.

The TPS769xx-Q1 also features a logic-enabled sleep mode to shut down the regulator. This reduces quiescent current to 1 uA typical at $T_J = 25^{\circ}$ C. The TPS769xx-Q1 is offered in 1.2-V, 1.5-V, 1.8-V, 2.5-V, 2.7-V, 2.8-V, 3.0-V, 3.3-V and 5-V fixed-voltage versions and in a variable version (programmable over the range of 1.2 V to 5.5 V).

KEY FEATURES/BENEFITS

- Qualified in Accordance with AEC-Q100 (Contact the Product Information Center for details. Q100 qualification data available upon request.)
- 100-mA Low-Dropout Regulator
- Available in 1.2-V, 1.5-V, 1.8-V, 2.5-V, 2.7-V, 2.8-V, 3.0-V, 3.3-V, and 5-V Fixed-Output and Adjustable Versions
- Only 17-µA Quiescent Current at 100 mA
- 1-µA Quiescent Current in Standby Mode
- Dropout Voltage Typically 71 mV at 100mA
- Over Current Limitation
- -40°C to 125°C Operating Junction Temperature Range
- 5-Pin SOT-23 (DBV) Package



PACKAGING

Package Option: 5-Pin SOT-23 (DBV) Package

POWER DISSIPATION

The table below shows modeled data. This data can be used for approximating system thermal characteristics:

Package Thermal Data

Package	R ₀ JA	R _θ JC
5 Pin DBV (High K board)	180.0 °C/W	65.8 °C/W

PROCESS/PERFORMANCE OPTIONS

Available Devices

TJ	VOLTAGE	PACKAGE	PART NUMBER		SYMBOL
–40 °C to 125 °C	Variable 1.2V to 5.5V	SOT-23 (DBV)	TPS76901QDBVTQ1*	TPS76901QDBVRQ1**	PCFQ
	1.2V		TPS76912QDBVTQ1*	TPS76912QDBVRQ1**	PCGQ
	1.5V		TPS76915QDBVTQ1*	TPS76915QDBVRQ1**	PCHQ
	1.8V		TPS76918QDBVTQ1*	TPS76918QDBVRQ1**	PCIQ
	2.5V		TPS76925QDBVTQ1*	TPS76925QDBVRQ1**	PCJQ
	2.7V		TPS76927QDBVTQ1*	TPS76927QDBVRQ1**	PCKQ
	2.8V		TPS76928QDBVTQ1*	TPS76928QDBVRQ1**	PCLQ
	3.0V		TPS76930QDBVTQ1*	TPS76930QDBVRQ1**	PCMQ
	3.3V		TPS76933QDBVTQ1*	TPS76933QDBVRQ1**	PCNQ
	5.0V		TPS76950QDBVTQ1*	TPS76950QDBVRQ1**	PCOQ

- * The DBVT indicates tape and reel of 250 parts.
- ** The DBVR indicates tape and reel of 3000 parts.

PRODUCT INFORMATION CENTER

http://www.ti.com/sc/docs/pic/home.htm

Americas: (972) 644-5580

Europe: Francais: +33-(0)1-30 70 11 64 Italiano: 800 79 11 37 (free phone)

English: +33-(0)1-30 70 11 65 Deutsch: +49-(0)8161-80 33 11



IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third—party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Mailing Address:

Texas Instruments Post Office Box 655303 Dallas, Texas 75265

Copyright © 2002, Texas Instruments Incorporated