

TVP7002 PCB Layout Guidelines

TVP7002 PCB Layout Guidelines

- A High-K printed circuit board having a minimum of 4 layers is recommended for best thermal transfer and performance.
- The choice of single GND plane or split DGND/AGND plane will depend on board content and parts placement. If a single GND plane is used, keep digital components and return currents away from the analog section. If separate planes are used, keep analog power, decoupling, and traces over the AGND plane and digital traces over the DGND plane.
- Maintain clean power especially analog and PLL. Maintain recommended recommend power supply levels, and beware of IR drop across supply filtering.
- For minimum PLL clock jitter, a dedicated analog regulator is preferred for the PLL. If a dedicated regulator is not used, use good filtering and isolation on the PLL supply.
- Keep PLL loop filter components close to the inputs, and keep digital and analog inputs traces away from these components.
- Place 0.1µF power decoupling capacitors close to each power pin.
- Keep traces short and delay matched. Avoid clock and bus daisy-chaining to prevent reflections.
- Series termination resistors (22-Ω for 50-Ω trace impedance) are recommended on all digital outputs for best signal integrity and electro magnetic compliance (EMC). These terminations should be placed as close as possible to the TVP7002 output pins.
- Use 0.1µF AC-coupling capacitors for analog RGB inputs and 1nF AC-coupling capacitors for the SOG inputs. Unused analog inputs may be left floating or tied to GND with 0.1µF capacitors.
- SDA/SCL traces should be routed together and kept a minimum of 10x clearance away from any adjacent traces.
- All analog input traces should have a minimum of 10x (x means trace width) clearance between each other and other adjacent traces to minimize any potential crosstalk.
- Place the TVP7002 as close as possible to the video/graphics input connector and maintain matched trace length. 75-Ω trace impedance is preferred for the analog traces.
- All high speed signals routed on the bottom of board should be routed over a solid GND/Power plane and not routed over power/GND splits. Route signals over associated power plane where possible.
- Minimize vias in the high speed data and clock traces.
- Using GND fills on the top and bottom of the board will improve trace isolation and also help maximize EMC.
- Avoid routing traces under the PowerPad. Connect PowerPad to GND plane. When split GND planes
 are used, connect the PowerPad to the digital GND.
- See Figure 1 below for recommended GND split when split planes are used.






Figure 1. Recommended Split Between Ground Planes

IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

TI products are not authorized for use in safety-critical applications (such as life support) where a failure of the TI product would reasonably be expected to cause severe personal injury or death, unless officers of the parties have executed an agreement specifically governing such use. Buyers represent that they have all necessary expertise in the safety and regulatory ramifications of their applications, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of TI products in such safety-critical applications, notwithstanding any applications-related information or support that may be provided by TI. Further, Buyers must fully indemnify TI and its representatives against any damages arising out of the use of TI products in such safety-critical applications.

TI products are neither designed nor intended for use in military/aerospace applications or environments unless the TI products are specifically designated by TI as military-grade or "enhanced plastic." Only products designated by TI as military-grade meet military specifications. Buyers acknowledge and agree that any such use of TI products which TI has not designated as military-grade is solely at the Buyer's risk, and that they are solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI products are neither designed nor intended for use in automotive applications or environments unless the specific TI products are designated by TI as compliant with ISO/TS 16949 requirements. Buyers acknowledge and agree that, if they use any non-designated products in automotive applications, TI will not be responsible for any failure to meet such requirements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

Products		Applications	
Amplifiers	amplifier.ti.com	Audio	www.ti.com/audio
Data Converters	dataconverter.ti.com	Automotive	www.ti.com/automotive
DLP® Products	www.dlp.com	Communications and Telecom	www.ti.com/communications
DSP	<u>dsp.ti.com</u>	Computers and Peripherals	www.ti.com/computers
Clocks and Timers	www.ti.com/clocks	Consumer Electronics	www.ti.com/consumer-apps
Interface	interface.ti.com	Energy	www.ti.com/energy
Logic	logic.ti.com	Industrial	www.ti.com/industrial
Power Mgmt	power.ti.com	Medical	www.ti.com/medical
Microcontrollers	microcontroller.ti.com	Security	www.ti.com/security
RFID	www.ti-rfid.com	Space, Avionics & Defense	www.ti.com/space-avionics-defense
RF/IF and ZigBee® Solutions	www.ti.com/lprf	Video and Imaging	www.ti.com/video
		Wireless	www.ti.com/wireless-apps