











CSD95472Q5MC

SLPS599-FEBRUARY 2016

CSD95472Q5MC Synchronous Buck NexFET™ Smart Power Stage

Features

- 60-A Continuous Operating Current Capability
- 94.4% System Efficiency at 1.2 V / 30 A
- Low Power Loss of 2.3 W at 30 A
- High-Frequency Operation (up to 1.25 MHz)
- Diode Emulation Mode With FCCM
- Temperature-Compensated Bidirectional Current Sense
- Analog Temperature Output (600 mV at 0°C)
- **Fault Monitoring**
 - High-Side Short, Overcurrent, and Overtemperature Protection
- 3.3-V and 5-V PWM Signal Compatible
- Tri-State PWM Input
- Integrated Bootstrap Diode
- Optimized Deadtime for Shoot-Through Protection
- High-Density SON 5 × 6 mm Footprint
- Ultralow Inductance Package
- System-Optimized PCB Footprint
- DualCool™ Packaging
- RoHS Compliant Lead-Free Terminal Plating
- Halogen Free

2 Applications

- Multiphase Synchronous Buck Converters
 - **High-Frequency Applications**
 - High-Current, Low Duty Cycle Applications
- POL DC-DC Converters
- Memory and Graphic Cards


3 Description

The CSD95472Q5MC NexFET™ smart power stage is a highly optimized design for use in a high-power, high-density synchronous buck converter. This product integrates the driver IC and Power MOSFETs to complete the power stage switching function. This combination produces high-current, high-efficiency, and high-speed switching capability in a small 5 mm x 6 mm outline package. It also integrates the accurate current sensing and temperature sensing functionality to simplify system design and improve accuracy. In addition, the PCB footprint has been optimized to help reduce design time and simplify the completion of the overall system design.

Device Information⁽¹⁾

DEVICE	MEDIA	QTY	PACKAGE	SHIP
CSD95472Q5MC	13-Inch Reel	2500	SON 5 × 6 mm	Tape
CSD95472Q5MCT	7-Inch Reel	250	DualCool Package	and Reel

For all available packages, see the orderable addendum at the end of the data sheet.










Table of Contents

1	Features 1	7 Application Schematic	5
2	Applications 1	· ·	
3	Description 1	8.1 Community Resources	6
	Revision History2	8.2 Trademarks	6
	Pin Configuration and Functions3	8.3 Electrostatic Discharge Caution	6
	Specifications4	8.4 Glossary	6
•	6.1 Absolute Maximum Ratings 4	9 Mechanical, Packaging, and Orderable Information	7
	6.2 ESD Ratings	9.1 Mechanical Drawing 9.2 Recommended PCB Land Pattern	
	6.4 Thermal Information	9.3 Recommended Stencil Opening	

4 Revision History


DATE	REVISION	NOTES
February 2016	*	Initial release.

Submit Documentation Feedback

SLPS599 - FEBRUARY 2016

5 Pin Configuration and Functions

Top View



Pin Functions

PI	N	DESCRIPTION
NUMBER	NAME	DESCRIPTION
1	IOUT	Output of current sensing amplifier. V(IOUT) – V(REFIN) is proportional to the phase current.
2	REFIN	External reference voltage input for current sensing amplifier.
3	ENABLE	Enables device operation. If ENABLE = logic HIGH, turns on device. If ENABLE = logic LOW, the device is turned off and both MOSFET gates are actively pulled low. An internal 100 k Ω pulldown resistor will pull the ENABLE pin LOW if left floating.
4	P_{GND}	Power ground, connected directly to pin 13.
5	V_{DD}	Supply voltage to gate driver and internal circuitry.
6	V_{SW}	Phase node connecting the HS MOSFET source and LS MOSFET drain – pin connection to the output inductor.
7	V_{IN}	Input voltage pin. Connect input capacitors close to this pin.
8	BOOT_R	Return path for HS gate driver, connected to V _{SW} internally.
9	воот	Bootstrap capacitor connection. Connect a minimum of 0.1 µF 16 V X7R ceramic capacitor from BOOT to BOOT_R pins. The bootstrap capacitor provides the charge to turn on the control FET. The bootstrap diode is integrated.
10	FCCM	This pin enables the diode emulation function. When this pin is held LOW, diode emulation mode is enabled for sync FET. When FCCM is HIGH, the device is operated in forced continuous conduction mode. An internal 5 μ A current source will pull the FCCM pin to 3.3 V if left floating.
11	TAO/ FAULT	Temperature Analog Output. Reports a voltage proportional to the die temperature. An ORing diode is integrated in the IC. When used in multiphase application, a single wire can be used to connect the TAO pins of all the ICs. Only the highest temperature will be reported. TAO will be pulled up to 3.3 V if thermal shutdown occurs. TAO should be bypassed to P _{GND} with a 1 nF 16 V X7R ceramic capacitor.
12	PWM	Pulse width modulated tri-state input from external controller. Logic LOW sets control FET gate low and sync FET gate high. Logic HIGH sets control FET gate high and sync FET gate low. Open or High Z sets both MOSFET gates low if greater than the tri-state shutdown hold-off time (t _{3HT}).
13	P_{GND}	Power ground.

TEXAS INSTRUMENTS

6 Specifications

6.1 Absolute Maximum Ratings

 $T_A = 25$ °C (unless otherwise noted)⁽¹⁾

		MIN	MAX	UNIT
	V _{IN} to P _{GND}	-0.3	20	V
	V_{IN} to V_{SW}	-0.3	20	V
	V _{IN} to V _{SW} (10 ns)		23	V
	V _{SW} to P _{GND}	-0.3	20	V
	V _{SW} to P _{GND} (10 ns)	-7	23	V
	V _{DD} to P _{GND}	-0.3	7	V
	ENABLE, PWM, FCCM, TAO, IOUT, REFIN to P _{GND} ⁽²⁾	-0.3	$V_{DD} + 0.3 V$	V
	BOOT to BOOT_R ⁽²⁾	-0.3	$V_{DD} + 0.3 V$	V
P_D	Power dissipation		12	W
T_J	Operating junction	– 55	150	°C
T _{stg}	Storage temperature	– 55	150	C

⁽¹⁾ Stresses beyond those listed under Absolute Maximum Ratings may cause permanent damage to the device. These are stress ratings only, which do not imply functional operation of the device at these or any other conditions beyond those indicated under Recommended Operating Conditions. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

6.2 ESD Ratings

	-		VALUE	UNIT
V	Clastrostatia diasharas	Human body model (HBM)	±2000	\/
V _(ESD)	Electrostatic discharge	Charged device model (CDM)	±500	V

6.3 Recommended Operating Conditions

 $T_A = 25^{\circ}$ (unless otherwise noted)

			MIN	MAX	UNIT
V_{DD}	Gate drive voltage		4.5	5.5	V
V _{IN}	Input supply voltage (1)			16	V
V _{OUT}	Output voltage			5.5	V
I _{OUT}	Continuous output current	$V_{IN} = 12 \text{ V}, V_{DD} = 5 \text{ V}, V_{OUT} = 1.2 \text{ V},$ $f_{SW} = 500 \text{ kHz}, L_{OUT} = 0.225 \mu H^{(2)}$		60	Α
I _{OUT-PK}	Peak output current ⁽³⁾	$f_{\text{SW}} = 500 \text{ kHz}, L_{\text{OUT}} = 0.225 \mu\text{H}^{(2)}$		90	Α
$f_{\sf SW}$	Switching frequency	$C_{BST} = 0.1 \mu F \text{ (min)}$		1250	kHz
	On time duty cycle	$f_{SW} = 1 \text{ MHz}$		85%	
	Minimum PWM on time		40		ns
	Operating temperature		-40	125	°C

⁽¹⁾ Operating at high V_{IN} can create excessive AC voltage overshoots on the switch node (V_{SW}) during MOSFET switching transients. For reliable operation, the switch node (V_{SW}) to ground voltage must remain at or below the Absolute Maximum Ratings.

6.4 Thermal Information

 $T_A = 25^{\circ}C$ (unless otherwise noted)

	THERMAL METRIC	MIN	TYP	MAX	UNIT
$R_{\theta JC(top)}$	Junction-to-case (top of package) thermal resistance (1)			5	°C/W
$R_{\theta JB}$	Junction-to-board thermal resistance (2)			1.5	C/VV

⁽¹⁾ R_{BJC(top)} is determined with the device mounted on a 1 inch² (6.45 cm²), 2-oz (0.071 mm thick) Cu pad on a 1.5 inches x 1.5 inches, 0.06-inch (1.52-mm) thick FR4 board.

Submit Documentation Feedback

⁽²⁾ Should not exceed 7 V.


⁽²⁾ Measurement made with six 10 µF (TDK C3216X5R1C106KT or equivalent) ceramic capacitors placed across V_{IN} to P_{GND} pins.

⁽³⁾ System conditions as defined in Note 1. Peak Output Current is applied for $t_p = 50 \mu s$.

R_{AJB} value based on hottest board temperature within 1 mm of the package.



7 Application Schematic



TEXAS INSTRUMENTS

8 Device and Documentation Support

8.1 Community Resources

The following links connect to TI community resources. Linked contents are provided "AS IS" by the respective contributors. They do not constitute TI specifications and do not necessarily reflect TI's views; see TI's Terms of Lise

TI E2E™ Online Community TI's Engineer-to-Engineer (E2E) Community. Created to foster collaboration among engineers. At e2e.ti.com, you can ask questions, share knowledge, explore ideas and help solve problems with fellow engineers.

Design Support *TI's Design Support* Quickly find helpful E2E forums along with design support tools and contact information for technical support.

8.2 Trademarks

NexFET, DualCool, E2E are trademarks of Texas Instruments. All other trademarks are the property of their respective owners.

8.3 Electrostatic Discharge Caution



These devices have limited built-in ESD protection. The leads should be shorted together or the device placed in conductive foam during storage or handling to prevent electrostatic damage to the MOS gates.

8.4 Glossary

SLYZ022 — TI Glossary.


This glossary lists and explains terms, acronyms, and definitions.

www.ti.com

9 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.


9.1 Mechanical Drawing



DIM	М	ILLIMETERS		INCHES				
DIN	MIN	NOM	MAX	MIN	NOM	MAX		
Α	0.950	1.000	1.050	0.037	0.039	0.041		
a1	0.000	0.000	0.050	0.000	0.000	0.002		
b	0.200	0.250	0.320	0.008	0.010	0.013		
b1		2.750 TYP			0.108 TYP			
b2	0.200	0.250	0.320	0.008	0.010	0.013		
b3		0.250 TYP			0.010 TYP			
c1	0.150	0.200	0.250	0.006	0.008	0.010		
c2	0.200	0.250	0.300	0.008	0.010	0.012		
D2	5.300	5.400	5.500	0.209	0.213	0.217		
d	0.200	0.250	0.300	0.008	0.010	0.012		
d1	0.350	0.400	0.450	0.014	0.016	0.018		
d2	1.900	2.000	2.100	0.075	0.079	0.083		
E	5.900	6.000	6.100	0.232	0.236	0.240		
E1	4.900	5.000	5.100	0.193	0.197	0.201		
E2	3.200 3.300		3.400	0.126	0.130	0.134		
е		0.500 TYP		0.020 TYP				
K		0.350 TYP						
L	0.400	0.500	0.600	0.016	0.020	0.024		
L1	0.210	0.310	0.410	0.008	0.012	0.016		
θ	0.00	_	_	0.00		_		


TEXAS INSTRUMENTS

9.2 Recommended PCB Land Pattern



1. Dimensions are in mm (inches).

9.3 Recommended Stencil Opening



- 1. Dimensions are in mm (inches).
- 2. Stencil thickness is 100 μm.

www.ti.com 16-Apr-2021

PACKAGING INFORMATION

Orderable Device	Status (1)	Package Type	Package Drawing	Pins	Package Qty	Eco Plan	Lead finish/ Ball material	MSL Peak Temp	Op Temp (°C)	Device Marking (4/5)	Samples
CSD95472Q5MC	ACTIVE	VSON-CLIP	DMC	12	2500	RoHS-Exempt & Green	SN	Level-2-260C-1 YEAR	-55 to 150	95472MC	Samples
CSD95472Q5MCT	ACTIVE	VSON-CLIP	DMC	12	250	RoHS-Exempt & Green	SN	Level-2-260C-1 YEAR	-55 to 150	95472MC	Samples

(1) The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

OBSOLETE: TI has discontinued the production of the device.

(2) RoHS: TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (CI) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

- (3) MSL, Peak Temp. The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.
- (4) There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.
- (5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.
- (6) Lead finish/Ball material Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.



PACKAGE OPTION ADDENDUM

www.ti.com 16-Apr-2021

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale (https://www.ti.com/legal/termsofsale.html) or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2021, Texas Instruments Incorporated