## **Assembly Bill of Materials**

## **Texas Instruments**

Enter search term in cell K2 below

Search Findchips.com
Search Digi-Key
Search Mouser
Search Newark
Search RS Components

Project Name: 10W UCC28720 5V 2A
Project File: PMP9135 \_REV.PrjPcb
Base ID: PMP9135
Schematic Rev: E2
Assembly Variant: -001
Build Quantity: 100
Generated: 08/01/2014 12:17:04

Item	Designator	Description	RoHS	Manufacturer	PartNumber	Quantity	Required	Supplier 1	Supplier Part Number 1	Supplier 2	Supplier Part Number 2	Alternate Manufacturer	Alternate PartNumber
1		Printed Circuit Board		Any	PMP9135	1	100					-	-
2		CAP, CERM, 10uF, 16V, +/-10%, X5R, 1210		AVX	1210YD106KAT2A	1	100	Digi-Key	478-1629-1-ND	Mouser	581-1210YD106K		
3		CAP, CERM, 100pF, 500V, +/-5%, C0G/NP0, 1206	÷	Kemet	C1206C101JCGACTU	1	100	Digi-Key	399-7073-2-ND	Mouser	80-C1206C101JCG		
4		CAP, CERM, 1000pF, 300V, +/-3/8, COG/NFO, 1200	Ÿ	Vishav-Bccomponents	VY2102M29Y5UG63V7	1	100	Digi-Key	BC2752-ND	Mouser	72-VY2102M29Y5UG63V7		
4		ls=7.5		, ,				Digi-Key	BG2732-ND	Wouser	72*V12102W29130G03V7		
5		CAP, [Technology], xxxF, xxV, +/-xx%, xxOhm ESR, [MountType]	RoHS Compliant	Nichicon	RNE0J122MDN1PX	2	200						
6		CAP, CERM, 0.1uF, 50V, +/-5%, X7R, 0805	Y	AVX	08055C104JAT2A	1	100	Digi-Key	478-3352-1-ND	Mouser	581-08055C104J		
7		CAP, AL, 10uF, 400V, +/-20%, TH	Y	Nichicon	UVK2G4R7MPD	2	200	Digi-Key	UVK2G4R7MPD-ND	Mouser	647-UVK2G4R7MPD		
8		Diode, Switching-Bridge, 600V, 1A, TH	Υ		MB6S	1	100	Mouser	512-MB6S				
9		Diode, Switching, 200V, 0.2A, SOD-123	Y	Diodes Inc.	BAV21W-7-F	1	100	Digi-Key	BAV21W-FDICT-ND	Mouser	621-BAV21W-F		
10	D3	Diode, TVS, Uni, 170V, 600W, SMB	Y	ST Microelectronics	SMBJ170A-TR	1	100	Digi-Key	497-6511-1-ND	Mouser	511-SMBJ170A-TR		
11	D4	Diode, [Type], xxxV, x.xxA, [PackageReference]	RoHS Compliant	Diodes Inc	DFLR1600-7	1	100						
12	D5	Diode, Schottky, 40V, 3.5A, DPAK	RoHS Compliant	Diodes Inc	PDS1040L-13	1	100						
13	H1, H2, H5, H6	Machine Screw, Round, #4-40 x 1/4, Nylon, Philips panhead		B&F Fastener Supply	NY PMS 440 0025 PH	4	400	Digi-Key	H542-ND			-	-
14	H3, H4, H7, H8	Standoff, Hex, 0.5"L #4-40 Nylon	Y	Keystone	1902C	4	400	Digi-Key	1902CK-ND			-	-
15		CONN USB 3.0 RCPT ST A R/A	RoHS Compliant	FCÍ	10117835-002LF	1	100	3 ,					
16	1	Test Point, Compact, Red, TH	Ý	Keystone	5005	1	100	Digi-Key	5005K-ND				
17	L1	Inductor, Wirewound, Ferrite, 1mH, 2.4A, 0.1 ohm, TH	RoHS Compliant	Wurth Electronics Inc		1	100	g,					
18	N	Test Point, Compact, Black, TH	Ý	Keystone	5006	1	100	Digi-Key	5006K-ND				
19	Q1	Transistor, NPN, 400V, 1.5A, TO-92AP	RoHS Compliant	STMicroelectronics	2STL2580	1	100	g,					
20	R1	RES 6.8 OHM 1W 5% AXIAL	RoHS Compliant	TT Electronics/IRC	SPP1UL6R80JLF	1	100						
21	R2	RES, 6.8k ohm, 5%, 0.125W, 0805	Ý	Vishay-Dale	CRCW08056K80JNEA	1	100	Mouser	71-CRCW08056K80JNEA	Famell	1537444		
22		RES. 0 ohm, 5%, 0.125W, 0805	Y	Rohm	MCR10EZPJ000	1	100	Digi-Key	RHM0.0ARCT-ND				
23		RES, 39k ohm, 5%, 0.1W, 0603	Ý	Vishay-Dale	CRCW060339K0JNEA	1	100	Mouser	71-CRCW0603J-39K-E3	Famell	1514761		
24		RES. 1.50k ohm. 1%, 0.1W, 0603	Ÿ	Vishay-Dale	CRCW06031K50FKEA	1	100	Digi-Key	541-1.50KHCT-ND	Mouser	71-CRCW0603-1.5K-E3		
25		RES, 2.20 ohm, 1%, 0.125W, 0805	÷	Panasonic	ERJ-6RQF2R2V	1	100	Digi-Key	P2.2DCT-ND	Mouser	667-ERJ-6RQF2R2V		
26		RES, 100k ohm, 1%, 0.25W, 1206	÷	Yageo America	RC1206FR-07100KL	1	100	Digi-Key	311-100KFRCT-ND	Mouser	603-RC1206FR-07100KL		
27		RES, 4.7 ohm, 5%, 0.125W, 0805	·	Vishav-Dale	CRCW08054R70JNEA	1	100	Digi-Key	541-4.7ACT-ND	Mouser	71-CRCW08054R70JNEA		
28		RES, 33 ohm, 5%, 0.1W, 0603	Ý	Vishay-Dale Vishay-Dale	CRCW060333R0JNEA	1	100	Digi-Key	541-33GCT-ND	Mouser	71-CRCW0603J-33-E3		
29		RES, 1.50k ohm, 1%, 0.25W, 1206	· v	Vishay-Dale Vishay-Dale	CRCW12061K50FKEA	1	100	Digi-Key	541-1.50KFCT-ND	Mouser	71-CRCW1206-1.5K-E3		
30		RES, 100k ohm, 1%, 0.1W, 0603	· ·	Vishay-Dale Vishay-Dale	CRCW0603100KFKEA	1	100	Digi-Key	541-100KHCT-ND	Mouser	71-CRCW0603-100K-E3		
31		RES, 27k ohm, 5%, 0.1W, 0603	·	Yageo America	RC0603JR-0727KL	1	100	Digi-Key	311-27KGRCT-ND	Mouser	603-RC0603JR-0727KL		
		RES, 6.81k ohm, 1%, 0.1W, 0603	·	Yageo America	RC0603JR-0727KL RC0603FR-076K81L	1	100	Digi-Key Digi-Key	311-6.81KHRCT-ND	Mouser	603-RC0603FR-076K81L		
32 33	K14	NEO, 0.0 IK UHIII, 176, U. IVV, UUU3	V	rayeo America	EFD20 10W	1	100	Digi-Ney	311-0.01KHKU1-ND	iviouser	003-NC0003FR-070N81L		
34		CONSTANT-VOLTAGE, CONSTANT-CURRENT	Y	Texas Instruments	UCC28720D		100					None	
34	U1	CONTROLLER WITH PRIMARY SIDE REGULATION, D0007A		l exas instruments	UCC28720D	1	100					None	
35		CAP, [Technology], xxxF, xxV, +/-xx%, xxOhm ESR, [MountType]	RoHS Compliant	Nichicon	UVR2G100MHD	0	0						
36	C6	CAP, CERM, 2200pF, 50V, +/-10%, X7R, 0805	Ý	AVX	08055C222KAT2A	0	0	Digi-Key	478-1375-1-ND	Mouser	581-08055C222K		
37	L2	Inductor, Wirewound, Ferrite, 10uH, 0.3A, 0.9 ohm, SMD	Υ	TDK	CPL2512T100M	0	0	Digi-Key	445-4176-1-ND	Mouser	810-CPL2512T100M		
38	R13	RES, 180 ohm, 5%, 0.125W, 0805	Υ	Vishay-Dale	CRCW0805180RJNEA	0	0	Digi-Key	541-180ACT-ND	Mouser	71-CRCW0805180RJNEA		

## IMPORTANT NOTICE FOR TI REFERENCE DESIGNS

Texas Instruments Incorporated ("TI") reference designs are solely intended to assist designers ("Buyers") who are developing systems that incorporate TI semiconductor products (also referred to herein as "components"). Buyer understands and agrees that Buyer remains responsible for using its independent analysis, evaluation and judgment in designing Buyer's systems and products.

TI reference designs have been created using standard laboratory conditions and engineering practices. TI has not conducted any testing other than that specifically described in the published documentation for a particular reference design. TI may make corrections, enhancements, improvements and other changes to its reference designs.

Buyers are authorized to use TI reference designs with the TI component(s) identified in each particular reference design and to modify the reference design in the development of their end products. HOWEVER, NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY THIRD PARTY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT, IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of such information may require a license from a third party, or a license from TI under the patents or other intellectual property of TI.

TI REFERENCE DESIGNS ARE PROVIDED "AS IS". TI MAKES NO WARRANTIES OR REPRESENTATIONS WITH REGARD TO THE REFERENCE DESIGNS OR USE OF THE REFERENCE DESIGNS, EXPRESS, IMPLIED OR STATUTORY, INCLUDING ACCURACY OR COMPLETENESS. TI DISCLAIMS ANY WARRANTY OF TITLE AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, QUIET ENJOYMENT, QUIET POSSESSION, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS WITH REGARD TO TI REFERENCE DESIGNS OR USE THEREOF. TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY BUYERS AGAINST ANY THIRD PARTY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON A COMBINATION OF COMPONENTS PROVIDED IN A TI REFERENCE DESIGN. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, SPECIAL, INCIDENTAL, CONSEQUENTIAL OR INDIRECT DAMAGES, HOWEVER CAUSED, ON ANY THEORY OF LIABILITY AND WHETHER OR NOT TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES, ARISING IN ANY WAY OUT OF TI REFERENCE DESIGNS OR BUYER'S USE OF TI REFERENCE DESIGNS.

TI reserves the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques for TI components are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

Reproduction of significant portions of TI information in TI data books, data sheets or reference designs is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards that anticipate dangerous failures, monitor failures and their consequences, lessen the likelihood of dangerous failures and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in Buyer's safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed an agreement specifically governing such use.

Only those TI components that TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components that have *not* been so designated is solely at Buyer's risk, and Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.