

Bill of Materials

TI DESIGNS
TIDA-00150
Automotive Resistive Pressure Sensor Interface

Item #	Quantity	Designator	Comment	Description	Footprint	PN	P/N (DIGIKEY)	REMARKS	P/N (NEWARK)
CAPACITORS									
1	5	C1, C35, C42, C52, C53		1uF 0805 16V 10% X7R	0805	C2012X7R1C105K	445-1358-1-ND		
2	13	C2, C3, C4, C5, C34, C36, C37, C39, C40, C46, C48, C68		0.1uF 16V X7R	0603	399-1096-1-ND, C0603C104K4RACU	399-1096-1-ND, C0603C104K4RACU		
3	2	C6, C7		366F 50V COG	0603	GRM1885E1H362QA01D	450-1414-1-ND		
4	1	C8		0.1uF 0805 16V 10% X7R	0805	C0603C104K4RACU	399-1096-1-ND	603 VS 805 PACKAGE USE 805 package	
5	12	C9, C17, C43, C45, C49, C51, C54, C60, C61, C62, C63, C64		0.1uF 805V 50V 10% X7R	0805	C2012X7R1H104K	445-1349-2-ND		
6	4	C10, C15, C26, C31		0.01uF 0805 50V 10% X7R	0805	C2012X7R1H103K	445-1348-1-ND		
7	1	C12		10uF 16V Tantal	1206	B45196H3104K109	495-2236-1-ND		
8	1	C14		22uF 16V Tantal	1210	TC1AL1C226M8R	511-1502-1-ND		
9	2	C18, C21		Cap Var	Cap Var - Murata	TZB4R500BA10R00	490-1903-6-ND		
10	2	C19, C22		30pF	0805	08051A300JA72A	478-3738-1-ND		
11	2	C20, C23		56pF 0805 100V 5% COG	0805	08051A560JA72A	478-5023-1-ND		
12	4	C24, C27, C28, C32		10pF	0805	C2012X7R1H102K	445-1347-1-ND		
13	4	C30, C33, C38, C41		2.2nF 0603 16V 10% X7R	0603	C0603C223K4RACU	399-1093-1-ND	2.2NF VS .22NF USE 2.2NF	
14	2	C44, C47		100pF 50V X7R	0805	C2012C0G1H101J1	445-1329-1-ND	5% VS .10% USE Either Tolerance	
15	1	C50		100pF 250V COG	0603	C1408C0G2E101J	445-2314-1-ND		
16	1	CBulk1		100uF 16V AL	100uF 16V 20% AL	CAP 6.6 X 6.6 MM SMD	EEV1G1C101P	PCE361RCT-ND	
JUMPERS / HEADERS									
17	1	J1	Female	Receptacle Assembly, 9 Position, RAJF	D5UB1-385-RAJF	A35109-ND	1734348-1		
The Following Four Parts (Item # 18-21) Will Be Cut from the Larger Part (A26513-40) to the Appropriate Number of Pins									
18	19	JP1, JP2, JP3, JP4, JP5, JP6, JP7, JP8, JP9, JP11, JP13, JP14, JP15, JP16, JP18, JP22, JP23, JP28, JP29	JUMPER 2 PIN	Two Pin Jumper	JMPO 2	4-103185-0	A36513-40-ND		
19	6	JP10, JP12, JP17, JP19, JP26, JP27	JUMPER 3 PIN	Three Pin Jumper	JMPO 3	4-103185-0	A36513-40-ND		
20	1	H1	Header 4	Header, 4 Pin	HDR1X4				
21	1	H2	Header 6	Header, 6 Pin	HDR1X6				
22	1	P1, P3	END, VPWR	BANANA STACK (FEMALE END)	BANANA LARGX HEX / R2D2	39F845			66856-1
23	1	P2	2 Pos Term Block	2 Pos Term Block	1229018		277-1236-ND		
24	1	H4	Header 20X2	Header, 20 Pin, Dual row	HDR2X20	4-103240-0	A36528-40-ND		
25	1	P6	TIGER - A	TIGER - A	HDR-2x15-M	TSW-115-08-T-D-RA	SAM1049-15-ND		
INDUCTORS, COILS, ETC.									
26	4	L1, L2, L3, L4	DR		0805	MCR10E2P1000	RHM0.GARCT-ND		
RESISTORS									
27	6	R1, R2, R12, R13, R22, R23	DR	0.0 0603 1/10W 5%	0603	MCR03E2P1000	RHM0.GCCT-ND		
28	1	R5	1M	1M 0603 1/10W 5%	0603	MCR03E2P105	RHM1.0MGCT-ND		
29	1	R6	200R	200 0805 1/8W 1%	0805	MCR10E2P201	RHM200ARCT-ND		
30	1	R7	1k	1k 0805 1/4 1%	0805	MCR10E2PF1001	RHM1.00KCRCT-ND		
31	1	R8	47k	47k 0805 1/10W 5%	0805 x4 Concave (2012 metric)	743C081473JPTFR	743C081473JPCCT-ND		
32	4	R9, R10, R19, R20	DR	10k 0805 1/8W 5%	0805	MCR10E2PF1002	RHM10.0KCRCT-ND		
33	4	R14, R15, R27, R28	DR	5M 427X502	0805_murata	SMA427X502	SMA427X502CT-ND		
34	4	R17, R18, R29, R30	DR	7.5k 0805 1/8W 5%	0805	MCR10E2H752, RHM7.5KACT-ND	MCR10E2H752, RHM7.5KACT-ND		
35	8	R24, R25, R31, R32, R35, R36, R40, R41	DR	1k 0603 1/10W 1%	0603	MCR03E2PFX1001	RHM1.00KICT-ND		
36	19	R33, R34, R37, R38, R39, R42, R43, R49, R50, R51, R52, R60, R76, R77, R78, R79, R80, R89, R91	DR	49.9k 0603 5% 1/10W	0603	MCR03E2PFX4992, RHM49.9KCHCT-ND	MCR03E2PFX4992, RHM49.9KCHCT-ND		
37	4	R44, R45, R47, R48	DR	49k 0805 1/8W 5%	0805	MCR03E2PFX4992	RHM49.9KCHCT-ND	49.9k VS 49k OR 603 VS 805 USE 805 49.9k	
38	1	R46	200R	200 0805 1/8W 5%	0805	MCR10E2P201	RHM200ARCT-ND		
39	2	R53, R55	4.99k	4.99k 0603 1/10W 1%	0603	MCR03E2PFX4991	RHM4.99KCHCT-ND		
40	1	R54	200R	200 0805 1/8W 1%	0805	MCR10E2P201	RHM200ARCT-ND		
41	1	R64	1k	1k 0603 1/10W 5%	0603	MCR03E2PF1001	RHM1.00KICT-ND		
42	1	R66	220k	220k 0603 1/10W 5%	0603	MCR03E2P1224	RHM220KGCCT-ND		
43	1	R68	5R	5R 1206 1/3W 5%	1206	ESR1E2P15R1	RHM5.1ICT-ND	5 VS 5.1" USE 5.1 Ohms	
44	1	R70	10R	10R 0603 1/10W 1%	0805	MCR03E2PFX10R0	RHM10.0HCT-ND		
45	4	R75, R81, R87, R94	100 0805 1/10W 5%	100 0805 1/10W 5% - NETWORK	0805 x4 Concave (2012 metric)	743C081101JPTFR	743C081101JPCCT-ND		
46	1	R80	332 0805 1/8W 5%	332 0805 1/8W 5%	0805	MCR10E2PF3320	RHM332CRCT-ND		
47	1	R92, R93	110 0805 1/8W 5%	110 0805 1/8W 5%	0805	MCR03E2PF1101	RHM33.0ARCT-ND		
48	1	R93	11k	1100 0805 1/8W 5%	0805	MCR10E2P112	RHM11.0KARCT-ND		
TI - SEMICONDUCTORS									
The Following Parts (Item # 49-64) Will Be Provided By Texas Instruments									
49	1	U1	PSA400 - PSSC OFN			790-41036-101T		QFN ICs are not available from standard inventory. They are orderable here: http://www.ti.com/psa/cisevm.nsf/Request?OpenForm	
50	1	U2	TLV1117	TLV1117CDCYR	PG-SOT-223	296-17598-1-ND	296-17598-1-ND		
51	1	U4	REG102-5	REG102NA-5/250	DBV (R-PDSO-G5)	REG102NA-5/250	REG102NA-5CT-ND		
52	3	U5, U10, U19	OPA2335UA	OPA2335AIDR	183H-L	OPA2335AIDR	296-14170-5-ND should be 296-13462-1-ND	MPN & DIGIKEY PART NOT SAME	
53	4	U6, U7, U9, U11	TSSA3359	TSSA3359DCUR	MSOHR (DQCL)	TSSA3359DCUR	296-21193-1-ND		
54	1	U8	DAC8574	DAC8574IDR	PNV (R-PDSO-G1-16)	DAC8574IDR	296-14170-5-ND		
55	2	U12, U13	SN74LVC1G07	SN74LVC1G07DBVR	DBV (R-PDSO-G6)	SN74LVC1G07DBVR	296-8485-1-ND		
56	1	U14	ADS1100A2	ADS1100A2IDBVT	DBV (R-PDSO-G6)	ADS1100A2IDBVT	296-12966-1-ND should be 296-14239-1-ND	MPN & DIGIKEY PART NOT SAME	

Item #	Quantity	Designator	Comment	Description	Footprint	P/N	P/N (DIGIKEY)	REMARKS	P/N (NEWARK)
57	1	U15		TS12A44514	PW (R-PD50-G)-14	TS12A44514PWR			
58	1	U16		ADS1100A3	DBV (R-PD50-G)6	ADS1100A3DBVT	296-14298-1-ND should be 296-14300-1-ND	MPN & DIGIKEY PART NOT SAME	
59	2	U17, U27		TS5A23159	MSOP10 (R)55	TS5A23159QCSR	296-18598-1-ND		
60	1	U18		ADS1100A4	DBV (R-PD50-G)6	ADS1100A4DBVT	296-14299-1-ND should be 296-14301-1-ND	MPN & DIGIKEY PART NOT SAME	
61	1	U20		ADS1100A5	DBV (R-PD50-G)6	ADS1100A5DBVT	296-14300-1-ND should be 296-14302-1-ND	MPN & DIGIKEY PART NOT SAME	
62	1	U23		MAX3221ECAF	S5DP16	MAX3221DBR	296-9595-1-ND		
63	1	U25		SN74LVC1G240	DCK (R-PD50-G)5	SN74LVC1G240DCKR	296-11610-1-ND		
64	1	U26		SN74CBTLV257	P/W (R-PD50-G)-18	SN74CBT257CPWR	296-19211-1-ND		
SEMICONDUCTORS									
65	1	D1		Diode Schottky	DO-214AA	5SR44 E3R2T	5SR44 E3R2TQICT-ND		
66	4	D2, D3, D30, D31		LED2	Typical RED, GREEN, YELLOW, AMBER GaAs LED	9805 - Lumileds	67-1553-2 SML-LXT0805GW-TR		
67	1	DZ1		13V Zener	DO-214aa	SMBJ5350B-TP	SMBJ5350B-TPMSCT-ND		
68	1	DZ4		5.1V Zener	SOT-23	BZX84C5V1-7-F	BZX84C5V1-FDICT-ND		
69	1	D3		SU2319DS-T1-E3	SOT-23	SU2319DS-T1-E3	SU2319DS-T1-E3CT-ND		
70	1	D4		2N2222	SOT-23	SMBT2222AE6327	SMBT2222AICT-ND		
71	1	X1		EC5-400-20-30B-DU	Crystal 4	EC5-400-20-30B-DU	XC1520CT-ND		
TESTPOINTS AND SWITCHES									
72	3	T1, T2, T3		-5V, +7.5V, VPWR	TEST POINT 0.042	151-107-RC		151-107-RC	
73	29	TP11, TP12, TP13, TP14, TP15, TP16, TP17, TP18, TP19		GPIO5, GPIO6, ICAP1, ICAP2, MISO, MOSI, OWI, RX	TEST POINT 0.042	151-201-RC		151-201-RC	
74	1								
75	5	TP1, TP2, TP3, TP4, TP200		+2.5V, AVDD, DVDD, VDD, VP_OTP	TEST POINT 0.042	151-207-RC		151-207-RC	
76	1	TP29		GND	TEST POINT 0.042	151-203-RC		151-203-RC	
77	15	TP39, TP40, TP41, TP42, TP44, TP45		GND	TEST POINT 0.052	151-103-RC		151-103-RC	
STANDOFFS and HARDWARE									
78	4	SPC TECHNOLOGY - 2401 - Spacer		n/a		2401			22N4906
79	4	SPC TECHNOLOGY - 80-705 - Open Crimmel		n/a		80-705			13F475
80	8	KEYSTONE - 09300 - Machine Screw		n/a		9300			10M0258
SHUNTS									
SHUNTS Will Be Installed According to the Diagram in the "Hardware Assembly" Document									
81	24	CONN_JUMPER SHORTING GOLD FLASH		N/A		N/A	SPC025YAN	59001-ND	
NOT INSTALLED COMPONENTS									
82	2	R3, R4		0.0R	0805	MCROSE 2P3900	01M0-0CCT-ND		
83	2	C25, C29		100F - X2Y	180F - X2Y	50BX14W10MVA7	206-1008-1-ND		
84	1	C59		3300F 16V X7R	3300F 0603 16V 10% X7R	9603	C1608XR1C334K	445-5126-1-ND	

IMPORTANT NOTICE FOR TI REFERENCE DESIGNS

Texas Instruments Incorporated ("TI") reference designs are solely intended to assist designers ("Buyers") who are developing systems that incorporate TI semiconductor products (also referred to herein as "components"). Buyer understands and agrees that Buyer remains responsible for using its independent analysis, evaluation and judgment in designing Buyer's systems and products.

TI reference designs have been created using standard laboratory conditions and engineering practices. **TI has not conducted any testing other than that specifically described in the published documentation for a particular reference design.** TI may make corrections, enhancements, improvements and other changes to its reference designs.

Buyers are authorized to use TI reference designs with the TI component(s) identified in each particular reference design and to modify the reference design in the development of their end products. HOWEVER, NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY THIRD PARTY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT, IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI REFERENCE DESIGNS ARE PROVIDED "AS IS". TI MAKES NO WARRANTIES OR REPRESENTATIONS WITH REGARD TO THE REFERENCE DESIGNS OR USE OF THE REFERENCE DESIGNS, EXPRESS, IMPLIED OR STATUTORY, INCLUDING ACCURACY OR COMPLETENESS. TI DISCLAIMS ANY WARRANTY OF TITLE AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, QUIET ENJOYMENT, QUIET POSSESSION, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS WITH REGARD TO TI REFERENCE DESIGNS OR USE THEREOF. TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY BUYERS AGAINST ANY THIRD PARTY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON A COMBINATION OF COMPONENTS PROVIDED IN A TI REFERENCE DESIGN. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, SPECIAL, INCIDENTAL, CONSEQUENTIAL OR INDIRECT DAMAGES, HOWEVER CAUSED, ON ANY THEORY OF LIABILITY AND WHETHER OR NOT TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES, ARISING IN ANY WAY OUT OF TI REFERENCE DESIGNS OR BUYER'S USE OF TI REFERENCE DESIGNS.

TI reserves the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques for TI components are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

Reproduction of significant portions of TI information in TI data books, data sheets or reference designs is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards that anticipate dangerous failures, monitor failures and their consequences, lessen the likelihood of dangerous failures and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in Buyer's safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed an agreement specifically governing such use.

Only those TI components that TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components that have **not** been so designated is solely at Buyer's risk, and Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.