Bill Of Materials

TI Designs # TIDA-00175

Interface to an BiSS-C Position Encoder

Quantity	Designator	Value	Description (1997)	Manufacturer		PackageReferer	
3	C1, C5, C6		CAP, CERM, 10uF, 25V, +/-10%, X5R, 0805		C2012X5R1E106K1		Fitted
), C11, C19, (CAP, CERM, 2.2uF, 50V, +/-10%, X5R, 1206		GRM31CR61H225k		Fitted
1	C12	100uF	CAP, AL, 100uF, 63V, +/-20%, 0.35 ohm, SMD	Panasonic	EEE-FK1J101P	SMT Radial G	Fitted
1	C14	2200pF	CAP, CERM, 2200pF, 16V, +/-10%, X7R, 0603	MuRata	GRM188R71C222K	0603	Fitted
1	C16	12pF	CAP, CERM, 12pF, 50V, +/-5%, C0G/NP0, 0603	MuRata	GRM1885C1H120J	0603	Fitted
1	C17	0.012uF	CAP, CERM, 0.012uF, 50V, +/-10%, X7R, 0603	MuRata	GRM188R71H123K	0603	Fitted
1	C18	0.022uF	CAP, CERM, 0.022uF, 16V, +/-10%, X7R, 0603	MuRata	GRM188R71C223K	0603	Fitted
1	C2	0.1uF	CAP, CERM, 0.1uF, 25V, +/-10%, X7R, 0603	TDK	C1608X7R1E104K	0603	Fitted
2		10uF	CAP, CERM, 10uF, 10V, +/-20%, X5R, 0603		C1608X5R1A106M		Fitted
1		0.033uF			GRM188R71C333K		Fitted
6	, , ,	0.1uF	CAP, CERM, 0.1uF, 25V, +/-10%, X5R, 0603		06033D104KAT2A		Fitted
6	1, C32, C33, (CAP, CERM, 220pF, 50V, +/-10%, X7R, 0603		GRM188R71H221K		Fitted
1		0.033uF	CAP, CERM, 0.033uF, 50V, +/-10%, X7R, 0603		GRM188R71H333K		Fitted
	C4, C25, C26				GRM188R61C104K		Fitted
2		1uF	CAP, CERM, 1uF, 50V, +/-10%, X7R, 0805		GRM21BR71H105k		Fitted
2	D1, D4	Green	LED, Green, SMD		LG L29K-G2J1-24-2	1.7x0.65x0.8mm	Fitted
2	D2, D3	60V	Diode, Schottky, 60V, 1A, SMA	ON Semiconductor		SMA	Fitted
1	J1		Header, 2 Pos, 6A, 63V, TH	Phoenix Contact	1725656	6.2x8.5x5.54 mm	Fitted
1	J2		Header, 100mil, 3x1, Tin plated, TH	Sullins Connector S		Header, 3 PIN, 10	
1	J22		Header, 8x1, 100mil, Tin, TH	Sullins Connector S		Header, 8x1, 100	
1	J3		Header, 100mil, 5x2, Tin plated, TH	Sullins Connector S		Header, 5x2, 100	
1	J4		Conn D-SUB RCPT R/A 9POS GOLD/FL, TH				Fitted
1	J6		Header, 100mil, 4x2, Tin plated, TH	Sullins Connector S		Header, 4x2, 100	
1		82uH	Inductor, Shielded Drum Core, Ferrite, 82uH,	Wurth Elektronik ei			Fitted
•			0.84A, 0.25 ohm, SMD				
1		4.7uH	Inductor, Wirewound, Ferrite, 4.7uH, 0.9A, 0.2 ohm, SMD		NLCV32T-4R7M-PF		Fitted
1		0.05	RES, 0.05 ohm, 1%, 0.1W, 0603				Fitted
	R37, R41, R42		RES, 10 ohm, 5%, 0.25W, 0603		CRCW060310R0JN		Fitted
	, -, ,	0	RES, 0 ohm, 5%, 0.1W, 0603		CRCW06030000Z0		Fitted
	3, R39, R45, I		RES, 4.7k ohm, 5%, 0.1W, 0603		CRCW06034K70JN		Fitted
2		51	RES, 51 ohm, 5%, 0.1W, 0603		CRCW060351R0JN		Fitted
1	R17	54.9k	RES, 54.9k ohm, 1%, 0.1W, 0603		CRCW060354K9Fk	0603	Fitted
2	R19, R28	10.0k	RES, 10.0k ohm, 1%, 0.1W, 0603	Vishay-Dale	CRCW060310K0Fk	0603	Fitted
1	R2	50	RES, 50 ohm, 1%, 0.1W, 0603	Vishay-Dale	CRCW060350R0Fk	0603	Fitted
1	R20	38.3k	RES, 38.3k ohm, 1%, 0.1W, 0603	Vishay-Dale	CRCW060338K3Fk	0603	Fitted
1	R21	165k	RES, 165k ohm, 1%, 0.1W, 0603		CRCW0603165KFk		Fitted
1		90.9k	RES, 90.9k ohm, 1%, 0.1W, 0603		CRCW060390K9Fk		Fitted
1	R25	15.4k	RES, 15.4k ohm, 1%, 0.1W, 0603		CRCW060315K4FK		Fitted
1		36.5k	RES, 36.5k ohm, 1%, 0.1W, 0603		CRCW060336K5FK		Fitted
1	R29	10	RES, 10 ohm, 5%, 3W, TH	Vishay Draloric	AC03000001009JA		Fitted
1	R30	390	RES, 390 ohm, 5%, 0.1W, 0603		CRCW0603390RJN		Fitted
1	R36	120	RES, 120 ohm, 5%, 0.5W, 0805			0805	Fitted
1		1.0k	RES, 1.0k ohm, 5%, 0.1W, 0603		CRCW06031K00JN		Fitted
4		22	RES, 22 ohm, 5%, 0.1W, 0603		CRCW06031R0031		Fitted
1	, , -,	1.69k	RES, 1.69k ohm, 1%, 0.1W, 0603		CRCW060322R05R		Fitted
2		4.99k	RES, 4.99k ohm, 1%, 0.1W, 0603		CRCW06031K09FK		Fitted
1		93.1k	RES, 93.1k ohm, 1%, 0.1W, 0603		CRCW06034R99FR		Fitted
1		20.5k	RES, 20.5k ohm, 1%, 0.1W, 0603		CRCW060393K1FK		Fitted
1	R9	30.0k					
			RES, 30.0k ohm, 1%, 0.1W, 0603		RC0603FR-0730KL	Red Miniature Te	Fitted
2		Red	Test Point, Miniature, Red, TH				
1	U1		2.5 to 18 V Positive Voltage 10A Integrated Hot- Swap Controller, RUV0036A			RUV0036A	Fitted
1	U2		0.5 Å, 42 V Step Down DC/DC Converter with Eco-mode, DGQ0010D	Texas Instruments	TPS54040ADGQ	DGQ0010D	Fitted
1	U3		1A SIMPLE SWITCHER® Power Module with 42V Maximum Input, 7 pin TO-PMOD	National Semicondu	LMZ14201TZ-ADJ/I	TZA07A	Fitted
1	U4		200-mA, Low-IQ, LDO Regulator for Portable	Texas Instruments	TLV70025DDC	DDC0005A	Fitted
			Devices, DDC0005A	. Jaco mondinonto			

Quantity	Designator	Value	Description	Manufacturer	PartNumber	PackageReferer	Fitted
2	U5, U7		8-BIT DUAL-SUPPLY BUS TRANSCEIVER	Texas Instruments	SN74AVC8T245PW	PW0024A	Fitted
			WITH CONFIGURABLE VOLTAGE				
			TRANSLATION AND 3-STATE OUTPUTS,				
			PW0024A				
2	U6, U8		3.3-V Full-Duplex RS-485 Transceivers With ±12-	Texas Instruments	SN65HVD77D	D0008A	Fitted
			kV IEC ESD, D0008A				
0	C13	10uF	CAP, CERM, 10uF, 6.3V, +/-20%, X5R, 0603	MuRata	GRM188R60J106M	0603	Not Fitted
0	C15	10pF	CAP, CERM, 10pF, 50V, +/-5%, C0G/NP0, 0603	TDK	C1608C0G1H100D	0603	Not Fitted
0	C23	10uF	CAP, CERM, 10uF, 10V, +/-20%, X5R, 0603	TDK	C1608X5R1A106M	0603	Not Fitted
0	C7	10uF	CAP, CERM, 10uF, 25V, +/-10%, X5R, 0805	TDK	C2012X5R1E106K1	0805	Not Fitted
0	D5, D6, D7	7V	Diode, TVS, Bi, 7V, 400W, SOT-23	Bourns	CDSOT23-SM712	SOT-23	Not Fitted
0	J40, J41		Header, 100mil, 2x1, Tin plated, TH	Sullins Connector S	PEC02SAAN	Header, 2 PIN, 1	Not Fitted
0	R13	10k	RES, 10k ohm, 5%, 0.125W, 0805	Vishay-Dale	CRCW080510K0JN	0805	Not Fitted
0	R18	3.9k	RES, 3.9k ohm, 5%, 0.1W, 0603	Vishay-Dale	CRCW06033K90JN	0603	Not Fitted
0	R43	0	RES, 0 ohm, 5%, 0.1W, 0603	Vishay-Dale	CRCW06030000Z0	0603	Not Fitted
0	TP3	White	Test Point, Miniature, White, TH	Keystone	5002	White Miniature	Not Fitted
0	TP5	Red	Test Point, Miniature, Red, TH	Keystone	5000	Red Miniature Te	Not Fitted

Notes:

Substitutions made according to Alternate PartNumber must meet datasheet parameters, not just the Description specified.

IMPORTANT NOTICE FOR TI REFERENCE DESIGNS

Texas Instruments Incorporated ("TI") reference designs are solely intended to assist designers ("Buyers") who are developing systems that incorporate TI semiconductor products (also referred to herein as "components"). Buyer understands and agrees that Buyer remains responsible for using its independent analysis, evaluation and judgment in designing Buyer's systems and products.

TI reference designs have been created using standard laboratory conditions and engineering practices. TI has not conducted any testing other than that specifically described in the published documentation for a particular reference design. TI may make corrections, enhancements, improvements and other changes to its reference designs.

Buyers are authorized to use TI reference designs with the TI component(s) identified in each particular reference design and to modify the reference design in the development of their end products. HOWEVER, NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY THIRD PARTY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT, IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of such information may require a license from a third party, or a license from TI under the patents or other intellectual property of TI.

TI REFERENCE DESIGNS ARE PROVIDED "AS IS". TI MAKES NO WARRANTIES OR REPRESENTATIONS WITH REGARD TO THE REFERENCE DESIGNS OR USE OF THE REFERENCE DESIGNS, EXPRESS, IMPLIED OR STATUTORY, INCLUDING ACCURACY OR COMPLETENESS. TI DISCLAIMS ANY WARRANTY OF TITLE AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, QUIET ENJOYMENT, QUIET POSSESSION, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS WITH REGARD TO TI REFERENCE DESIGNS OR USE THEREOF. TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY BUYERS AGAINST ANY THIRD PARTY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON A COMBINATION OF COMPONENTS PROVIDED IN A TI REFERENCE DESIGN. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, SPECIAL, INCIDENTAL, CONSEQUENTIAL OR INDIRECT DAMAGES, HOWEVER CAUSED, ON ANY THEORY OF LIABILITY AND WHETHER OR NOT TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES, ARISING IN ANY WAY OUT OF TI REFERENCE DESIGNS OR BUYER'S USE OF TI REFERENCE DESIGNS.

TI reserves the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques for TI components are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

Reproduction of significant portions of TI information in TI data books, data sheets or reference designs is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards that anticipate dangerous failures, monitor failures and their consequences, lessen the likelihood of dangerous failures and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in Buyer's safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed an agreement specifically governing such use.

Only those TI components that TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components that have *not* been so designated is solely at Buyer's risk, and Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.