

Battery Management Solutions for Wearable and Fitness Devices

Innovative, Space-Saving, Chargers, Gauges and Harvesters



Overview

Multi-function wearable devices help people track and manage fitness, health, and medical functions. As these devices become smaller and more comfortable for the user, the demand for additional features and longer run time presents new challenges for designers. Whether powered from conventional or renewable sources, tiny and efficient low-power chargers from Texas Instruments enable peak performance for a wide range of wearable electronic devices.


Broadest Portfolio of Wireless Charging ICs, Nano-Power Harvesting ICs, Traditional Chargers, and Gauges

- Smallest footprint, space-saving solutions for tight form factors
- Very high-efficiencies allow lower heat dissipation and longer battery run times
- Most accurate gauging for extended run time
- Reference design and evaluation boards available for rapid prototyping

Application Examples

- Sensor integration
- Smart watches, bio-metric monitors
- ID tags
- Augmented reality, fashion design

Wearable System Diagram



Battery Management Solutions for Wearable and Fitness Devices

Featured Chargers, Gauges, and Evaluation Modules

Product	Description	EVM
bq25570	Ultra-low power boost charger with integrated DC/DC conversion	bq25570EVM-206
bq25505/04	Ultra-low power boost converter with battery management and autonomous power path multi-plexing	bq25505EVM-218, bq25504EVM
TPS62736/37	Ultra-low Iq nano-buck regulators with 50/100 mA load capability	TPS62736EVM-205, TPS62737EVM-560
bq25100/A	Smallest 250 mA single-cell Li-Ion charger with 75 nA low IQ, 1 mA termination for ultra-low-power designs	bq25100EVM-654
bq24040/45	1A, 4.2/4.35V single-cell Li-Ion and Li-Pol linear chargers with Auto Start	bq24040EVM, bq24045EVM
bq24090/95	1A, 4.2/4.35V single-cell Li-Ion linear chargers with temperature monitoring	bq24090EVM, bq24095EVM-005
bq24232	USB-friendly 0.5A Li-Ion charger with Power Path management	bq24232EVM
bq27421	System-side Impedance Track™ fuel gauge with integrated sense resistor	bq27421EVM-G1A, bq27421EVM-G1B
bq27621	System-side fuel gauge with Dynamic Voltage Correlation	bq27621EVM-G1
bq51003	WPC 1.1 integrated wireless power supply receiver optimized for 2.5W applications	bq51003EVM-764
bq51013B	WPC 1.1 integrated wireless power receiver with 5V regulated output	bq51013BEVM-764
bq51050B/51B	WPC 1.1 integrated wireless power receiver and 4.2V / 4.35V Li-Ion charger receivers	bq51050BEVM-764
bq500212A	WPC 1.1-compliant 5V wireless power transmitter manager with lowest total device count	bq500212EVM-550

bq24040/45

Single-cell Li-Ion linear battery chargers

Key Features

- 1% charge voltage accuracy, 10% charge current accuracy
- USB port or AC adapter operation
- 30V input rating with 6.6V or 7.1V input overvoltage protection supports low-cost, unregulated adapters
- Automatic Termination and Timer Disable Mode (TTDM) for absent battery pack with thermistor



bq24232

Integrated Li-Ion linear charger and power-path management IC

Key Features

- Fully-compliant USB charger, selectable 100 mA or 500 mA Max V_{IN}
- 28V input rating with over-voltage protection
- Integrated Dynamic Power Path Management (DPPM) powers system and charges battery
- Supports up to 500 mA charge current with current monitoring output (ISET)



bq51003

Advanced, integrated receiver for wireless power transfer

Key Features

- High efficiency DC/DC boost converter/charger with built-in buck regulation
- MPPT with cold start feature
- Flexible energy storage options
- Battery charging and protection



bq25100 series

Single input, single-cell Li-Ion and Li-Pol linear chargers

Key Features

- Ultra-small WCSP package, 0.9 mm x 1.6 mm
- 1 mA minimum programmable termination current
- 75 nA maximum battery leakage current
- 30V input rating with 6.5V over-voltage protection



bq25504/05

Ultra-low power boost converters with battery management for charging and protection

Key Features

- High-efficiency DC/DC boost converters/chargers
- Programmable dynamic Maximum Power Point Tracking (MPPT) with cold start feature
- Flexible energy storage options



bq27421/621

Low-power, high accuracy single-cell Li-Ion fuel gauges

Key Features

- 5% accuracy, longer run-time, less charging needed
- Low power consumption, suitable for small batteries
- Small form factor, no external sense resistor required



For more information, visit ti.com/battery

The platform bar is a trademark of Texas Instruments.

All other trademarks are the property of their respective owners.

© 2014 Texas Instruments Incorporated

Printed in U.S.A. by Almaden Press, San Jose, CA



IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products (also referred to herein as "components") are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of significant portions of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI components or services with statements different from or beyond the parameters stated by TI for that component or service voids all express and any implied warranties for the associated TI component or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards which anticipate dangerous consequences of failures, monitor failures and their consequences, lessen the likelihood of failures that might cause harm and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed a special agreement specifically governing such use.

Only those TI components which TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components which have **not** been so designated is solely at the Buyer's risk, and that Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.

Products

Audio	www.ti.com/audio
Amplifiers	amplifier.ti.com
Data Converters	dataconverter.ti.com
DLP® Products	www.dlp.com
DSP	dsp.ti.com
Clocks and Timers	www.ti.com/clocks
Interface	interface.ti.com
Logic	logic.ti.com
Power Mgmt	power.ti.com
Microcontrollers	microcontroller.ti.com
RFID	www.ti-rfid.com
OMAP Applications Processors	www.ti.com/omap
Wireless Connectivity	www.ti.com/wirelessconnectivity

Applications

Automotive and Transportation	www.ti.com/automotive
Communications and Telecom	www.ti.com/communications
Computers and Peripherals	www.ti.com/computers
Consumer Electronics	www.ti.com/consumer-apps
Energy and Lighting	www.ti.com/energy
Industrial	www.ti.com/industrial
Medical	www.ti.com/medical
Security	www.ti.com/security
Space, Avionics and Defense	www.ti.com/space-avionics-defense
Video and Imaging	www.ti.com/video

TI E2E Community

e2e.ti.com