



Project Name:	Change in menu Project
Project File:	PMP9484.PrjPcb
Base ID:	XX####
Schematic Rev:	E1
Assembly Variant:	None
Build Quantity:	100
Generated:	8/19/2014 3:49:30 PM

Item	Designator	Quantity	Required	Manufacturer	PartNumber	Description
1	!PCB1	1	100	Any	XX####	Printed Circuit Board
2	C1	1	100	AVX	08051A151JAT2A	CAP, CERM, 150 pF, 100 V, +/- 5%, C0G/NP0, 0805
3	C2, C3, C4, C10	4	400	MuRata	GRM32DR71H335KA88L	CAP, CERM, 3.3uF, 50V, +/-10%, X7R, 1210
4	C5	1	100	Nichicon	UCD2A331MNQ1MS	CAP, Al Electrolytic, 330uF, 100V, +/-20%, SMT
5	C6, C7, C8, C9	4	400	Panasonic	EEE-FP1V331AP	CAP, AL, 330 µF, 35 V, +/- 20%, 0.06 ohm, SMD
6	C11, C13, C14	3	300	Taiyo Yuden	GMK325AB7106MM-T	CAP, CERM, 10 µF, 35 V, +/- 20%, X7R, 1210
7	C12	1	100	MuRata	GRM32CR72A105KA35L	CAP, CERM, 1uF, 100V, +/-10%, X7R, 1210
8	C15	1	100	AVX	08053C104KAT2A	CAP, CERM, 0.1uF, 25V, +/-10%, X7R, 0805
9	C16, C18, C20	3	300	MuRata	GRM1885C1H101JA01D	CAP, CERM, 100pF, 50V, +/-5%, C0G/NP0, 0603
10	C17	1	100	MuRata	GRM21BR71C475KA73L	CAP, CERM, 4.7uF, 16V, +/-10%, X7R, 0805
11	C19, C21	2	200	MuRata	GRM188R71E474KA12D	CAP, CERM, 0.47uF, 25V, +/-10%, X7R, 0603
12	C22	1	100	AVX	06033C104KAT2A	CAP, CERM, 0.1 µF, 25 V, +/- 10%, X7R, 0603
13	C23	1	100	AVX	06031C471JAT2A	CAP, CERM, 470 pF, 100 V, +/- 5%, X7R, 0603
14	C24	1	100	MuRata	GRM188R71H393KA61D	CAP, CERM, 0.039 µF, 50 V, +/- 10%, X7R, 0603
15	C25, C29	2	200	AVX	0603YC104JAT2A	CAP, CERM, 0.1 µF, 16 V, +/- 5%, X7R, 0603
16	C26, C28, C30, C31, C33, C49	6	600	Taiyo Yuden	LMK212B7475KG-T	CAP, CERM, 4.7 µF, 10 V, +/- 10%, X7R, 0805
17	C27	1	100	Panasonic	EEE-FC1V100R	CAP, AL, 10 µF, 35 V, +/- 20%, 1.8 ohm, SMD
18	C32	1	100	MuRata	GRM21BR71A475KA73L	CAP, CERM, 4.7 µF, 10 V, +/- 10%, X7R, 0805
19	C34, C35, C54, C55	4	400	Panasonic	EEE-FK1V470P	CAP, AL, 47 µF, 35 V, +/- 20%, 0.36 ohm, SMD
20	C36, C58	2	200	AVX	08055C104KAT2A	CAP, CERM, 0.1 µF, 50 V, +/- 10%, X7R, 0805
21	C37, C57	2	200	AVX	08055C102KAT2A	CAP, CERM, 1000 pF, 50 V, +/- 10%, X7R, 0805
22	C38, C42, C46, C50	4	400	TDK	C1608X7R1H224K080AB	CAP, CERM, 0.22 µF, 50 V, +/- 10%, X7R, 0603
23	C39, C43, C47, C52	4	400	MuRata	GRM1885C1H331JA01D	CAP, CERM, 330 pF, 50 V, +/- 5%, C0G/NP0, 0603
24	C40, C48, C59, C60	4	400	MuRata	GRM21BR72A103KA01L	CAP, CERM, 0.01 µF, 100 V, +/- 10%, X7R, 0805
25	C41, C45, C51, C53	4	400	MuRata	GRM31MR71H684KA88L	CAP, CERM, 0.68 µF, 50 V, +/- 10%, X7R, 1206
26	C44	1	100	AVX	08055C105KAT2A	CAP, CERM, 1 µF, 50 V, +/- 10%, X7R, 0805
27	C56	1	100	AVX	06035A470JAT2A	CAP, CERM, 47 pF, 50 V, +/- 5%, C0G/NP0, 0603
28	D1	1	100	Diodes Inc.	DFLS1100-7	Diode, Schottky, 100V, 1A, PowerDI123
29	D2	1	100	ON Semiconductor	1SMB5920BT3G	Diode, Zener, 6.2V, 550 mW, SMB
30	FID1, FID2, FID3	3	300	N/A	N/A	Fiducial mark. There is nothing to buy or mount.
31	H1, H2, H3, H4	4	400	B&F Fastener Supply	NY PMS 440 0025 PH	Machine Screw, Round, #4-40 x 1/4, Nylon, Philips panhead
32	H5, H6, H7, H8	4	400	Keystone	1902C	Standoff, Hex, 0.5"L #4-40 Nylon
33	H9, H10, H11, H12	4	400	3M	SJ-5303 (CLEAR)	Bumpon, Hemisphere, 0.44 X 0.20, Clear
34	J1	1	100	Phoenix Contact	1715721	Conn Term Block, 2POS, 5.08mm, TH
35	J2	1	100	Phoenix Contact	1751248	Conn Term Block, 2POS, 3.5mm, TH
36	J3, J5	2	200	Sullins Connector Solutions	PBC02SAAN	Header, 100mil, 2x1, Gold, TH
37	J4	1	100	Switchcraft	PJРАН1X1U01X	RCA Jack, R/A, Black, TH
38	J6	1	100	Switchcraft	PJРАН1X1U03X	RCA Jack, R/A, Red, TH
39	J7, J8, J12	3	300	Sullins Connector Solutions	PBC03SAAN	Header, 100mil, 3x1, Gold, TH
40	J9, J11, J13	3	300	Keystone	7006	Binding Post, RED, TH
41	J10	1	100	Keystone	7007	Binding Post, BLACK, TH
42	L1	1	100	Würth Elektronik eiSos	74435581000	Inductor, Drum Core, Ferrite, 10uH, 21A, 0.0034 ohm, SMD
43	L2, L3, L4, L5	4	400	Toko	931BS-100M	Inductor, Shielded, Ferrite, 10uH, 7.8A, 0.011 ohm, SMD

Item	Designator	Quantity	Required	Manufacturer	PartNumber	Description
44	LBL1	1	100	Brady	THT-14-423-10	Thermal Transfer Printable Labels, 0.650" W x 0.200" H - 10,000 per roll
45	Q1, Q2	2	200	Texas Instruments	CSD18501Q5A	MOSFET, N-CH, 40V, 22A, SON 5x6mm
46	R1	1	100	Bourns	CRM2010-JW-4R7ELF	RES, 4.7 ohm, 5%, 1W, 2010
47	R2	1	100	Susumu Co Ltd	KRL7638-C-R003-F-T1	RES, 0.003, 1%, 4 W, 3015 WIDE
48	R3, R4	2	200	Vishay-Dale	CRCW0603100RFKEA	RES, 100 ohm, 1%, 0.1W, 0603
49	R5, R6, R7, R8, R12, R15	6	600	Panasonic	ERJ-3GEY0R00V	RES, 0 ohm, 5%, 0.1W, 0603
50	R9	1	100	Vishay-Dale	CRCW060349K9FKEA	RES, 49.9k ohm, 1%, 0.1W, 0603
51	R10	1	100	Vishay-Dale	CRCW08052R20JNEA	RES, 2.2 ohm, 5%, 0.125W, 0805
52	R11	1	100	Vishay-Dale	CRCW0603124KFKEA	RES, 124 k, 1%, 0.1 W, 0603
53	R13	1	100	Yageo America	RT0603BRD079K2L	RES, 9.20 k, 0.1%, 0.1 W, 0603
54	R14	1	100	Yageo America	RT0603BRD0764K2L	RES, 64.2 k, 0.1%, 0.1 W, 0603
55	R16	1	100	Yageo America	RC0603FR-0739KL	RES, 39.0 k, 1%, 0.1 W, 0603
56	R17	1	100	Vishay-Dale	CRCW06032K49FKEA	RES, 2.49 k, 1%, 0.1 W, 0603
57	R18	1	100	Yageo America	RT0603BRD0747KL	RES, 47.0 k, 0.1%, 0.1 W, 0603
58	R19	1	100	Vishay-Dale	CRCW080548R7FKEA	RES, 48.7 ohm, 1%, 0.125W, 0805
59	R20	1	100	Vishay-Dale	CRCW060313K0JNEA	RES, 13 k, 5%, 0.1 W, 0603
60	R21, R26	2	200	Vishay-Dale	CRCW060322K0JNEA	RES, 22 k, 5%, 0.1 W, 0603
61	R22, R23	2	200	Vishay-Dale	CRCW060315K0JNEA	RES, 15 k, 5%, 0.1 W, 0603
62	R24	1	100	Vishay-Dale	CRCW12061K00FKEA	RES, 1.00 k, 1%, 0.25 W, 1206
63	R25, R27	2	200	Vishay-Dale	CRCW060310K0JNEA	RES, 10 k, 5%, 0.1 W, 0603
64	R28	1	100	Vishay-Dale	CRCW12065K60JNEA	RES, 5.6 k, 5%, 0.25 W, 1206
65	R29, R37	2	200	Vishay-Dale	CRCW0603100KFKEA	RES, 100 k, 1%, 0.1 W, 0603
66	R30, R34, R39, R41	4	400	Vishay-Dale	CRCW06033R32FKEA	RES, 3.32, 1%, 0.1 W, 0603
67	R31, R33, R35, R38	4	400	Stackpole Electronics Inc	RNCP0805FTD10R0	RES, 10.0 ohm, 1%, 0.25W, 0805
68	R32	1	100	Vishay-Dale	CRCW060375K0FKEA	RES, 75.0 k, 1%, 0.1 W, 0603
69	R36	1	100	Yageo America	RC0603FR-0747KL	RES, 47.0 k, 1%, 0.1 W, 0603
70	R40	1	100	Yageo America	RC0603FR-074K7L	RES, 4.70 k, 1%, 0.1 W, 0603
71	TP1, TP3	2	200	Keystone	5010	Test Point, Multipurpose, Red, TH
72	TP2, TP7, TP8	3	300	Keystone	5012	Test Point, Multipurpose, White, TH
73	TP4, TP5	2	200	Keystone	5011	Test Point, Multipurpose, Black, TH
74	TP6	1	100	Keystone	5009	Test Point, Compact, Yellow, TH
75	TP9, TP10, TP13, TP15, TP17, TP18, TP19	7	700	Keystone	5000	Test Point, Miniature, Red, TH
76	TP11, TP12, TP14, TP16, TP20	5	500	Keystone	5001	Test Point, Miniature, Black, TH
77	U1	1	100	TI	LM5122MH	
78	U2	1	100	National Semiconductor	LM324AM	Low Power Quad Op Amp
79	U3	1	100	Texas Instruments	TPA3116D2DAD	IC AMP AUD 50W STER D 32HTSSOP

IMPORTANT NOTICE FOR TI REFERENCE DESIGNS

Texas Instruments Incorporated ("TI") reference designs are solely intended to assist designers ("Buyers") who are developing systems that incorporate TI semiconductor products (also referred to herein as "components"). Buyer understands and agrees that Buyer remains responsible for using its independent analysis, evaluation and judgment in designing Buyer's systems and products.

TI reference designs have been created using standard laboratory conditions and engineering practices. **TI has not conducted any testing other than that specifically described in the published documentation for a particular reference design.** TI may make corrections, enhancements, improvements and other changes to its reference designs.

Buyers are authorized to use TI reference designs with the TI component(s) identified in each particular reference design and to modify the reference design in the development of their end products. HOWEVER, NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY THIRD PARTY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT, IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI REFERENCE DESIGNS ARE PROVIDED "AS IS". TI MAKES NO WARRANTIES OR REPRESENTATIONS WITH REGARD TO THE REFERENCE DESIGNS OR USE OF THE REFERENCE DESIGNS, EXPRESS, IMPLIED OR STATUTORY, INCLUDING ACCURACY OR COMPLETENESS. TI DISCLAIMS ANY WARRANTY OF TITLE AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, QUIET ENJOYMENT, QUIET POSSESSION, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS WITH REGARD TO TI REFERENCE DESIGNS OR USE THEREOF. TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY BUYERS AGAINST ANY THIRD PARTY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON A COMBINATION OF COMPONENTS PROVIDED IN A TI REFERENCE DESIGN. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, SPECIAL, INCIDENTAL, CONSEQUENTIAL OR INDIRECT DAMAGES, HOWEVER CAUSED, ON ANY THEORY OF LIABILITY AND WHETHER OR NOT TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES, ARISING IN ANY WAY OUT OF TI REFERENCE DESIGNS OR BUYER'S USE OF TI REFERENCE DESIGNS.

TI reserves the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques for TI components are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

Reproduction of significant portions of TI information in TI data books, data sheets or reference designs is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards that anticipate dangerous failures, monitor failures and their consequences, lessen the likelihood of dangerous failures and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in Buyer's safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed an agreement specifically governing such use.

Only those TI components that TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components that have **not** been so designated is solely at Buyer's risk, and Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.