Welcome to the C5517 Evaluation Module (EVM) Quick Start Guide. The guide is designed to help you through the initial setup of the EVM. The C5517 EVM contains the following:

- C5517 DSP general-purpose board with:
- C5517 ultra-low power DSP
- TPS65023 power management IC
- MSP430F5529 MCU
- 2× AIC3204 audio codecs
- On-board emulation (XDS510 class)
- 128 Mb SDRAM

- Printed documents
- C5517 Quick Start Guide (this document)
- Miscellaneous
- Power supply with international adapters
- 2× USB cables
- 1× 3.5-mm AUX cable





Verify that **SW4** is set to **HPI ON** only, and **SW3** is set to **BOOTMODE4** to boot from NOR Flash at 12MHz.



Verify that all power-related SW5 and SW6 are set to **ON** on all switches.



Verify that MSP430 SW11 is configured ON for MSP430_SPI_OEN (required for DSP to communicate to OLED display) and MSP_430_SPI_ DIR. Verify jumper JP52 connects pins 1 and 2.



Connect micro USB cable to EMU USB and 5 the development computer. This will enable programming and debugging through Code Composer Studio[™] (CCStudio) Integrated Development Environment.



Optional: Connect 3.5-mm AUX cable or headphones to the green connection (**P8** or **P9**) on the audio interface for audio output.





Configure audio codec jumpers JP29 and JP30. JP29 should connect pins 1 and 3; 2 and 4. JP30 should also connect pins 1 and 3; 2 and 4.



P

Optional: Connect optional USB B cable to the C5517 USB data port for USB boot and data transfer. Insert the SD card for additional storage memory.





Plug in 5-V DC power supply to **J18** input and switch (SW7) the board on.



Navigate through demos and examples on the OLED display using the navigation buttons.

Warning! To minimize risk of personal injury or property damage, never use rechargeable batteries to power the boards. Only use 1.5V AAA alkaline batteries

External Power Supply Requirements: Nom Voltage: 5 VDC Max Current: 3 A Efficiency Level V

Please visit www.ti.com/DevelopC5517 for the full EVM user's guide and information on CCStudio IDE configuration and software installation.

For more information on the C5517 DSP or to download the latest software, please visit www.ti.com/c5517

For support questions, please contact: support@ti.com or www.ti.com/e2e

Important Notice: The products and services of Texas Instruments Incorporated and its subsidiaries described herein are sold subject to TI's standard terms and conditions of sale. Customers are advised to obtain the most current and complete information about TI products and services before placing orders. TI assumes no liability for applications assistance, customer's applications or product designs, software performance, or infringement of patents. The publication of information regarding any other company's products or services does not constitute TI's approval, warranty or endorsement thereof.

Note that there should only be one active power source at any one time. Do not leave the EVM powered when unattended.

External Power Supply Regulatory Compliance Certifications: Recommend selection and use of an external a power supply which meets TI's required minimum electrical ratings in addition to complying with applicable regional product regulatory/ safety certification requirements such as (by example) UL, CSA, VDE, CCC, PSE, etc.



TI Worldwide Technical Support

Internet

TI Semiconductor Product Information Center Home Page support.ti.com

TI E2E[™] Community Home Page e2e.ti.com

Product Information Centers

Americas	Phone	+1(512) 434-15	60		
Brazil	Phone	0800-891-2616	i		
Mexico	Phone	0800-670-7544			
Ir	Fax nternet/Email	+1(972) 927-63 support.ti.com/se	77 c/pic/americas.htm		
Europe, Middle I Phone	East, and Afri	ca			
European Free C	all	00800-ASK-TEX (00800 275 839	AS 127)		
International		+49 (0) 8161 80) 2121		
Russian Support		+7 (4) 95 98 10	701		
Note: The Europ If you have techr number above.	ean Free Call (Tol ical difficulty call	I Free) number is no ing the free call num	t active in all countries. ber, please use the interna		
Fax Internet Direct Email		+(49) (0) 8161 8 www.ti.com/askt asktexas@ti.com	+(49) (0) 8161 80 2045 www.ti.com/asktexas asktexas@ti.com		
Japan					
Phone	Domestic (t	oll-free number)	0120-92-3326		
Fax	Internationa Domestic	al	+81-3-3344-5317 0120-81-0036		

ational

Japan		
Phone	Domestic (toll-free	e number) 0120-92-3326
Fax	International Domestic	+81-3-3344-5317 0120-81-0036
Internet/Email	International Domestic	support.ti.com/sc/pic/japan.htm www.tij.co.jp/pic

© 2014 Texas Instruments Incorporated Printed by Seebridge Media in USA (Houston, Texas).



Important Notice: The products and services of Texas Instruments Incorporated and its subsidiaries described herein are sold subject to TI's standard terms and conditions of sale. Customers are advised to obtain the most current and complete information about TI products and services before placing orders. TI assumes no liability for applications assistance, customer's applications or product designs, software performance, or infringement of patents. The publication of information regarding any other company's products or services does not constitute TI's approval, warranty or endorsement thereof

B012014

The platform bar, Code Composer Studio and E2E are trademarks of Texas Instruments. All other trademarks are the property of their respective owners.





SPRW257 514667-4001A

For more information: www.ti.com/c5517

TEXAS INSTRUMENTS

C5517 EVM Quick Start Guide

IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products (also referred to herein as "components") are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of significant portions of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI components or services with statements different from or beyond the parameters stated by TI for that component or service voids all express and any implied warranties for the associated TI component or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards which anticipate dangerous consequences of failures, monitor failures and their consequences, lessen the likelihood of failures that might cause harm and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed a special agreement specifically governing such use.

Only those TI components which TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components which have *not* been so designated is solely at the Buyer's risk, and that Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.

Products		Applications		
Audio	www.ti.com/audio	Automotive and Transportation	www.ti.com/automotive	
Amplifiers	amplifier.ti.com	Communications and Telecom	www.ti.com/communications	
Data Converters	dataconverter.ti.com	Computers and Peripherals	www.ti.com/computers	
DLP® Products	www.dlp.com	Consumer Electronics	www.ti.com/consumer-apps	
DSP	dsp.ti.com	Energy and Lighting	www.ti.com/energy	
Clocks and Timers	www.ti.com/clocks	Industrial	www.ti.com/industrial	
Interface	interface.ti.com	Medical	www.ti.com/medical	
Logic	logic.ti.com	Security	www.ti.com/security	
Power Mgmt	power.ti.com	Space, Avionics and Defense	www.ti.com/space-avionics-defense	
Microcontrollers	microcontroller.ti.com	Video and Imaging	www.ti.com/video	
RFID	www.ti-rfid.com			
OMAP Applications Processors	www.ti.com/omap	TI E2E Community	e2e.ti.com	
Wireless Connectivity	www.ti.com/wirelessconnectivity			

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2014, Texas Instruments Incorporated