Variant: 001

Generated: 11/5/2015 1:33:44 PM

TID #: PMP4496

PMP4496 REV 1.0 Bill of Materials



Item #	Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
1	C1	1	0.047uF	C1005X7R1C473K	TDK	CAP, CERM, 0.047 µF, 16 V, +/- 10%, X7R, 0402	0402
2	C2, C14, C17, C18, C22, C24, C25, C26	8	0.1uF	GRM155R61C104KA88D	MuRata	CAP, CERM, 0.1 μF, 16 V, +/- 10%, X5R, 0402	0402
3	C3	1	10uF	C1608X5R1E106M080AC	TDK	CAP, CERM, 10 µF, 25 V, +/- 20%, X5R, 0603	0603
4	C4, C7, C9, C10	4	10uF	C0603C106M9PACTU	Kemet	CAP, CERM, 10 µF, 6.3 V, +/- 20%, X5R, 0603	0603
5	C5, C6, C11, C12	4	47uF	JMK212BJ476MG-T	Taiyo Yuden	CAP, CERM, 47 μF, 6.3 V, +/- 20%, X5R, 0805	0805
6	C8, C15	2	4.7uF	C1005X5R0J475M050BC	TDK	CAP, CERM, 4.7 µF, 6.3 V, +/- 20%, X5R, 0402	0402
7	C13	1	0.01uF	GRM155R60J103KA01D	MuRata	CAP, CERM, 0.01 µF, 6.3 V, +/- 10%, X5R, 0402	0402
8	C16	1	1uF	C1005X5R1C105K050BC	TDK	CAP, CERM, 1 µF, 16 V, +/- 10%, X5R, 0402	0402
9	C21	1	100pF	GRM1535C1H101JDD5D	MuRata	CAP, CERM, 100 pF, 50 V, +/- 5%, C0G/NP0, 0402	0402
10	C23	1	1000pF	C1005C0G1E102J	TDK	CAP, CERM, 1000 pF, 25 V, +/- 5%, C0G/NP0, 0402	0402
11	D1, D2	2	3.3V	CDSOD323-T03SC	Bourns	Diode, TVS, Bi, 3.3 V, 400 W, SOD323, 2-Leads, Body 1.9x1.45mm, No Polarity Mark	SOD323, 2-Leads, Body 1.9x1.45mm, N Polarity Mark
12	D3	1	30V	BAT54C-7-F	Diodes Inc.	Diode, Schottky, 30 V, 0.2 A, SOT-23	SOT-23
13	D4, D5, D6, D7	4	Green	LTST-C190KGKT	Lite-On	LED, Green, SMD	1.6x0.8x0.8mm
14	J1	1		UT12113-11602-7H	Foxconn	Connector, Receptacle, USB TYPE C, R/A, SMT	Connector, Receptacle, USB TYPE C, R/A, SMT
15	L1	1	1uH	XAL7030-102MEB	Coilcraft	Inductor, Shielded, Composite, 1 µH, 21.8 A, 0.00455 ohm, SMD	XAL7030
16	L2	1	2.2uH	XAL7030-222MEB	Coilcraft	Inductor, Shielded, Composite, 2.2 µH, 12.9 A, 0.0137 ohm, SMD	XAL7030
17	P1	1		M22-5330405	Harwin	Header, 2mm, 4x1, Gold, Black, R/A, SMT	Header, 2mm, 4x1, R/A, SMT
18	Q1, Q2	2	-20V	CSD25310Q2	Texas Instruments	MOSFET, P-CH, -20 V, -20 A, SON 2x2mm	SON 2x2mm
19	Q3	1	40 V	MMBT3906TT1G	ON Semiconductor	Transistor, PNP, 40 V, 0.2 A, SOT-416	SOT-416
20	Q4	1	30V	CSD17483F4T	Texas Instruments	MOSFET, N/P-CH, 30 V, 1.5 A,	
21	Q5	1	V	CSD83325L	Texas Instruments	MOSFET, N-CH, V, A, YJE0006A	YJE0006A
22	R1	1	110	CRCW0402110RFKED	Vishay-Dale	RES, 110, 1%, 0.063 W, 0402	0402
23	R2 R3	1	41.2k 5.23k	CRCW040241K2FKED	Vishay-Dale	RES, 41.2 k, 1%, 0.063 W, 0402	0402 0402
24 25	R4	1	1.00Meg	CRCW04025K23FKED CRCW04021M00FKED	Vishay-Dale Vishay-Dale	RES, 5.23 k, 1%, 0.063 W, 0402 RES, 1.00 M, 1%, 0.063 W, 0402	0402
26	R5	1	30.1k	CRCW04021W00FRED	Vishay-Dale Vishay-Dale	RES, 30.1 k, 1%, 0.063 W, 0402	0402
27	R6	1	10k ohm	ERT-J0EG103HA	Panasonic	Thermistor NTC, 10k ohm, 3%, 0402	0402
28	R7, R11, R12, R13, R14, R16, R22, R26, R32	9	10k	CRCW040210K0JNED	Vishay-Dale	RES, 10 k, 5%, 0.063 W, 0402	0402
29	R8, R17	2	51k	CRCW040251K0JNED	Vishay-Dale	RES, 51 k, 5%, 0.063 W, 0402	0402
30	R9	1	6.19k	CRCW04026K19FKED	Vishay-Dale	RES, 6.19 k, 1%, 0.063 W, 0402	0402
31	R10	1	1.0k	CRCW04021K00JNED	Vishay-Dale	RES, 1.0 k, 5%, 0.063 W, 0402	0402
32	R15	1	5.11k	CRCW04025K11FKED	Vishay-Dale	RES, 5.11 k, 1%, 0.063 W, 0402	0402
33	R18, R20, R23, R28	4	3.3k	CRCW04023K30JNED	Vishay-Dale	RES, 3.3 k, 5%, 0.063 W, 0402	0402
34	R19	1	330	CRCW0402330RJNED	Vishay-Dale	RES, 330, 5%, 0.063 W, 0402	0402
35	R21, R27, R31	3	200k	CRCW0402200KJNED	Vishay-Dale	RES, 200 k, 5%, 0.063 W, 0402	0402
36	R24	1	2.2k	CRCW04022K20JNED	Vishay-Dale	RES, 2.2 k, 5%, 0.063 W, 0402	0402
37	R25	1	910k	CRCW0402910KJNED	Vishay-Dale	RES, 910 k, 5%, 0.063 W, 0402	0402
38	R29, R30	2	5.1Meg	CRCW04025M10JNED	Vishay-Dale	RES, 5.1 M, 5%, 0.063 W, 0402	0402
39 40	S1 U1	1		EVP-ANDA1A BQ25895RTWR	Panasonic Texas Instruments	Switch, Slide, SPST-NO, Off-Mom, 0.05 A, 12V, SMD 12C Controlled 5A Single Cell Charger with NVDC Power Path Management and MaxChargeTM High Voltage Adapter Support, RTW0024H	3.5x2.9mm RTW0024H
41	U2	1		TPS61235RWLR	Texas Instruments	7-A Synchronous Boost Converter with Programmable Output Current Limit, RWL0009A	RWL0009A
	U3	1		TPS2514ADBV	Texas Instruments	USB Dedicated Charging Port Controller, DBV0006A	DBV0006A
43	U4	1		TLV70430DBVR	Texas Instruments	Single Output LDO, 150 mA, Fixed 3 V Output, 2.5 to 24 V Input, with Ultra Low IQ, 5-pin SOT-23 (DBV), -40 to 125 degC, Green (RoHS & no Sb/Br)	DBV0005A
44	U5	1		TS3USB221RSER	Texas Instruments	High-Speed USB 2.0 (480 Mbps) 1:2 Multiplexer / Demultiplexer Switch with Single Enable, 6 ohm RON, 2.5 to 3.3V, -40 to 85 degC, 10-Pin UQFN (RSE), Green (RoHS & no Sb/Br)	RSE0010A
45	U6	1		MSP430G2332IPW20R	Texas Instruments	16 MHz Mixed Signal Microcontroller with 4 KB Flash, 256 B SRAM and 16 GPIOs, 20-pin SOP (PW), Green (RoHS & no Sb/Br)	PW0020A
46	U8	1		TL431AIDCKRA	Texas Instruments	Adjustable Precision Shunt Regulator, 34 ppm / degC, 100 mA, -40 to 85 degC, 6-pin SC70 (DCK), Green (RoHS & no Sb/Br)	DCK0006A
47	U9	1		BQ29700DSER	Texas Instruments	Cost-Effective Voltage and Current Protection Integrated Circuit for Single- Cell Li-Ion/Li-Polymer Batteries, DSE0006A	DSE0006A

IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products (also referred to herein as "components") are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of significant portions of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI components or services with statements different from or beyond the parameters stated by TI for that component or service voids all express and any implied warranties for the associated TI component or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards which anticipate dangerous consequences of failures, monitor failures and their consequences, lessen the likelihood of failures that might cause harm and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed a special agreement specifically governing such use.

Only those TI components which TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components which have *not* been so designated is solely at the Buyer's risk, and that Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.

Products	Applications
Products	Applications

Audio www.ti.com/audio Automotive and Transportation www.ti.com/automotive **Amplifiers** amplifier.ti.com Communications and Telecom www.ti.com/communications **Data Converters** dataconverter.ti.com Computers and Peripherals www.ti.com/computers **DLP® Products** www.dlp.com Consumer Electronics www.ti.com/consumer-apps DSP dsp.ti.com **Energy and Lighting** www.ti.com/energy Clocks and Timers www.ti.com/clocks Industrial www.ti.com/industrial Interface interface.ti.com Medical www.ti.com/medical Logic Security www.ti.com/security logic.ti.com

Power Mgmt power.ti.com Space, Avionics and Defense www.ti.com/space-avionics-defense

Microcontrollers microcontroller.ti.com Video and Imaging www.ti.com/video

RFID www.ti-rfid.com

OMAP Applications Processors www.ti.com/omap TI E2E Community e2e.ti.com

Wireless Connectivity www.ti.com/wirelessconnectivity