# Texas Instruments C2000<sup>™</sup> Piccolo<sup>™</sup> F28004x Real-Time Controller Series

# **TEXAS INSTRUMENTS**

#### **Optimized for power-control applications**

- Streamlined performance and power
  - 100 MHz / 256 KB Flash / 100 KB SRAM
  - Floating-point and trigonometric math unit
  - Next-generation CLA; support for continuous background task
  - 60% lower power consumption vs. F2806x + DC-DC option
- Advanced actuation and design flexibility
  - 4<sup>th</sup> generation ePWM enables implementation of the most advanced switching techniques for increased efficiency and power density
  - Enhanced crossbars provide flexibility in combining inputs, outputs and internal resources for most advanced control and protection mechanisms

 Integrated analog and protection

- 3 12-bit 3.45-MSPS ADC with post processing and threshold actions
- 7 on-chip PGA (3/6/12/24) with post gain filtering and bypass option
- 7 windowed comparators + 2 12-bit output DACs
- 4 sigma-delta demodulation channels

With streamlined performance, the new C2000 F28004x MCU family is optimized for power control in cost-sensitive applications for electric vehicles, motor control inverters and industrial power supplies.

F28004x		Temperatures		125C	Q100
Sensing	Processing		Actuation		
ADC1: 12-bit, 3.45 MSPS, 8ch	C28x <sup>™</sup> DSP core		8x ePWM Modules		
ADC2: 12-bit, 3.45 MSPS, 8ch	100 MHz		Tex Outputs (Tex High-Res)		
ADC3: 12-bit, 3.45 MSPS, 8ch	FPU		Fault Trip Zones		
7x Windowed Comparator Subsystem	TMU VCU-I		2x 12-bit DAC		
w/Integrated 12-bit DAC			Connectivity		
7x PGAs	CLA core 100 MHz Floating Point Math 6ch DMA		2x UART, 1x LIN/UART		
4x Sigma Delta Channels			2x 12C (1x true PMBus)		Bus)
Tomporatura Sansor			2x SPI		
			2x CAN 2.0B		
7x eCAP (2x HRCAP)			FSI		
		lomony	Pow	ver & Clocl	king
System Modules		viennory	2x ·	10 MHz 0-pin C	sc
3x 32-bit CPU Timers	Up to 256 KB	Flash (dual-bank) • ECC		1.2V VREG	
NMI Watchdog Timer	Up to 100 KB SRAM • parity		POR/BOR Protection		
192 Interrupt PIE	22 120-	Boot ROM		Debug	
	InstaSF	PIN™ Motor ROM	- 17	Dobug	
			cJT/	AG/Real-time J	TAG
			Embedde Diag	d Real-time Ana gnostic unit (ER	alysis and IAD)

#### www.ti.com/F28004x

Markets	EV/HEV and Industrial Power	Motor Drive
Applications	On-board charging, DC/DC, charging pile, UPS, solar, servers, rectifiers, converters	Servo, robotics, CNC, AC drives, elevators, textile, compressors, pumps
Features	<ul> <li>Unique PWM capabilities for exotic switching topologies</li> <li>Extensive analog integration</li> <li>CLA for high speed parallel control loops</li> <li>PMBus peripheral support</li> <li>AEC Q100 qualification</li> <li>Functional safety support planned</li> <li>DigitalPower Software Development Kit with powerSUITE support along with multiple TI Designs available now</li> </ul>	<ul> <li>Floating-point and trigonometric math units for high-performance processing</li> <li>Three analog-to-digital converters with up to seven programmable gain amplifiers</li> <li>Four sigma-delta demodulation channels</li> <li>New fast serial interface for high-speed serial communications across isolation boundary</li> <li>MotorControl Software Development Kit with InstaSPIN-FOC<sup>TM</sup> and DesignDRIVE support planned</li> </ul>
Get started	Introduction video     Introduction whitep     Data sheet     Fechnical reference manual	paper • Comparison whitepaper N • EVM • C2000Ware software

Piccolo F28004x MCU	Flash	CLA	Extras
F280049C	256 KB	Yes	InstaSPIN-FOC motor control solutions and the configurable logic block (CLB)
F280049	256 KB	Yes	-
F280045	256 KB	No	-
F280041C	128 KB	No	InstaSPIN-FOC motor control solutions and the CLB
F280041	128 KB	No	-

#### C2000 Portfolio

The C2000 Piccolo F28004x MCU series builds on the generational improvements introduced in the Delfino<sup>™</sup> F2837x and Piccolo F2807x series. These new real-time control solutions offer code compatibility with existing Piccolo MCUs, allowing customers to take advantage of the family's unique combination of premium performance in an affordable offering.



Piccolo<sup>™</sup> Delfino<sup>™</sup>

Generation compatible

### Comparison of Piccolo F2803x to F28004x series

	F28035	F280049	
Total MIPS	120	200	
CPU	60	100	
FPU	No	Yes	
TMU	No	Yes	
VCU	No	Yes	
DMA	No	Yes	
CLA	Type-1	Type-2	
Flash (KB)	128	256	
RAM (KB)	20	100	
ADC	1× 12-bit	3× 12 bit	
Sample & Hold	2	3	
ADC channels	16	21	
ADC post processing	No	Yes	
PGA channels	0	7	
Comparators	3	CMPSS	
CMPSS	No	7	
Sigma-delta filter	0	4	
ePWM technology	Туре-2	Type 4	
PWM channels	14	16	
HRPWM channels	7	16	
CLB / Position manager	No	Yes	
InstaSPIN enabled	No	Yes	
QEP	1	2	
CAN	1	2	
UART	1	2	
I <sup>2</sup> C	1	1	
SPI	2	2	
PMBus	0 1		
Packages	56, 64, 80	56, 64, 100	
1 Ku SRP	U.S. \$3.05–\$5.80	U.S. \$4.85–\$7.95	

## Comparison of Piccolo F2806x to F28004x series

	F28069	F280049	
Total MIPS	180	200	
CPU	90	100	
FPU	Yes	Yes	
TMU	No	Yes	
VCU	Yes	Yes	
DMA	Yes	Yes	
CLA	Туре-1	Type-2	
Flash (KB)	256	256	
RAM (KB)	100	100	
ADC	1× 12-bit	3× 12 bit	
Sample & Hold	2	3	
ADC channels	16	21	
ADC post processing	No	Yes	
PGA channels	0	7	
Comparators	3	CMPSS	
CMPSS	No	7	
Sigma-delta filter	0	4	
ePWM technology	Туре-2	Type 4	
PWM channels	16	16	
HRPWM channels	8 16		
CLB / Position manager	Yes	Yes	
InstaSPIN enabled	Yes	Yes	
QEP	2	2	
CAN	1	2	
UART	2	2	
I <sup>2</sup> C	1 1		
SPI	2		
USB	1	2	
PMBus	0	1	
Packages	80, 100	56, 64, 100	
1 Ku SRP	U.S. \$4.95-\$10.51	U.S. \$4.85-\$7.95	

The platform bar, C2000, Delfino, InstaSPIN-FOC and Piccolo are trademarks of Texas Instruments. All other trademarks are the property of their respective owners.



#### IMPORTANT NOTICE FOR TI DESIGN INFORMATION AND RESOURCES

Texas Instruments Incorporated ('TI") technical, application or other design advice, services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using any particular TI Resource in any way, you (individually or, if you are acting on behalf of a company, your company) agree to use it solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources.

You understand and agree that you remain responsible for using your independent analysis, evaluation and judgment in designing your applications and that you have full and exclusive responsibility to assure the safety of your applications and compliance of your applications (and of all TI products used in or for your applications) with all applicable regulations, laws and other applicable requirements. You represent that, with respect to your applications, you have all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. You agree that prior to using or distributing any applications. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

You are authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING TI RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY YOU AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

You agree to fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of your noncompliance with the terms and provisions of this Notice.

This Notice applies to TI Resources. Additional terms apply to the use and purchase of certain types of materials, TI products and services. These include; without limitation, TI's standard terms for semiconductor products <a href="http://www.ti.com/sc/docs/stdterms.htm">http://www.ti.com/sc/docs/stdterms.htm</a>), evaluation modules, and samples (<a href="http://www.ti.com/sc/docs/stdterms.htm">http://www.ti.com/sc/docs/stdterms.htm</a>), evaluation

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2018, Texas Instruments Incorporated