

PMP10145 REV A Bill of Materials

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
C1000	1	4700pF	C3216X7R2J472K	TDK	CAP, CERM, 4700 pF, 630 V, +/- 10%, X7R, 1206	1206
C1001	1	68uF	EKXG451ELL680MMN3S	Chemi-Con	CAP, AL, 68 µF, 450 V, +/- 20%, ohm, TH	D18xL31.5mm
C1002, C1003	2	0.22uF	B32922C3224K	EPCOS Inc	CAP, Film, 0.22 μF, 630 V, +/- 10%, TH	B32922_12.5mm
C1004, C1005	2	680uF	EKZE350ELL681MK20S	Chemi-Con	CAP, AL, 680 µF, 35 V, +/- 20%, 0.021 ohm, TH	D12.5xL20mm
C1006, C1007,	3	22uF	GRM32ER71C226ME18L	MuRata	CAP, CERM, 22 µF, 16 V, +/- 20%, X7R, 1210	1210
C1008						
C1009	1	DNP	Used in BOM report	Used in BOM report	CAP, CERM, xxxF, xxV, [TempCo], xx%, [PackageReference]	0603
C1010	1	47uF	EEE-FC1V470P	Panasonic	CAP, AL, 47 μF, 35 V, +/- 20%, 0.4 ohm, SMD	SMT Radial E
C1011	1	1uF	GRM219R71E105KA88D	MuRata	CAP, CERM, 1 µF, 25 V, +/- 10%, X7R, 0805	0805
C1012, C1013	2	0.1uF	08055C104JAT2A	AVX	CAP, CERM, 0.1 µF, 50 V, +/- 5%, X7R, 0805	0805
C1014	1	2200pF	GRM2165C2A222JA01D	MuRata	CAP, CERM, 2200 pF, 100 V, +/- 5%, C0G/NP0, 0805	0805
C1015	1	DNP	Used in BOM report	Used in BOM report	CAP, CERM, xxxF, xxV, [TempCo], xx%, [PackageReference]	0805
C1016	1	0.033uF	GRM188R71H333KA61D	MuRata	CAP, CERM, 0.033 µF, 50 V, +/- 10%, X7R, 0603	0603
C1017	1	10pF	06035A100JAT2A	AVX	CAP, CERM, 10 pF, 50 V, +/- 5%, C0G/NP0, 0603	0603
C1018	1	SHORT	SHORT	TDK	CAP, CERM, 2200 pF, 250 V, +/- 20%, E, TH, 2-Leads, Body 11.5x7mm,	TH, 2-Leads, Body
					Pin Spacing 10mm	11.5x7mm, Pin
						Spacing 10mm
C1019	1	3300pF	DE1E3KX332MN4AP01F	TDK	CAP, CERM, 3300 pF, 300 V, Y1	TH, 2-Leads, Body
						11.5x7mm, Pin
						Spacing 10mm
D1000	1	600V	GBU4J	Vishay-Semiconductor	Diode, Switching-Bridge, 600 V	GBU
D1001	1	600V	MURA160T3G	ON Semiconductor	Diode, Ultrafast, 600 V, 1 A, SMA	SMA
D1002	1	40V	MBR0540T1G	ON Semiconductor	Diode, Schottky, 40 V, 0.5 A, SOD-123	SOD-123
D1003	1	200V	BAS21-7-F	Diodes Inc.	Diode, Switching, 200 V, 0.2 A, SOT-23	SOT-23
D1004	1	22V	MMSZ5251BS-7-F	Diodes Inc.	Diode, Zener, 22 V, 200 mW, SOD-323	SOD-323
F1000	1	2A	37212000001	Littelfuse	Fuse, 2 A, 250 V, TH	TR5 fuse 8.5mm DIA
L1000	1	DNP	7447480331	Wurth Elektronik	Inductor, Wirewound, Ferrite, 330 µH, 1.4 A, 0.3 ohm, TH	TH, Dia 10.5mm
L1001	1	10mH	744823210	Wurth Elektronik eiSos	Coupled inductor, 10 mH, 2 A, 0.125 ohm, +/- 30%, TH	13x22x17.5mm
Q1000	1	710V	STB8N65M5	STMicroelectronics	MOSFET, N-CH, 710 V, 7 A, DDPAK	DDPAK
Q1001	1	100V	CSD19531Q5A	Texas Instruments	MOSFET, N-CH, 100 V, 16 A, SON 5x6mm	SON 5x6mm
R1000, R1001	2	100k	CRCW2512100KJNEG	Vishay-Dale	RES, 100 k, 5%, 1 W, 2512	2512
R1002, R1004,	3	1.00Meg	CRCW08051M00FKEA	Vishay-Dale	RES, 1.00 M, 1%, 0.125 W, 0805	0805
R1005						
R1003	1	20	CRCW201020R0JNEF	Vishay-Dale	RES, 20, 5%, 0.75 W, 2010	2010
R1006, R1009,	4	10	CRCW080510R0JNEA	Vishay-Dale	RES, 10, 5%, 0.125 W, 0805	0805
R1012, R1018						
R1007	1	191k	CRCW0603191KFKEA	Vishay-Dale	RES, 191 k, 1%, 0.1 W, 0603	0603
R1008, R1011	2	374k	RC0603FR-07374KL	Yageo America	RES, 374 k, 1%, 0.1 W, 0603	0603
R1010, R1020,	3	10.0k	RC0603FR-0710KL	Yageo America	RES, 10.0 k, 1%, 0.1 W, 0603	0603
R1022						
R1013	1	34.8k	CRCW060334K8FKEA	Vishay-Dale	RES, 34.8 k, 1%, 0.1 W, 0603	0603
R1014, R1027	2	100k	CRCW0603100KFKEA	Vishay-Dale	RES, 100 k, 1%, 0.1 W, 0603	0603
R1015	1	56.2k	CRCW060356K2FKEA	Vishay-Dale	RES, 56.2 k, 1%, 0.1 W, 0603	0603
R1016	1	49.9k	CRCW060349K9FKEA	Vishay-Dale	RES, 49.9 k, 1%, 0.1 W, 0603	0603
R1017, R1024	2	1.00k	CRCW06031K00FKEA	Vishay-Dale	RES, 1.00 k, 1%, 0.1 W, 0603	0603
R1019	1	10	CRCW120610R0JNEA	Vishay-Dale	RES, 10, 5%, 0.25 W, 1206	1206
R1021	1	49.9	CRCW060349R9FKEA	Vishay-Dale	RES, 49.9, 1%, 0.1 W, 0603	0603

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
R1023	1	3.01k	RC0603FR-073K01L	Yageo America	RES, 3.01 k, 1%, 0.1 W, 0603	0603
R1025	1	DNP	Used in BOM report	Used in BOM report	RES, xxx ohm, x%, xW, [PackageReference]	0603
R1026	1	20.0k	CRCW060320K0FKEA	Vishay-Dale	RES, 20.0 k, 1%, 0.1 W, 0603	0603
R1028	1	3.83k	RC0603FR-073K83L	Yageo America	RES, 3.83 k, 1%, 0.1 W, 0603	0603
RT1000	1	short	B57236S0100M000	EPCOS Inc	Thermistor NTC, 10 ohm, 20%, Disc_11.5mmx6mm	Disc_11.5mmx6mm
T1000	1	100 uH	750315783r00	Wurth Elektronik	Transformer, 100uH, TH	
TP1004, TP1005	2	Red	5000	Keystone	Test Point, Miniature, Red, TH	Red Miniature
						Testpoint
TP1006	1	Black	5001	Keystone	Test Point, Miniature, Black, TH	Black Miniature
						Testpoint
U1000	1		UCC24630DBV	Texas Instruments	SYNCRONOUS RECTIFIER CONTROLLER WITH LOW POWER	DBV0006A
					STANDBY, DBV0006A	
U1001	1		UCC28610D	Texas Instruments	Green-Mode Flyback Power Supply Controller with Discontinuous Current	D0008A
					Control, -40 to +125 degC, 8-pin SOIC (D), Green (RoHS & no Sb/Br)	
U1002	1		FOD817A	Fairchild Semiconductor	High Operating Temperature Phototransistor Optocoupler, DIP-4	DIP, 4-Leads, Body
						6.86x4.83mm, Pitch
						2.54mm
U1003	1		TL431AIDBZ	Texas Instruments	PRECISION PROGRAMMABLE REFERENCE, DBZ0003A	DBZ0003A

IMPORTANT NOTICE FOR TI REFERENCE DESIGNS

Texas Instruments Incorporated ("TI") reference designs are solely intended to assist designers ("Buyers") who are developing systems that incorporate TI semiconductor products (also referred to herein as "components"). Buyer understands and agrees that Buyer remains responsible for using its independent analysis, evaluation and judgment in designing Buyer's systems and products.

TI reference designs have been created using standard laboratory conditions and engineering practices. **TI has not conducted any testing other than that specifically described in the published documentation for a particular reference design.** TI may make corrections, enhancements, improvements and other changes to its reference designs.

Buyers are authorized to use TI reference designs with the TI component(s) identified in each particular reference design and to modify the reference design in the development of their end products. HOWEVER, NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY THIRD PARTY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT, IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of TI.

TI REFERENCE DESIGNS ARE PROVIDED "AS IS". TI MAKES NO WARRANTIES OR REPRESENTATIONS WITH REGARD TO THE REFERENCE DESIGNS OR USE OF THE REFERENCE DESIGNS, EXPRESS, IMPLIED OR STATUTORY, INCLUDING ACCURACY OR COMPLETENESS. TI DISCLAIMS ANY WARRANTY OF TITLE AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, QUIET ENJOYMENT, QUIET POSSESSION, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS WITH REGARD TO TI REFERENCE DESIGNS OR USE THEREOF. TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY BUYERS AGAINST ANY THIRD PARTY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON A COMBINATION OF COMPONENTS PROVIDED IN A TI REFERENCE DESIGN. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, SPECIAL, INCIDENTAL, CONSEQUENTIAL OR INDIRECT DAMAGES, HOWEVER CAUSED, ON ANY THEORY OF LIABILITY AND WHETHER OR NOT TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES, ARISING IN ANY WAY OUT OF TI REFERENCE DESIGNS OR BUYER'S USE OF TI REFERENCE DESIGNS.

TI reserves the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques for TI components are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

Reproduction of significant portions of TI information in TI data books, data sheets or reference designs is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards that anticipate dangerous failures, monitor failures and their consequences, lessen the likelihood of dangerous failures and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in Buyer's safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed an agreement specifically governing such use.

Only those TI components that TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components that have **not** been so designated is solely at Buyer's risk, and Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2016, Texas Instruments Incorporated