



Post Office Box 84  
 Sherman, Texas 75090  
 6412 Highway 75 South  
 Sherman, Texas 75090

(903) 868-7111

Texas Instruments High Rel Products Reliability Report

Device Type/Device Family: INA271SHKJ/INA271SHKQ  
 Package Type: 8CFP/8CSOIC  
 Wafer Fabrication Facility: Ti Sherman  
 Assembly/Test Facility: Millennium Microtech  
 Reporting Period: 04/12

Biased Life Test

Test Method: JESD22-A108  
 Test Condition: 210°C / 1000 hours  
 Sample Size: 45  
 Rejects: 0  
 Activation Energy (eV): .7  
 Equivalent Device Hours: 45000  
 Failure Rate (FIT)\*: 20492

\* 60% confidence level of random failure rate during nominal 1000 hour life based on test sample size. This not based on wear out failure mechanisms which will begin to affect above the 1000 hr test limit.

Group B Tests (Weekly by Package Family)			
Description	Condition	Referenced Method	Sample Size/Rejects
B1 Resistance to Solvents		Mil Std 883 Method 2015	3/0
B2 Bond strength	Test condition F (FC)	Mil Std 883 Method 2011/2019/2027	22/0-3/0
B3 Solderability	Soldering temperature of 245C±5	Mil Std 883 Method 2003	22/0
Group C Test (Per 3 Month Period by Family)			
Description	Condition	Referenced Method	Sample Size/Rejects
C1 Steady-state life test	125C/1000Hrs 4.6V	Mil Std 883 Method 1005	45/0
End point electrical			45/0

Texas Instruments High Rel Products Reliability Report

		Group D Tests (Annually by Package Family)		
Description	Condition	Referenced Method	Sample Size/Rejects	
D1 Physical Dimensions		Mil Std 883 Method 2016	15/0	*
D2 Lead Integrity		Mil Std 883 Method 2004 & 2028	45/0	*
Seal(Fine and Gross)		Mil Std 883 Method 1014	45/0	*
D3 Thermal Shock	-65°C to +150°C 15 cycles	Mil Std 883 Method 1011		
Temperature Cycle	-65°C to +150°C 100 cycles	Mil Std 883 Method 1010		*
Moisture Resistance		Mil Std 883 Method 1004		
Seal(Fine and Gross)		Mil Std 883 Method 1014		*
Visual examination		Mil Std 883 Method 1004 & 1010		
End point electrical D4			15/0	*
Mechanical Shock		Mil Std 883 Method 2002		
Variable Freq Vibration		Mil Std 883 Method 2007		*
Constant acceleration		Mil Std 883 Method 2001		
Seal		Mil Std 883 Method 1014		*
Visual Examination		Mil Std 883 Method 2009		
End point electrical D5			15/0	*
Salt Atmosphere		Mil Std 883 Method 1009		
Seal		Mil Std 883 Method 1014		*
Visual Examination		Mil Std 883 Method 1009	15/0	
D6 Internal Water Vapor		Mil Std 883 Method 1018	3/0	
D7 Adhesion of Lead Finish		Mil Std 883 Method 2025	15/0	

### Supplemental Device Characteristics

Die Revision:	C	Assembly Site:	MMT
Master Die:	JINA271AAH	Package Type:	CFP/CSOIC
Wafer Fab:	She	Pin Count:	8
Fab Technology:	BiCMOS	Mold Compound:	Ceramic
Fab Process:	LBC-SOI	Mount Compound:	JM7000
Process Code:	N/A	Bond:	Al
Passivation:	6kA MLO/11kA Nitride	Lead Composition:	Kovar
Lead Finish:	Au		

---

*TI may provide technical, applications or design advice, quality characterization, and reliability data or service providing these items shall not expand or otherwise affect TI's warranties as set forth in the Texas Instruments Incorporated Standard Terms and Conditions of Sale for Semiconductor Products and no obligation or liability shall arise from TI's provision of such items.*

---



## IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

TI products are not authorized for use in safety-critical applications (such as life support) where a failure of the TI product would reasonably be expected to cause severe personal injury or death, unless officers of the parties have executed an agreement specifically governing such use. Buyers represent that they have all necessary expertise in the safety and regulatory ramifications of their applications, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of TI products in such safety-critical applications, notwithstanding any applications-related information or support that may be provided by TI. Further, Buyers must fully indemnify TI and its representatives against any damages arising out of the use of TI products in such safety-critical applications.

TI products are neither designed nor intended for use in military/aerospace applications or environments unless the TI products are specifically designated by TI as military-grade or "enhanced plastic." Only products designated by TI as military-grade meet military specifications. Buyers acknowledge and agree that any such use of TI products which TI has not designated as military-grade is solely at the Buyer's risk, and that they are solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI products are neither designed nor intended for use in automotive applications or environments unless the specific TI products are designated by TI as compliant with ISO/TS 16949 requirements. Buyers acknowledge and agree that, if they use any non-designated products in automotive applications, TI will not be responsible for any failure to meet such requirements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

### Products

Audio	<a href="http://www.ti.com/audio">www.ti.com/audio</a>
Amplifiers	<a href="http://amplifier.ti.com">amplifier.ti.com</a>
Data Converters	<a href="http://dataconverter.ti.com">dataconverter.ti.com</a>
DLP® Products	<a href="http://www.dlp.com">www.dlp.com</a>
DSP	<a href="http://dsp.ti.com">dsp.ti.com</a>
Clocks and Timers	<a href="http://www.ti.com/clocks">www.ti.com/clocks</a>
Interface	<a href="http://interface.ti.com">interface.ti.com</a>
Logic	<a href="http://logic.ti.com">logic.ti.com</a>
Power Mgmt	<a href="http://power.ti.com">power.ti.com</a>
Microcontrollers	<a href="http://microcontroller.ti.com">microcontroller.ti.com</a>
RFID	<a href="http://www.ti-rfid.com">www.ti-rfid.com</a>
OMAP Mobile Processors	<a href="http://www.ti.com/omap">www.ti.com/omap</a>
Wireless Connectivity	<a href="http://www.ti.com/wirelessconnectivity">www.ti.com/wirelessconnectivity</a>

### Applications

Automotive and Transportation	<a href="http://www.ti.com/automotive">www.ti.com/automotive</a>
Communications and Telecom	<a href="http://www.ti.com/communications">www.ti.com/communications</a>
Computers and Peripherals	<a href="http://www.ti.com/computers">www.ti.com/computers</a>
Consumer Electronics	<a href="http://www.ti.com/consumer-apps">www.ti.com/consumer-apps</a>
Energy and Lighting	<a href="http://www.ti.com/energy">www.ti.com/energy</a>
Industrial	<a href="http://www.ti.com/industrial">www.ti.com/industrial</a>
Medical	<a href="http://www.ti.com/medical">www.ti.com/medical</a>
Security	<a href="http://www.ti.com/security">www.ti.com/security</a>
Space, Avionics and Defense	<a href="http://www.ti.com/space-avionics-defense">www.ti.com/space-avionics-defense</a>
Video and Imaging	<a href="http://www.ti.com/video">www.ti.com/video</a>

TI E2E Community Home Page

[e2e.ti.com](http://e2e.ti.com)

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265  
Copyright © 2012, Texas Instruments Incorporated