# TPS66X20:USB-PD Power Switch Layout Made Easy



#### Introduction

Texas Instruments offers a diverse portfolio of power switch products, also known as power multiplexers, for different power distribution applications, including USB Type-C/PD (Power Delivery). The product tree includes sink-only and sink/source switches with dead-battery LDO and OVP and RCP protection schemes.

This TI Tech Note provides layout guideline recommendations, permitting the use of non-HDI PCBs while benefitting from ultra-small 0.4-mm pitch WCSP packages.

## **Layout Guidelines**

The 28-pin WSCP package used on the power switches described in this tech note have an optimized pin to function assignment and can be connected with the minimum numbers of metal layers. By following the layout guidelines described in coming sections, the user can use a non-HDI PCB process to save PCB cost.

## **TPS66120 Layout Guidelines**

The TPS6612x contains an integrated 4-V to 22-V sink power path. The power path supports overtemperature and reverse current protection. VBUS has overvoltage protection with the level being set by an optional external resistor divider. If no overvoltage protection is desired, it may be disabled by grounding the OVP terminal.

The TPS6612x supports a fault pin that indicates overtemperature events. The TPS6612x series also supports a high-voltage VBUS LDO regulator, useful for supplying power to the device and other system components when operating in dead-battery conditions.

### TPS66120 Pin Map

Figure 1 shows the top view of the TPS66120 Power switch multiplexer pin-to-function mapping.




Figure 1. TPS66120 Pin Map

#### **TPS66120 Layout Guidelines**

The layout guidelines shown in Figure 2 provide all the connections for power path, including VBUS, PPHV, GND, VIN, and VLDO. The signal pins are all at the edge of the ball array, therefore all of them can be connected out with one metal layer.




Figure 2. TPS66120 Layout

#### **TPS66020 Layout Guidelines**



The TPS66020 is a full-featured power switch multiplexer that contains an integrated 5-V source power path and a 4-V to 22-V sink power path. The 5-V Source path limits the output current to a safe level by operating in a constant-current mode when the output load exceeds the selected current-limit threshold.

Each power path supports overtemperature and reverse current protection. VBUS has overvoltage protection, with the level being set by an optional external resistor divider. If no overvoltage protection is desired, it may be disabled by grounding the OVP terminal. The TPS6602x series supports a fault pin that indicates overcurrent and overtemperature events.

## TPS66020 Pin Map

Figure 3 shows top view of the TPS66020 power switch multiplexer pin-to-function mapping.




Figure 3. TPS66020 Pin Map

# **TPS66020 Layout Guidelines**

The layout guidelines shown in Figure 4 provide all the connections for power path, including VBUS, PPHV, PP5V, GND, VIN, and VLDO. The signal pins are all at the edge of the ball array, therefore all of them can be connected out with one metal layer.




Figure 4. TPS66020 Layout

**Table 1. Related Documentation** 

Device	Description
TPS66120	USB-C/PD high voltage power switch for sink with 3.3V dead battery LDO
TPS66020	USB-C/PD 20V sink & 5V source power switch with 3.3V dead battery LDO
TPS66020EVM	TPS66020 integrated source and sink power multiplexer evaluation module

# IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2022, Texas Instruments Incorporated