Filename: Pro13CF.tmp

Variant: 001

Generated: 8/4/2017 11:35:41 AM

ΠD #: TIDA-01518



TIDA-01518 REV A Bill of Materials

Item #	Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
1	!PCB	1		TIDA-01518	Any	Printed Circuit Board	1
2	BT1	1		BAT-HLD-001	Linx Technologies	Battery Holder, Retainer clip, SMT	22.9x4.2x15.5mm
3	BUZZ, DRDY,	8	SMT	5015	Keystone	Test Point, Miniature, SMT	Testpoint_Keystone_
	GND, GND,						Miniature
	LEAK, POW,						
	SCL, SDA						
4	BUZZER	1		CEP-1112	CUI Inc.	Piezo Audio Transducer, TH	D24xH7.3mm
5	C1	1	4700pF	06031C472JAT2A	AVX	CAP, CERM, 4700 pF, 100 V,+/- 5%, X7R, 0603	0603
6	C2	1	1uF	06033C105KAT2A	AVX	CAP, CERM, 1 µF, 25 V,+/- 10%, X7R, 0603	0603
7	C3	1	100uF	C3216X5R1A107M160AC	TDK	CAP, CERM, 100 μF, 10 V, +/- 20%, X5R, 1206_190	1206_190
8	C4, C6, C7	3	330uF	T495C337K004ATE700	Kemet	CAP, TA, 330 µF, 4 V, +/- 10%, 0.7 ohm, SMD	6032-28
9	C5	1	10uF	0805YD106KAT2A	AVX	CAP, CERM, 10 μF, 16 V,+/- 10%, X5R, 0805	0805
10	C8	1	0.01uF	06031C103JAT2A	AVX	CAP, CERM, 0.01 μF, 100 V,+/- 5%, X7R, 0603	0603
11	C9	1	0.1uF	GCM21BR71H104KA37K	MuRata	CAP, CERM, 0.1 µF, 50 V,+/- 10%, X7R, AEC-Q200 Grade 1, 0805	0805
12	C31	1	0.1uF	GCM155R71H104KE02D	MuRata	CAP, CERM, 0.1 µF, 50 V,+/- 10%, X7R, AEC-Q200 Grade 1, 0402	0402
13	CURRENT,	4		61300211121	Wurth Elektronik	Header, 2.54 mm, 2x1, Gold, TH	Header, 2.54mm,
	POW_2_LEAK,						2x1, TH
	POW_2_TEMP,						
	POWER						
14	D_ESD	1		TPD1E10B06DPYR	Texas Instruments	ESD in 0402 Package with 10 pF Capacitance and 6 V Breakdown, 1	DPY0002A
						Channel, -40 to +125 degC, 2-pin X2SON (DPY), Green (RoHS & no	
						Sb/Br)	
15	L1	1	47mH	RLB0913-473K	Bourns	Inductor, Wirewound, Ferrite, 47 mH, .03 A, 99 ohm, TH	D8.5xL12.5mm
16	LEFT, RIGHT	2		SSQ-110-03-T-D	Samtec	Receptacle, 2.54mm, 10x2, Tin, TH	10x2 Receptacle
17	Q1, Q2	2	60 V	MMBT2907ALT1G	ON Semiconductor	Transistor, PNP, 60 V, 0.6 A, SOT-23	SOT-23
18	Q3	1	-20V	SI2323DS	Vishay-Siliconix	MOSFET, P-CH, -20 V, -3.7 A, SOT-23	SOT-23
19	R1, R2	2	10.0k	CRCW040210K0FKED	Vishay-Dale	RES, 10.0 k, 1%, 0.063 W, 0402	0402
20	R3	1	330	CRCW1206330RJNEA	Vishay-Dale	RES, 330, 5%, 0.25 W, 1206	1206
21	R4	1	20k	CRCW060320K0JNEA	Vishay-Dale	RES, 20 k, 5%, 0.1 W, 0603	0603
22	R5, R7	2	560k	CRCW0603560KJNEA	Vishay-Dale	RES, 560 k, 5%, 0.1 W, 0603	0603
23	R6	1	5.6k	CRCW06035K60JNEA	Vishay-Dale	RES, 5.6 k, 5%, 0.1 W, 0603	0603
24	R8	1	10.2	CMF5010R200FHEB	Vishay-Dale	RES, 10.2, 1%, 0.25 W, Axial	Axial
25	R9	1	0	CRCW06030000Z0EA	Vishay-Dale	RES, 0, 5%, 0.1 W, 0603	0603
26	R19	1	330k	CRCW0402330KJNED	Vishay-Dale	RES, 330 k, 5%, 0.063 W, 0402	0402
27	SH-J1, SH-J2, SH-	4	1x2	2SN-BK-G	Samtec	Shunt, 2mm, Gold plated, Black	2mm Shunt, Closed
	J3, SH-J4						Тор
28	U1	1		HDC2010YPAR	Texas Instruments	HDC2010 Low Power Humidity and Temperature Digital Sensor,	YPA0006ABAB
						YPA0006ABAB (DSBGA-6)	
29	Water_Probe	1		22-27-2021	Molex	Header (friction lock), 100mil, 2x1, Tin, TH	Header, 2x1, 100mil,
					1		ТН

IMPORTANT NOTICE FOR TI DESIGN INFORMATION AND RESOURCES

Texas Instruments Incorporated ('TI") technical, application or other design advice, services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using any particular TI Resource in any way, you (individually or, if you are acting on behalf of a company, your company) agree to use it solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources.

You understand and agree that you remain responsible for using your independent analysis, evaluation and judgment in designing your applications and that you have full and exclusive responsibility to assure the safety of your applications and compliance of your applications (and of all TI products used in or for your applications) with all applicable regulations, laws and other applicable requirements. You represent that, with respect to your applications, you have all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. You agree that prior to using or distributing any applications that include TI products, you will thoroughly test such applications and the functionality of such TI products as used in such applications. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

You are authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING TI RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY YOU AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

You agree to fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of your non-compliance with the terms and provisions of this Notice.

This Notice applies to TI Resources. Additional terms apply to the use and purchase of certain types of materials, TI products and services. These include; without limitation, TI's standard terms for semiconductor products http://www.ti.com/sc/docs/stdterms.htm), evaluation modules, and samples (http://www.ti.com/sc/docs/sampterms.htm).

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2017, Texas Instruments Incorporated