PMP20904 REV A Bill of Materials



Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
!PCB1	1		PMP20904	Any	Printed Circuit Board	
C1	1	0.1uF	GRM188R71E104KA01D	MuRata	CAP, CERM, 0.1 μF, 25 V, +/- 10%, X7R, 0603	0603
C2, C3, C7, C8, C9, C10	6	10uF	UMK325AB7106KM-T	Taiyo Yuden	CAP, CERM, 10 μF, 50 V, +/- 10%, X7R, 1210	1210
C4, C5	2	4.7uF	GRM32ER71K475KE14L	MuRata	CAP, CERM, 4.7 µF, 80 V, +/- 10%, X7R, 1210	1210
C11, C20	2	68uF	UUD1V680MCL1GS	Nichicon	CAP, AL, 68 µF, 35 V, +/- 20%, 0.34 ohm, SMD	6.3x7.7
C12, C17, C19	3	0.47uF	CGA3E3X7R1H474M080AE	TDK	CAP, CERM, 0.47 µF, 50 V, +/- 20%, X7R, AEC-Q200 Grade 1, 0603	0603
C13	1	1uF	GRM188R71C105KE15D	MuRata	CAP, CERM, 1 µF, 16 V, +/- 10%, X7R, 0603	0603
C15	1	47pF	GRM1885C1H470JA01D	MuRata	CAP, CERM, 47 pF, 50 V, +/- 5%, C0G/NP0, 0603	0603
C16	1	470pF	GRM1885C1H471JA01D	MuRata	CAP, CERM, 470 pF, 50 V, +/- 5%, C0G/NP0, 0603	0603
C18	1	6800pF	GRM188R71H682KA01D	MuRata	CAP, CERM, 6800 pF, 50 V, +/- 10%, X7R, 0603	0603
C21	1	820pF	GRM1885C1H821JA01D	MuRata	CAP, CERM, 820 pF, 50 V, +/- 5%, C0G/NP0, 0603	0603
D1	1	60V	PMEG6010CEH,115	Nexperia	Diode, Schottky, 60 V, 1 A, SOD-123F	SOD-123F
H1, H2, H3, H4	4		NY PMS 440 0025 PH	B&F Fastener Supply	Machine Screw, Round, #4-40 x 1/4, Nylon, Philips panhead	Screw
H5, H6, H7, H8	4		1902C	Keystone	Standoff, Hex, 0.5"L #4-40 Nylon	Standoff
L1	1	20uH	B82559A203A20	TDK	Inductor, Wirewound, Ferrite, 20 uH, 14.3 A, 0.0064 ohm, AEC-Q200 Grade 0, SMD	21.5x21mm
Q1, Q2	2	80V	BSC123N08NS3 G	Infineon Technologies	MOSFET, N-CH, 80 V, 55 A, PG-TDSON-8	PG-TDSON-8
R1	1	3.0	CRCW06033R00JNEA	Vishay-Dale	RES, 3.0, 5%, 0.1 W, 0603	0603
R2	1	3.9	CRCW06033R90JNEA	Vishay-Dale	RES, 3.9, 5%, 0.1 W, 0603	0603
R3		8.06	CRCW06038R06FKEA	Vishay-Dale	RES, 8.06, 1%, 0.1 W, 0603	0603
R4	1	49.9k	CRCW060349K9FKEA	Vishay-Dale	RES, 49.9 k, 1%, 0.1 W, 0603	0603
R6	1	51.1k	CRCW060351K1FKEA	Vishay-Dale	RES, 51.1 k, 1%, 0.1 W, 0603	0603
R7	1	0	CRCW06030000Z0EA	Vishay-Dale	RES, 0, 5%, 0.1 W, 0603	0603
R8	1	33.2k	CRCW060333K2FKEA	Vishay-Dale	RES, 33.2 k, 1%, 0.1 W, 0603	0603
R9	1	3.32k	CRCW06033K32FKEA	Vishay-Dale	RES, 3.32 k, 1%, 0.1 W, 0603	0603
R10	1	1.74k	CRCW06031K74FKEA	Vishay-Dale	RES, 1.74 k, 1%, 0.1 W, 0603	0603
R11	1	24.9k	CRCW060324K9FKEA	Vishay-Dale	RES, 24.9 k, 1%, 0.1 W, 0603	0603
R13	1	0.007	PE1206FRF470R007L	Yageo America	RES, 0.007, 1%, 1 W, AEC-Q200 Grade 0, 1206	1206
R14	1	348k	CRCW0603348KFKEA	Vishay-Dale	RES, 348 k, 1%, 0.1 W, 0603	0603
TP1, TP8	2	White	5002	Keystone	Test Point, TH, Miniature, White	Keystone5002
TP2, TP5, TP6, TP10	4		1502-2	Keystone	Terminal, Turret, TH, Double	Keystone1502-2
TP3, TP9	2	Red	5000	Keystone	Test Point, TH, Miniature, Red	Keystone5000
TP4, TP7	2	Black	5001	Keystone	Test Point, TH, Miniature, Black	Keystone5001
U1	1		LM5117PMHX/NOPB	Texas Instruments	5.5-65V Wide Vin, Current Mode Synchronous Buck Controller with Analog Current Monitor, PWP0020A (TSSOP-20)	PWP0020A
C14	0	100pF	GRM2165C2A101JA01D	MuRata	CAP, CERM, 100 pF, 100 V, +/- 5%, C0G/NP0, 0805	0805
R5	0	49.9k	CRCW060349K9FKEA	Vishay-Dale	RES, 49.9 k, 1%, 0.1 W, 0603	0603
R12		10	CRCW120610R0JNEA	Vishay-Dale	RES, 10, 5%, 0.25 W, 1206	1206

IMPORTANT NOTICE FOR TI DESIGN INFORMATION AND RESOURCES

Texas Instruments Incorporated ('TI") technical, application or other design advice, services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using any particular TI Resource in any way, you (individually or, if you are acting on behalf of a company, your company) agree to use it solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources.

You understand and agree that you remain responsible for using your independent analysis, evaluation and judgment in designing your applications and that you have full and exclusive responsibility to assure the safety of your applications and compliance of your applications (and of all TI products used in or for your applications) with all applicable regulations, laws and other applicable requirements. You represent that, with respect to your applications, you have all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. You agree that prior to using or distributing any applications that include TI products, you will thoroughly test such applications and the functionality of such TI products as used in such applications. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

You are authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING TI RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY YOU AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

You agree to fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of your non-compliance with the terms and provisions of this Notice.

This Notice applies to TI Resources. Additional terms apply to the use and purchase of certain types of materials, TI products and services. These include; without limitation, TI's standard terms for semiconductor products http://www.ti.com/sc/docs/stdterms.htm), evaluation modules, and samples (http://www.ti.com/sc/docs/sampterms.htm).

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2017, Texas Instruments Incorporated