

**Further Range.
Better Coexistence.
Lower Power.**



RF performance line

Industry's highest performance sub-1 GHz RF family

Range and Coexistence

Meeting the most stringent RF requirements in the market, the TI RF performance line family has the most reliable range in the industry. TI's range is achieved by high output power (up to +16 dBm) and excellent sensitivity (-123 dBm @ 1.2 kbps). 60 dB selectivity along with 90 dB blocking enables exceptional coexistence. The RF performance line family can be in closer proximity to the other RF systems and potential interferers without any disturbance to the RF link.

Low-power sniff mode

The RF family's advanced RF channel sniff mode feature ensures quick startup and settling time, and enables a current consumption of sub-3 mA in Rx sniff mode. The sniff mode allows systems to listen for RF packets using very low power consumption while maintaining full RF performance.

www.ti.com/rfperformanceline



Introducing the CC1200 RF transceiver

Ideally suited for low-power, high-performance systems, the CC1200 RF transceiver offers a data rate up to 1 Mbps and years of life for battery-powered applications through low-power operation with sniff modes and fast settling time.

The CC1200 supports all the IEEE 802.15.4g FSK modes with hardware packet handling as well as hardware AES security support and all wM-Bus modes with great performance. Pin-for-pin compatibility with the CC1120 allows manufacturers to easily adopt the CC1200 for new designs.

CC1200 highlights:

- Up to 1 Mbps radio ensures high effective data rate for large sensor networks
- 60 dB selectivity and 90 dB blocking guarantee for up to 143 dB link budget and best-in-class coexistence in noisy RF environments
- 0.3 μ A power-down current and 2 mA RX sniff mode provide for several years of battery life on AA cells



CC1200 development kit



The CC1200 development kit provides a complete platform for hardware performance testing and software development for TI's sub-1 GHz CC1200 device. The development kit comes pre-programmed with a packet error rate test for easy out-of-the-box evaluation of the CC1200. RF range and robustness can be tested with different RF settings, and power consumption can be measured easily. This kit supports the frequency range from 868 to 930 MHz. Additional plug-in boards

(EMK) can be purchased separately to support other frequencies.

Performance line feature matrix

	CC1200	CC1120	CC1201	CC1121	CC1175	CC1125
Narrow band (12.5 / 25 kHz channels)	•	•			•	•
Up to 200 kbps data rate	•	•	•	•	•	•
Up to 1 Mbps data rate	•		•			
AES security hardware support	•		•			
802.15.4g FSK mandatory mode (50 kbps)	•	•	•	•	•	•
802.15.4g FSK 100 kbps	•	•	•	•	•	•
802.15.4g FSK all rates	•		•			
802.15.4g hardware packet support:						
DualSync (two concurrent sync words)	•	•	•	•	•	•
CRC and whitening	•		•			
Forward error correction (FEC)	•		•			
wM-BUS all modes (C, N, S, T)	•	•	•	•	•	•
WaveMatch and RX SniffMode	•	•	•	•	N/A	•
ETSI Category 1 at 868 MHz					N/A	•
ETSI Category 1 at 169 MHz	•	•			N/A	•

www.ti.com/rfperformanceline



IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products (also referred to herein as "components") are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of significant portions of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI components or services with statements different from or beyond the parameters stated by TI for that component or service voids all express and any implied warranties for the associated TI component or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards which anticipate dangerous consequences of failures, monitor failures and their consequences, lessen the likelihood of failures that might cause harm and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed a special agreement specifically governing such use.

Only those TI components which TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components which have **not** been so designated is solely at the Buyer's risk, and that Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.

Products

Audio	www.ti.com/audio
Amplifiers	amplifier.ti.com
Data Converters	dataconverter.ti.com
DLP® Products	www.dlp.com
DSP	dsp.ti.com
Clocks and Timers	www.ti.com/clocks
Interface	interface.ti.com
Logic	logic.ti.com
Power Mgmt	power.ti.com
Microcontrollers	microcontroller.ti.com
RFID	www.ti-rfid.com
OMAP Applications Processors	www.ti.com/omap
Wireless Connectivity	www.ti.com/wirelessconnectivity

Applications

Automotive and Transportation	www.ti.com/automotive
Communications and Telecom	www.ti.com/communications
Computers and Peripherals	www.ti.com/computers
Consumer Electronics	www.ti.com/consumer-apps
Energy and Lighting	www.ti.com/energy
Industrial	www.ti.com/industrial
Medical	www.ti.com/medical
Security	www.ti.com/security
Space, Avionics and Defense	www.ti.com/space-avionics-defense
Video and Imaging	www.ti.com/video

TI E2E Community

e2e.ti.com