TIDA-01524 REV E1 Bill of Materials



Item #	Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageRefer
2	!PCB1 0.9V, 1.2V, 1.8V,	1	Double	TIDA-01524 1503-2	Any Keystone	Printed Circuit Board Terminal, Turret, TH, Double	Keystone1503-2
2	5V, GND2,	0	Double	1503-2	Reystone	Terminai, Turret, TH, Double	Reystone 1503-2
	GND3, GND4,						
3	GND5 C0_2, C1_2,	4	0.1uF	GRM188R71C104KA01D	MuRata	CAP, CERM, 0.1 µF, 16 V, +/- 10%, X7R, 0603	0603
	C2_2, C3_2						
4	C0_3, C1_3, C2_3, C3_3	4	3300pF	GRM155R71H332KA01D	MuRata	CAP, CERM, 3300 pF, 50 V, +/- 10%, X7R, 0402	0402
5	C1, C2, C3, C8,	5	0.1uF	GCM188R71C104KA37J	MuRata	CAP, CERM, 0.1 µF, 16 V, +/- 10%, X7R, AEC-Q200 Grade 1, 0603	0603
6	Cbias1 C4, C5, C6, C7	4	10uF	GCM21BR71A106KE22L	MuRata	CAP, CERM, 10 µF, 10 V, +/- 10%, X7R, 0805	0805
7	C9, C10	2	4700pF	C0603C472J1GAC7867	Kemet	CAP, CERM, 4700 pF, 100 V, +/- 5%, C0G/NP0, 0603	0603
8	C11	1	2.2uF	C2012X5R1H225K125AB	TDK	CAP, CERM, 2.2 µF, 50 V, +/- 10%, X5R, 0805	0805
9	C12, C13, C14, C15	4	10uF	GRM32ER71H106KA12L	MuRata	CAP, CERM, 10 µF, 50 V, +/- 10%, X7R, 1210	1210
10	C16, C17, C24,	4	390pF	GRM155R71H391KA01D	MuRata	CAP, CERM, 390 pF, 50 V, +/- 10%, X7R, 0402	0402
11	C25 C18, C21, C26,	4	6800pF	GRM155R71H682KA88D	MuRata	CAP, CERM, 6800 pF, 50 V, +/- 10%, X7R, 0402	0402
12	C29 C19, C22, C27,	4	10uF	GRM21BR60J106KE19L	MuRata	CAP, CERM, 10 μF, 6.3 V, +/- 10%, X5R, 0805	0805
	C30						
13	C20, C23, C28,	11	0.1uF	GRM155R71C104JA88D	MuRata	CAP, CERM, 0.1 µF, 16 V, +/- 5%, X7R, 0402	0402
	C31, C34, C35, C38, C39, C44,						
14	C49, C51 C32, C33, C36,	10	10uF	GCM31CR71A106KA64L	MuRata	CAP, CERM, 10 µF, 10 V, +/- 10%, X7R, AEC-Q200 Grade 1, 1206	1206
	C37, C40, C41,						
	C42, C43, C48,						
15	C50 C45, C47	2	2.2uF	GRM188R61A225KE34D	MuRata	CAP, CERM, 2.2 µF, 10 V, +/- 10%, X5R, 0603	0603
16	C46	1	1uF	C0603C105K8PACTU	Kemet	CAP, CERM, 1 µF, 10 V, +/- 10%, X5R, 0603	0603
17	C52, C58	2	2200pF	C0603C222K5RACTU	Kemet	CAP, CERM, 2200pF, 50V, +/-10%, X7R, 0603	0603
18	C53	1	0.47uF	GRM188R71A474KA61D	MuRata	CAP, CERM, 0.47uF, 10V, +/-10%, X7R, 0603	0603
19	C54, C55, C56, C57	4	22uF	GCM31CR71A226KE02	MuRata	CAP, CERM, 22 µF, 10 V, +/- 10%, X7R, AEC-Q200 Grade 1, 1206	1206
20	Cboot1	1	0.47uF	GRM188R71E474KA12D	MuRata	CAP, CERM, 0.47 µF, 25 V, +/- 10%, X7R, 0603	0603
21	Cbulk1	1	100uF	HHXB500ARA101MJA0G	Chemi-Con	CAP, Aluminum Polymer, 100 µF, 50 V, +/- 20%, 0.025 ohm, AEC- Q200 Grade 2, D10xL10mm SMD	D10xL10mm
22	CF1, CF2, CF3, CF4	4	4.7uF	CGA6P3X7R1H475M250AB	ток	CAP, CERM, 4.7 µF, 50 V, +/- 20%, X7R, AEC-Q200 Grade 1, 1210	1210
23	CFF1	1	91pF	GRM1555C1H910JA01D	MuRata	CAP, CERM, 91 pF, 50 V, +/- 5%, C0G/NP0, 0402	0402
24	Cin_hf1, Cin_hf2	2	0.047uF	GRM188R71H473KA61D	MuRata	CAP, CERM, 0.047 µF, 50 V, +/- 10%, X7R, 0603	0603
25	Co1, Co2, Co3, Co4, Co5, Co6	6	47uF	GRM32ER71A476KE15L	MuRata	CAP, CERM, 47 µF, 10 V, +/- 10%, X7R, 1210	1210
26	Cvcc1	1	4.7uF	GCM21BR71C475KA73L	MuRata	CAP, CERM, 4.7 µF, 16 V, +/- 10%, X7R, AEC-Q200 Grade 1, 0805	0805
27	D1	1	28V	SMBJ28CA-13-F	Diodes Inc.	Diode, TVS, Bi, 28 V, 45.4 Vc, SMB	SMB
28	FB1	1	800 ohm	HR2220V801R-10	Laird-Signal Integrity Products	Ferrite Bead, 800 ohm @ 100 MHz, 8 A, 2220	2220
29	FID1, FID2, FID3, FID4, FID5, FID6	6		N/A	N/A	Fiducial mark. There is nothing to buy or mount.	Fiducial
30	GND1	1		6092	Keystone	Standard Banana Jack, Insulated, Black	6092
31	L1	1	10uH	XAL6060-103MEB	Coilcraft	Inductor, Shielded, Composite, 10 µH, 7.6 A, 0.03 ohm, SMD	IND_6.4x6.1x6.6
32	L2, L3, L4, L5	4	30 ohm	BLM21PG300SH1D	MuRata	Ferrite Bead, 30 ohm @ 100 MHz, 4 A, 0805	0805
33 34	L6, L7, L8, L9	4	470nH 1.2uH	DFE252012F-R47M=P2 XAL5030-122MEB	MuRata Toko	Inductor, Powdered Iron, 470 nH, 5.8 A, 0.017 ohm, SMD Inductor, Shielded, Composite, 1.2 µH, 11.1 A, 0.01 ohm, SMD	2.5x1.2x2mm
34	L10, L11 LF1	2	1.2uH 4.7uH	XAL5030-122MEB XAL6060-472MEB	Coilcraft Coilcraft	Inductor, Shielded, Composite, 1.2 µH, 11.1 A, 0.01 onm, SMD Inductor, Shielded, Composite, 4.7 µH, 10.5 A, 0.015 ohm, SMD	5.3x31.x5.5mm IND_6.4x6.1x6.0
36	Q1	1	40V	SQJ422EP-T1-GE3	Vishay-Siliconix	MOSFET, N-CH, 40 V, 75 A, PowerPAK_SO-8L	PowerPAK SO
37	R1, R2, R3, R4	4	3.9	CRCW08053R90JNEA	Vishay-Dale	RES, 3.9, 5%, 0.125 W, 0805	0805
38	R5, R6, R7, R8	4	100k	CRCW0402100KFKED	Vishay-Dale	RES, 100 k, 1%, 0.063 W, 0402	0402
39	R9	1	4.99	RC0805FR-074R99L	Yageo America	RES, 4.99 ohm, 1%, 0.125W, 0805	0805
	R10, R16	2	4.7	CRCW08054R70JNEA	Vishay-Dale	RES, 4.7 ohm, 5%, 0.125W, 0805	0805
41	R11, R13	2	49.9k	CRCW060349K9FKEA	Vishay-Dale	RES, 49.9k ohm, 1%, 0.1W, 0603	0603
42	R12	1	12.4k	CRCW060312K4FKEA	Vishay-Dale	RES, 12.4k ohm, 1%, 0.1W, 0603	0603
43 44	R14 R15, R17	1	4.99k 10k	CRCW06034K99FKEA CRCW060310K0JNEA	Vishay-Dale Vishay-Dale	RES, 4.99 k, 1%, 0.1 W, 0603 RES, 10k ohm, 5%, 0.1W, 0603	0603 0603
44	R15, R17 Rbias1	2	10K 3.0	CRCW060310K0JNEA CRCW04023R00JNED	Vishay-Dale	RES, 10k onm, 5%, 0.1W, 0603 RES, 3.0, 5%, 0.063 W, 0402	0402
40	RFBB1	1	34.8k	CRCW040234K8FKED	Vishay-Dale	RES, 34.8 k, 1%, 0.063 W, 0402	0402
47	RFBT1	1	80.6k	CRCW040280K6FKED	Vishay-Dale	RES, 80.6 k, 1%, 0.063 W, 0402	0402
48	R_EN1, R_Reset1	2	100k	CRCW0603100KJNEA	Vishay-Dale	RES, 100 k, 5%, 0.1 W, 0603	0603
	K_Reset1	1		LM74700QDBVTQ1	Texas Instruments	Low Iq Always ON Smart Diode Controller, DDC0006A (SOT-6)	DDC0006A
49		1		LMS3655LQRNLRQ1	Texas Instruments	5.5A Synchronous Buck Regulator for Automotive Applications, RNL0022A (VQFN-HR-22)	RNL0022A
49 50	U2						
50		1		LP87561IRNERQ1	Texas Instruments	Four-Phase Buck Converter, RNE0026C (VOEN-HR-26)	RNF0026C
	U2 U3 U4	1		LP87561IRNFRQ1 LM2775DSGR	Texas Instruments Texas Instruments	Four-Phase Buck Converter, RNF0026C (VQFN-HR-26) Switched Capacitor 5 V Boost Converter, DSG0008A (WSON-8)	RNF0026C DSG0008A
50 51	U3						

IMPORTANT NOTICE FOR TI DESIGN INFORMATION AND RESOURCES

Texas Instruments Incorporated ('TI") technical, application or other design advice, services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using any particular TI Resource in any way, you (individually or, if you are acting on behalf of a company, your company) agree to use it solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources.

You understand and agree that you remain responsible for using your independent analysis, evaluation and judgment in designing your applications and that you have full and exclusive responsibility to assure the safety of your applications and compliance of your applications (and of all TI products used in or for your applications) with all applicable regulations, laws and other applicable requirements. You represent that, with respect to your applications, you have all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. You agree that prior to using or distributing any applications. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

You are authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING TI RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY YOU AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

You agree to fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of your noncompliance with the terms and provisions of this Notice.

This Notice applies to TI Resources. Additional terms apply to the use and purchase of certain types of materials, TI products and services. These include; without limitation, TI's standard terms for semiconductor products http://www.ti.com/sc/docs/stdterms.htm), evaluation modules, and samples (http://www.ti.com/sc/docs/stdterms.htm), evaluation

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2017, Texas Instruments Incorporated