Filename: TIDA-01359A(001)_BOM.xls

Variant: 001

Generated: 12/4/2017 11:08:31 AM

SideGig-OPA1632EVM

Designator	Quantity	Value	Description	PackageReference	PartNumber	Manufacturer	Alternate PartNumber	Alternate Manufacturer
!PCB	1	value	Printed Circuit Board	Fackageneierence	TIDA-01359	Any	-	- Alternate Manufacturer
C1, C14	2	10uF	CAP, CERM, 10 µF, 25 V, +/- 10%, X7R, 1210	1210	12103C106KAT2A	AVX		
C2, C6, C15, C19	4	0.1uF	CAP, CERM, 0.1 µF, 25 V, +/- 5%, X7R, 0603	0603	06033C104JAT2A	AVX		
C3, C4, C16, C17	4	10uF	CAP, Film, 10 μF, 63 V, +/- 10%, TH	18x17.5x9mm	B32522C106K	TDK		
C7, C8,	8	47pF	CAP, CERM, 47 pF, 50 V, +/- 5%, C0G/NP0, 0603	0603	06035A470JAT2A	AVX		
C10, C11, C20, C21, C23, C24								
C9, C12, C22, C25	4	150pF	CAP, CERM, 150 pF, 50 V, +/- 5%, C0G/NP0, 0603	0603	06035A151JAT2A	AVX		
C13, C26	2	3300pF	CAP, CERM, 3300 pF, 50 V, +/- 5%, C0G/NP0, 0805	0805	GRM2165C1H332JA01 D	MuRata		
H1, H2, H3, H4	4		MACHINE SCREW PAN PHILLIPS 4-40	Machine Screw, 4-40, 1/4 inch	PMSSS 440 0025 PH	B&F Fastener Supply		
H5, H6, H7, H8	4		Standoff, Threaded, 1.5", 4-40, Aluminum	1/4 Round Female Standoff	3483	Keystone		
J1, J12	2		XLR Receptacle and 1/4" Phone Jack, 8-Pin, TH	TH, 8-Leads, Body 27x37mm	NCJ6FI-H	Neutrik		
J2	1		RCA Jack, Vertical, White, TH	RCA JACK, WHITE	RCJ-023	CUI Inc.		
J3	1		RCA Jack, Vertical, Blue, TH	RCA Jack, Vertical, Blue, TH	RCJ-025	CUI Inc.		
J4, J5, J9, J10, J15, J16, J20, J21	8		SMA Straight PCB Socket Die Cast, 50 Ohm, TH	SMA Straight PCB Socket Die Cast, TH	5-1814832-1	TE Connectivity		
J6, J8, J17, J19, J23	5		Header, 2.54mm, 3x1, Tin, TH	Header, 2.54mm, 3x1, TH	68001-403HLF	FCI		
J7, J18	2		Header, 2.54mm, 2x1, TH	Header, 2.54mm, 2x1, TH	961102-6404-AR	ЗМ		
J11, J22	2		Connector, 3 pole male receptacle, TH	Connector, 3 pole male receptacle, TH	NC3MD-V-BAG	Neutrik		
J13	1		RCA Jack, Vertical, Red, TH	RCA JACK, RED	RCJ-022	CUI Inc.		
J14	1		RCA Jack, Vertical, Black, TH	RCA Jack, Vertical, Black, TH	RCJ-021	CUI Inc.		
J24	1		Connector, Banana Jack, Double, Black Base, 15A, TH	1380x1220x630	2269-0	Pomona Electronics		
J25	1		Header, 100mil, 14x2, Gold, TH	14x2 Header	TSW-114-07-G-D	Samtec		
J26	1		Receptacle, 100mil, 2x1, Tin, TH	Receptacle, 2x1, 100mil, Tin	PPTC021LFBN-RC	Sullins Connector Solutions		
LBL1	1		Thermal Transfer Printable Labels, 0.650" W x 0.200" H - 10,000 per roll	PCB Label 0.650"H x 0.200"W		Brady	-	-
R1, R2, R11, R12	4	7.50k	RES, 7.50 k, 0.1%, 0.1 W, 0603	0603	RG1608P-752-B-T5	Susumu Co Ltd		
R3, R4, R6, R7, R13, R14, R16, R17	8	30.0k	RES, 30.0 k, 0.1%, 0.1 W, 0603	0603	RG1608P-303-B-T5	Susumu Co Ltd		
R5, R8, R15, R18	4	10.0k	RES, 10.0 k, 0.1%, 0.1 W, 0603	0603	RG1608P-103-B-T5	Susumu Co Ltd		
R9, R10, R19, R20	4	100	RES, 100, 1%, 0.1 W, 0603	0603	CRCW0603100RFKEA	Vishay-Dale		
R21, R22	2	0	RES, 0, 5%, 0.1 W, 0603	0603	CRCW06030000Z0EA	Vishay-Dale		
SH1, SH2, SH3, SH4, SH5	5	1x2	Shunt, 100mil, Gold plated, Black		382811-6	AMP		
TP1, TP2	2		Test Point, Compact, White, TH	White Compact Testpoint	5007	Keystone		
TP3	1		Test Point, Compact, Black, TH	Black Compact Testpoint	5006	Keystone		
U1, U2	2		High-Performance, Fully-Differential AUDIO OPERATIONAL AMPLIFIER, DGN0008D	DGN0008D	OPA1632DGNR	Texas Instruments	OPA1632DGN	Texas Instruments
C5, C18	0		CAP, CERM, xxxF, xxV, [TempCo], xx%, [PackageReference]	Used in PnP output and some BOM reports	Used in BOM report	Used in BOM report	-	-
FID1, FID2, FID3, FID4, FID5, FID6	0		Fiducial mark. There is nothing to buy or mount.	Fiducial	N/A	N/A		

Notes:

Unless otherwise noted in the Alternate PartNumber and/or Alternate Manufacturer columns, all parts may be substituted with equivalents.

IMPORTANT NOTICE FOR TI DESIGN INFORMATION AND RESOURCES

Texas Instruments Incorporated ("TI") technical, application or other design advice, services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using any particular TI Resource in any way, you (individually or, if you are acting on behalf of a company, your company) agree to use it solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources.

You understand and agree that you remain responsible for using your independent analysis, evaluation and judgment in designing your applications and that you have full and exclusive responsibility to assure the safety of your applications and compliance of your applications (and of all TI products used in or for your applications) with all applicable regulations, laws and other applicable requirements. You represent that, with respect to your applications, you have all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. You agree that prior to using or distributing any applications that include TI products, you will thoroughly test such applications and the functionality of such TI products as used in such applications. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

You are authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING TI RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY YOU AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

You agree to fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of your non-compliance with the terms and provisions of this Notice.

This Notice applies to TI Resources. Additional terms apply to the use and purchase of certain types of materials, TI products and services. These include; without limitation, TI's standard terms for semiconductor products http://www.ti.com/sc/docs/stdterms.htm), evaluation modules, and samples (http://www.ti.com/sc/docs/sampterms.htm).

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2018, Texas Instruments Incorporated