Change in menu Project

\$

				1			1	1
Designator		Value	Description	PackageReference	PartNumber	Manufacturer	Alternate PartNumber	Alternate Manufacturer
C1, C2	2	1000uF	CAP, AL, 1000 μF, 25 V, +/- 20%, 0.018 ohm, TH	TH, 2-Leads, Dia	25ZLH1000MEFC10X23	Rubycon		
				10mm, Pin Spacing				
				5mm				
C3, C4	2	10uF	CAP, CERM, 10 µF, 63 V, +/- 10%, X7R, 1210	1210	GRM32ER71J106KA12	MuRata		
					L			
C5, C9,	4	10uF	CAP, CERM, 10 µF, 25 V, +/- 10%, X7R, 1210	1210	12103C106KAT2A	AVX		
C12, C22								
C6, C7	2	560uF	CAP, AL, 560 µF, 50 V, +/- 20%, 0.023 ohm, TH	D12.5xL25mm	50ZL560MEFC12.5X25	Rubycon		
C8, C15	2	3.3uF	CAP, CERM, 3.3 µF, 50 V, +/- 10%, X7R, 1206	1206	C3216X7r1H335K160A	TDK		
00, 013	2	3.5ui	CAI , CERWI, 3.3 μΙ , 30 V, 47- 10/6, Χ/ΤΚ, 1200	1200	C 5210X/11115551X100A	TBR		
C10, C13,	4	2200pF	CAP, CERM, 2200 pF, 50 V, +/- 10%, X7R, 0603	0603	C0603C222K5RAC	Kemet		
	4	2200pr	CAF, CERIVI, 2200 pF, 30 V, 4/- 10 %, A/R, 0003	0003	C0003C22ZK3KAC	Keillet		
C20, C23	_		04D 05DM 47 5 05 V / 000/ V5D 0005	0005	0011010001513511110			
C11, C14	2	4.7uF	CAP, CERM, 4.7 µF, 25 V, +/- 20%, X5R, 0805	0805	GRM21BR61E475MA12	MuRata		
					L			
C16	1	0.01uF	CAP, CERM, 0.01 µF, 50 V, +/- 10%, X7R, 0603	0603	C1608X7R1H103K	TDK		
C17	1	1uF	CAP, CERM, 1 µF, 25 V, +/- 10%, X7R, 0603	0603	C0603C105K3RACTU	Kemet		
C18	1	100pF	CAP, CERM, 100 pF, 50 V, +/- 5%, C0G/NP0, 0603	0603	C1608C0G1H101J	TDK		
C19	1	0.47uF	CAP, CERM, 0.47 µF, 25 V, +/- 10%, X5R, 0805	0805	08053D474KAT2A	AVX		
C21	1	1000pF	CAP, CERM, 1000 pF, 50 V, +/- 5%, C0G/NP0, 0603	0603	C1608C0G1H102J	TDK		
		· ·						
D1	1	75V	Diode, Ultrafast, 75 V, 0.3 A, SOT-23	SOT-23	BAS16-7-F	Diodes Inc.		
D1	1	open	Diode, Ultrafast, 75 V, 0.3 A, SOT-23	SOT-23	BAS16-7-F	Diodes Inc.		
D3, D6	2	60V	Diode, Ottalast, 75 V, 0.3 A, SO1-23 Diode, Schottky, 60 V, 20 A, AEC-Q101, DDPAK	DDPAK	VS-48CTQ060SPBF	Vishay-Semiconductor		1
	4						+	
D4		10V	Diode, Zener, 10 V, 225 mW, SOT-23	SOT-23	MMBZ5240BLT1G	ON Semiconductor		
D5	1	6.8V	Diode, Zener, 6.8 V, 225 mW, SOT-23	SOT-23	MMBZ5235BLT1G	ON Semiconductor		
J1	1		Terminal Block, 30A, 9.52mm (.375) Pitch, 2-Pos, TH	19.62x21.5x12.5mm	OSTT7022150	On-Shore Technology		
J2	1		Terminal Block, 6A, 3.5mm Pitch, 2-Pos, TH	7.0x8.2x6.5mm	ED555/2DS	On-Shore Technology		1
L1	1	470nH	Inductor, Shielded Drum Core, Powdered Iron, 470 nH,	IHLP-5050FD	IHLP5050FDERR47M01	Vishay-Dale		
			41 A, 0.001 ohm, SMD					
L2, L3, L4,	4	3.3uH	Inductor, Shielded Drum Core, Powdered Iron, 3.3 µH,	IHLP-5050FD	IHLP5050FDER3R3M01	Vishay-Dale		
L5			18 A, 0.0057 ohm, SMD	I		""	1	1
Q1	1	40 V	Transistor, NPN, 40 V, 1 A, SOT-223	SOT-223	PZT2222A	Fairchild Semiconductor		
Q2, Q3, Q5,	4	60V	MOSFET, N-CH, 60 V, 50 A, SON 5x6mm	SON 5x6mm	CSD18534Q5A	Texas Instruments		None
	4	00 V	WOSFET, N-CH, 60 V, 50 A, SON SXIIIIII	SON SXUIIIII	C3D18334Q3A	rexas iristruments		Notice
Q6 Q4		60V	MODEET NICH COV 0.47 A COT CO	SOT-23	0NIZ000 Z E	Diadas Isa		Mana
			MOSFET, N-CH, 60 V, 0.17 A, SOT-23		2N7002-7-F	Diodes Inc.		None
R1, R2	2	4.99k	RES, 4.99 k, 0.1%, 0.063 W, 0603	0603	CPF0603B4K99E	TE Connectivity		
R3	1	16.2k	RES, 16.2 k, 1%, 0.1 W, 0603	0603	CRCW060316K2FKEA	Vishay-Dale		
R4	1	7.50k	RES, 7.50 k, 1%, 0.1 W, 0603	0603	CRCW06037K50FKEA	Vishay-Dale		
R5, R13	2	2.00k	RES, 2.00 k, 1%, 0.1 W, 0603	0603	CRCW06032K00FKEA	Vishay-Dale		
R6, R14,	4	200	RES, 200, 1%, 0.1 W, 0603	0603	CRCW0603200RFKEA	Vishay-Dale		
R20, R33						_		
R7, R8,	8	0.01	RES, 0.01, 1%, 0.5 W, 1206	1206	CSR1206FK10L0	Stackpole Electronics Inc		
R15, R16,			, , , , , , , , , , , , , , , , , , , ,					
R23, R24,								
R34, R35								
R9	1	133k	RES, 133 k, 1%, 0.1 W, 0603	0603	CRCW0603133KFKEA	Vishay-Dale		
	6	10.0k		0603	CRCW060310K0FKEA	Vishay-Dale		
R10, R19,	0	10.0K	RES, 10.0 k, 1%, 0.1 W, 0603	0603	CRCW060310K0FKEA	Visitay-Dale		
R26, R27,								
R28, R29								
R11	1	8.66k	RES, 8.66 k, 1%, 0.1 W, 0603	0603	CRCW06038K66FKEA	Vishay-Dale		
R12	1	2.49k	RES, 2.49 k, 1%, 0.1 W, 0603	0603	CRCW06032K49FKEA	Vishay-Dale		
R17	11	6.19k	RES, 6.19 k, 1%, 0.1 W, 0603	0603	CRCW06036K19FKEA	Vishay-Dale		
R18	1	10.0	RES, 10.0, 1%, 0.1 W, 0603	0603	CRCW060310R0FKEA	Vishay-Dale		
R21	1	49.9k	RES, 49.9 k, 1%, 0.1 W, 0603	0603	CRCW060349K9FKEA	Vishay-Dale		
R22	1	93.1k	RES, 93.1 k, 1%, 0.1 W, 0603	0603	CRCW060393K1FKEA	Vishay-Dale		
R25	1	20.0k	RES, 20.0 k, 1%, 0.1 W, 0603	0603	CRCW060320K0FKEA	Vishay-Dale		
R30	1	49.9	RES, 49.9, 1%, 0.1 W, 0603	0603	CRCW060320R0FREA	Vishay-Dale		
R31	1					Vishay-Dale Vishay-Dale		1
		43.2k 806	RES, 43.2 k, 1%, 0.1 W, 0603	0603	CRCW060343K2FKEA CRCW0603806RFKEA	Vishay-Dale Vishay-Dale		
R32	1		RES, 806, 1%, 0.1 W, 0603	0603				
T1, T2	2	50A	Terminal 50A Lug	CB35-36-CY	CB35-36-CY	Panduit		
TP1, TP3,	13	Red	Test Point, Miniature, Red, TH	Red Miniature	5000	Keystone		
TP4, TP6,				Testpoint				
TP7, TP9,								
TP10,								
TP11,								
TP12,								
TP13,								
TP14,								
TP15, TP16								
TP2, TP5,	3	Black	Test Point, Miniature, Black, TH	Black Miniature	5001	Keystone		İ
	3	Diack	reactionic, Williadule, Diack, TH		3001	Troystolle		1
			LinCMOS Dual Differential Comments - DOCCA	Testpoint	TI COZOCDE	Tayon Instrum	TI 02720D	Tayaa laatuum
TP8			LinCMOS Dual Differential Comparators, D0008A	D0008A	TLC372CDR	Texas Instruments	TLC372CD	Texas Instruments
TP8 U1	1		Adjustable Descision Obsert D. 11. Ct. 11. C		TL431ACDBZT	Texas Instruments	Equivalent	Texas Instruments
TP8	1		Adjustable Precision Shunt Regulator, 34 ppm / degC,	DBZ0003A			1 3	
TP8 U1			100 mA, 0 to 70 degC, 3-pin SOT-23 (DBZ), Green	DB20003A			'	
TP8 U1 U2	1		100 mA, 0 to 70 degC, 3-pin SOT-23 (DBZ), Green (RoHS & no Sb/Br)				·	
TP8 U1			100 mA, 0 to 70 degC, 3-pin SOT-23 (DBZ), Green (RoHS & no Sb/Br) DUAL 4-A PEAK HIGH SPEED LOW- SIDE POWER	D0008A	UCC27324DR	Texas Instruments	UCC27324D	Texas Instruments
TP8 U1 U2 U3, U5	1		100 mA, 0 to 70 degC, 3-pin SOT-23 (DBZ), Green (RoHS & no Sb/Br) DUAL 4-A PEAK HIGH SPEED LOW- SIDE POWER MOSFET DRIVERS, D0008A	D0008A	UCC27324DR	Texas Instruments	UCC27324D	
TP8 U1 U2	1		100 mA, 0 to 70 degC, 3-pin SOT-23 (DBZ), Green (RoHS & no Sb/Br) DUAL 4-A PEAK HIGH SPEED LOW- SIDE POWER			Texas Instruments Texas Instruments	UCC27324D	Texas Instruments Texas Instruments

Notes:

Unless otherwise noted in the Alternate PartNumber and/or Alternate Manufacturer columns, all parts may be substituted with equivalents.

IMPORTANT NOTICE FOR TI REFERENCE DESIGNS

Texas Instruments Incorporated ("TI") reference designs are solely intended to assist designers ("Buyers") who are developing systems that incorporate TI semiconductor products (also referred to herein as "components"). Buyer understands and agrees that Buyer remains responsible for using its independent analysis, evaluation and judgment in designing Buyer's systems and products.

TI reference designs have been created using standard laboratory conditions and engineering practices. TI has not conducted any testing other than that specifically described in the published documentation for a particular reference design. TI may make corrections, enhancements, improvements and other changes to its reference designs.

Buyers are authorized to use TI reference designs with the TI component(s) identified in each particular reference design and to modify the reference design in the development of their end products. HOWEVER, NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY THIRD PARTY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT, IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI REFERENCE DESIGNS ARE PROVIDED "AS IS". TI MAKES NO WARRANTIES OR REPRESENTATIONS WITH REGARD TO THE REFERENCE DESIGNS OR USE OF THE REFERENCE DESIGNS, EXPRESS, IMPLIED OR STATUTORY, INCLUDING ACCURACY OR COMPLETENESS. TI DISCLAIMS ANY WARRANTY OF TITLE AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, QUIET ENJOYMENT, QUIET POSSESSION, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS WITH REGARD TO TI REFERENCE DESIGNS OR USE THEREOF. TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY BUYERS AGAINST ANY THIRD PARTY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON A COMBINATION OF COMPONENTS PROVIDED IN A TI REFERENCE DESIGN. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, SPECIAL, INCIDENTAL, CONSEQUENTIAL OR INDIRECT DAMAGES, HOWEVER CAUSED, ON ANY THEORY OF LIABILITY AND WHETHER OR NOT TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES, ARISING IN ANY WAY OUT OF TI REFERENCE DESIGNS OR BUYER'S USE OF TI REFERENCE DESIGNS.

TI reserves the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques for TI components are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

Reproduction of significant portions of TI information in TI data books, data sheets or reference designs is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards that anticipate dangerous failures, monitor failures and their consequences, lessen the likelihood of dangerous failures and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in Buyer's safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed an agreement specifically governing such use.

Only those TI components that TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components that have *not* been so designated is solely at Buyer's risk, and Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.