Filename: PMP30605 Rev_A-BOM.xls

Variant: None

Generated: 12/18/2018 11:50:33 AM

TID #: PMP30605

TEXAS INSTRUMENTS

PMP30605 REV A Bill of Materials

Item #	Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
1	C1	1	DNP	DNP	TDK	DNP	1206
2	C2, C3	2	15uF	UVC2G150MPD	Nichicon	CAP, AL, 15 μF, 400 V, +/- 20%, TH	Cap, 10x18mm
3	C4	1	0.1uF	R46KF310000P1M	Kemet	CAP, Film, 0.1 µF, 275 Vac, +/- 20%, TH	13x11x5mm
4	C5	1	1000uF	16ZLJ1000MCE10X16	Rubycon	CAP, AL, 1000 μF, 16 V, +/- 20%, TH	CAPPR5-10x16
5	C6	1	22uF	GRM21BR61E226ME44L	MuRata	CAP, CERM, 22 µF, 25 V, +/- 20%, X5R, 0805	0805
6	C7, C11	2	0.1uF	C1608X7R1H104K	TDK	CAP, CERM, 0.1 µF, 50 V, +/- 10%, X7R, 0603	0603
7	C8, C9	2	2200pF	R413F12200000M	Kemet	CAP, Film, 2200 pF, 300 VAC, Class Y2, R41 +/- 20%, TH	13x4x9mm
8	C10	1	47uF	EEU-FM1E470	Panasonic	CAP, AL, 47 µF, 25 V, +/- 20%, 0.3 ohm, TH	5.0x11.0mm
9	D1, D3	2	ES2D-13-F	ES2D-13-F	Diodes Inc.	Diode, Ultrafast, 200 V, 2 A, SMB	SMB
10	D2	1	DF406SL	DF406SL	Bourns	Diode, Bridge, 600 V, 4 A	0.41 " x 0.32 "
11	D4	1	US1J-13-F	US1J-13-F	Diodes Inc.	Diode, Ultrafast, 600 V, 1 A, SMA	SMA
12	D5	1	BAS20HT1G	BAS20HT1G	ON Semiconductor	DIODE SWITCH 200V 200MA SOD323	SOD-323
13	D100	1	58V	SMAJ58A	Diodes Inc.	Diode, TVS, Uni, 58 V, 400 W, SMA	SMA
14	D101	1	75V	SMAJ75A	Diodes Inc.	Diode, TVS, Uni, 58 V, 400 W, SMA	SMA
15	F1	1	1A	RST 1-BULK	Bel Fuse	FUSE BOARD MOUNT 1A 250VAC RAD	8.35x7.7x4mm
16	J1	1		CIM029P5	CIM	Header (Shrouded), 5.08 mm, 2x1, Tin, R/A, TH	Header, 5.08 mm, 2x1, R/A, TH
17	L1	1	1mH	7447462102	Wurth Elektronik	Inductor, Unshielded Drum Core, Ferrite, 1 mH, 0.25 A, 4.38 ohm, TH	D6 x 8.5mm
18	L2	1	10mH	744821110	Wurth Elektronik	Coupled inductor, 10 mH, 0.7 A, 0.35 ohm, TH	15 x 18 x 7.5mm
19	R1, R3	2	47k	DNP	Vishay-Dale	DNP	1206
20	R2	1	47k	0 Ohm	Vishay-Dale	0 Ohm	1206
21	R4	1	18.2k	CRCW060318K2FKEA	Vishay-Dale	RES, 18.2 k, 1%, 0.1 W, 0603	0603
22	R5	1	47.5	CRCW080547R5FKEA	Vishay-Dale	RES, 47.5, 1%, 0.125 W, 0805	0805
23	R6	1	15.0	CRCW060315R0FKEA	Vishay-Dale	RES, 15.0 ohm, 1%, 0.1W, 0603	0603
24	R7	1	73.2k	CRCW060373K2FKEA	Vishay-Dale	RES, 73.2 k, 1%, 0.1 W, 0603	0603
25	R8	1	24.0k	RC0603FR-0724KL	Yageo America	RES, 24.0 k, 1%, 0.1 W, 0603	0603
26	R9	1	1.00k	CRCW06031K00FKEA	Vishay-Dale	RES, 1.00 k, 1%, 0.1 W, 0603	0603
27	RT1	1	5 ohm	MF72-005D5	Cantherm	Thermistor NTC, 5 ohm, 20%, MF72D5 TH	MF72D5 TH
28	RV1	1	275Vac	B72214S271K101	TDK	VARISTOR 275Vac 6KA DISC 14MM	D15.5xT5mm
29	T1	1	880 uH	BS64048CT	Bourns	Transformer, 880 uH, TH	TH, 9-Leads, Body 21.2x22 mm
30	TP1, TP18	2	Red	5000	Keystone	Test Point, Miniature, Red, TH	Red Miniature Testpoint
31	TP2	1	Black	5001	Keystone	Test Point, Miniature, Black, TH	Black Miniature Testpoint
32	U1	1	UCC28911DR	UCC28911DR	Texas Instruments	High Voltage Flyback Switcher with Primary-side Regulation and Constant Current Control, D0007A	- D0007A

DNP = "do not populate"

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale (www.ti.com/legal/termsofsale.html) or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2019, Texas Instruments Incorporated