Filename: PMP2661REVA_bom.xls									
Date: 08/		TITE VII_DOTTI.XIS							
Date. 00/	PMP2661REVA BOM								
	PIMP	2661KEVA	BOM						
COUNT	RefDes	Value	Description	Size	Part Number	MFR			
1	C1	680uF	Capacitor, Alum, 680uF, 25V, 23 milliohm	0.315 inch	25ZL680M10X20	Rubycon			
1	C2	10uF	Capacitor, Ceramic, 10uF, 25V, X5R	1206	C3216X5R1E106MT	TDK			
1	C3	0.1uF	Capacitor, Ceramic, 50V, X7R, 15%	0603	std	TDK			
1	C4	560pF	Capacitor, Ceramic, 50V, X7R, 15%	0603	Std	TDK			
2	C5	1000uF	Capacitor, Alum, 1000uF, 16V, 23 milliohms	0.315 inch	16ZL1000M10x20	Rubycon			
	C6	1000uF	Capacitor, Alum, 1000uF, 16V, 23 milliohms	0.315 inch	16ZL1000M10x20	Rubycon			
1	C7	10uF	Capacitor, Ceramic, 10uF, 25V, X5R	1206	C3216X5R1E106M	TDK			
2	C8	1uF	Capacitor, Ceramic, 16V, X7R, 15%	0603	std	TDK			
1	C9	470pF	Capacitor, Ceramic, 50V, X7R, 15%	0603	std	TDK			
	C10	1uF	Capacitor, Ceramic, 16V, X7R, 15%	0603	std	TDK			
1	C11	330pF	Capacitor, Ceramic, 50V, X7R, 15%	0603	std	TDK			
1	C12	47nF	Capacitor, Ceramic, 50V, X7R, 15%	0603	std	TDK			
1	C13	1nF	Capacitor, Ceramic, 50V, X7R, 15%	0603	std	TDK			
1	D1	MBR30H30CTG	Diode, Dual Schottky, 30V, 30A	TO-220V	MBR30H30CTG	ONsemi			
1	HS1	SK 437 35 STC 2	Heatsink, TO-220/218 veritcal, Rth 18K/W	0.640 x 0.640 inch	SK 437 35 STC 2 and THF 409 220 2	Fischer Elektronik			
2	J1	D120/2DS	Terminal Block, 2-pin, 15-A, 5.1mm	0.40 x 0.35 inch	D120/2DS	OST			
	J2	D120/2DS	Terminal Block, 2-pin, 15-A, 5.1mm	0.40 x 0.35 inch	D120/2DS	OST			
1	L1	4.7uH	Inductor, SMT, 4.7uH, 10A, 15milliohm	0.51 x 0.51 inch	IHLP5050FDER4R7M01	Vishay			
1	Q1	Si7686DP	MOSFET, NCh, 30V, 35A, 10 millohm	PWRPAK S0-8	Si7686DP	Vishay			
1	R1	10	Resistor, Chip, 1/16W, 1%	0603	Std	Std			
1	R2	392K	Resistor, Chip, 1/16W, 1%	0603	Std	Std			
2	R4	10	Resistor, Chip, 1/4W, 1%	1206	Std	Std			
1	R5	1K	Resistor, Chip, 1/16W, 1%	0603	Std	Std			
1	R6	0.005	Resistor, 5 milliOhm, 2W, 1%	2512	2.32276E+11	Phycomp			
1	R7	19.1K	Resistor, Chip, 1/16W, 1%	0603	Std	Std			
1	R8	24.9K	Resistor, Chip, 1/16W, 1%	0603	Std	Std			
1	R9	49.9	Resistor, Chip, 1/16W, 1%	0603	Std	Std			
1	R10	2.0K	Resistor, Chip, 1/16W, 1%	0603	Std	Std			
	R11	10	Resistor, Chip, 1/4W, 1%	1206	Std	Std			
1	TP1	VIN	Test Point, Red, Thru Hole Color Keyed	0.100 x 0.100 inch	5000	Keystone			
2	TP2	GND	Test Point, Black, Thru Hole Color Keyed	0.100 x 0.100 inch	5001	Keystone			
1	TP3	VOUT	Test Point, Red, Thru Hole Color Keyed	0.100 x 0.100 inch	5000	Keystone			

1	TP4	SW	Test Point, Red, Thru Hole Color Keyed	0.100 x 0.100 inch	5000	Keystone			
	TP5	GND	Test Point, Black, Thru Hole Color Keyed	0.100 x 0.100 inch	5001	Keystone			
2	TP7	5000	Test Point, Red, Thru Hole Color Keyed	0.100 x 0.100 inch	5000	Keystone			
	TP8	5000	Test Point, Red, Thru Hole Color Keyed	0.100 x 0.100 inch	5000	Keystone			
1	U1	TPS40210DGQ	IC, 4.5V-52V I/P, Current Mode Boost Controller	DGQ10	TPS40210DGQ	TI			
Notes:	Notes: 1. These assemblies are ESD sensitive, ESD precautions shall be observed.								
	2. These	assemblies must be	e clean and free from flux and all contaminants.						
	Use of	no clean flux is not	acceptable.						
	3. These	assemblies must co	omply with workmanship standards IPC-A-610 Class						
4. Ref designators marked with an asterisk ('**') cannot be substituted.									
	All othe	er components can	be substituted with equivalent MFG's components.						

IMPORTANT NOTICE FOR TI REFERENCE DESIGNS

Texas Instruments Incorporated ("TI") reference designs are solely intended to assist designers ("Buyers") who are developing systems that incorporate TI semiconductor products (also referred to herein as "components"). Buyer understands and agrees that Buyer remains responsible for using its independent analysis, evaluation and judgment in designing Buyer's systems and products.

TI reference designs have been created using standard laboratory conditions and engineering practices. TI has not conducted any testing other than that specifically described in the published documentation for a particular reference design. TI may make corrections, enhancements, improvements and other changes to its reference designs.

Buyers are authorized to use TI reference designs with the TI component(s) identified in each particular reference design and to modify the reference design in the development of their end products. HOWEVER, NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY THIRD PARTY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT, IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI REFERENCE DESIGNS ARE PROVIDED "AS IS". TI MAKES NO WARRANTIES OR REPRESENTATIONS WITH REGARD TO THE REFERENCE DESIGNS OR USE OF THE REFERENCE DESIGNS, EXPRESS, IMPLIED OR STATUTORY, INCLUDING ACCURACY OR COMPLETENESS. TI DISCLAIMS ANY WARRANTY OF TITLE AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, QUIET ENJOYMENT, QUIET POSSESSION, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS WITH REGARD TO TI REFERENCE DESIGNS OR USE THEREOF. TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY BUYERS AGAINST ANY THIRD PARTY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON A COMBINATION OF COMPONENTS PROVIDED IN A TI REFERENCE DESIGN. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, SPECIAL, INCIDENTAL, CONSEQUENTIAL OR INDIRECT DAMAGES, HOWEVER CAUSED, ON ANY THEORY OF LIABILITY AND WHETHER OR NOT TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES, ARISING IN ANY WAY OUT OF TI REFERENCE DESIGNS OR BUYER'S USE OF TI REFERENCE DESIGNS.

TI reserves the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques for TI components are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

Reproduction of significant portions of TI information in TI data books, data sheets or reference designs is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards that anticipate dangerous failures, monitor failures and their consequences, lessen the likelihood of dangerous failures and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in Buyer's safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed an agreement specifically governing such use.

Only those TI components that TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components that have *not* been so designated is solely at Buyer's risk, and Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.