PMP4489 REV E1 Bill of Materials



Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
C1	1	0.047uF	B32921C3473K	TDK	CAP, Film, 0.047 µF, 630 V, +/- 10%, TH	B32921 11mm
C2, C29	2	10uF	106CKE450MLU	Illinois Capacitor	CAP, AL, 10 µF, 450 V, +/- 20%, 33.157 ohm, TH	D10x20Lmm
C6	1	1000pF	GRM31A7U2J102JW31D	MuRata	CAP, CERM, 1000 pF, 630 V, +/- 5%, U2J, 1206	1206
C7	1	0.1uF	C0805C104K5RACAUTO	Kemet	CAP, CERM, 0.1 µF, 50 V, +/- 10%, X7R, AEC-Q200 Grade 0, 0805	0805
C8	1	1uF	C3216X7R1H105K	TDK	CAP, CERM, 1 µF, 50 V, +/- 10%, X7R, 1206	1206
C9	1	6800pF	GRM188R71H682KA01D	MuRata	CAP, CERM, 6800 pF, 50 V, +/- 10%, X7R, 0603	0603
C10, C11, C18	3	0.22uF	06033D224KAT2A	AVX	CAP, CERM, 0.22 μF, 25 V, +/- 10%, X5R, 0603	0603
C12	1	2200pF	C0805C222K2RAC	Kemet	CAP, CERM, 2200 pF, 200 V, +/- 10%, X7R, 0805	0805
C14, C28	2	470uF	RL80J471MDNASQKX	Nichicon	CAP, AL, 470 μF, 6.3 V, +/- 20%, 0.008 ohm, TH	D8xL8
C15	1	1uF	C1608X5R1E105K080AC	TDK	CAP, CERM, 1 µF, 25 V, +/- 10%, X5R, 0603	0603
C16	1	22pF	06035A220JAT2A	AVX	CAP, CERM, 22 pF, 50 V, +/- 5%, C0G/NP0, 0603	0603
C19, C20	2	0.1uF	06033D104KAT2A	AVX	CAP, CERM, 0.1 µF, 25 V, +/- 10%, X5R, 0603	0603
C21	1	10uF	C1206C106K3RACTU	Kemet	CAP, CERM, 10 µF, 25 V, +/- 10%, X7R, 1206_190	1206 190
C22	1	22uF	EKXG401ELL220MK20S	Chemi-Con	CAP, AL, 22 µF, 400 V, +/- 20%, TH	12.5x20mm
C23	1	150pF	C0603C151J5GACTU	Kemet	CAP, CERM, 150 pF, 50 V, +/- 5%, C0G/NP0, 0603	0603
C24, C25	2	390pF	GRM188R71H391KA01D	MuRata	CAP, CERM, 390 pF, 50 V, +/- 10%, X7R, 0603	0603
C26	1	2200pF	DE1E3KX222MA4BL01	MuRata	CAP, CERM, 2200 pF, 250 V, +/- 20%, E, Cap, 7x12x9 mm	Cap, 7x12x9 mm
C27	1	330pF	GRM188R72A331KA01D	MuRata	CAP, CERM, 330 pF, 100 V, +/- 10%, X7R, 0603	0603
D1	1	800V	3KBP08M-E4/45	Vishay-Semiconductor	Diode, Switching-Bridge, 800 V, 3 A, TH	KBPM
D2	1	600V	1N4007	Diodes Inc.	Diode, Standard Recovery Rectifier, 600 V, 1 A, PowerDI123	PowerDI123
D3	1	200V	BAS20HT1G	ON Semiconductor	Diode, Switching, 200 V, 0.2 A, AEC-Q101, SOD-323	SOD-323
D4	1	18V	MMSZ4705T1G	ON Semiconductor	Diode, Zener, 18 V, 500 mW, SOD-123	SOD-123
D7	1	100V	SS5P10-M3/86A	Vishay-Semiconductor	Diode, Schottky, 100 V, 5 A, TO-277A	TO-277A
D8	1	30V	BAT43W-7-F	Diodes Inc.	Diode, Schottky, 30 V, 0.2 A, SOD-123	SOD-123
D9	1	24V	BZT52C24T-7	Diodes Inc.	Diode, Zener, 24 V, 300 mW, SOD-523	SOD-523
D11	1	100V	1N4148-7-F	Diodes Inc.	Diode, Ultrafast, 100 V, 0.15 A, SOT-123	SOT-123
F1	1		39213150000	Littelfuse	Fuse, 3.15 A, 250 V, TH	8x8.5x4mm
J1	1		20-0000016-01	Lintes Technology	Connector, Receptacle, USB Type C, R/A, SMT	Connector, Receptacle, USB Type C, SMT
L1	1	4mH	744821240	Wurth Elektronik	Coupled inductor, 4 mH, 1.5 A, 0.14 ohm, +/- 30%, TH	15 x 18 x 7.5mm
L2	1	100uH	7447462101	Wurth Elektronik	Inductor, Unshielded Drum Core, Ferrite, 100 µH, 0.8 A, 0.457 ohm, TH	D6 x 8.5mm
Line, Neutral	2	Blue	5117	Keystone	Test Point, Miniature, Blue, TH	Blue Miniature Testpoint
Q1	1	650V	AOW25S65	AOS	MOSFET, N-CH, 650 V, 25 A, TO-262	TO-262
Q2	1	100V	CSD19533Q5A	Texas Instruments	MOSFET, N-CH, 100 V, 13 A, SON 5x6mm	SON 5x6mm
Q3	1	30V	CSD17579Q5A	Texas Instruments	MOSFET, N-CH, 30 V, 25 A, SON 5x6mm	SON 5x6mm
Q6	1	40 V	MMBT3904-7-F	Diodes Inc.	Transistor, NPN, 40 V, 0.2 A, SOT-23	SOT-23
R2, R54	2	100k	CRCW1206100KFKEA	Vishay-Dale	RES, 100 k, 1%, 0.25 W, 1206	1206
R4, R5	2	100	CRCW1206100RFKEA	Vishay-Dale	RES, 100, 1%, 0.25 W, 1206	1206
R7	1	22	CRCW080522R0JNEA	Vishay-Dale	RES, 22, 5%, 0.125 W, 0805	0805
R8	1	100k	CRCW0805100KJNEA	Vishay-Dale	RES, 100 k, 5%, 0.125 W, 0805	0805
R9	1	150k	CRCW0603150KJNEA	Vishay-Dale	RES, 150 k, 5%, 0.1 W, 0603	0603
R12	1	15.0k	CRCW060315K0FKEA	Vishay-Dale	RES, 15.0 k, 1%, 0.1 W, 0603	0603

Page 1 of 2

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
R16, R42	2	0	CRCW06030000Z0EA	Vishay-Dale	RES, 0, 5%, 0.1 W, 0603	0603
R17	1	470	CRCW0603470RJNEA	Vishay-Dale	RES, 470, 5%, 0.1 W, 0603	0603
R18, R51	2	0.68	ERJ-8RQFR68V	Panasonic	RES, 0.68, 1%, 0.25 W, 1206	1206
R19, R52	2	160k	CRCW0603160KJNEA	Vishay-Dale	RES, 160 k, 5%, 0.1 W, 0603	0603
R20	1	1.00k	CRCW06031K00FKEA	Vishay-Dale	RES, 1.00 k, 1%, 0.1 W, 0603	0603
R21	1	2.00k	CRCW06032K00FKEA	Vishay-Dale	RES, 2.00 k, 1%, 0.1 W, 0603	0603
R22, R23, R24, R35	4	10.0k	CRCW060310K0FKEA	Vishay-Dale	RES, 10.0 k, 1%, 0.1 W, 0603	0603
R25	1	8.25	CRCW06038R25FKEA	Vishay-Dale	RES, 8.25, 1%, 0.1 W, 0603	0603
R26	1	7.87k	RC0603FR-077K87L	Yageo America	RES, 7.87 k, 1%, 0.1 W, 0603	0603
R33	1	10.0	CRCW120610R0FKEA	Vishay-Dale	RES, 10.0, 1%, 0.25 W, 1206	1206
R34	1	330k	RC0603FR-07330KL	Yageo America	RES, 330 k, 1%, 0.1 W, 0603	0603
R36	1	20.0k	CRCW060320K0FKEA	Vishay-Dale	RES, 20.0 k, 1%, 0.1 W, 0603	0603
R37, R40	2	1.00	CRCW06031R00FKEA	Vishay-Dale	RES, 1.00, 1%, 0.1 W, 0603	0603
R38	1	300k	CRCW0603300KFKEA	Vishay-Dale	RES, 300 k, 1%, 0.1 W, 0603	0603
R39	1	47.0k	RC0603FR-0747KL	Yageo America	RES, 47.0 k, 1%, 0.1 W, 0603	0603
R41	1	200k	CRCW0603200KFKEA	Vishay-Dale	RES, 200 k, 1%, 0.1 W, 0603	0603
R43	1	75.0	CRCW080575R0FKEA	Vishay-Dale	RES, 75.0, 1%, 0.125 W, 0805	0805
R44	1	0.005	WSL12065L000FEA	Vishay-Dale	RES, 0.005, 1%, 0.25 W, 1206	1206
R45, R46	2	100	CRCW0603100RFKEA	Vishay-Dale	RES, 100, 1%, 0.1 W, 0603	0603
R47	1	1.00Meg	CRCW06031M00FKEA	Vishay-Dale	RES, 1.00 M, 1%, 0.1 W, 0603	0603
R48	1	220	RC0603FR-07220RL	Yageo America	RES, 220, 1%, 0.1 W, 0603	0603
R55, R56	2	1.00Meg	ERJ-8ENF1004V	Panasonic	RES, 1.00 M, 1%, 0.25 W, 1206	1206
R57, R58	2	0	CRCW08050000Z0EA	Vishay-Dale	RES, 0, 5%, 0.125 W, 0805	0805
R59	1	10k	CRCW080510K0JNEA	Vishay-Dale	RES, 10 k, 5%, 0.125 W, 0805	0805
RT1	1		NA	NA	NA	NA
T1	1	200uH	750343141	Wurth Elektronik	RM8 Core	
U1	1		UCC28740DR	Texas Instruments	Constant-Voltage, Constant-Current Flyback Controller Using Opto- Coupler Feedback, D0007A	D0007A
U2	1		UCC24630DBVR	Texas Instruments	SYNCRONOUS RECTIFIER CONTROLLER WITH LOW POWER STANDBY, DBV0006A	DBV0006A
U3	1		TPS25740RGE	Texas Instruments	USB Power Delivery (PD) Provider-Only and Type-C Downward Facing Port (DFP) Port Controller, RGE0024F	RGE0024F
U5	1		TL431AIDBZR	Texas Instruments	Adjustable Precision Shunt Regulator, 34 ppm / degC, 100 mA, -40 to 85 degC, 3-pin SOT-23 (DBZ), Green (RoHS & no Sb/Br)	DBZ0003A
U7	1		FOD817AS	Fairchild Semiconductor	Optocoupler, 5 kV, 80-160% CTR, SMT	DIP-4L Gullwing

IMPORTANT NOTICE FOR TI REFERENCE DESIGNS

Texas Instruments Incorporated ('TI") reference designs are solely intended to assist designers ("Designer(s)") who are developing systems that incorporate TI products. TI has not conducted any testing other than that specifically described in the published documentation for a particular reference design.

Tl's provision of reference designs and any other technical, applications or design advice, quality characterization, reliability data or other information or services does not expand or otherwise alter Tl's applicable published warranties or warranty disclaimers for Tl products, and no additional obligations or liabilities arise from Tl providing such reference designs or other items.

TI reserves the right to make corrections, enhancements, improvements and other changes to its reference designs and other items.

Designer understands and agrees that Designer remains responsible for using its independent analysis, evaluation and judgment in designing Designer's systems and products, and has full and exclusive responsibility to assure the safety of its products and compliance of its products (and of all TI products used in or for such Designer's products) with all applicable regulations, laws and other applicable requirements. Designer represents that, with respect to its applications, it has all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. Designer agrees that prior to using or distributing any systems that include TI products, Designer will thoroughly test such systems and the functionality of such TI products as used in such systems. Designer may not use any TI products in life-critical medical equipment unless authorized officers of the parties have executed a special contract specifically governing such use. Life-critical medical equipment is medical equipment where failure of such equipment would cause serious bodily injury or death (e.g., life support, pacemakers, defibrillators, heart pumps, neurostimulators, and implantables). Such equipment includes, without limitation, all medical devices identified by the U.S. Food and Drug Administration as Class III devices and equivalent classifications outside the U.S.

Designers are authorized to use, copy and modify any individual TI reference design only in connection with the development of end products that include the TI product(s) identified in that reference design. HOWEVER, NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of the reference design or other items described above may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI REFERENCE DESIGNS AND OTHER ITEMS DESCRIBED ABOVE ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING THE REFERENCE DESIGNS OR USE OF THE REFERENCE DESIGNS, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY DESIGNERS AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS AS DESCRIBED IN A TI REFERENCE DESIGN OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF THE REFERENCE DESIGNS OR USE OF THE REFERENCE DESIGNS, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

Tl's standard terms of sale for semiconductor products (http://www.ti.com/sc/docs/stdterms.htm) apply to the sale of packaged integrated circuit products. Additional terms may apply to the use or sale of other types of TI products and services.

Designer will fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of Designer's non-compliance with the terms and provisions of this Notice.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2016, Texas Instruments Incorporated