Filename: PMP30224RevB - BoM.xls

Variant: None

Generated: 4/6/2017 11:50:53 AM
TID #: <Parameter TID not found>

## PMP30224 REV B Bill of Materials



Item #	Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
1	C1, C12	2	47uF	EEE-FK1H470P	Panasonic	CAP, AL, 47 µF, 50 V, +/- 20%, 0.68 ohm, AEC-Q200 Grade 2, SMD	SMT Radial E
2	C2, C13	2	4.7uF	GRM319R61H475KA12	MuRata	CAP, CERM, 4.7 µF, 50 V, +/- 10%, X5R, 1206	1206
3	C3, C9,	4	0.1uF	GRM188R71H104KA93D	MuRata	CAP, CERM, 0.1 µF, 50 V, +/- 10%, X7R, 0603	0603
	C10, C14						
4	C4, C5,	4	22uF	GRM32ER61C226ME20L	MuRata	CAP, CERM, 22 μF, 16 V, +/- 20%, X5R, 1210	1210
	C15, C16						
5	C6, C17	2	220pF	GRM188R71H221KA01D	MuRata	CAP, CERM, 220 pF, 50 V, +/- 10%, X7R, 0603	0603
6	C8, C18	2	0.01uF	GRM188R71H103KA01D	MuRata	CAP, CERM, 0.01 µF, 50 V, +/- 10%, X7R, 0603	0603
7	C11, C23	2	0.22uF		MuRata	CAP, CERM, 0.22 μF, 25 V, +/- 10%, X7R, 0603	0603
8	C20	1	2700pF		MuRata	CAP, CERM, 2700 pF, 50 V, +/- 10%, X7R, 0603	0603
9	C21, C22	2	1uF	GRM185R61C105KE44D	MuRata	CAP, CERM, 1 µF, 16 V, +/- 10%, X5R, 0603	0603
10	D1, D2	2	50V	SS3P5L	Vishay-Semiconductor	Diode, Schottky, 50 V, 3 A, TO-277A	TO-277A
11	FID1, FID2, FID3, FID4	4		N/A	N/A	Fiducial mark. There is nothing to buy or mount.	N/A
12	J1, J2	2		61300211121	Wurth Elektronik	Header, 2.54 mm, 2x1, Gold, TH	Header, 2.54mm, 2x1, TH
13	L1, L2	2	22uH	XAL6060-223MEB	Coilcraft	Inductor, Shielded, Composite, 22 µH, 5.6 A, 0.06 ohm, SMD	IND_6.4x6.1x6.6
14	P1, P2, P3,	6		ED555/2DS	On-Shore Technology	Terminal Block, 3.5mm Pitch, 2x1, TH	7.0x8.2x6.5mm
	P4, P5, P6						
15	R1	1	147k	CRCW0603147KFKEA	Vishay-Dale	RES, 147 k, 1%, 0.1 W, 0603	0603
16	R2, R10, R13	3	52.3k	CRCW060352K3FKEA	Vishay-Dale	RES, 52.3 k, 1%, 0.1 W, 0603	0603
17	R3	1	51.1k	CRCW060351K1FKEA	Vishay-Dale	RES, 51.1 k, 1%, 0.1 W, 0603	0603
18	R4	1	174k	CRCW0603174KFKEA	Vishay-Dale	RES, 174 k, 1%, 0.1 W, 0603	0603
19	R5, R8, R12, R15	4	10.0k	CRCW060310K0FKEA	Vishay-Dale	RES, 10.0 k, 1%, 0.1 W, 0603	0603
20	R6	1	12.7k	CRCW060312K7FKEA	Vishay-Dale	RES, 12.7 k, 1%, 0.1 W, 0603	0603
21	R7, R14	2	40.2k	CRCW060340K2FKEA	Vishay-Dale	RES, 40.2 k, 1%, 0.1 W, 0603	0603
22	R9	1	165k	CRCW0603165KFKEA	Vishay-Dale	RES, 165 k, 1%, 0.1 W, 0603	0603
23	R11	1	69.8k	CRCW060369K8FKEA	Vishay-Dale	RES, 69.8 k, 1%, 0.1 W, 0603	0603
24	TP1, TP3, TP5, TP7	4		5000	Keystone	Test Point, Miniature, Red, TH	Red Miniature Testpoint
25	TP2, TP4, TP6, TP8	4		5001	Keystone	Test Point, Miniature, Black, TH	Black Miniature Testpoint
26	U1	1		TPS54540DDA	Texas Instruments	42V, 5A, Step-Down Regulator with Integrated High Side MOSFET, DDA0008E (SOIC-8)	DDA0008E
27	U2	1		TLV71318PDBVR	Texas Instruments	150-mA, Low-Dropout Regulator with Foldback Current Limit for Portable Devices, DBV0005A (SOT-5)	DBV0005A
28	U3	1		TPS54531DDAR	Texas Instruments	3.5V to 28V Input, 5A, 570kHz Step-Down Converter with Eco-mode, DDA0008E (SOIC-8)	DDA0008E
29	U4	1		TLV70018DDCR	Texas Instruments	Single Output LDO, 200 mA, Fixed 1.8 V Output, 2 to 5.5 V Input, with Low IQ, 5-pin SOT (DDC), -40 to 125 degC, Green (RoHS & no Sb/Br)	DDC0005A

## IMPORTANT NOTICE FOR TI DESIGN INFORMATION AND RESOURCES

Texas Instruments Incorporated ('TI") technical, application or other design advice, services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using any particular TI Resource in any way, you (individually or, if you are acting on behalf of a company, your company) agree to use it solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources.

You understand and agree that you remain responsible for using your independent analysis, evaluation and judgment in designing your applications and that you have full and exclusive responsibility to assure the safety of your applications and compliance of your applications (and of all TI products used in or for your applications) with all applicable regulations, laws and other applicable requirements. You represent that, with respect to your applications, you have all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. You agree that prior to using or distributing any applications that include TI products, you will thoroughly test such applications and the functionality of such TI products as used in such applications. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

You are authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING TI RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY YOU AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

You agree to fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of your non-compliance with the terms and provisions of this Notice.

This Notice applies to TI Resources. Additional terms apply to the use and purchase of certain types of materials, TI products and services. These include; without limitation, TI's standard terms for semiconductor products <a href="http://www.ti.com/sc/docs/stdterms.htm">http://www.ti.com/sc/docs/stdterms.htm</a>), evaluation modules, and samples (<a href="http://www.ti.com/sc/docs/sampterms.htm">http://www.ti.com/sc/docs/sampterms.htm</a>).

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2017, Texas Instruments Incorporated