

TIDA-01465 REV E1 Bill of Materials

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
C1, C31	2	10uF	C1608X5R1A106M	TDK	CAP, CERM, 10uF, 10V, +/-20%, X5R, 0603	0603
C2, C9, C30, C32, C33, C34	6	0.1uF	GRM155R71C104JA88D	Murata Electronics North Ame	CAP CER 0.1UF 16V 5% X7R 0402	0402
C3	1	2.2uF	C0603C225K8PACTU	Kemet	CAP, CERM, 2.2uF, 10V, +/-10%, X5R, 0603	0603
C4, C5	2	0.01uF	C1608C0G1E103J	TDK	CAP, CERM, 0.01uF, 25V, +/-5%, C0G/NP0, 0603	0603
C6	1	0.01uF	C1005X7R1C103K	TDK	CAP, CERM, 0.01 uF, 16 V, +/- 10%, X7R, 0402	0402
C7, C10, C15, C17	4	39pF	06035A390JAT2A	AVX	CAP, CERM, 39 pF, 50 V, +/- 5%, C0G/NP0, 0603	0603
C8	1	22uF	C2012X5R1C226K125AC	TDK	CAP, CERM, 22uF, 16V, +/-10%, X5R, 0805	0805
C11, C12, C13, C14, C16, C18, C19, C20, C21, C23, C35, C36, C37, C38, C39, C41, C42, C44	18	18pF	GRM1885C2A180JA01D	MuRata	CAP, CERM, 18pF, 100V, +/-5%, C0G/NP0, 0603	0603
C25	1	1uF	GRM155R61A105KE15D	MuRata	CAP, CERM, 1uF, 10V, +/-10%, X5R, 0402	0402
C26, C28	2	0.22uF	08053C224JAT2A	AVX	CAP, CERM, 0.22 uF, 25 V, +/- 5%, X7R, 0805	0805
C27	1	2200pF	C0603X222K5RACTU	Kemet	CAP, CERM, 2200pF, 50V, +/-10%, X7R, 0603	0603
C29	1	220PF	C1005C0G1H221F050BA	TDK Corporation	CAP CER 220PF 50V 1% NP0 0402	0402
D1	1	5.6V	MMSZ5232B-7-F	Diodes Inc.	Diode, Zener, 5.6V, 500mW, SOD-123	SOD-123
D2, D4, D7	3	Green	LG L29K-G2J1-24-Z	OSRAM	LED, Green, SMD	1.7x0.65x0.8mm
D3, D5, D6	3	Red	SML-LX0603SRW-TR	Lumex	LED, Super Red, SMD	LED, 1.6x.6x.8mm
D8	1	Yellow	19-21UYC/S530-A4/TR8	Everlight	LED, Yellow, SMD	0.8x1.6mm
GND1, GND2, GND3	3	SMT	5015	Keystone	Test Point, Miniature, SMT	Testpoint_Keystone_Minature
J1	1		ZX62R-B-5P(30)	Hirose Electric Co. Ltd.	Connector, Receptacle, Micro-USB Type B, SMT	Connector USB Mini B
J2	1		61300411121	Würth Elektronik	Header, 2.54 mm, 4x1, Gold, TH	Header, 2.54mm, 4x1, TH
J3	1		TSW-107-07-G-D	Samtec	Header, 100mil, 7x2, Gold, TH	7x2 Header
J4, J5, J6, J7	4	2x1	1727010	Phoenix Contact	Conn Term Block, 2POS, 3.81mm, TH	2POS Terminal Block
J8, J9, J10	3		TSW-102-07-G-S	Samtec, Inc.	Header, TH, 100mil, 2x1, Gold plated, 230 mil above insulator	TSW-102-07-G-S
L10	1	10uH	VLS201610ET-100M	TDK	Inductor, Shielded, Ferrite, 10 uH, 0.4 A, 1.38 ohm, SMD	2.0x0.95x1.6mm
R1, R2, R3, R4, R5, R21, R25	7	1.0k	CRCW04021K00JNED	Vishay-Dale	RES, 1.0k ohm, 5%, 0.063W, 0402	0402
R6	1	1.5K	CRCW04021K50JNED	Vishay Dale	RES 1.5K OHM 1/16W 5% 0402 SMD	0402
R7, R17	2	33	CRCW060333R0JNEA	Vishay-Dale	RES, 33 ohm, 5%, 0.1W, 0603	0603
R8, R9	2	10.0	CRCW040210R0FKED	Vishay-Dale	RES, 10.0, 1%, 0.063 W, 0402	0402
R10, R16, R18	3	0	CRCW06030000Z0EA	Vishay-Dale	RES, 0 ohm, 5%, 0.1W, 0603	0603
R12, R13	2	4.70k	RC0603FR-074K7L	Yageo America	RES, 4.70k ohm, 1%, 0.1W, 0603	0603
R15	1	1M	RC0402JR-071ML	Yageo	RES, 1M ohm, 5%, 0.063W, 0402	0402
R19, R20, R23, R24, R26, R27, R28, R33	8	0	CRCW08050000Z0EA	Vishay-Dale	RES, 0 ohm, 5%, 0.125W, 0805	0805

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
R29	1	33k	CRCW040233K0JNED	Vishay-Dale	RES, 33k ohm, 5%, 0.063W, 0402	0402
U1	1		FDC2214RGHR	Texas Instruments	Noise-immune Capacitive Sensing Solution for Proximity Sensing, RGH0016A (WQFN-16)	RGH0016A
U2	1		LP2985AIM5-3.3/NOPB	Texas Instruments	Micropower 150 mA Low-Noise Ultra Low-Dropout Regulator, 5-pin SOT-23, Pb-Free	MF05A
U3	1		TPD2E001DRLR	Texas Instruments	Low-Capacitance + / - 15 kV ESD-Protection Array for High-Speed Data Interfaces, 2 Channels, -40 to +85 degC, 5-pin SOT (DRL), Green (RoHS & no Sb/Br)	DRL0005A
U4	1		TPL0401A-10DCKR	Texas Instruments	128 TAPS Single Channel Digital Potentiometer with I2C Interface, DCK0006A (SOT-6)	DCK0006A
U5	1		MSP430F5528IRGCR	Texas Instruments	Mixed Signal MicroController, RGC0064B	RGC0064B
Y1	1		ABM8-24.000MHZ-B2-T	Abracon Corporation	Crystal, 24.000MHz, 18pF, SMD	3.2x0.8x2.5mm
Y2	1		625L3C040M00000	CTS Electrocomponents	OSC, 40 MHz, 3.3 V, SMD	2.5x1x2.5mm

IMPORTANT NOTICE FOR TI DESIGN INFORMATION AND RESOURCES

Texas Instruments Incorporated ("TI") technical, application or other design advice, services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using any particular TI Resource in any way, you (individually or, if you are acting on behalf of a company, your company) agree to use it solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources.

You understand and agree that you remain responsible for using your independent analysis, evaluation and judgment in designing your applications and that you have full and exclusive responsibility to assure the safety of your applications and compliance of your applications (and of all TI products used in or for your applications) with all applicable regulations, laws and other applicable requirements. You represent that, with respect to your applications, you have all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. You agree that prior to using or distributing any applications that include TI products, you will thoroughly test such applications and the functionality of such TI products as used in such applications. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

You are authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING TI RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY YOU AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

You agree to fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of your non-compliance with the terms and provisions of this Notice.

This Notice applies to TI Resources. Additional terms apply to the use and purchase of certain types of materials, TI products and services. These include; without limitation, TI's standard terms for semiconductor products (<http://www.ti.com/sc/docs/stdterms.htm>), [evaluation modules](#), and [samples](http://www.ti.com/sc/docs/sampterm.htm) (<http://www.ti.com/sc/docs/sampterm.htm>).

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2017, Texas Instruments Incorporated