

001						
6/19/2017 5:02:06 PM						
N/A						
PMP20981 REV A Bill of Materials						
<b>Designator</b>	<b>Quantity</b>	<b>Value</b>	<b>PartNumber</b>	<b>Manufacturer</b>	<b>Description</b>	<b>PackageReference</b>
C15, C16, C21	3	100pF	GRM1885C1H101JA01D	MuRata	CAP, CERM, 100 pF, 50 V,+/- 5%, C0G/NP0, 0603	0603
C24	1	220pF	GRM1885C1H221JA01D	MuRata	CAP, CERM, 220 pF, 50 V,+/- 5%, C0G/NP0, 0603	0603
C31, C32, C33, C34	4	0.01uF	GRM188R72A103KA01D	MuRata	CAP, CERM, 0.01 µF, 100 V,+/- 10%, X7R, 0603	0603
C23	1	0.027uF	GRM188R71H273KA61D	MuRata	CAP, CERM, 0.027uF, 50V, +/-10%, X7R, 0603	0603
C22, C25, C26, C27, C28	5	0.1uF	GRM188R71H104KA93D	MuRata	CAP, CERM, 0.1 µF, 50 V,+/- 10%, X7R, 0603	0603
C17, C19	2	0.22uF	C1608X7R1E224K080AC	TDK	CAP, CERM, 0.22 µF, 25 V,+/- 10%, X7R, 0603	0603
C18	1	1uF	C1608X7R1C105K080AC	TDK	CAP, CERM, 1 µF, 16 V,+/- 10%, X7R, 0603	0603
C13	1	100pF	GRM21A5C2E101JW01D	MuRata	CAP, CERM, 100pF, 250V, +/-5%, C0G/NP0, 0805	0805
C3	1	0.01uF	GRM21BR72E103KW03L	MuRata	CAP, CERM, 0.01 µF, 250 V,+/- 10%, X7R, 0805	0805
C20	1	0.047uF	C2012X7R2A473K125AA	TDK	CAP, CERM, 0.047 µF, 100 V,+/- 10%, X7R, 0805	0805
C14, C29	2	0.1uF	C2012X7R2A104K125AA	TDK	CAP, CERM, 0.1 µF, 100 V,+/- 10%, X7R, 0805	0805
C7	1	0.22uF	C2012X7R1H224K125AA	TDK	CAP, CERM, 0.22 µF, 50 V,+/- 10%, X7R, 0805	0805
C30	1	0.22uF	GRM31MR72A224KA01L	MuRata	CAP, CERM, 0.22uF, 100V, +/-10%, X7R, 1206	1206
C5, C6	2	10uF	GRM32DR71E106KA12L	MuRata	CAP, CERM, 10 µF, 25 V,+/- 10%, X7R, 1210	1210
C9, C10, C11, C12	4	2.2uF	GRM32ER72A225KA35L	MuRata	CAP, CERM, 2.2 µF, 100 V,+/- 10%, X7R, 1210	1210
C35, C36	2	1000pF	GR443QR73D102KW01L	MuRata	CAP, CERM, 1000 pF, 2000 V,+/- 10%, X7R, 1812	1812
C1, C2	2	2200pF	C4532X7R3D222K130KA	TDK	CAP, CERM, 2200 pF, 2000 V,+/- 10%, X7R, 1812	1812
C4	1	100uF	EEE-FK1E101P	Panasonic	CAP, AL, 100uF, 25V, +/-20%, 0.26 ohm, SMD	SMT Radial E
C8	1	22uF	EEE-FK1J220P	Panasonic	CAP, AL, 22 µF, 63 V, +/- 20%, 1.2 ohm, AEC-Q200 Grade 2, SMD	SMT Radial E
D1	1		ES1D-13-F	Diodes Inc.	Diode, Ultrafast, 200 V, 1 A, SMA	SMA
D2	1		ES2D-13-F	Diodes Inc.	Diode, Ultrafast, 200 V, 2 A, SMB	SMB
D3	1		ES3AB-13-F	Diodes Inc.	Diode, Superfast Rectifier, 50 V, 3 A, SMB	SMB
D4	1	9.1V	BZX84C9V1LT1G	ON Semiconductor	Diode, Zener, 9.1V, 225mW, SOT-23	SOT-23
D5, D6	2		MMDL914-TP	Micro Commercial Component	Diode, Switching, 100 V, 0.2 A, SOD-323	SOD-323
D7	1	20V	BZX84C20LT1G	ON Semiconductor	Diode, Zener, 20V, 225mW, SOT-23	SOT-23
D8	1	58V	SMAJ58A-13-F	Diodes Inc.	Diode, TVS, Uni, 58 V, SMA	SMA
D9	1	Green	LTST-C190GKT	Lite-On	LED, Green, SMD	1.6x0.8x0.8mm
J1, J2	2		ED555/2DS	On-Shore Technology	Terminal Block, 3.5mm Pitch, 2x1, TH	7.0x8.2x6.5mm
J3, J4	2		1-406541-1	TE Connectivity	RJ-45, No LED, tab up, R/A, TH	16.26x14.54x15.75
L1	1	1uH	XAL4020-102MEB	Coilcraft	Inductor, Shielded, Composite, 1 µH, 8.75 A, 0.01 ohm, SMD	4x2.1x4mm
L2	1	1uH	LPS4012-102NLB	Coilcraft	Inductor, Shielded Drum Core, Ferrite, 1 µH, 2.4 A, 0.06 ohm, SMD	LPS4012
L3	1	60uH	H6502NL	Pulse Engineering	Coupled inductor, 60 µH, 0.25 ohm, SMD	9.27x5.5x6.22mm
Q1	1		CSD18504Q5A	Texas Instruments	MOSFET, N-CH, 40 V, 15 A, DQJ0008A (VSONP-8)	DQJ0008A
R14	1	0	ERJ-3GEY0R00V	Panasonic	RES, 0 ohm, 5%, 0.1W, 0603	0603
R6, R10	2	10	CRCW060310R0JNEA	Vishay-Dale	RES, 10, 5%, 0.1 W, 0603	0603
R25, R26, R27, R29, R30, R31, R32, R33	8	75.0	CRCW060375R0FKEA	Vishay-Dale	RES, 75.0 ohm, 1%, 0.1W, 0603	0603
R13	1	750	CRCW0603750RFKEA	Vishay-Dale	RES, 750 ohm, 1%, 0.1W, 0603	0603
R9, R17, R22, R23	4	1.00k	CRCW06031K00FKEA	Vishay-Dale	RES, 1.00k ohm, 1%, 0.1W, 0603	0603
R20	1	2.74k	CRCW06032K74FKEA	Vishay-Dale	RES, 2.74k ohm, 1%, 0.1W, 0603	0603
R12	1	3.32k	CRCW06033K32FKEA	Vishay-Dale	RES, 3.32k ohm, 1%, 0.1W, 0603	0603
R18	1	4.99k	CRCW06034K99FKEA	Vishay-Dale	RES, 4.99k ohm, 1%, 0.1W, 0603	0603
R19	1	10.0k	CRCW060310K0FKEA	Vishay-Dale	RES, 10.0k ohm, 1%, 0.1W, 0603	0603
R7	1	23.7k	CRCW060323K7FKEA	Vishay-Dale	RES, 23.7k ohm, 1%, 0.1W, 0603	0603

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
R16, R28	2	49.9k	CRCW060349K9FKEA	Vishay-Dale	RES, 49.9k ohm, 1%, 0.1W, 0603	0603
R15	1	82.5k	CRCW060382K5FKEA	Vishay-Dale	RES, 82.5 k, 1%, 0.1 W, 0603	0603
R5, R21	2	100k	CRCW0603100KFKEA	Vishay-Dale	RES, 100 k, 1%, 0.1 W, 0603	0603
R24	1	124k	CRCW0603124KFKEA	Vishay-Dale	RES, 124k ohm, 1%, 0.1W, 0603	0603
R2	1	24k	CRCW080524K0JNEA	Vishay-Dale	RES, 24k ohm, 5%, 0.125W, 0805	0805
R3	1	0	ERJ-8GEY0R00V	Panasonic	RES, 0 ohm, 5%, 0.25W, 1206	1206
R11	1	0.015	CSRN2010FK15L0	Stackpole Electronics Inc	RES, 0.015, 1%, 1 W, 2010	2010
R4	1	200	CRCW2010200RJNEF	Vishay-Dale	RES, 200, 5%, 0.75 W, AEC-Q200 Grade 0, 2010	2010
R8	1	5.6k	CRCW20105K60JNEF	Vishay-Dale	RES, 5.6 k, 5%, 0.75 W, AEC-Q200 Grade 0, 2010	2010
R1	1	27k	CRCW201027K0JNEF	Vishay-Dale	RES, 27 k, 5%, 0.75 W, AEC-Q200 Grade 0, 2010	2010
T1	1		PA4191NL	Pulse Engineering	Transformer, 10 uH, SMT	SMD, 10-Leads, Body 13.44 x 13.44 mm, Pitch 2.5 mm
T2	1		H6062FNLT	Pulse Engineering	Transformer Module, 350 uH, Gigabit, 1 port, POE, 1:1, SMT	17.5x15.24mm
TP1	1	White	5002	Keystone	Test Point, Miniature, White, TH	Keystone5002
U2	1		HMHA2801A	Fairchild Semiconductor	Optocoupler, 3.75 kV, 80-160% CTR, SMT	Mini Flat Package
U1	1		LM3481MM/NOPB	Texas Instruments	High Efficiency Low-Side N-Channel Controller for Switching Regulators, 10-pin MSOP	MUB10A
U3	1		TL431AIDBZR	Texas Instruments	Adjustable Precision Shunt Regulator, 34 ppm / degC, 100 mA, -40 to 85 degC, 3-pin SOT-23 (DBZ), Green (RoHS & no Sb/Br)	DBZ0003A
U4	1		TPS2384PAPR	Texas Instruments	Quad Ethernet Power Sourcing Equipment Power Manager, -40 to 125 degC, 64-pin QFP (PAP64), Green (RoHS & no Sb/Br)	PAP0064F

## IMPORTANT NOTICE FOR TI DESIGN INFORMATION AND RESOURCES

Texas Instruments Incorporated ("TI") technical, application or other design advice, services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using any particular TI Resource in any way, you (individually or, if you are acting on behalf of a company, your company) agree to use it solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources.

You understand and agree that you remain responsible for using your independent analysis, evaluation and judgment in designing your applications and that you have full and exclusive responsibility to assure the safety of your applications and compliance of your applications (and of all TI products used in or for your applications) with all applicable regulations, laws and other applicable requirements. You represent that, with respect to your applications, you have all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. You agree that prior to using or distributing any applications that include TI products, you will thoroughly test such applications and the functionality of such TI products as used in such applications. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

You are authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING TI RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY YOU AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

You agree to fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of your non-compliance with the terms and provisions of this Notice.

This Notice applies to TI Resources. Additional terms apply to the use and purchase of certain types of materials, TI products and services. These include; without limitation, TI's standard terms for semiconductor products (<http://www.ti.com/sc/docs/stdterms.htm>), [evaluation modules](#), and [samples](http://www.ti.com/sc/docs/sampterm.htm) (<http://www.ti.com/sc/docs/sampterm.htm>).

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265  
Copyright © 2017, Texas Instruments Incorporated