PMP7466REVA-BOM.xls

Count	RefDes	Value	Description	Size	Manufacture Part #
0	C1,C2,C4,C5	100PF	CAP_SM-CE,100PF,50V,5%,0402_PB-FR	C0402	STD
3	C3,C12,C14	1UF	CAP_SM-CE,1UF,16V,10%,0603_X5R_PB-FR	C0603	STD
2	C6,C7	1800PF	CAP_SM-CE,1800PF,25V,5%,0402_X7R	C0402	STD
2	C8,C10	180PF	CAP_SM-CE,180PF,50V,5%,0402_A-TEMP_PB-FR	C0402	STD
1	C9	2200PF	CAP_SM-CE,2200PF,25V,10%,0402	C0402	STD
1	C11	2700PF	CAP_SM-CE,2700PF,16V,10%,0402_X7R	C0402	STD
	C16,C17,C19,C20,				
6	C21,C22	22UF	CAP_SM-CE,22UF,16V,20%,1210_X5R_PB-FR	C1210	GRM32ER61C226ME20B
1	C18	10UF	CAP_SM-CE,10UF,10V,10%,0805_X5R_PB-FR	C0805	STD
2	C23,C24	0.22UF	CAP_SM-CE,0.22UF,16V,10%,0402_X5R_PB-FR	C0402	STD
	C25,C26,C29,C30,				
6	C35,C36	0.1UF	CAP_SM-CE,0.1UF,10V,10%,0402_X5R_PB-FR	C0402	STD
4	C31,C32,C33,C34	100UF	CAP_SM-CE,100UF,6.3V,20%,1210_X5R_PB-FR	C1210	GRM32ER60J107ME20K
2	C37,C38	1000PF	CAP_SM-CE,1000PF,50V,10%,0402_X7R_PB-FR	C0402	STD
0	C43,C44	1000PF	CAP_SM-CE,1000PF,50V,10%,0603_PB-FR	C0603	STD
	C101,C102,C103,				
4	C104	47UF	PCAP_SM-TA,47UF,16V,20%,7343_LOW_ESR_PB-FR	C7343	16TQC47M
	C105,C106,C107,				
6	C108,C109,C110	470UF	PCAP_SM-TA,470UF,4V,20%,2816_GSM_PREFRD	C7343	4TPF470ML
	C111,C112,C113,				
6	C114,C115,C116	470UF	PCAP_SM-TA,470UF,6.3V,20%,2816_LOW_ESR_PB-FR	C7343	T530X477M06ATE010
1	C117	470UF	PCAP_SM-AL,470UF,16V,20%,8MMD_10.8MML	C3333	16SVPE470M
2	J1,J2		CON1X3_F-ST,NONE,AMP_A-1JA,COAX_AMC_PB-FR	CON-3	A-1JA-CR
2	L1,L2	0.47UH	IND_PWR_SM-0.47UH,20%,23A,PA0515.471NLT	L4444	PA0515-321NL
1	P1		HDR1X2_M-ST,NONE,TSW-102-08-G-S	CON-2	TSW-102-08-G-S
1	P2		HDR1X3_M-ST,NONE,MOLEX_22-28-4036	CON-3	TSW-103-08-G-S
3	P3,P4,P5		PWR4_M-ST,MOLEX_15-24-4345,0.200C	CON-4	EDZ350
2	Q1,Q2		DUAL_NCH_PWRBLK9_SON8-NONE,CSD87350Q5D	QFN-8	CSD87350Q5D

PMP7466REVA-BOM.xls

2	Q3,Q4		NPN_SOT_BCE-NONE,MMBT3904SL	SOT923F	MMBT3904SL
0	R1,R2,R3,R4	100K	RES_SM-TF,100K,0.063W,1%,0402_PB-FR	R0402	STD
0	R5,R33	0	RES_SM-TF,0,0.063W,5%,0402_PBFREE	R0402	STD
2	R6,R8	10	RES_SM-TF,10,0.063W,1%,0402_PB-FR	R0402	STD
2	R7,R9	0	RES_SM-TF,0,0.063W,5%,0402_PBFREE	R0402	STD
2	R10,R15	10K	RES_SM-TF,10K,0.063W,0.1%,0402_25PPM_PB-FR	R0402	STD
1	R11	6.65K	RES_SM-TF,6.65K,0.063W,0.1%,0402_RG-S	R0402	STD
1	R12	66.5K	RES_SM-TF,66.5K,0.063W,1%,0402_PB-FR	R0402	STD
2	R13,R14	1	RES_SM-TF,1,0.063W,1%,0402_PB-FR	R0402	STD
1	R16	3.16K	RES_SM-TF,3.16K,0.063W,0.1%,THIN_0402_PB_FR	R0402	STD
2	R17,R18	1.62K	RES_SM-TF,1.62K,0.063W,1%,0402	R0402	STD
1	R19	10K	RES_SM-TF,10K,0.063W,1%,0402	R0402	STD
1	R20	7.68K	RES_SM-TF,7.68K,0.063W,1%,0402_PB-FR	R0402	STD
2	R21,R22	2.2	RES_SM-TF,2.2,0.063W,5%,0402	R0402	STD
2	R23,R24	49.9	RES_SM-TF,49.9,0.063W,1%,0402_PB-FR	R0402	STD
2	R25,R26	4.99K	RES_SM-TKF,4.99K,0.063W,1%,0402	R0402	STD
0	R27,R28	3.57K	RES_SM-TF,3.57K,0.063W,1%,0402	R0402	STD
2	R29,R30	36.5K	RES_SM-TF,36.5K,0.063W,1%,0402_PB-FR	R0402	STD
2	R31,R32	0	RES_SM-TF,0,0.063W,5%,0402_PB-FR	R0402	STD
0	R34,R35	100	RES_SM-TF,100,0.100W,5%,0805	R0805	STD
0	R36	10K	RES_SM-TF,10K,0.063W,1%,0402_FB-FR	R0402	STD
0	R101,R102,R103	0.001	RES_SM-MF,0.001,2.00W,1%,2512	R2512	STD
1	U1		TPS40422_QFN40-DUAL_PMB_BUCK_CNTLR_PB-FR	QFN-40	TPS40422

IMPORTANT NOTICE FOR TI DESIGN INFORMATION AND RESOURCES

Texas Instruments Incorporated ('TI") technical, application or other design advice, services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using any particular TI Resource in any way, you (individually or, if you are acting on behalf of a company, your company) agree to use it solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources.

You understand and agree that you remain responsible for using your independent analysis, evaluation and judgment in designing your applications and that you have full and exclusive responsibility to assure the safety of your applications and compliance of your applications (and of all TI products used in or for your applications) with all applicable regulations, laws and other applicable requirements. You represent that, with respect to your applications, you have all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. You agree that prior to using or distributing any applications that include TI products, you will thoroughly test such applications and the functionality of such TI products as used in such applications. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

You are authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING TI RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY YOU AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

You agree to fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of your non-compliance with the terms and provisions of this Notice.

This Notice applies to TI Resources. Additional terms apply to the use and purchase of certain types of materials, TI products and services. These include; without limitation, TI's standard terms for semiconductor products http://www.ti.com/sc/docs/stdterms.htm), evaluation modules, and samples (http://www.ti.com/sc/docs/sampterms.htm).

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2017, Texas Instruments Incorporated