PMP21386

Fitted	Description	Designator	PartNumber	Quantity	Manufacturer	PackageReference	Value
Fitted	Printed Circuit Board	PCB?	PMP21386	1	Any		
	CAP, CERM, 4.7 μF,						
	25 V,+/- 10%, X7R,		C2012X7R1E475K125				
Fitted	0805	C10, C20	AB	2	TDK	0805	4.7uF
	CAP, CERM, 1000 pF,						
	50 V, +/- 10%,						
Fitted	C0G/NP0, 0603	C11, C21	06035A102KAT2A	2	AVX	0603	1000pF
	CAP, CERM, 0.1 μF,						
	25 V,+/- 20%, X7R,						
Fitted	0402	C12, C22	TMK105B7104MV-FR	2	Taiyo Yuden	0402	0.1uF
	CAP, CERM, 1 µF, 25		C1608X7R1E105K080				
Fitted	V,+/- 10%, X7R, 0603	C13, C23	AB	2	TDK	0603	1uF
	CAP, CERM, 10 µF, 25	C14, C15,	C3225X7R1E106M250				
Fitted	V,+/- 20%, X7R, 1210	C16, C24,	AC	6	TDK	1210	10uF
	CAP, CERM, 0.1 μF,						
	25 V, +/- 10%, X7R,		GRM188R71E104KA0				
Fitted	0603	C17, C27	1D	2	MuRata	0603	0.1uF
	CAP, Aluminum						
	Polymer, 470 µF, 2.5						
	V,+/- 20%, 4.5 ohm,	C50, C51,					
Fitted	7.3x1.8x4.3mm SMD	C52, C56	EEFSX0E471E4	4	Panasonic	7.3x1.8x4.3mm	470uF
	CAP, CERM, 100 µF,						
	6.3 V,+/- 20%, X6S,		C3225X6S0J107M250				
Fitted	1210	C53, C54, C55	AC	3	TDK	1210	100uF
	CAP, AL, 330 µF, 25						
	V, +/- 20%, 0.15						
Fitted	ohm, SMD	C100, C101	EEE-FC1E331P	2	Panasonic	SMT Radial G	330uF
	CAP, CERM, 0.1 μF,						
	10 V,+/- 10%, X7R,						
Fitted	0603	C300, C319	C0603X104K8RACTU	2	Kemet	0603	0.1uF
	Machine Screw,						
	Round, #4-40 x 1/4,						
	Nylon, Philips	H1, H2, H3,					
Fitted	panhead	H4	NY PMS 440 0025 PH	4	B&F Fastener Supply	Screw	
	Standoff, Hex, 0.5"L	H5, H6, H7,					
Fitted	#4-40 Nylon	H8	1902C	4	Keystone	Standoff	
	Header, 100mil, 2x1,		800-10-002-10-			Header, 2x1,	
Fitted	тн	J101	001000	1	Mill-Max	100mil, TH	
	Terminal Block, 5.08					2x1 5.08 mm	
Fitted	mm, 2x1, Brass, TH	J300	ED120/2DS	1	On-Shore Technology	Terminal Block	
	Terminal Block, 5.08					4x1 5.08 mm	
Fitted	mm, 4x1, Brass, TH	J302, J303	ED120/4DS	2	On-Shore Technology	Terminal Block	
	Header, 100mil, 3x1,		800-10-003-10-		5,	Header, 3x1,	
Fitted	тн	J304	001000	1	Mill-Max	100mil, TH	
	Connector, Ultra-Mini					Ultra small CO-	
Fitted	Coaxial, SMD	J309, J319	U.FL-R-SMT-1	2	Hirose Electric Co. Ltd.	AX SMD	
	Inductor, Wirewound,						
	Ferrite, 300 nH, 35 A,						
Fitted	0.00029 ohm, SMD	L1, L2	FP1007R3-R30-R	2	Coiltronics	FP1007R3	300nH
	Thermal Transfer						
	Printable Labels,					PCB Label	
	0.650" W x 0.200" H -					0.650"H x	
Fitted	10,000 per roll	LBL1	THT-14-423-10	1	Brady	0.200"W	

	MOSFET, N-CH, 25 V,		[
	113 A, DQH0008A						
Fitted	(VSON-CLIP-8)	Q300	CSD16408Q5	1	Texas Instruments	DQH0008A	25V
	RES, 23.7 k, 1%, 0.1						
	W, AEC-Q200 Grade						
Fitted	0, 0402	R10	ERJ-2RKF2372X	1	Panasonic	0402	23.7k
	RES, 40.2 k, 1%, 0.063						
Fitted	W, 0402	R11	CRCW040240K2FKED	1	Vishay-Dale	0402	40.2k
	RES, 45.3 k, 1%, 0.063					0.400	
Fitted	W, 0402 RES, 187 k, 1%, 0.063	R13, R21	CRCW040245K3FKED	2	Vishay-Dale	0402	45.3k
Fitted	W, 0402	R15, R25	CRCW0402187KFKED	2	Vishey Dele	0402	187k
	RES, 3.0 ohm, 5%,	R15, R25 R16, R17,		2	Vishay-Dale	0402	107K
Fitted	0.125W, 0805	R26, R27	RC0805JR-073RL	1	Yageo America	0805	3.0
	RES, 0, 5%, 0.063 W,	R19, R29,		-	Tageo America		5.0
Fitted	0402	R31, R41,	CRCW04020000Z0ED	7	Vishay-Dale	0402	0
Titteu	RES, 51.1 k, 1%, 0.063						-
Fitted	W, 0402	R24	CRCW040251K1FKED	1	Vishay-Dale	0402	51.1k
	RES, 100 k, 5%, 0.063				-		
Fitted	W, 0402	R30	CRCW0402100KJNED	1	Vishay-Dale	0402	100k
	RES, 10, 5%, 0.063 W,						
Fitted	0402	R50, R53	CRCW040210R0JNED	2	Vishay-Dale	0402	10
	RES, 1.00 k, 1%, 0.063						
Fitted	W, 0402	R52	CRCW04021K00FKED	1	Vishay-Dale	0402	1.00k
	RES, 1.00, 1%, 0.1 W,						
Fitted	0603	R301	CRCW06031R00FKEA	1	Vishay-Dale	0603	1.00
	RES, 10.0 k, 1%, 0.1						
	W, AEC-Q200 Grade 0, 0603	R302	RMCF0603FT10K0	1		0602	10.01
Fitted	RES, 0.02, 1%, 3 W,	R302	RIVICF0603F1 TUKU	ľ	Stackpole Electronics I	0603	10.0k
Either al	2512	R303	CRA2512-FZ-R020ELF	1	Bourns	2512	0.02
Fitted	RES, 49.9, 1%, 0.063	1303		1	Bourns	2312	0.02
Fitted	W, 0402	R304, R314	CRCW040249R9FKED	2	Vishay-Dale	0402	49.9
Titteu	, • · • -	TP102, TP103,		-	visitay bare		15.5
	Test Point, Miniature,	TP105, TP106,				Red Miniature	
Fitted	Red, TH	TP300, TP301,	5000	8	Keystone	Testpoint	Red
	Test Point, Miniature,					White Miniature	
Fitted	White, TH	TP107	5002	1	Keystone	Testpoint	
	Test Point, Miniature,	TP109, TP303,				Black Miniature	
Fitted	Black, TH		5001	4	Keystone	Testpoint	Black
	Test Point, Compact,	TP305, TP308,				Testpoint_Keysto	
Fitted		TP309, TP315	5016	4	Keystone	ne_Compact	
	FREQUENCY NON-						
	COMPENSATON						
	STACKABLE						
	SYNCHRONOUS						
	BUCK CONVERTER,						
Fitted	RVF0040A	U1, U2	TPS543C20RVFT	า	Texas Instruments	RVF0040A	
	Fiducial mark. There	51, 52		2			
	is nothing to buy or	FID1, FID2,					
Not Fitted	mount.	FID3	N/A	0	N/A	Fiducial	
	RES, 8.66 k, 1%, 0.063						
Not Fitted	W, 0402	R12, R14	CRCW04028K66FKED	0	Vishay-Dale	0402	8.66k
	RES, 40.2 k, 1%, 0.063				-		Ì
Not Fitted	W, 0402	R23	CRCW040240K2FKED	0	Vishay-Dale	0402	40.2k
	RES, 9.76 M, 1%,						
Not Fitted	0.063 W, 0402	R51	CRCW04029M76FKED	0	Vishay-Dale	0402	9.76Meg

IMPORTANT NOTICE FOR TI DESIGN INFORMATION AND RESOURCES

Texas Instruments Incorporated ('TI") technical, application or other design advice, services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using any particular TI Resource in any way, you (individually or, if you are acting on behalf of a company, your company) agree to use it solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources.

You understand and agree that you remain responsible for using your independent analysis, evaluation and judgment in designing your applications and that you have full and exclusive responsibility to assure the safety of your applications and compliance of your applications (and of all TI products used in or for your applications) with all applicable regulations, laws and other applicable requirements. You represent that, with respect to your applications, you have all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. You agree that prior to using or distributing any applications. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

You are authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING TI RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY YOU AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

You agree to fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of your noncompliance with the terms and provisions of this Notice.

This Notice applies to TI Resources. Additional terms apply to the use and purchase of certain types of materials, TI products and services. These include; without limitation, TI's standard terms for semiconductor products http://www.ti.com/sc/docs/stdterms.htm), evaluation modules, and samples (http://www.ti.com/sc/docs/stdterms.htm), evaluation

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2018, Texas Instruments Incorporated