

AN-1669 LM3743 High Performance Controller with Comprehensive Fault Protection Features Designed for High Reliability Systems

ABSTRACT

This application report discusses how the Texas Instruments LM3743 minimizes power consumption during fault conditions thereby reducing thermal loads and increasing reliability.

Contents

1	Introduction	2
2	Typical Application Circuit	2
3	LM3743 Comprehensive Fault Protection Features	3
4	Protecting Typical Fault Conditions in High-Reliability Systems	3

List of Figures

1	Typical Application Circuit	2
2	Hiccup Time Out and Internal Soft-Start	3
3	Output Short-Circuit to Ground.....	4
4	Switch Node Short-Circuit to Ground.....	4
5	Low Side MOSFETOpen-Circuit Failure	4

1 Introduction

The LM3743 is a DC-DC voltage mode PWM buck controller featuring synchronous rectification at 300 kHz or 1 MHz. It can deliver current as high as 20A and step down from an input voltage between 3V and 5.5V down to a minimum output voltage of 0.8V. It is a highly integrated device in a small MSOP-10 package. Features include; pre-biased soft-start, tracking capability, and comprehensive fault protection features suitable for high reliability systems such as rack mounted servers and telecom base station subsystems.

Data center facilities and telecom base station subsystems must manage the balance of two essential commodities - power and cooling capacity. For example, processors in rack mounted servers demand large amounts of power and are one of the greatest sources of heat during normal operation. Substantial increases in heat during normal operation and fault conditions will reduce the reliability of many components in the server racks including semiconductor components, hard drives, and fans. The LM3743 will minimize power consumption during fault conditions thereby reducing thermal loads and increasing reliability.

2 Typical Application Circuit




Figure 1. Typical Application Circuit

3 LM3743 Comprehensive Fault Protection Features

The LM3743 provides the following comprehensive fault protection features: high side current limit (HSCL), output under-voltage protection (UVP), and low side current limit (LSCL). When engaged, these three features can each independently initiate a hiccup protection mode which disables both the high-side and low-side FETs and begin a cool down period of 5.5 ms, see [Figure 2](#). At the conclusion of this cool down period, the LM3743 performs an internal 3.6 ms soft-start to check for the removal of the fault condition and to continue normal operation. Hiccup protection mode enables the system designer to avoid the need to over design components due to thermal runaway during fault conditions resulting in a lower bill of material cost.




Figure 2. Hiccup Time Out and Internal Soft-Start

To help quantify the power consumption during a persistent fault condition, let us examine an application with a 10A low-side current limit. Once in overload, the low-side current limit controls the valley current and only allows an average of 10A plus the ripple current to pass through the inductor and MOSFETs. Hiccup mode initializes after 15 switching cycles allowing only a very small temperature rise. Once in hiccup mode, the average current through the high-side FET is:

$$I_{HSF-AVE} = (I_{CLIM} + \Delta I) \times [D(15 \text{ cycles} \times T_{SW})] / 5.5 \text{ ms} = 71 \text{ mA} \quad (1)$$

With an arbitrary D = 60%, ripple current of 3A, and a 300 kHz switching frequency.

The average current through the low-side FET is:

$$I_{LSF-AVE} = (I_{CLIM} + \Delta I) \times [(1-D) \times (15 \text{ cycles} \times T_{SW})] / 5.5 \text{ ms} = 47 \text{ mA} \quad (2)$$

And the average current through the inductor is:

$$I_{L-AVE} = (I_{CLIM} + \Delta I) \times [(15 \text{ cycles} \times T_{SW})] / 5.5 \text{ ms} = 118 \text{ mA} \quad (3)$$

4 Protecting Typical Fault Conditions in High-Reliability Systems

Server racks and telecom base station subsystems require high reliability to enable uninterrupted flow of data and communication. When unexpected failures occur, the LM3743 fault protection features can help to prevent further electrical and thermal stress. Examining some typical system fault conditions, we can elaborate on the protection modes of the LM3743 device and the operational benefit:

1. A capacitor such as a POS-cap located at the output of the LM3743 fails as a short circuit after an over-voltage surge exceeds the maximum capacitor voltage rating, see [Figure 3](#). In such a situation duty cycle and the inductor current increase cycle by cycle, but fortunately input current is decreased because the LM3743 UVP initializes Hiccup-Mode.
2. A small piece of metal falling into the product from the outside or a piece of metal that was loose in the product changes positions during shipment and lands across the switch node (V_{SW}) and ground, see [Figure 4](#). High side current limit immediately senses the short circuit fault condition.

3. Excessive load and/or incorrect selection of the MOSFET results in an open circuit failure. For example; if the low side MOSFET (Q2) fails, shown in [Figure 5](#), the inductor current will not flow during the time Q2 should be on, thus the inductor current will increase cycle by cycle. The high side current limit will capture the over current event, thereby protecting the high side MOSFET (Q1) from over heating and failure.




Figure 3. Output Short-Circuit to Ground




Figure 4. Switch Node Short-Circuit to Ground




Figure 5. Low Side MOSFET Open-Circuit Failure

In all these situations, the LM3743 provides fault protection, reduces the average input current, and relieves the power components from thermal stress during persistent fault conditions. After the removal of the fault condition, the LM3743 performs an automatic self test and recovery sequence. User intervention is not required, so reduces maintenance cost and designed in circuit complexity.

The LM3743 provides comprehensive fault protection and a reduction in server power consumption during fault conditions. It also combines high efficiency with high drive capabilities for loads up to 20A. With the LM3743, the balance between power and cooling capacity are much more manageable during device failure and short circuit conditions.

For datasheet, evaluation board, application note, and reference design information, see *LM3743 High-Performance Synchronous Buck Controller with Comprehensive Fault Protection Features* ([SNVS427](#)).

IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products (also referred to herein as "components") are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of significant portions of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI components or services with statements different from or beyond the parameters stated by TI for that component or service voids all express and any implied warranties for the associated TI component or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards which anticipate dangerous consequences of failures, monitor failures and their consequences, lessen the likelihood of failures that might cause harm and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed a special agreement specifically governing such use.

Only those TI components which TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components which have **not** been so designated is solely at the Buyer's risk, and that Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.

Products	Applications		
Audio	www.ti.com/audio	Automotive and Transportation	www.ti.com/automotive
Amplifiers	amplifier.ti.com	Communications and Telecom	www.ti.com/communications
Data Converters	dataconverter.ti.com	Computers and Peripherals	www.ti.com/computers
DLP® Products	www.dlp.com	Consumer Electronics	www.ti.com/consumer-apps
DSP	dsp.ti.com	Energy and Lighting	www.ti.com/energy
Clocks and Timers	www.ti.com/clocks	Industrial	www.ti.com/industrial
Interface	interface.ti.com	Medical	www.ti.com/medical
Logic	logic.ti.com	Security	www.ti.com/security
Power Mgmt	power.ti.com	Space, Avionics and Defense	www.ti.com/space-avionics-defense
Microcontrollers	microcontroller.ti.com	Video and Imaging	www.ti.com/video
RFID	www.ti-rfid.com	TI E2E Community	
OMAP Applications Processors	www.ti.com/omap	e2e.ti.com	
Wireless Connectivity	www.ti.com/wirelessconnectivity		