

ADS1209EVM

This user's guide describes the characteristics, operation, and use of the ADS1209EVM. This EVM is an evaluation module for the [ADS1209](#), a two-channel, high-performance, delta-sigma ($\Delta\Sigma$) modulator designed for use with the [AMC1210](#), a four-channel digital filter designed specifically for current measurement and resolver position decoding in motor control applications. The ADS1209EVM is designed for prototyping and evaluation. A complete circuit description, schematic diagram, and bill of materials are included.

The following related documents are available through the Texas Instruments web site at www.ti.com.

Device	Literature Number
ADS1209	SBAS491
AMC1210	SBAS372

Contents

1	ADS1209EVM Overview	2
1.1	Features	2
1.2	Introduction	2
2	Analog Interface	2
2.1	Analog Inputs	3
3	Digital Interface	3
4	Power Supplies	4
5	EVM Operation	4
5.1	Analog Inputs: J1	4
5.2	Device Operation	5
6	BOM, Schematic, and Layout	5
6.1	Schematic	5
6.2	Printed Circuit Board Layout	5
6.3	Bill of Materials	6

1 ADS1209EVM Overview

1.1 Features

ADS1209EVM:

- Full-featured evaluation module for the ADS1209 two-channel, $\Delta\Sigma$ modulator
- 9-pin sub-D connector for interfacing to the AMC1210 digital filter evaluation module
- Screw terminals for easy access to analog inputs

1.2 Introduction

The ADS1209EVM is an evaluation board for the ADS1209 two-channel $\Delta\Sigma$ modulator. This EVM features a 9-pin, female sub-D connector that allows digital outputs from the ADS1209 to be fed directly to the AMC1210 digital filter chip.

The ADS1209 is a two-channel modulator that offers 86-dB dynamic performance, operating from a single 5-V supply. When used in combination with the AMC1210 or other digital filter, the ADS1209 can be used to achieve 16-bit analog-to-digital (A/D) conversion with no missing codes.

For use in high-resolution measurement applications, an effective accuracy of 14 bits can be obtained with a digital filter bandwidth of 20 kHz at a modulator rate of 10 MHz.

Throughout this document, the abbreviation *EVM* and the term *evaluation module* are synonymous with the ADS1209EVM.

2 Analog Interface

The analog input to the ADS1209 is routed from a five-wire screw terminal screw at J1. This screw terminal gives the user access to the inverting and noninverting inputs of both channels of the ADS1209. A convenient ground terminal is also provided.

2.1 Analog Inputs

The analog input to the ADS1209EVM board consist of two simple R/C filter circuits. The input circuit for the ADS1209 is shown in Figure 1.




Figure 1. ADS1209EVM Schematic: Analog Input Section

3 Digital Interface

The ADS1209EVM is designed for use with digital filters such as the AMC1210. The output and power for the ADS1209 are routed to a 9-pin, female D-type connector. Both the analog and digital power for the ADS1209, as well as the modulator data and clock outputs from the device under test, are routed to J2, as Figure 2 illustrates.




Figure 2. Power and Digital Outputs

4 Power Supplies

J2 provides access to the +5 VA for the AV_{DD} supply, and +2.7 to 5.5 VD for the BV_{DD} supply. It is recommended that all power to the board be sourced from a well-regulated linear supply with current-limiting capabilities. Power is to be applied through J2. [Table 1](#) describes the pinout for J2.

Table 1. J2: Power Supply and Digital Outputs

Signal	Pin Number		Signal
Ground	1	2	Not used
2.7 to 5.5 BV_{DD} Supply	3	4	+5 AV_{DD} Supply
Ground	5	6	Clock OUT 2
Clock OUT 1	7	8	Modulator Data: CHB
Modulator Data: CHA	9		

For standalone operation, power sources can also be applied via a mating connector to J2, and the digital output data streams can be wired directly to an FPGA or other digital filter module for further processing. Refer to [Figure 2](#) or the schematic appended to the end of this document for additional details.

5 EVM Operation

This section describes the general operation of the ADS1209EVM.

5.1 Analog Inputs: J1

The analog input to the ADS1209EVM printed circuit board (PCB) can be applied directly to J1, pins 1 and 2 for channel A and J1, pins 4 and 5 for channel B.

CAUTION

Carefully review the [ADS1209 product data sheet](#) for the limitations of the analog input range, and ensure that the appropriate analog/digital voltages are applied before connecting any analog input to the EVM.

[Table 2](#) lists the details of J1.

Table 2. J1: Analog Inputs

Pin Number	Signal	Description
J1.1	CHA+	Noninverting analog input to channel A
J1.2	CHA-	Inverting input to channel A
J1.3	GND	Ground
J1.4	CHB-	Inverting input to channel B
J1.5	CHB+	Noninverting input to channel B

5.2 Device Operation

Once the analog and digital power sources are applied to the ADS1209EVM, the digital outputs become active. The ADS1209 is configured to use its onboard oscillator by tying the clock in (CLKIN) and clock select (CLKSEL) pins to the applied digital power supply. The internal reference of the ADS1209 is used as the conversion reference inputs by tying the REFOUT pin to both REFIN A and REFIN B.

Additionally, an analog input signal may be applied to the unipolar differential input pair of either channel at screw terminal J1. See [Figure 1](#) and [Table 2](#) for more details. The analog input range is $\pm 0.92 \times V_{REF}$ with a common mode input of +2.5 V. With the nominal internal reference voltage of +2.5 V, the maximum analog input voltage ranges from +0.125 V to +4.875 V.

As the input voltage approaches the maximum input level of +4.875 V, the 1s density of the modulator output approaches 92%. Likewise, when the input voltage approaches the lower limit of +0.124 V, the 1s density is approximately 8%.

6 BOM, Schematic, and Layout

This section contains the complete bill of materials, schematic diagram, and printed circuit board (PCB) layout for the ADS1209EVM.

NOTE: Board layouts are not to scale. These are intended to show how the board is laid out; they are not intended to be used for manufacturing ADS1209EVM PCBs.

6.1 Schematic

The ADS1209EVM schematic is appended to this document.

6.2 Printed Circuit Board Layout





Figure 3. ADS1209EVM Silk Screen Drawing

6.3 Bill of Materials

Table 3. ADS1209EVM Bill of Materials

Reference Designator	Description	Vendor	Part Number
C1, C3, C4, C5	Not installed	—	—
C2, C6	Capacitor, ceramic 4700pF 50V 10% X7R 0603	Murata	GRM188R71H472KA01D
C7 - C13	Capacitor, ceramic 0.1 μ F 50V 10% X7R 0603	Murata	GRM188R71H104KA93D
C14	Capacitor, ceramic 1 μ F 25V 10% X5R 0603	Murata	GRM188R61E105KA12D
C15, C16	Capacitor, ceramic 4.7 μ F 16V 10% X5R 0805	Murata	GRM21BR61C475KA88L
J1	Terminal block, 3.5MM, 5-Pos PCB	On Shore	ED555/5DS
J2	Connector, DB-9 Female solder cup, Tin	Norcomp	172-009-202R001
R1, R2, R3, R4	Resistor, 47.0 Ω 1/10W 1% 0603 SMD	Yageo	RC0603FR-0747RL
R5, R6	Resistor, 12.0 Ω 1/10W 1% 0603 SMD	Yageo	RC0603FR-0712RL
U1	ADS1209, ADS1209SPW	TI	ADS1209SPW

REVISION HISTORY		
REV	ENGINEERING CHANGE NUMBER	APPROVED



Precision Analog
HIGH-PERFORMANCE ANALOG DIVISION
SEMICONDUCTOR GROUP

12500 TI Blvd, Dallas, TX 75243

TITLE		ADS1209EVM	
ENGINEER	Tom Hendrick	SIZE A	DATE 2/17/2010
DRAWN BY	Tom Hendrick	REV A	
DOCUMENT CONTROL NO.	6516845	FILE ADS1209_sch_a	

SHEET 1	OF 1
---------	------

Evaluation Board/Kit Important Notice

Texas Instruments (TI) provides the enclosed product(s) under the following conditions:

This evaluation board/kit is intended for use for **ENGINEERING DEVELOPMENT, DEMONSTRATION, OR EVALUATION PURPOSES ONLY** and is not considered by TI to be a finished end-product fit for general consumer use. Persons handling the product(s) must have electronics training and observe good engineering practice standards. As such, the goods being provided are not intended to be complete in terms of required design-, marketing-, and/or manufacturing-related protective considerations, including product safety and environmental measures typically found in end products that incorporate such semiconductor components or circuit boards. This evaluation board/kit does not fall within the scope of the European Union directives regarding electromagnetic compatibility, restricted substances (RoHS), recycling (WEEE), FCC, CE or UL, and therefore may not meet the technical requirements of these directives or other related directives.

Should this evaluation board/kit not meet the specifications indicated in the User's Guide, the board/kit may be returned within 30 days from the date of delivery for a full refund. **THE FOREGOING WARRANTY IS THE EXCLUSIVE WARRANTY MADE BY SELLER TO BUYER AND IS IN LIEU OF ALL OTHER WARRANTIES, EXPRESSED, IMPLIED, OR STATUTORY, INCLUDING ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR ANY PARTICULAR PURPOSE.**

The user assumes all responsibility and liability for proper and safe handling of the goods. Further, the user indemnifies TI from all claims arising from the handling or use of the goods. Due to the open construction of the product, it is the user's responsibility to take any and all appropriate precautions with regard to electrostatic discharge.

EXCEPT TO THE EXTENT OF THE INDEMNITY SET FORTH ABOVE, NEITHER PARTY SHALL BE LIABLE TO THE OTHER FOR ANY INDIRECT, SPECIAL, INCIDENTAL, OR CONSEQUENTIAL DAMAGES.

TI currently deals with a variety of customers for products, and therefore our arrangement with the user **is not exclusive.**

TI assumes **no liability for applications assistance, customer product design, software performance, or infringement of patents or services described herein.**

Please read the User's Guide and, specifically, the Warnings and Restrictions notice in the User's Guide prior to handling the product. This notice contains important safety information about temperatures and voltages. For additional information on TI's environmental and/or safety programs, please contact the TI application engineer or visit www.ti.com/esh.

No license is granted under any patent right or other intellectual property right of TI covering or relating to any machine, process, or combination in which such TI products or services might be or are used.

FCC Warning

This evaluation board/kit is intended for use for **ENGINEERING DEVELOPMENT, DEMONSTRATION, OR EVALUATION PURPOSES ONLY** and is not considered by TI to be a finished end-product fit for general consumer use. It generates, uses, and can radiate radio frequency energy and has not been tested for compliance with the limits of computing devices pursuant to part 15 of FCC rules, which are designed to provide reasonable protection against radio frequency interference. Operation of this equipment in other environments may cause interference with radio communications, in which case the user at his own expense will be required to take whatever measures may be required to correct this interference.

EVM Warnings and Restrictions

It is important to operate this EVM within the input voltage range of 0V to 5V and the output voltage range of 0V to 5V.

Exceeding the specified input range may cause unexpected operation and/or irreversible damage to the EVM. If there are questions concerning the input range, please contact a TI field representative prior to connecting the input power.

Applying loads outside of the specified output range may result in unintended operation and/or possible permanent damage to the EVM. Please consult the EVM User's Guide prior to connecting any load to the EVM output. If there is uncertainty as to the load specification, please contact a TI field representative.

During normal operation, some circuit components may have case temperatures greater than +30°C. The EVM is designed to operate properly with certain components above +30°C as long as the input and output ranges are maintained. These components include but are not limited to linear regulators, switching transistors, pass transistors, and current sense resistors. These types of devices can be identified using the EVM schematic located in the EVM User's Guide. When placing measurement probes near these devices during operation, please be aware that these devices may be very warm to the touch.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2010, Texas Instruments Incorporated

IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

TI products are not authorized for use in safety-critical applications (such as life support) where a failure of the TI product would reasonably be expected to cause severe personal injury or death, unless officers of the parties have executed an agreement specifically governing such use. Buyers represent that they have all necessary expertise in the safety and regulatory ramifications of their applications, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of TI products in such safety-critical applications, notwithstanding any applications-related information or support that may be provided by TI. Further, Buyers must fully indemnify TI and its representatives against any damages arising out of the use of TI products in such safety-critical applications.

TI products are neither designed nor intended for use in military/aerospace applications or environments unless the TI products are specifically designated by TI as military-grade or "enhanced plastic." Only products designated by TI as military-grade meet military specifications. Buyers acknowledge and agree that any such use of TI products which TI has not designated as military-grade is solely at the Buyer's risk, and that they are solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI products are neither designed nor intended for use in automotive applications or environments unless the specific TI products are designated by TI as compliant with ISO/TS 16949 requirements. Buyers acknowledge and agree that, if they use any non-designated products in automotive applications, TI will not be responsible for any failure to meet such requirements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

Products		Applications	
Amplifiers	amplifier.ti.com	Audio	www.ti.com/audio
Data Converters	dataconverter.ti.com	Automotive	www.ti.com/automotive
DLP® Products	www.dlp.com	Communications and Telecom	www.ti.com/communications
DSP	dsp.ti.com	Computers and Peripherals	www.ti.com/computers
Clocks and Timers	www.ti.com/clocks	Consumer Electronics	www.ti.com/consumer-apps
Interface	interface.ti.com	Energy	www.ti.com/energy
Logic	logic.ti.com	Industrial	www.ti.com/industrial
Power Mgmt	power.ti.com	Medical	www.ti.com/medical
Microcontrollers	microcontroller.ti.com	Security	www.ti.com/security
RFID	www.ti-rfid.com	Space, Avionics & Defense	www.ti.com/space-avionics-defense
RF/IF and ZigBee® Solutions	www.ti.com/lprf	Video and Imaging	www.ti.com/video
		Wireless	www.ti.com/wireless-apps

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2010, Texas Instruments Incorporated