

N2G Module TPS40190DRC_12V_5V_6A_EVM BOM RevA

COUNT	RefDes	Value	Description	Size	Part Number	MFR	AREA	EXT	Pr/Ea*	EXT
1	C1	.01uF	Capacitor, Ceramic, 50V, X7R, 10%	0603	C1608X7R1C103K	Std	5650	5650	0.005	0.005
1	C12	.01uF	Capacitor, Ceramic, 50V, X7R, 10%	0603	C1608X7R1C103K	Std	5650	5650	0.005	0.005
4	C3,C4,C5	10uF	Capacitor, Ceramic, 16V, X7R, 20%	1210	C3225X5R1C106M	TDK	83,600	334400	0.04	0.16
	C116									
1	C6	3300pF	Capacitor, Ceramic, 25V, X7R, 10%	0603	C1608COG1E682J	Std	5650	5650	0.040	0.04
1	C7	330pF	Capacitor, Ceramic, 50V, X7R, 10%	0603	C1608COG1H680J	Std	5650	5650	0.005	0.005
2	C8,C14	0.1uF	Capacitor, Ceramic, 16V, X7R, 10%	0603	C1608X7R1C105K	TDK	5650	11300	0.005	0.01
2	C11,C117	100uF	Capacitor, Ceramic, 6.3V, X5R, 20%	1210	C3225X5R0J107M	TDK	83,600	167200	0.19	0.38
1	C12	0.01uF	Capacitor, Ceramic, 16V, X7R, 10%	0603	C1608X7R1C104K	TDK	5650	5650	0.005	0.005
1	C13	4.7uF	Capacitor, Ceramic, 6.3V, X5R, 20	0805	C2012X5R0J475M	TDK	10560	10560	0.03	0.03
1	C15	open	Capacitor, Ceramic, 25V, COG, 10%	0603	C1608X7R1C104K	Std	5650	5650	0.005	0.005
2	C118,C119	1uF	Capacitor, Ceramic, 16V, X7R, 10%	0603	C1608X7R1C105K	TDK	5650	11300	0.005	0.01
1	D1	MBR0530	Diode, Schottky, 0.5-, 30V	SOD-123	MBR0530T1	ON	13300	13300	0.03	0.03
1	L1	4.7uH	Inductor, SMT, 10A, 15mΩ	13x13x10	IHLP5050CE-4R7-01	Vishay	296,400	296400	0.3	0.3
2	Q2,Q4	Si4390DY	MOSFET, N-ch, 30V, 10.5A, 13.5mΩ	S08	Si4390DY	Vishay	52,578	105156	0.25	0.5
1	R2	249	Resistor, Chip, 1/16W, 1%	0603	Std	Std	5650	5650	0.005	0.005
1	R3	10K	Resistor, Chip, 1/16W, 1%	0603	Std	Std	5650	5650	0.005	0.005
1	R4	49.9	Resistor, Chip, 1/16W, 1%	0603	Std	Std	5650	5650	0.005	0.005
1	R5	open	Resistor, Chip, 1/16W, 1%	0603	Std	Std	5650	5650	0.005	0.005
1	R6	3.3	Resistor, Chip, 1/16W,1%	0603	Std	Std	5650	5650	0.005	0.005
1	R7	open	Resistor, Chip, 1/10W, 1%	0805	Std	Std	15300	15300	0.01	0.01
1	R8	3.01K	Resistor, Chip, 1/16W, 1%	0603	Std	Std	5650	5650	0.005	0.005
1	R9	open	Resistor, Chip, 1/16W, 1%	0603	Std	Std	5650	5650	0.005	0.005
1	R10	1.33K	Resistor, Chip, 1/16W, 1%	0603	Std	Std	5650	5650	0.005	0.005
1	U1	TPS40190DRC	IC, Low cost synchronous buck controller	DRC10	TPS40190DRC	TI	36,229	36229	0.34	0.34

* Pricing for Budgetary Purposes

Total Area(in) 1.08
 Total Cost (\$) \$1.88

R1 100K Resistor, Chip, 1/16W, 1%
 Q1 2N7002 MOSFET - 2N7002
 J1,J2,J3

IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

TI products are not authorized for use in safety-critical applications (such as life support) where a failure of the TI product would reasonably be expected to cause severe personal injury or death, unless officers of the parties have executed an agreement specifically governing such use. Buyers represent that they have all necessary expertise in the safety and regulatory ramifications of their applications, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of TI products in such safety-critical applications, notwithstanding any applications-related information or support that may be provided by TI. Further, Buyers must fully indemnify TI and its representatives against any damages arising out of the use of TI products in such safety-critical applications.

TI products are neither designed nor intended for use in military/aerospace applications or environments unless the TI products are specifically designated by TI as military-grade or "enhanced plastic." Only products designated by TI as military-grade meet military specifications. Buyers acknowledge and agree that any such use of TI products which TI has not designated as military-grade is solely at the Buyer's risk, and that they are solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI products are neither designed nor intended for use in automotive applications or environments unless the specific TI products are designated by TI as compliant with ISO/TS 16949 requirements. Buyers acknowledge and agree that, if they use any non-designated products in automotive applications, TI will not be responsible for any failure to meet such requirements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

Products

Amplifiers	amplifier.ti.com
Data Converters	dataconverter.ti.com
DSP	dsp.ti.com
Clocks and Timers	www.ti.com/clocks
Interface	interface.ti.com
Logic	logic.ti.com
Power Mgmt	power.ti.com
Microcontrollers	microcontroller.ti.com
RFID	www.ti-rfid.com
RF/IF and ZigBee® Solutions	www.ti.com/lprf

Applications

Audio	www.ti.com/audio
Automotive	www.ti.com/automotive
Broadband	www.ti.com/broadband
Digital Control	www.ti.com/digitalcontrol
Medical	www.ti.com/medical
Military	www.ti.com/military
Optical Networking	www.ti.com/opticalnetwork
Security	www.ti.com/security
Telephony	www.ti.com/telephony
Video & Imaging	www.ti.com/video
Wireless	www.ti.com/wireless

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2008, Texas Instruments Incorporated