



#### 1 Startup

The photo below shows the output voltage startup waveform after the application of 24V in. The 100V output was loaded to 0A. (20V/DIV, 5mS/DIV)




The photo below shows the output voltage startup waveform after the application of 24V in. The 100V output was loaded to 280mA. (20V/DIV, 5mS/DIV)





# 2 Efficiency


The boost converter efficiency is shown below.






# 3 Output Ripple Voltage

The 100V output ripple voltage is shown in the figure below. The image was taken with the output loaded to 280mA. The input voltage is set to 24V. (200mV/DIV, 1uS/DIV)




The 100V output ripple voltage is shown in the figure below. The image was taken with the output loaded to 280mA. The input voltage is set to 30V. (200mV/DIV, 1uS/DIV)






#### 4 Load Transients

The photo below shows the output voltage (ac coupled) when the load current is stepped between 150mA and 250mA. Vin = 24V. (500mV/DIV, 100mA/DIV, 10mS/DIV)




The photo below shows the output voltage (ac coupled) when the load current is stepped between 150mA and 250mA. Vin = 30V. (500mV/DIV, 100mA/DIV, 10mS/DIV)






### 5 Switch Node Waveforms

The photo below shows the FET switching voltage. The input voltage is 30V and the output is loaded to 280mA. (20V/DIV, 500nS/DIV)




The photo below shows the FET switching voltage. The input voltage is 30V and the output is loaded to 25mA. (20V/DIV, 500nS/DIV)






The photo below shows the FET switching voltage. The input voltage is 20V and the output is loaded to 280mA. (20V/DIV, 500nS/DIV)



The photo below shows the FET switching voltage. The input voltage is 20V and the output is loaded to 25mA. (20V/DIV, 500nS/DIV)






### 6 Control Loop Gain / Stability

The plot below shows the loop gain and phase margin with the output loaded to 50mA, 150mA, and 280mA. The input voltage was set to 24V.


 $\begin{array}{lll} Band\ Width = 3.13 KHz, & Phase\ Margin = 76\ degrees & (100V@280mA) \\ Band\ Width = 2.15 KHz, & Phase\ Margin = 79\ degrees & (100V@150mA) \\ Band\ Width = 1.69 KHz, & Phase\ Margin = 82\ degrees & (100V@50mA) \\ \end{array}$ 





### 7 Photo


The photo below shows the PMP8913 REVB assy.





# 8 Thermal Image

A thermal image is shown below when operating in parallel at 24V input and 280mA output, with no airflow.



#### IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale (https://www.ti.com/legal/termsofsale.html) or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2021, Texas Instruments Incorporated