



1 Photo

The photographs below show the PMP9009 Rev A assembly. This circuit was built on a PMP9009 Rev A PCB.

Top side




Bottom side





2 Converter Efficiency

The efficiency data is shown in the tables and graph below.



V_{in}=23V_{DC}

Vin(V)	lin(A)	Pin(W)	Vout(V)	lout(A)	Pout(W)	Losses(W)	Efficiency (%)
23.02	0.1612	3.710824	4.95	0.602	2.9799	0.730924	80.30%
23.08	0.1345	3.10426	4.94	0.501	2.47494	0.62932	79.73%
23.12	0.1106	2.557072	4.93	0.412	2.03116	0.525912	79.43%
23.18	0.0816	1.891488	4.93	0.304	1.49872	0.392768	79.23%
23.23	0.0541	1.256743	4.93	0.1996	0.984028	0.272715	78.30%
23.26	0.0419	0.974594	4.93	0.1527	0.752811	0.221783	77.24%
23.28	0.02931	0.682337	4.93	0.1038	0.511734	0.1706028	75.00%
23.3	0.01777	0.414041	4.96	0.05799	0.28763	0.1264106	69.47%

V_{in}=36V_{DC}

Vin(V)	lin(A)	Pin(W)	Vout(V)	lout(A)	Pout(W)	Losses(W)	Efficiency (%)
36	0.1026	3.6936	4.95	0.606	2.9997	0.6939	81.21%
36.03	0.0857	3.087771	4.94	0.505	2.4947	0.593071	80.79%
36.06	0.0694	2.502564	4.93	0.408	2.01144	0.491124	80.38%
36.09	0.0526	1.898334	4.92	0.308	1.51536	0.382974	79.83%
36.13	0.03521	1.272137	4.92	0.2036	1.001712	0.2704253	78.74%
36.14	0.02744	0.991682	4.92	0.1566	0.770472	0.2212096	77.69%
36.16	0.01944	0.70295	4.93	0.1075	0.529975	0.1729754	75.39%
36.18	0.01018	0.368312	4.96	0.05005	0.248248	0.1200644	67.40%

06/26/2013 PMP9009 Rev A Test Results




V_{in}=48V_{DC}

Vin(V)	lin(A)	Pin(W)	Vout(V)	lout(A)	Pout(W)	Losses(W)	Efficiency (%)
48	0.0767	3.6816	4.95	0.606	2.9997	0.6819	81.48%
48	0.0641	3.0768	4.94	0.505	2.4947	0.5821	81.08%
48	0.0519	2.4912	4.93	0.407	2.00651	0.48469	80.54%
48	0.0394	1.8912	4.92	0.308	1.51536	0.37584	80.13%
48	0.02644	1.26912	4.92	0.2037	1.002204	0.266916	78.97%
48.1	0.02062	0.991822	4.92	0.1567	0.770964	0.220858	77.73%
48.1	0.01465	0.704665	4.92	0.1077	0.529884	0.174781	75.20%
48.1	0.00773	0.371813	4.95	0.0502	0.24849	0.123323	66.83%




3 Thermal Images

The thermal images below show a top view and bottom view of the board with $23V_{DC}$ input. The ambient temperature was 20°C with no forced air flow. The output was at full load: 5V/0.6A. **Top Side**




Bottom Side





4 Startup

The output voltage at $23V_{in}$ and full load (5V/0.6A) startup is shown in the image below.



5 Turn off

The output voltage at 23V_{in} and full load (5V/0.6A) turn off transient is shown in the image below.







6 Output Ripple Voltages - Full Load

The output ripple voltages are shown in the plots below.

6.1 V_{in}=23V_{DC}: 5V/0.6A.






6.2 V_{in}=56V_{DC}: 5V/0.6A.



7 Load Transient

The image below shows $5V_{\text{out}}$ voltage response to a 0.3A to 0.6A load transient at $23V_{\text{in}}.$







8 Switching Waveforms

The image below shows key switching waveforms of PMP9009RevA. The waveforms are measured with 0.6A output current.

8.1 Primary MOSFET Q1 @ 23Vin




8.2 Primary MOSFET Q1 @ 56Vin





8.3 Secondary Diode D1 @ 56V_{in} (AC level)



IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale (https://www.ti.com/legal/termsofsale.html) or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2021, Texas Instruments Incorporated