TIDEP-0091

Designator	PartNumber	Quantity	Description	Value	Manufacturer
!PCB1		1	Printed Circuit Board		Any
C1, C2, C20	GCM155R71C104KA55D	3	CAP, CERM, 0.1 µF, 16 V, +/- 10%, X7R, 0402	0.1uF	MuRata
C3, C4, C7, C8, C11, C13, C17, C18,	GCM155R71C224KE02	9	CAP, CERM, 0.22 μF, 16 V, +/- 10%, X7R, AEC-Q200 Grade	0.22uF	MuRata
C5, C6	GCM188R71C105KA64D	2	CAP, CERM, 1 µF, 16 V, +/- 10%, X7R, AEC-Q200 Grade 1,	1uF	MuRata
C9, C12, C14, C19, C33	GCM21BR71A106KE22L	5	CAP, CERM, 10 μF, 10 V, +/- 10%, X7R, 0805	10uF	MuRata
C10	GCM21BR71A106KE22L	1	CAP, CERM, 10 µF, 10 V, +/- 10%, X7R, 0805	10uF	MuRata
C15, C16	GRM1555C1H4R7WA01D	2	CAP, CERM, 4.7 pF, 50 V, +/- 1%, C0G/NP0, 0402	4.7pF	MuRata
C22	GJM1555C1H4R7BB01D	1	CAP, CERM, 4.7 pF, 50 V, +/- 2%, C0G/NP0, 0402	4.7pF	MuRata
C23, C24, C29, C30, C31, C32, C35	CGA2B3X7R1H104K050BB	7	CAP, CERM, 0.1 µF, 50 V, +/- 10%, X7R, AEC-Q200 Grade 1	0.1uF	TDK
C25	C1005X5R1A104K050BA	1	CAP, CERM, 0.1 µF, 10 V, +/- 10%, X5R, 0402	0.1uF	TDK
C26	GRM155R6YA105ME11D	1	CAP, CERM, 1 µF, 35 V, +/- 20%, X5R, 0402	1uF	MuRata
C27, C28, C34, C37	C1005C0G1H220J050BA	4	CAP, CERM, 22 pF, 50 V, +/- 5%, C0G/NP0, 0402	22pF	TDK
C36	LMK212BJ475KD-T	1	CAP, CERM, 4.7 μF, 10 V, +/- 10%, X5R, 0805	4.7uF	Taiyo Yuden
C38, C44, C49, C55	06035A391JAT2A	4	CAP, CERM, 390 pF, 50 V, +/- 5%, C0G/NP0, 0603	390pF	AVX
C39, C45, C53, C58, C62, C65, C66,	C0805C106M8PACTU	12	CAP, CERM, 10 µF, 10 V, +/- 20%, X5R, 0805	10uF	Kemet
C40, C41, C43, C46, C48, C51, C54,	GRM155R61A104KA01D	15	CAP, CERM, 0.1 µF, 10 V, +/- 10%, X5R, 0402	0.1uF	MuRata
C42, C47, C50, C56, C61, C69, C72,	GRM31CR61C226ME15L	8	CAP, CERM, 22 µF, 16 V, +/- 20%, X5R, 1206	22uF	MuRata
C52, C75, C83	LLL219R71A474MA01L	3	CAP, CERM, 0.47 μF, 10 V, +/- 20%, X7R, 0508	0.47uF	MuRata
C60	GRM188R71C102KA01D	1	CAP, CERM, 1000 pF, 16 V, +/- 10%, X7R, 0603	1000pF	MuRata
C64, C68, C76, C84	C1608X7R1H103K080AA	4	CAP, CERM, 0.01 μF, 50 V, +/- 10%, X7R, 0603	0.01uF	TDK
C85, C86, C87, C92	TPSE156M050T0250V	4	CAP, TA, 15 μF, 50 V, +/- 20%, 0.25 ohm, SMD	22uF	AVX
C88	885012206087	1	CAP, CERM, 4700 pF, 50 V, +/- 10%, X7R, 0603	4700pF	Wurth Elektronik
C89	CEU4J2X7R1H104K125AE	1	CAP, CERM, 0.1 µF, 50 V, +/- 10%, X7R, 0805	0.1uF	TDK
C90	GRM188R71A225KE15D	1	CAP, CERM, 2.2 μF, 10 V, +/- 10%, X7R, 0603	2.2uF	MuRata
C91	GRM188R71E474KA12D	1	CAP, CERM, 0.47 μF, 25 V, +/- 10%, X7R, 0603	0.47uF	MuRata
C93	08055C472JAT2A	1	CAP, CERM, 4700 pF, 50 V, +/- 5%, X7R, 0805	4700pF	AVX
C94	08055C124KAT2A	1	CAP, CERM, 0.12 μF, 50 V, +/- 10%, X7R, 0805	0.12uF	AVX
C95, C96	EMK212BBJ226MG-T	2	CAP, CERM, 22 μF, 16 V, +/- 20%, X5R, 0805	22uF	Taiyo Yuden
C97	GRM155R61C104KA88D	1	CAP, CERM, 0.1 µF, 16 V, +/- 10%, X5R, 0402	0.1uF	MuRata
C98	GCM155R7IC104KA55D	1	CAP, CERM, 0.1 µF, 16 V, +/- 10%, X7R, 0402	0.1uF	MuRata
C99	GRM188R71A225KE15D	1	CAP, CERM, 2.2 µF, 10 V, +/- 10%, X7R, 0603	2.2uF	MuRata
D1, D2	CD0603-B0230	2	Diode, Schottky, 35 V, 0.2 A, 0603 Diode	35V	Bourns
D3, D4	SMBJ30A-13-F	2	Diode, TVS, Uni, 30 V, 48.4 Vc, SMB	30V	Diodes Inc.
F1	0ZCC0075BF2B	1	Fuse, 0.75 A, 33 VDC, SMD		Bel Fuse
FID1, FID2, FID3, FID4	N/A	4	Fiducial mark. There is nothing to buy or mount.		N/A
H1, H2, H3, H4	NY PMS 440 0025 PH	4	Machine Screw, Round, #4-40 x 1/4, Nylon, Philips panhea		B&F Fastener Supply
H5, H6, H7, H8	1902C	4	Standoff, Hex, 0.5"L #4-40 Nylon		Keystone
H9, H10, H11, H12	SJ-5303 (CLEAR)	4	Bumpon, Hemisphere, 0.44 X 0.20, Clear		3M

J1	OSTTE030161	1 Terminal Block, 3.5mm, 3x1, Tin, R/A, TH		On-Shore Technology
J2, J3, J4, J5	PEC02SAAN	4 Header, 100mil, 2x1, Tin, TH		Sullins Connector Solutions
J6	FTSH-105-01-F-D-K	1 Header, 1.27 mm, 5x2, Gold, TH		Samtec
J7	1727010	1 Conn Term Block, 2POS, 3.81mm, TH	2x1	Phoenix Contact
L1	BRC2012T4R7MD	1 Inductor, Wirewound, 4.7 μH, 0.6 A, 0.265 ohm, SMD	4.7uH	Taiyo Yuden
L2, L3, L4, L5	IHLP1616ABERR47M01	4 Inductor, Shielded Drum Core, Powdered Iron, 470 nH, 5 A	470nH	Vishay-Dale
L6	IFSC0806AZER1R0M01	1 Inductor, Shielded, Ferrite, 1 μH, 1.6 A, 0.115 ohm, SMD	1uH	Vishay-Dale
L7	IHLP2020BZER2R2M01	1 Inductor, Shielded Drum Core, Powdered Iron, 2.2 μH, 4.2	2.2uH	Vishay-Dale
LBL1	THT-14-423-10	1 Thermal Transfer Printable Labels, 0.650" W x 0.200" H - 1		Brady
Q1	SQ4850EY	1 MOSFET, N-CH, 60 V, 12 A, SO-8	60V	Vishay-Siliconix
R1, R6, R7, R19, R24, R28	CRCW040210K0FKED	6 RES, 10.0 k, 1%, 0.063 W, 0402	10.0k	Vishay-Dale
R2, R4, R13, R14, R39, R40	RC0402JR-070RL, RC0402JR-070RL, C	6 RES, 0, 5%, 0.063 W, 0402, RES, 0, 5%, 0.063 W, 0402, RES,	0, 0, 10k, 0, 0	Yageo America, Yageo America, Vishay-Dale, Yageo America, Pan
R3, R5, R11, R16, R21, R41, R42	RC0402JR-070RL	7 RES, 0, 5%, 0.063 W, 0402	0	Yageo America
R8, R9, R10	ERJ-2GEJ101X	3 RES, 100, 5%, 0.1 W, AEC-Q200 Grade 0, 0402	100	Panasonic
R12, R17	CRCW040261R9FKED	2 RES, 61.9, 1%, 0.063 W, 0402	61.9	Vishay-Dale
R15, R30, R32	CRCW040210K0JNED	3 RES, 10 k, 5%, 0.063 W, 0402	10k	Vishay-Dale
R18, R23, R27	CRCW0402750RFKED	3 RES, 750, 1%, 0.063 W, AEC-Q200 Grade 0, 0402	750	Vishay-Dale
R20, R25, R29	CRCW04027K87FKED	3 RES, 7.87 k, 1%, 0.063 W, AEC-Q200 Grade 0, 0402	7.87k	Vishay-Dale
R22, R26, R33	CRCW040282K5FKED	3 RES, 82.5 k, 1%, 0.063 W, AEC-Q200 Grade 0, 0402	82.5k	Vishay-Dale
R31, R34, R35	CRCW020133R2FNED	3 RES, 33.2, 1%, 0.05 W, 0201	33.2	Vishay-Dale
R36	CRCW040247K5FKED	1 RES, 47.5 k, 1%, 0.063 W, 0402	47.5k	Vishay-Dale
R37	ERJ-2GE0R00X	1 RES, 0, 5%, 0.063 W, 0402	0	Panasonic
R38	RG2012P-913-B-T5	1 RES, 91.0 k, 0.1%, 0.125 W, 0805	91.0k	Susumu Co Ltd
R43, R46, R49, R56	CRCW04023R90JNED	4 RES, 3.9, 5%, 0.063 W, 0402	3.9	Vishay-Dale
R44, R55	CRCW060320K0FKEA	2 RES, 20.0 k, 1%, 0.1 W, 0603	20.0k	Vishay-Dale
R45, R51, R57, R58, R60, R61, R62,	CRCW06033K24FKEA	9 RES, 3.24 k, 1%, 0.1 W, 0603	3.24k	Vishay-Dale
R47, R52, R54	CRCW060310K2FKEA	3 RES, 10.2 k, 1%, 0.1 W, 0603	10.2k	Vishay-Dale
R48, R59	CRCW06031K00FKEA	2 RES, 1.00 k, 1%, 0.1 W, 0603	1.00k	Vishay-Dale
R50, R53	CRCW060310R0JNEA	2 RES, 10, 5%, 0.1 W, 0603	10	Vishay-Dale
R63, R65	ERJ-3GEY0R00V	2 RES, 0, 5%, 0.1 W, 0603	0	Panasonic
R67, R71	RT0603DRE071K96L	2 RES, 1.96 k, 0.5%, 0.1 W, 0603	1.96k	Yageo America
R68, R72	RT0603DRE072K8L	2 RES, 2.80 k, 0.5%, 0.1 W, 0603	2.80k	Yageo America
R69	RT0603BRD0712K7L	1 RES, 12.7 k, 0.1%, 0.1 W, 0603	12.7k	Yageo America
R70	CRCW060310K0FKEA	1 RES, 10.0 k, 1%, 0.1 W, 0603	10.0k	Vishay-Dale
R73	CRCW06031K00JNEA	1 RES, 1.0 k, 5%, 0.1 W, 0603	1.0k	Vishay-Dale
R74	CRCW040210K0JNED	1 RES, 10 k, 5%, 0.063 W, 0402	10k	Vishay-Dale
R75, R76	CRCW04024R99FKED	2 RES, 4.99, 1%, 0.063 W, 0402	4.99	Vishay-Dale
SW1	KMR243GLFG	1 Switch, SPST-NO, Off-Mom, 0.01 A, 32 VDC, SMD		C&K Components
U1	XI1443QGABL	1 Single Chip 77 and 79 GHz FMCW Transceiver, ABL0161A		Texas Instruments

U2	SN65HVDA540QDR	1 5 V CAN Transceiver with I/O Level Shifting and Supply Op	Texas Instruments
U3	S25FL116K0XNFV010	1 16 Mbit (2 Mbyte), 3.0 V SPI Flash Memory, WND008	Cypress Semiconductor
U4	MSP432P401RIPZR	1 Mixed-Signal Microcontroller, PZ0100A (LQFP-100)	Texas Instruments
U5	LP87524FRNFRQ1	1 Four-Phase Buck Converter Up to 10-A Total Current with	Texas Instruments
U6	TPS3780ADRYR	1 Low Power, Dual Voltage Detector in Small uSON package	Texas Instruments
U7	TPS7A8801RTJR	1 Dual, 1-A, Low Noise (3.8-μVRMS), LDO Voltage Regulator	Texas Instruments
U8	TPS7A8101DRBR	1 Low-Noise, High-Bandwidth PSRR, Low-Dropout 1-A Linea	Texas Instruments
U9	LM74610QDGKRQ1	1 Smart Diode Controller, DGK0008A	Texas Instruments
U10	LM536025QPWPTQ1	1 5V, 2A, Buck Regulator For Automotive Applications, PWP	Texas Instruments
Y1	CX3225SA40000D0PTWCC	1 Crystal, 40 MHz, 8pF, SMD	Kyocera
Y2	X1A0001410014	1 Crystal, 32.768 KHz, 12.5 pF, SMD	Epson
Y3	FA-238 48.0000MB-W0	1 Crystal, 48MHz, 12pF, SMD	Epson

IMPORTANT NOTICE FOR TI DESIGN INFORMATION AND RESOURCES

Texas Instruments Incorporated ('TI") technical, application or other design advice, services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using any particular TI Resource in any way, you (individually or, if you are acting on behalf of a company, your company) agree to use it solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources.

You understand and agree that you remain responsible for using your independent analysis, evaluation and judgment in designing your applications and that you have full and exclusive responsibility to assure the safety of your applications and compliance of your applications (and of all TI products used in or for your applications) with all applicable regulations, laws and other applicable requirements. You represent that, with respect to your applications, you have all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. You agree that prior to using or distributing any applications that include TI products, you will thoroughly test such applications and the functionality of such TI products as used in such applications. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

You are authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING TI RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY YOU AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

You agree to fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of your non-compliance with the terms and provisions of this Notice.

This Notice applies to TI Resources. Additional terms apply to the use and purchase of certain types of materials, TI products and services. These include; without limitation, TI's standard terms for semiconductor products http://www.ti.com/sc/docs/stdterms.htm), evaluation modules, and samples (http://www.ti.com/sc/docs/sampterms.htm).

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2017, Texas Instruments Incorporated