

Fitted	Description	Designator	PartNumber	Quantity	Manufacturer	Package/Reference	Value
Fitted	Printed Circuit Board	PCB1	IDA-010232	1	Any		
Fitted	CAP. CERM. 0.1 uF, 25 V, +/- 10%, X5R, 0402	C1, C3, C4, C5	GRM155R61E104K4B7D	4	MuRata	0402	0.1uF
Fitted	CAP. CERM. 1 uF, 25 V, +/- 10%, X5R, 0402	C2	GRM155R61E105KE11D	1	MuRata	0402	1uF
Fitted	CAP. CERM. 0.22 uF, 25 V, +/- 5%, X7R, 0603	C6, C8	00603C2243RAC7867	2	Kemet	0603	0.22uF
Fitted	CAP. CERM. 1000 pF, 50 V, +/- 5%, X7R, 0603	C7, C19, C20, C31	CL10C102JB8NNNC	4	Samsung Electro-Mechanics	0603	1000pF
Fitted	CAP. CERM. 1 uF, 25 V, +/- 10%, X7R, 0603	C9, C22	CG3E1X7R1E105K0804C	2	TDK	0603	1uF
Fitted	CAP. CERM. 1000 pF, 50 V, +/- 10%, X7R, 0603	C10, C23	00603C102K5RAC7TU	2	Kemet	0603	1000pF
Fitted	CAP. CERM. 0.1 uF, 50 V, +/- 10%, X7R, AEC-Q200 Grade 1, 0603	C11, C13, C24, C25	00603C104K5RAC7AUTO	4	Kemet	0603	0.1uF
Fitted	CAP. CERM. 0.1 uF, 25 V, +/- 5%, X7R, 0603	C12, C21	00603C104J3RAC	2	Kemet	0603	0.1uF
Fitted	CAP. CERM. 8200 pF, 50 V, +/- 10%, X7R, 0603	C14, C26	CL10B822KB8NNNC	2	Samsung Electro-Mechanics	0603	8200pF
Fitted	CAP. CERM. 1000 pF, 50 V, +/- 10%, X7R, 1206	C15, C17, C27, C29	12065C102KAT2A	4	AVX	1206	1000pF
Fitted	CAP. CERM. 0.1 uF, 50 V, +/- 10%, X7R, 1206	C16, C28	C1206C104K5RAC7TU	2	Kemet	1206	0.1uF
Fitted	CAP. CERM. 1 uF, 25 V, +/- 10%, X7R, 1206	C18, C30	12063C105KAT2A	2	AVX	1206	1uF
Fitted	Fiducial mark. There is nothing to buy or mount.	FID1, FID2, FID3, FID4, FID5, FID6	N/A	6	N/A	Fiducial	
Fitted	Receptacle, 2.54mm, 10x2, Tin, TH	J1, J2	SSQ-110-03-T-D	2	Samtec	10x2 Receptacle	
Fitted	Header (shrouded) 3.81mm, 8x1, Tin, R/A, TH	J5	H803332	1	Phoenix Contact	Header (shrouded) 3.81mm, 8x1, R/A, TH	
Fitted	Thermal Transfer Printable Labels, 0.650" W x 0.200" H - 10,000 per roll	J6, J7, J8	1888687	3	Phoenix Contact	HDR2	
Fitted	RES. 0.5%, 0.25 W, AEC-Q200 Grade 0, 1206	LBL1	THT-14-423-10	1	Brady	PCR Label 0.650 x 0.200 inch	
Fitted	RES. 0.5%, 0.25 W, AEC-Q200 Grade 0, 1206	R1	ERJ-8GEY0R00V	1	Panasonic	1206	0
Fitted	RES. 909 k, 1%, 0.1 W, AEC-Q200 Grade 0, 0603	R2	CRCW0603909KFKEA	1	Vishay-Dale	0603	909k
Fitted	6.81 kOhms +/- 1%, 0.4W, 2/SW Chip Resistor 1206 (216 Metric) Anti-Sulfur, Automotive AEC-Q200, Moisture Resistant Thin Film	R3, R4, R5, R6, R7, R9, R10, R11, R12, R13, R20, R22, R23, R24, R25, R28, R29, R30, R31, R32	TNPW12066K81BEEB	20	Vishay Dale	1206	
Fitted	RES. 301 k, 1%, 0.1 W, 0603	R8	CRCW0603301KFKEA	1	Vishay-Dale	0603	301k
Fitted	RES. 1.00 k, 1%, 0.063 W, 0402	R14	CRCW04021K00FKED	1	Vishay-Dale	0402	1.00k
Fitted	RES. 120, 0.1%, 0.1 W, 0603	R15	RT0603BRD07120BL	1	Yageo America	0603	120
Fitted	RES. 8.25 k, 0.1%, 0.1 W, 0603	R16, R27	RC1608P-8251-B-T5	2	Susumu Co Ltd	0603	8.25k
Fitted	RES. 1.00 k, 1%, 0.063 W, AEC-Q200 Grade 0, 0402	R17	CRCW04021K00FKED	1	Vishay-Dale	0402	1.00k
Fitted	RES 0 OHM JUMPER 1/4W 0603	R18, R33, R50, R51	HCJ06032TOR00	4	Stackpole Electronics	0603	0
Fitted	RES. 22.0, 0.1%, 0.063 W, 0603	R19, R45, R49	CFP0603B22R1	3	TE Connectivity	0603	22
Fitted	RES. 10.0 k, 0.1%, 0.1 W, 0603	R21, R26, R44, R46	RT0603BRD0710K	4	Yageo America	0603	10.0k
Fitted	RES. 110 k, 0.1%, 0.125 W, 0805	R34, R35, R36, R37, R38, R39, R41, R42, R43	RT0805BRD07110KL	9	Yageo America	0805	110k
Fitted	RES. 16.5 k, 0.1%, 0.1 W, 0603	R40, R48	RT0603BRD0716K5L	2	Yageo America	0603	16.5k
Fitted	RES. 2.10 k, 0.1%, 0.1 W, 0603	R47	RT0603BRD072K1L	1	Yageo America	0603	2.10k
Fitted	Linear Voltage Regulator IC 1 Output 200mA SOT-23-5	U1	TPS7A2401DBVR	1	Texas Instruments	SOT-23-5	
Fitted	Low-Drift, Low-Power, Dual-Output VREF and VREF/2 Voltage Reference, DDC0005A (SOT-23-T-5)	U2	REF2033AIDDR	1	Texas Instruments	DDC0005A	
Fitted	Isolated Solid State Relay	U3, U4	TPSI21400DWOR01	2	Texas Instruments	SOIC11	
Fitted	Precision, +/-V Input, Reinforced Isolated Amplifier With Integrated DC/DC Converter	U5, U7	AMC3330DWE	2	Texas Instruments	SOICW16	
Fitted	1-MHz, Low-Power Operational Amplifier for Cost-Sensitive Systems, DBV0005A (SOT-23-5)	U6, U8	TLV6001IDBVR	2	Texas Instruments	DBV0005A	

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#) or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2022, Texas Instruments Incorporated