Bill Of Mati Page

Dill Ol Wat Fa	dei						
tem Qu	antity Reference	Part	Comments	MFR	MFR Part#	Digi-Key Part#	PCB Footprint
1 2 3	1 C1 1 C2 5 C3,C4,C5,C28,C29	5pF_open 5pF_open 0.1uF	CAP 5.0PF 50V CERAMIC 0603 SMD. DO NOT PURCHASE, DO NOT MOUNT. CAP 5.0PF 50V CERAMIC 0603 SMD. DO NOT PURCHASE, DO NOT MOUNT. CAP CERAMIC : 1UF 50V X7R 0603	Panasonic Panasonic Panasonic	ECJ-1VC1H050C_open ECJ-1VC1H050C_open ECJ-0EX1C104K	PCC050CVCT-ND PCC050CVTR-ND PCC2398CT-ND	CAP_HDC_0603 CAP_HDC_0603 CAP_HDC_0603
4 5	2 C6,C30 3 C7,C35,C52 9 C8,C16,C18,C57,C59,C70,	10uF 1uF 10uF	CAP CER 10UF 6.3V X5R 20% 0603 CAP CER 1.0UF 16V X7R 10% 0603 CAP CER 10UF 16V X7R 10% 1206	TDK TDK TDK	C1608X5R0J106M C1608X7R1C105K C3216X7R1C106K	445-4112-1-ND 445-1604-1-ND 445-4042-1-ND	CAP_HDC_0603 CAP_HDC_0603 CAP_HDC_1206
7 8	C72,C73,C75 1 C9 14 C10,C11,C13,C19,C20,C22,	10uF 0.01uF	CAP CER 10UF 16V X7R 10% 1206 CAP CER .01UF 25V X7R 0603	Murata Johanson Dielectrics Inc	C3216X7R1C106K 250R14W103KV4T	445-4042-1-ND 709-1154-1-ND	CAP_HDC_1206 CAP_HDC_0603
9	C24,C31,C32,C36,C38,C43, C47,C60 25 C12,C14,C15,C17,C21,C23,		CAP .1UF 16V CERAMIC X7R 0603	Panasonic	ECJ-1VB1C104K	PCC1762CT-ND	CAP_HDC_0603
	C25,C33,C37,C39,C44,C45, C46,C48,C51,C53,C55,C56, C58,C61,C63,C64,C69,C71, C74						
10	2 C26,C27	100pF	CAP CERAMIC 100PF 50V 0603 SMD	Panasonic	ECJ-1VC1H101J	PCC101ACVCT-ND	CAP_HDC_0603
11	1 C34	22uF	CAP CER 22UF 6.3V X5R 20% 0805	Panasonic	C2012X5R0J226M	445-1422-1-ND	805
12	1 C40	22uF	CAP ELECT 22UF 63V FK SMD	Panasonic	EEE-FK1J220XP	PCE3821CT-ND	Radial_Surface_Mount
13	1 C41	0.1uF	CAP CER 0.1UF 50V X7R 0603	Kemet	C0603C104M5RACTU	C0603C104M5RACTU-ND	CAP_0603
14 15	1 C42 1 C49	1uF 100uF	CAP CER 1UF 50V X7R 0805	Murata	GRM21BR71H105KA12L		CAP_HDC_0805
			CAP TANTALUM 100UF 6.3V 20% SMD	Rohm Semiconductor	TCTAL0J107M8R	511-1498-2-ND	3216_12_EIA_1206
16 17	1 C50 2 C54.C62	0.01uF 10uF	CAP CER .01UF 25V X7R 0603 CAP CER 10UF 6.3V X7R 10% 0805	Johanson Dielectrics Inc Taivn Yuden	250R07W103KV4T .IMK212B7106KG-T	709-1154-1-ND 587-2396-1-ND	CAP_HDC_0603 CAP_HDC_0805
18	4 C65.C66.C67.C68	4.7uF	CAP CER 4.7UF 16V X7R 0805	Murata	GRM21BR71C475KA73L		CAP HDC 0805
19	1 D1	Green LED.0603	LED GREEN CLEAR THIN 0603 SMD	Liteon	LTST-C191KGKT	160-1446-1-ND	603
20	1 D2	DIODE SCHOTTKY	SCHOTTKY RECT 60V 1A SOD323F	NXP	PMEG6010CEJ,115	568-4138-1-ND	SC_90_SOD_323F
21	2 D3,D4	DIODE SCHOTTKY	DIODE SCHOTTKY 30V 1A SMINI	Panasonic	RSX101VA-30TR	MA21D3400LCT-ND	S_Mini_2P
22	1 D5	Orange_LED,0603	LED RED ORAN CLEAR THIN 0603 SMD	Liteon	LTST-C191KFKT	160-1445-1-ND	603
23	1 J1	HEADER 16X2	CONN FMALE 32POS DL .1" R/A GOLD	Sullins Connector Solutions	PPPC162LJBN-RC	S5569-ND	Through_Hole_Right_Angle
24 25	2 J2,J6 1 J3	IDC1X3 2x3-Pin Header	CONN HEADER .100 SINGL STR 3POS CONN HEADER .100 DUAL STR 6POS	Sullins Connector Solutions Sullins Connector Solutions	PBC03SAAN PBC03DFAN	S1011E-03-ND S2211E-03-ND	Header_1X3P Header_2X3P
26	2 J4.J7	P M5	CONN MOD JACK 8POS R/A G-Y PCB	Tyco	2-406549-1	A97715-ND	R.I45 I FD
27	1 J5	HEADER 16X2	CONN HEADER .100 DUAL R/A 32POS	Sullins Connector Solutions	PBC16DBBN	S2121E-16-ND	hdr_100mil_16X2
28	3 J8,J9,J11	CON2	CONN HEADER .100 SINGL STR 2POS	Sullins Connector Solutions	PBC02SAAN	S1011E-02-ND	CON2
29	1 J10	CONN JACK PWR	CONN POWERJACK MINI R/A PCMT	Switchcraft Inc.	RAPC712X	SC237-ND	3_terminal_thru_hole_power_jack
30	1 L1	39uH	INDUCTOR POWER 39UH 1.11A SMD	Wurth		32-1196-1-ND	Surface_Mount_
31 32	1 L2 11 L3.L4.L5.L6.L7.L8.L9.L10.	100uH	INDUCTOR 100UH 50MA 10% 0805 FERRITE CHIP 1000 OHM 0402	Taiyo Yuden	LBR2012T101K BLM15AX102SN1D	587-2048-1-ND 490-5442-1-ND	100uH RES HDC-0402
32	11 L3,L4,L5,L6,L7,L8,L9,L10, L11,L12,L13	FB 1000 Ohm,0402	FERRITE CHIP 1000 OHM 0402	Murata	BLM15AX102SN1D	490-5442-1-ND	RES_HDC-0402
33	1 P1	HSD_2X2_open	Automotive HSD Connector - Right Angle Plug for PCB. DO NOT PURCHASE, DO NOT LOAD.	Rosenberger	D4S20B-40ML5-Y_open		CON_HSD-4P_1
34	1 P2	HSD_2X2_open	Automotive HSD Connector - Right Angle Plug for PCB. DO NOT PURCHASE, DO NOT LOAD.	Rosenberger	D4S20B-40ML5-Y_open		CON_HSD-4P
35	2 Q1,Q2	MN1382N	TRANS GP SS NPN 40V SOT416	OnSemi	MMBT3904TT1G	MMBT3904TT1GOSCT-ND	SC_75
36 37	1 Q3 9 R1,R10,R12,R15,R32,R33,	PMOSFET 10K	MOSFET P-CH 20V 1.6A SSOT3 RES 10K OHM 1/10W 5% 0603 SMD	Fairchild Semiconductor Panasonic	FDN338P ERJ-3GEYJ103V	FDN338PCT-ND P10KGCT-ND	PMOSFET RES_0603
38	R35,R37,R46 4 R2,R3,R19,R29	4.7K	RES 4.7K OHM 1/10W 5% 0603 SMD	Panasonic	ERJ-3GEYJ472V	P4.7KGCT-ND	RES_0603
39	6 R4.R18.R20.R28.R31.R41	220 ohm	RES 220 OHM 1/10W 5% 0603 SMD	Panasonic	FR.I-3GFY.I221V	P220GCT-ND	RES 0603
40	9 R5,R7,R8,R9,R23,R24,R25, R26,R27		RES 33 OHM 1/10W 5% 0603 SMD	Panasonic	ERJ-3GEYJ330V	P33GCT-ND	RES_0603
41	1 R6	33 ohm	RES 33 OHM 1/10W 5% 0603 SMD	Panasonic	ERJ-3GEYJ330V	P33GCT-ND	RES_0603
42 43	5 R11,R13,R34,R36,R38 1 R14	1.0K 1K	RES 1.0K OHM 1/10W 5% 0603 SMD RES 1.0K OHM 1/10W 5% 0603 SMD	Panasonic Panasonic	ERJ-3GEYJ102V ERJ-3GEYJ102V	P1.0KGCT-ND P1.0KGCT-ND	RES_0603 RES_0603
44	2 R16,R17	33 ohm_open	RES 33 OHM 1/10W 5% 0603 SMD. DO NOT PURCHASE, DO NOT MOUNT.	Panasonic	ERJ-3GEYJ330V	P33GCT-ND	RES_0603
45	2 R21.R22	1.8K	RES 1.8K OHM 1/10W 5% 0603 SMD	Panasonic	ERJ-3GEYJ182V	P1.8KGCT-ND	RES 0603
46	2 R30,R54	75 ohm,0603	RES, 75 OHM, 5%, 1/16W, 0603	Panasonic	ERJ-3GEYJ750V	P75GCT-ND	RES_0603
47	1 R39	0 Ohm	RES ZERO OHM 1/10W 5% 0603 SMD	Panasonic	ERJ-3GEY0R00V	P0.0GTR-ND	RES_HDC_0603
48 49	1 R40 1 R42	1.0K_open 0ohm	RES 1.0K OHM 1/10W 5% 0603 SMD. DO NOT PURCHASE, DO NOT MOUNT. RES 0.0 OHM 1/10W 0603 SMD	Panasonic Panasonic	ERJ-3GEYJ102V_open ERJ-3GEY0R00V	P1.0KGCT-ND P0.0GCT-ND	RES_0603 RES_HDC_0603
50	1 R42	976_open	RES 910 OHM 1/10W 5% 0603 SMD. DO NOT PURCHASE, DO NOT MOUNT.	Panasonic	ERJ-3GEYJ911V_open	P910GCT-ND	RES_HDC_0603
51	1 R44	10K	RES 10K OHM 1/10W 5% 0603 SMD	Panasonic	ERJ-3GEYJ103V	P10KGCT-ND	RES_HDC_0402
52	1 R45	470K	RES 470K OHM 1/10W 5% 0603 SMD	Panasonic	ERJ-3GEYJ474V	P470KGCT-ND	RES_HDC_060
53	2 R47,R51	9.31K	RES 9.31K OHM 1/10W 1% 0603 SMD	Vishay/Dale	CRCW06039K31FKEA	541-9.31KHCT-ND	RES_HDC_0603
54	2 R48,R52	5.62K	RES 5.62K OHM 1/10W 1% 0603 SMD	Vishay	CRCW06035K62FKEA	541-5.62KHCT-ND	RES_HDC_0603
55 56	2 R49,R53 1 R50	51K Oohm open	RES 51K OHM 1/10W 5% 0603 SMD RES 0.0 OHM 1/10W 0603 SMD. DO NOT PURCHASE, DO NOT MOUNT.	Panasonic Panasonic	ERJ-3GEYJ513V ERJ-3GEY0R00V open	P51KGCT-ND P0.0GCT-ND	RES_HDC_0603 RES_HDC_0603
56 57	1 R50 2 R58,R59	0 ohm_open	RES 0.0 OHM 1/10W 0603 SMD. DO NOT PURCHASE, DO NOT MOUNT. RES 0.0 OHM 1/10W 0402 SMD. DO NOT PURCHASE, DO NOT MOUNT.	Panasonic Panasonic	ERJ-2GE0R00X_open	P0.0JCT-ND	RES_HDC_0603 RES_0402
58	1 S1	SW DIP-2	SWITCH DIP HALF PITCH 2POS	CTS	218-2I PST	CT2182I PST-ND	Surface Mount
59	2 S2,S4	SW PUSHBUTTON		Panasonic	EVQ-P2402M	P11080SCT-ND	SPST_NO
60	1 S3	SW DIP-4	SWITCH DIP HALF PITCH 4POS	CTS	218-4LPST	CT2184LPST-ND	CT2184LPST
61	1 U1	DS90UB901Q	IC SERIALIZER	TI	DS90UB901	DS90UB901QSQE/NOPBCT-ND	32ld_LLP
62	1 U2	ATtiny25	MCU AVR 2K ISP FLASH 1.8V 8-SOIC	Atmel	ATTINY25V-10SU	ATTINY25V-10SSU-ND	8_SOIC
63	2 U3,U7 1 U4	MN1382N, 3.4-3.7V	IC VOLT DETECT 3.4V CMOS SMD IC CONV DC/DC STEP-DOWN SOT23-5	Panasonic NSC	MN1382NP	MN1382NPCT-ND LP2992AIM5-3.3CT-ND.	Mini_3P SOT_23_5
64 65	1 U4 2 U5.U11	LP2992AIM5-3.3 LP2992AIM5-1.8	IC CONV DC/DC STEP-DOWN SOT23-5 IC REG LDO MICRPWR 250MA SOT23-5	NSC NSC	LP2992AIM5-3.3 LP2992AIM5-1.8	LP2992AIM5-3.3CT-ND. LP2992AIM5-1.8CT-ND	SOT_23_5 SOT 23 5
66	1 U6	DS90UB902Q	IC DESERIALIZER	TI	DS90UB902	DS90UB902QSQE/NOPBCT-ND	40ld_LLP
67	1 U8	LM22671MRE-5.0	IC REG SWITCH BUCK .5A 5V 8PSOP	Τi	LM22671MRE-5.0/NOPB	LM22671MRE-5.0CT-ND	8_PSOP
68	1 U9	NC7SZ14/SOT23	IC INVERTER UHS SCHMITT SC70-5	Fairchild	NC7SZ14P5X	NC7SZ14P5XCT-ND	SC70_5
69	1 U10	NC7SZ74	IC FLIP FLOP D-TYPESINGLE US8	Fairchild	NC7SZ74K8X	NC7SZ74K8XCT-ND	US8_8_VSSOP
70	2 U12,U13	LP38693MP-ADJ	IC REG LDO 500MA ADJ SOT223-4	NSC	LP38693MP-ADJ/NOPB	LP38693MP-ADJCT-ND	SOT223-4
71	1 Y1	OSC4/SM	OSCILLATOR 27.000MHZ 3.3V SMD	Abracon	ASFL1-27.000MHZ-EK-T	535-9263-1-ND	4_PIN_SMT

IMPORTANT NOTICE FOR TI REFERENCE DESIGNS

Texas Instruments Incorporated ("TI") reference designs are solely intended to assist designers ("Buyers") who are developing systems that incorporate TI semiconductor products (also referred to herein as "components"). Buyer understands and agrees that Buyer remains responsible for using its independent analysis, evaluation and judgment in designing Buyer's systems and products.

TI reference designs have been created using standard laboratory conditions and engineering practices. TI has not conducted any testing other than that specifically described in the published documentation for a particular reference design. TI may make corrections, enhancements, improvements and other changes to its reference designs.

Buyers are authorized to use TI reference designs with the TI component(s) identified in each particular reference design and to modify the reference design in the development of their end products. HOWEVER, NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY THIRD PARTY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT, Is GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of such information may require a license from a third party, or a license from TI under the patents or other intellectual property of TI.

TI REFERENCE DESIGNS ARE PROVIDED "AS IS". TI MAKES NO WARRANTIES OR REPRESENTATIONS WITH REGARD TO THE REFERENCE DESIGNS OR USE OF THE REFERENCE DESIGNS, EXPRESS, IMPLIED OR STATUTORY, INCLUDING ACCURACY OR COMPLETENESS. TI DISCLAIMS ANY WARRANTY OF TITLE AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, QUIET ENJOYMENT, QUIET POSSESSION, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS WITH REGARD TO TI REFERENCE DESIGNS OR USE THEREOF. TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY BUYERS AGAINST ANY THIRD PARTY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON A COMBINATION OF COMPONENTS PROVIDED IN A TI REFERENCE DESIGN. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, SPECIAL, INCIDENTAL, CONSEQUENTIAL OR INDIRECT DAMAGES, HOWEVER CAUSED, ON ANY THEORY OF LIABILITY AND WHETHER OR NOT TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES, ARISING IN ANY WAY OUT OF TI REFERENCE DESIGNS OR BUYER'S USE OF TI REFERENCE DESIGNS.

TI reserves the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques for TI components are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

Reproduction of significant portions of TI information in TI data books, data sheets or reference designs is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards that anticipate dangerous failures, monitor failures and their consequences, lessen the likelihood of dangerous failures and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in Buyer's safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed an agreement specifically governing such use.

Only those TI components that TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components that have *not* been so designated is solely at Buyer's risk, and Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.