

**PMP11500 REV A Bill of Materials**

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
!PCB1	1		PMP11500	Any	Printed Circuit Board	
C1, C2, C11, C12	4	1uF	GRM188R71E105KA12D	MuRata	CAP, CERM, 1 µF, 25 V, +/- 10%, X7R, 0603	0603
C3	1	10uF	UVR2E100MPD	Nichicon	CAP, AL, 10 µF, 250 V, +/- 20%, TH	10x16mm
C4	1	22uF	EEU-EE2E220	Panasonic	CAP, AL, 22 µF, 250 V, +/- 20%, TH	Cap, 10x20mm
C5	1	0.047uF	GRM32DR72J473KW01L	MuRata	CAP, CERM, 0.047 µF, 630 V, +/- 10%, X7R, 1210	1210
C7	1	0.1uF	B32520C3104K289	TDK	CAP, Film, 0.1 µF, 250 V, +/- 10%, TH	10x4x8.5mm
C8, C9	2	820uF	RL80J821MDN1KX	Nichicon	CAP, AL, 820 µF, 6.3 V, +/- 20%, 0.008 ohm, TH	D8xL8
C10	1	220uF	UKA1A221MED1TD	Nichicon	CAP, AL, 220 µF, 10 V, +/- 20%, TH	D6.3xL11mm
C13	1	1uF	GCM31MR71H105KA55L	MuRata	CAP, CERM, 1 µF, 50 V, +/- 10%, X7R, AEC-Q200 Grade 1, 1206	1206
C14	1	1000pF	DE1E3KX102MA5BA01	MuRata	CAP, CERM, 1000 pF, 250 V, +/- 20%, E, Disc, 8x12mm	Disc, 8x12mm
D1	1	600V	Z4DGP406L-HF	Comchip Technology	Diode, P-N-Bridge, 600 V, 4 A, Z4-D	Z4-D
D2	1	160V	SMCJ160A-TP	Micro Commercial Component	Diode, TVS, Uni, 160 V, 1500 W, SMC	SMC
D3	1	40V	PDS340	Diodes Inc.	Diode, Schottky, 40 V, 3 A, PowerDI5	PowerDI5
D4	1	600V	MURA160T3G	ON Semiconductor	Diode, Ultrafast, 600 V, 1 A, SMA	SMA
D5	1	100V	MMDL914-TP	Micro Commercial Component	Diode, Switching, 100 V, 0.2 A, SOD-323	SOD-323
F1	1		0452003.MRL	Littelfuse	Fuse, 3 A, 125VAC/VDC, SMD	SloBlo452
J1	1		1-1318301-2	TE Connectivity	Polarized Header, 7.92 mm, 2x1, Tin, TH	TH Header
L1	1	33uH	NR6028T330M	Taiyo Yuden	Inductor, Wirewound, Ferrite, 33 µH, 1.1 A, 0.22 ohm, SMD	6.0x2.8x6.0mm
L2	1	806uH	RLTI-1081	Renco Electronics	Coupled inductor, 806 µH, A, 0.27 ohm, TH	360x360x360mil
L3	1	470nH	SPM6530T-R47M170	TDK	Inductor, Shielded, Ferrite, 470 nH, 15.7 A, 0.0036 ohm, SMD	SMD 7.1x3.0x6.5mm
Q1	1	30V	CSD17559Q5	Texas Instruments	MOSFET, N-CH, 30 V, 100 A, SON 5x6mm	SON 5x6mm
Q2	1	650V	IPL60R299CP	Infineon Technologies	MOSFET, N-CH, 650 V, 11.1 A, PG-VSON-4	PG-VSON-4
R1	1	232k	CRCW0402232KFKED	Vishay-Dale	RES, 232 k, 1%, 0.063 W, 0402	0402
R2	1	150k	CRCW0402150KFKED	Vishay-Dale	RES, 150 k, 1%, 0.063 W, 0402	0402
R4, R14	2	10.0k	CRCW040210K0FKED	Vishay-Dale	RES, 10.0 k, 1%, 0.063 W, 0402	0402
R6	1	37.4k	CRCW040237K4FKED	Vishay-Dale	RES, 37.4 k, 1%, 0.063 W, 0402	0402
R7	1	20.0k	CRCW040220K0FKED	Vishay-Dale	RES, 20.0 k, 1%, 0.063 W, 0402	0402
R10	1	5.1	CRCW06035R10JNEA	Vishay-Dale	RES, 5.1, 5%, 0.1 W, 0603	0603
R11	1	76.8k	CRCW040276K8FKED	Vishay-Dale	RES, 76.8 k, 1%, 0.063 W, 0402	0402
R12	1	1.00k	CRCW04021K00FKED	Vishay-Dale	RES, 1.00 k, 1%, 0.063 W, 0402	0402
R13, R17	2	30.1k	CRCW040230K1FKED	Vishay-Dale	RES, 30.1 k, 1%, 0.063 W, 0402	0402
R15	1	0.82	ERJ-6RQFR82V	Panasonic	RES, 0.82, 1%, 0.125 W, 0805	0805
R16	1	1.00	CRCW08051R00FKEA	Vishay-Dale	RES, 1.00, 1%, 0.125 W, 0805	0805
T1	1	230uH	TBD	Renco Electronics	Transformer, 230 uH, TH	670x720mil
TP1	1	Red	5010	Keystone	Test Point, Multipurpose, Red, TH	Red Multipurpose Testpoint
TP2	1	Black	5011	Keystone	Test Point, Multipurpose, Black, TH	Black Multipurpose Testpoint
U1	1		UCC24650DBVR	Texas Instruments	200-V Wake-Up Monitor for Fast Transient PSR, DBV0005A	DBV0005A
U2	1		UCC24636DBVR	Texas Instruments	SYNCHRONOUS RECTIFIER CONTROLLER WITH LOW POWER STANDBY, DBV0006A	DBV0006A
U3	1		UCC28730DR	Texas Instruments	Constant-Voltage Constant-Current Flyback Controller With PSR and Wake-Up Monitoring, D0007A	D0007A
C6	0	2200pF	GRM1885C1H222JA01D	MuRata	CAP, CERM, 2200 pF, 50 V, +/- 5%, C0G/NP0, 0603	0603
C15	0	0.022uF	GRM155R71H223KA12D	MuRata	CAP, CERM, 0.022 µF, 50 V, +/- 10%, X7R, 0402	0402
C16	0	10uF	GRM219R61A106KE44D	MuRata	CAP, CERM, 10 µF, 10 V, +/- 10%, X5R, 0805	0805

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
D6	0	30V	BAT54ST-7-F	Diodes Inc.	Diode, Schottky, 30 V, 0.2 A, SOT-523	SOT-523
R3	0	4.7	CRCW12064R70JNEA	Vishay-Dale	RES, 4.7, 5%, 0.25 W, 1206	1206
R5, R8	0	0	CRCW12060000Z0EA	Vishay-Dale	RES, 0, 5%, 0.25 W, 1206	1206
R9	0	2.49k	CRCW04022K49FKED	Vishay-Dale	RES, 2.49 k, 1%, 0.063 W, 0402	0402
R18	0	0	CRCW04020000Z0ED	Vishay-Dale	RES, 0, 5%, 0.063 W, 0402	0402
R19	0	1.00k	CRCW04021K00FKED	Vishay-Dale	RES, 1.00 k, 1%, 0.063 W, 0402	0402
R20	0	4.99k	CRCW04024K99FKED	Vishay-Dale	RES, 4.99 k, 1%, 0.063 W, 0402	0402
R21	0	20.0k	CRCW040220K0FKED	Vishay-Dale	RES, 20.0 k, 1%, 0.063 W, 0402	0402
R22	0	30.1k	CRCW040230K1FKED	Vishay-Dale	RES, 30.1 k, 1%, 0.063 W, 0402	0402
R23	0	10.0k	CRCW040210K0FKED	Vishay-Dale	RES, 10.0 k, 1%, 0.063 W, 0402	0402
R24	0	5.23k	CRCW04025K23FKED	Vishay-Dale	RES, 5.23 k, 1%, 0.063 W, 0402	0402
R25	0	100k	CRCW0402100KFKED	Vishay-Dale	RES, 100 k, 1%, 0.063 W, 0402	0402
U4	0		VOS617A-7X001T	Vishay-Semiconductor	OptoCoupler, Phototransitor, 80-160%, SSOP-4	7x2.12x2.6mm
U5	0		TL431AIDBZR	Texas Instruments	Adjustable Precision Shunt Regulator, 34 ppm / degC, 100 mA, -40 to 85 degC, 3-pin SOT-23 (DBZ), Green (RoHS & no Sb/Br)	DBZ0003A

## IMPORTANT NOTICE FOR TI DESIGN INFORMATION AND RESOURCES

Texas Instruments Incorporated ("TI") technical, application or other design advice, services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using any particular TI Resource in any way, you (individually or, if you are acting on behalf of a company, your company) agree to use it solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources.

You understand and agree that you remain responsible for using your independent analysis, evaluation and judgment in designing your applications and that you have full and exclusive responsibility to assure the safety of your applications and compliance of your applications (and of all TI products used in or for your applications) with all applicable regulations, laws and other applicable requirements. You represent that, with respect to your applications, you have all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. You agree that prior to using or distributing any applications that include TI products, you will thoroughly test such applications and the functionality of such TI products as used in such applications. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

You are authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING TI RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY YOU AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

You agree to fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of your non-compliance with the terms and provisions of this Notice.

This Notice applies to TI Resources. Additional terms apply to the use and purchase of certain types of materials, TI products and services. These include; without limitation, TI's standard terms for semiconductor products (<http://www.ti.com/sc/docs/stdterms.htm>), [evaluation modules](#), and [samples](http://www.ti.com/sc/docs/sampterm.htm) (<http://www.ti.com/sc/docs/sampterm.htm>).

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265  
Copyright © 2017, Texas Instruments Incorporated