TID#	TIDA-01432					
REFERENCE DESIGNATOR			DESCRIPTION	PACKAGEREFERENCE	PART NUMBER	MANUFACTURER
C1			CAP, CERM, 2.2 µF, 50 V, +/- 10%, X5R, 0805	0805	C2012X5R1H225K125AB	TDK
C5	1	10uF	CAP, CERM, 10uF, 50V, +/-10%, X7R, 1210	1210	GRM32ER71H106KA12L	MuRata
C6, C9	2	4700pF	CAP, CERM, 4700 pF, 100 V, +/- 5%, C0G/NP0, 0603	0603	C0603C472J1GAC7867	Kemet
C7		•	CAP, CERM, 0.01 µF, 10 V, +/- 10%, X5R, 0402	0402	GRM155R61A103KA01D	MuRata
C8			CAP, CERM, 4.7 µF, 35 V, +/- 10%, X5R, 0603	0603	C1608X5R1V475K080AC	
C10	1		CAP, CERM, 12 pF, 25 V, +/- 5%, C0G/NP0, AEC-Q200 Grade 1, 0402	0402	C0402C120J3GACAUTO	Kemet
C13	1	470uF	CAP, AL, 470 µF, 50 V, +/- 20%, SMD	KG5	EMVA500ATR471MKG5S	Chemi-Con
C14, C16, C17	3	10uF	CAP, CERM, 10 µF, 10 V, +/- 10%, X7R, AEC-Q200 Grade 1, 1206_190	1206 190	GCM31CR71A106KA64L	MuRata
C15, C18, C20, C21, C22, C23	6	0.1uF	CAP, CERM, 0.1 µF, 50 V, +/- 10%, X7R, 0603	0603	GCM188R71H104KA57D	MuRata
C19	1		CAP, CERM, 2.2 µF, 25 V, +/- 10%, X5R, 0402	0402	C1005X5R1E225K050BC	TDK
Cbias1	1	0.1uF	CAP, CERM, 0.1 µF, 50 V, +/- 10%, X7R, 0402	0402	C1005X7R1H104K050BB	TDK
Cboot1	1	0.47uF	CAP, CERM, 0.47 µF, 10 V, +/- 10%, X5R, 0402	0402	C1005X5R1A474K050BB	TDK
Cin1	1	47uF	CAP, AL, 47 μF, 63 V, +/- 20%, 0.65 ohm, SMD	SMT Radial F	EEE-FK1J470P	Panasonic
Cin2, Cin3	2	10uF	CAP, CERM, 10 µF, 50 V, +/- 10%, X7R, 1210	1210	GRM32ER71H106KA12L	MuRata
Cin4, Cin5	2	0.047uF	CAP, CERM, 0.047 μF, 50 V,+/- 10%, X7R, 0603	0603	GRM188R71H473KA61D	MuRata
COUT1, COUT2	2	22uF	CAP, CERM, 22 μF, 25 V, +/- 10%, X5R, 1210	1210	GRM32ER61E226KE15L	MuRata
COUT3	1	120uF	CAP, AL, 120 μF, 10 V, +/- 20%, 0.025 ohm, SMD	F61	APXE100ARA121MF61G	Chemi-Con
COUT4	1	0.047uF	CAP, CERM, 0.047 µF, 25 V, +/- 10%, X7R, AEC-Q200 Grade 1, 0603	0603	GCM188R71E473KA37D	MuRata
Csnub1	1	3300pF	CAP, CERM, 3300 pF, 10 V, +/- 10%, X5R, 0201	0201	GRM033R61A332KA01D	MuRata
D1	1	28V	Diode, TVS, Bi, 28 V, 45.4 Vc, SMB	SMB	SMBJ28CA-13-F	Diodes Inc.
D2, D3	2	16V	Diode, TVS, Bi, 16 V, 400 W, SMA	SMA	SMAJ16CA	Littelfuse
D4	1	5V	Diode, TVS, Uni, 5 V, 20 W, AEC-Q101, SOT-416	SOT-416	ESDR0502BT1G	ON Semiconductor
J1	1		RF Coaxial Connector, Bordeaux, R/A, TH	Right Angle Plug for PCB, 6-Lead, TH	99S20D-40MA5-D	Rosenberger
J2	1		Receptacle, USB TYPE C, R/A, SMT	Receptacle, USB TYPE C, R/A, SMT	201267-0001	Molex
L1	1	10uH	Inductor, Shielded, Composite, 10 µH, 4.9 A, 0.05 ohm, SMD	XAL5050	XAL5050-103MEB	Coilcraft
L2	1	8.2uH	Inductor, Shielded, Ferrite, 8.2 µH, 4.5 A, 0.0505 ohm, SMD	Inductor, 7.2x4x6.5mm	SRP6540-8R2M	Bourns
Q1	1	40V	MOSFET, N-CH, 40 V, 75 A, PowerPAK_SO-8L	PowerPAK_SO-8L	SQJ422EP-T1-GE3	Vishay-Siliconix
R1	1	0	RES, 0, 5%, 0.063 W, 0402	0402	CRCW04020000Z0ED	Vishay-Dale
R2		1.00k	RES, 1.00 k, 1%, 0.1 W, 0402	0402	ERJ-2RKF1001X	Panasonic
R3, R20	2	0	RES, 0, 5%, 0.063 W, 0402	0402	MCR01MZPJ000	Rohm
R4		5.11k	RES, 5.11 k, 1%, 0.063 W, 0402	0402	CRCW04025K11FKED	Vishay-Dale
R5, R6, R7, R8, R9		100k	RES, 100 k, 1%, 0.063 W, AEC-Q200 Grade 0, 0402	0402	RMCF0402FT100K	Stackpole Electronics Inc
R10	1	2.00k	RES, 2.00 k, 1%, 0.063 W, 0402	0402	CRCW04022K00FKED	Vishay-Dale
R11	1	15.4k	RES, 15.4 k, 1%, 0.063 W, 0402	0402	CRCW040215K4FKED	Vishay-Dale
R12		80.6k	RES, 80.6 k, 1%, 0.063 W, 0402	0402	CRCW040280K6FKED	Vishay-Dale
R13, R14, R16		200k	RES, 200 k, 1%, 0.063 W, 0402	0402	CRCW0402200KFKED	Vishay-Dale
R15		26.1k	RES, 26.1 k, 1%, 0.063 W, 0402	0402	CRCW040226K1FKED	Vishay-Dale
R17		1.00k	RES, 1.00 k, 1%, 0.063 W, 0402	0402	CRCW04021K00FKED	Vishay-Dale
R18		10.0k	RES, 10.0 k, 1%, 0.063 W, 0402	0402	CRCW040210K0FKED	Vishay-Dale
R19		49.9k	RES, 49.9 k, 1%, 0.063 W, 0402	0402	CRCW040249K9FKED	Vishay-Dale
Rbias1		3.0	RES, 3.0, 5%, 0.063 W, 0402	0402	CRCW04023R00JNED	Vishay-Dale
RFA1		2.94k	RES, 2.94 k, 1%, 0.063 W, 0402	0402	CRCW04022K94FKED	Vishay-Dale
RFB1		49.9k	RES, 49.9 k, 1%, 0.1 W, AEC-Q200 Grade 0, 0402	0402	ERJ-2RKF4992X	Panasonic
RG1		12.1k	RES, 12.1 k, 1%, 0.063 W, 0402	0402	CRCW040212K1FKED	Vishay-Dale
Rsnub1		8.2	RES, 8.2, 5%, 0.063 W, 0402	0402	CRCW04028R20JNED	Vishay-Dale
TP1, TP2	2		Test Point, Miniature, Red, TH	Red Miniature Testpoint	5000	Keystone
TP3, TP5	2		Test Point, Miniature, Black, TH	Black Miniature Testpoint	5001	Keystone
U1	1		LMS3635AQRNLRQ1, RNL0022A (VQFN-HR-22)	RNL0022A	LMS3635AQRNLRQ1	Texas Instruments
U3	1		Automotive USB Charging Port Controller and Power Switch with Short to BAT protection, RVC0020A	RVC0020A	TPS254900IRVCRQ1	Texas Instruments
U4	1		USB 2.0 HIGH SPEED SIGNAL CONDITIONER, RGY0014A (VQFN-14)	RGY0014A	TUSB213RGYR	Texas Instruments
U5	1		USB Type-C DFP Port Controller, DRF0008A	DRF0008A	TUSB319DRFRQ1	Texas Instruments
U6	1		Single Inverter Gate, DCK0005A (SOT-5)	DCK0005A	SN74AHCT1G04DCKR	Texas Instruments
U7	1		Zero Iq Reverse Polarity Protection Smart Diode Controller, DGK0008A (VSSOP-8)	DGK0008A	LM74610QDGKRQ1	Texas Instruments

IMPORTANT NOTICE FOR TI DESIGN INFORMATION AND RESOURCES

Texas Instruments Incorporated ('TI") technical, application or other design advice, services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using any particular TI Resource in any way, you (individually or, if you are acting on behalf of a company, your company) agree to use it solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources.

You understand and agree that you remain responsible for using your independent analysis, evaluation and judgment in designing your applications and that you have full and exclusive responsibility to assure the safety of your applications and compliance of your applications (and of all TI products used in or for your applications) with all applicable regulations, laws and other applicable requirements. You represent that, with respect to your applications, you have all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. You agree that prior to using or distributing any applications. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

You are authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING TI RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY YOU AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

You agree to fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of your noncompliance with the terms and provisions of this Notice.

This Notice applies to TI Resources. Additional terms apply to the use and purchase of certain types of materials, TI products and services. These include; without limitation, TI's standard terms for semiconductor products http://www.ti.com/sc/docs/stdterms.htm), evaluation modules, and samples (http://www.ti.com/sc/docs/stdterms.htm), evaluation

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2017, Texas Instruments Incorporated