

Bill of Materials

Bill of Materials								
Ref.	Part name	Pcs/Unit	Description	Manufacturer	Part number	Supplier	Ordering code	Alt. Manufacturer
C11	C_47N_0402_X7R_K_25	1	Capacitor, 47n, 0402, X7R, 10%, 25V	Murata	GRM155R71E473KA88D			
C12	C_100N_0402_X5R_K_10	0	Do not mount					
C41	C_10N_0402_X7R_K_25	0	Do not mount					
G51	C_47N_0402_X7R_K_25	1	Capacitor, 47n, 0402, X7R, 10%, 25V	Murata	GRM155R71E473KA88D			
C52	C_2U2_0603_X5R_K_10	1	Capacitor, 2u2, 0603, X5R, 10%, 10V	Murata	GRM188R61A225KE34D			
G53	C_0402	0	Do not mount					
C61	C_220N_0402_X5R_K_10	1	Capacitor, 220n, 0402, X5R, 10%, 10V	Murata	GRM155R61A224KE19D			
C121	C_47N_0402_X7R_K_25	1	Capacitor, 47n, 0402, X7R, 10%, 25V	Murata	GRM155R71E473KA88D			
C131	C_47N_0402_X7R_K_25	1	Capacitor, 47n, 0402, X7R, 10%, 25V	Murata	GRM155R71E473KA88D			
C151	C_47N_0402_X7R_K_25	1	Capacitor, 47n, 0402, X7R, 10%, 25V	Murata	GRM155R71E473KA88D			
C171	C_10N_0402_X7R_K_25	1	Capacitor, 10n, 0402, X7R, 10%, 25V	Murata	GRM155R71E103KA01D			
C172	C_100P_0402_NP0_J_50	1	Capacitor, 100p, 0402, NP0, 5%, 50V	Murata	GRM1555C1H101JZ01D			
C173	C_33P_0402_NP0_J_50	1	Capacitor, 33p, 0402, NP0, 5%, 50V	Murata	GRM1555C1H330JZ01D			
C174	C_15P_0402_NP0_J_50	1	Capacitor, 15p, 0402, NP0, 5%, 50V	Murata	GRM1555C1H150JZ01D			
G175	C_3P0_0402_NP0_C_50	1	Capacitor, 3p0, 0402, NP0, +/-0.25pF, 50V	Murata	GRM1555C1H3R0CZ01D			
G176	C_1P0_0402_NP0_B_50	2	Capacitor, 1p, 0402, NP0, +/-0.1pF, 50V	Murata	GRM1555C1H1R0BZ01D			
C177	C_0402	0	Do not mount					
C181	C_2P2_0402_NP0_C_50	1	Capacitor, 2p2, 0402, NP0, +/-0.25pF, 50V	Murata	GRM1555C1H2R2CZ01D			
C191	C_3P3_0402_NP0_C_50	1	Capacitor, 3p3, 0402, NP0, +/-0.25pF, 50V	Murata	GRM1555C1H3R3CZ01D			
C201	C_3P3_0402_NP0_C_50	1	Capacitor, 3p3, 0402, NP0, +/-0.25pF, 50V	Murata	GRM1555C1H3R3CZ01D			
C211	C_10N_0402_X7R_K_25	1	Capacitor, 10n, 0402, X7R, 10%, 25V	Murata	GRM155R71E103KA01D			
C221	C_47N_0402_X7R_K_25	1	Capacitor, 47n, 0402, X7R, 10%, 25V	Murata	GRM155R71E473KA88D			
C231	C_1N8_0402_U2J_J_10	1	Capacitor, 1n8, 0402, U2J, 5%, 10V	Murata	GRM1557J1A182JA01D			
C251	C_47N_0402_X7R_K_25	1	Capacitor, 47n, 0402, X7R, 10%, 25V	Murata	GRM155R71E473KA88D			
C261	C_47N_0402_X7R_K_25	1	Capacitor, 47n, 0402, X7R, 10%, 25V	Murata	GRM155R71E473KA88D			
C271	C_47N_0402_X7R_K_25	1	Capacitor, 47n, 0402, X7R, 10%, 25V	Murata	GRM155R71E473KA88D			
C281	C_47N_0402_X7R_K_25	1	Capacitor, 47n, 0402, X7R, 10%, 25V	Murata	GRM155R71E473KA88D			
C291	C_47N_0402_X7R_K_25	1	Capacitor, 47n, 0402, X7R, 10%, 25V	Murata	GRM155R71E473KA88D			
C301	R_0_0402	1	Resistor, 0 ohm, 0402	Koa	RK73Z1ETTP	ELFA	60-470-05	
C302	C_0402	0	Do not mount					
C311	C_15P_0402_NP0_J_50	0	Do not mount					
C321	C_100N_0402_X5R_K_10	1	Capacitor, 100n, 0402, X5R, 10%, 10V	Murata	GRM155R71A104KA01D			
C322	C_22P_0402_NP0_J_50	1	Capacitor, 22p, 0402, NP0, 5%, 50V	Murata	GRM1555C1H220JZ01D			
L1	L_BEAD_102_0402	1	EMI filter bead, 0402, 1k ohms Tape GHz Band Gen	Murata	BLM15SHG102SN1D	ACTE		
L171	L_10N_0402_J_LOW	1	Inductor, 10n, 0402, a5%, wire-wound type	Murata	LOW15AN10NJ00D			
L172	L_7N5_0402_G_LOW	1	Inductor, 7n5, 0402, a2%, wire-wound type	Murata	LOW15AN7NSG00D			
L173	L_18N_0402_J_LOW	1	Inductor, 18n, 0402, a5%, wire-wound type	Murata	LOW15AN18NJ00D			
L174	L_12N_0402_J_LOW	1	Inductor, 12n, 0402, a5%, wire-wound type	Murata	LOW15AN12NJ00D			
L191	L_15N_0402_J_LOW	1	Inductor, 15n, 0402, a5%, wire-wound type	Murata	LOW15AN15NJ00D			
L192	L_12N_0402_J_LOW	1	Inductor, 12n, 0402, a5%, wire-wound type	Murata	LOW15AN12NJ00D			
L193	L_12N_0402_J_LOW	1	Inductor, 12n, 0402, a5%, wire-wound type	Murata	LOW15AN12NJ00D			
L201	L_12N_0402_J_LOW	1	Inductor, 12n, 0402, a5%, wire-wound type	Murata	LOW15AN12NJ00D			
P1	SMD_SOCKET_2x10	1	SMD pinrow socket, .050 spacing, 2x10	Samtec	SFM-110-02-SM-D-A-K-TR	Abacus		
P2	SMD_SOCKET_2x10	1	SMD pinrow socket, .050 spacing, 2x10	Samtec	SFM-110-02-SM-D-A-K-TR	Abacus		
P3	SMA_SMD	1	SMA connector, straight SMD-mount					
R12	R_0_0402	0	Do not mount					
R141	R_56K_0402_F	1	Resistor, 56k ohms, 0402, a1%	Koa	RK73H1ETTP5602F	ELFA	60-488-96	
R171	R_10_0402_J	1	Resistor, 10 ohms, 0402, 5%	Koa	RK73H1ETTP10R0F (a1%)	ELFA	60-470-96	
R321	R_0402	0	Do not mount					
R322	R_0_0402	1	Resistor, 0 ohm, 0402	Koa	RK73Z1ETTP	ELFA	60-470-05	
U1	CC112X	1	TI transceiver	Texas Instruments				
U2	TPS79930	0	Do not mount					
X1	X_32.000/15/18/60/10	0	Do not mount					#N/A
X2	TG_5021CG	1	TCXO 40.000000MHz (2.5x2.0x0.9mm) Supply volt	Epson Toyocom	TG_5021CG	ACTE	X1G003581000300	

IMPORTANT NOTICE FOR TI REFERENCE DESIGNS

Texas Instruments Incorporated ("TI") reference designs are solely intended to assist designers ("Buyers") who are developing systems that incorporate TI semiconductor products (also referred to herein as "components"). Buyer understands and agrees that Buyer remains responsible for using its independent analysis, evaluation and judgment in designing Buyer's systems and products.

TI reference designs have been created using standard laboratory conditions and engineering practices. **TI has not conducted any testing other than that specifically described in the published documentation for a particular reference design.** TI may make corrections, enhancements, improvements and other changes to its reference designs.

Buyers are authorized to use TI reference designs with the TI component(s) identified in each particular reference design and to modify the reference design in the development of their end products. HOWEVER, NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY THIRD PARTY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT, IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI REFERENCE DESIGNS ARE PROVIDED "AS IS". TI MAKES NO WARRANTIES OR REPRESENTATIONS WITH REGARD TO THE REFERENCE DESIGNS OR USE OF THE REFERENCE DESIGNS, EXPRESS, IMPLIED OR STATUTORY, INCLUDING ACCURACY OR COMPLETENESS. TI DISCLAIMS ANY WARRANTY OF TITLE AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, QUIET ENJOYMENT, QUIET POSSESSION, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS WITH REGARD TO TI REFERENCE DESIGNS OR USE THEREOF. TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY BUYERS AGAINST ANY THIRD PARTY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON A COMBINATION OF COMPONENTS PROVIDED IN A TI REFERENCE DESIGN. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, SPECIAL, INCIDENTAL, CONSEQUENTIAL OR INDIRECT DAMAGES, HOWEVER CAUSED, ON ANY THEORY OF LIABILITY AND WHETHER OR NOT TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES, ARISING IN ANY WAY OUT OF TI REFERENCE DESIGNS OR BUYER'S USE OF TI REFERENCE DESIGNS.

TI reserves the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques for TI components are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

Reproduction of significant portions of TI information in TI data books, data sheets or reference designs is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards that anticipate dangerous failures, monitor failures and their consequences, lessen the likelihood of dangerous failures and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in Buyer's safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed an agreement specifically governing such use.

Only those TI components that TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components that have **not** been so designated is solely at Buyer's risk, and Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.