

TIDM-TM4C129USBHS REV A0 Bill of Materials

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
IPCB	1		TIDM-TM4C129USBHS	Any	Printed Circuit Board	
C1, C3, C4, C5, C6, C7, C8, C9, C10, C11, C12, C13, C14, C19, C26	15	0.1uF	GRM155R71C104KA88D	MuRata	CAP, CERM, 0.1 μF, 16 V, +/- 10%, X7R, 0402	0402
C2, C18	2	1uF	C1005X5R1C105K050BC	TDK	CAP, CERM, 1 μF, 16 V, +/- 10%, X5R, 0402	0402
C15, C16	2	0.01uF	GRM155R71C103KA01D	MuRata	CAP, CERM, 0.01 μF, 16 V, +/- 10%, X7R, 0402	0402
C17	1	2.2uF	GRM155R61C225KE11D	MuRata	CAP, CERM, 2.2 μF, 16 V, +/- 10%, X5R, 0402	0402
C20, C21	2	22pF	C1005C0G1H220J050BA	TDK	CAP, CERM, 22 pF, 50 V, +/- 5%, C0G/NP0, 0402	0402
C22, C28, C29	3	0.1uF	C0603C104J3RAC	Kemet	CAP, CERM, 0.1 μF, 25 V, +/- 5%, X7R, 0603	0603
C23, C24	2	0.1uF	EMK107B7104KA-T	Taiyo Yuden	CAP, CERM, 0.1 μF, 16 V, +/- 10%, X7R, 0603	0603
C25	1	2.2uF	GRM188R61C225KE15D	MuRata	CAP, CERM, 2.2 μF, 16 V, +/- 10%, X5R, 0603	0603
C27	1	3300pF	C0603X332K5RACTU	Kemet	CAP, CERM, 3300 pF, 50 V, +/- 10%, X7R, 0603	0603
C30, C31, C33, C34	4	0.1uF	C1005X5R0J104K	TDK	CAP, CERM, 0.1 μF, 6.3 V, +/- 10%, X5R, 0402	0402
C32	1	0.1uF	08053C104KAT2A	AVX	CAP, CERM, 0.1 μF, 25 V, +/- 10%, X7R, 0805	0805
C35, C36, C37, C38	4	0.1uF	GCM155R71C104KA55D	MuRata	CAP, CERM, 0.1 μF, 16 V, +/- 10%, X7R, 0402	0402
C39, C52	2	4700pF	1812GC472KA1	AVX	CAP, CERM, 4700 pF, 2000 V, +/- 10%, X7R, 1812	1812
C40, C41, C42, C43, C45, C47, C51	7	0.1uF	06035C104KAT2A	AVX	CAP, CERM, 0.1 μF, 50 V, +/- 10%, X7R, 0603	0603
C44, C46	2	4.7uF	C2012X7R1A475M	TDK	CAP, CERM, 4.7 μF, 10 V, +/- 20%, X7R, 0805	0805
C48, C49	2	15pF	06035A150JAT2A	AVX	CAP, CERM, 15 pF, 50 V, +/- 5%, C0G/NP0, 0603	0603
C50	1	1uF	GRM188R71A105KA61D	MuRata	CAP, CERM, 1 μF, 10 V, +/- 10%, X7R, 0603	0603
D1, D2, D3	3	Green	QTLP630C4TR	Everlight	LED, Green, SMD	2x1.25mm
D4	1		SLVU2.8-4.TBT	Semtech	Diode, TVS, Uni, 2.8 V, 400 W, SO-8	SO-8
FB1, FB2	2	120 ohm	BLM18AG121SN1D	MuRata	Ferrite Bead, 120 ohm @ 100 MHz, 0.5 A, 0603	0603
FID1, FID2, FID3	3		N/A	N/A	Fiducial mark. There is nothing to buy or mount.	Fiducial
J1	1		TSW-102-07-G-S	Samtec	Header, 100mil, 2x1, Gold, TH	2x1 Header
J2, J4	2		FTSH-110-01-L-DV-K	Samtec	Header (Shrouded), 1.27mm, 10x2, Tin, SMT	Header (Shrouded), 1.27mm, 10x2, SMT
J3	1		FTSH-105-01-F-DV	Samtec	Header, 1.27mm, 5x2, Gold, Black, SMT	Header, 1.27mm, 5x2, SMT
J5	1		1734354-1	TE Connectivity	Receptacle, D-Sub, 9 Position, R/A, TH	Receptacle, D-Sub, 9 Position, R/A, TH
J6	1		A-2014-3-4-N-T-R	Assman WSW	Modular Connector, Jack, 4P4C, Gold, TH	CONN MOD JACK 4P4C VERT UNSHLD, TH
J7	1		TSM-110-01-L-DV-P	Samtec	Header, 2.54mm, 10x2, Gold, SMT	1000x180x290mil
J8	1		182-009-213R171	NorComp	CONN DB9 FEMALE R/A SOLDER TH	D-SUB 9 PIN
J9	1		J0011D21BNL	Pulse Engineering	Connector, RJ-45 with integrated magnetics, 1x1, Gold, R/A, TH	Connector, RJ-45
J10	1		1981568-1	TE Connectivity	Connector, Receptacle, Micro-USB Type B, R/A, Bottom Mount SMT	MICRO USB CONN, R/A
J11	1		TSW-103-07-G-D	Samtec	Header, 100mil, 3x2, Gold, TH	3x2 Header
R1	1	51	CRCW060351R0JNEA	Vishay-Dale	RES, 51, 5%, 0.1 W, 0603	0603
R2	1	0	ERJ-2GEOR00X	Panasonic	RES, 0, 5%, 0.063 W, 0402	0402
R3	1	4.87k	CRCW04024K87FKED	Vishay-Dale	RES, 4.87 k, 1%, 0.063 W, 0402	0402

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
R4, R23, R25	3	100	CRCW0402100RJNED	Vishay-Dale	RES, 100, 5%, 0.063 W, 0402	0402
R5, R24, R26	3	10k	CRCW040210K0JNED	Vishay-Dale	RES, 10 k, 5%, 0.063 W, 0402	0402
R6	1	100k	ERJ-2RKF1003X	Panasonic	RES, 100 k, 1%, 0.1 W, 0402	0402
R7, R21, R22, R32, R33	5	330	RC0603JR-07330RL	Yageo America	RES, 330, 5%, 0.1 W, 0603	0603
R8, R9	2	4.7k	CRCW06034K70JNEA	Vishay-Dale	RES, 4.7 k, 5%, 0.1 W, 0603	0603
R10	1	100	CRCW0603100RJNEA	Vishay-Dale	RES, 100, 5%, 0.1 W, 0603	0603
R11, R12, R13, R14	4	33	CRCW060333R0JNEA	Vishay-Dale	RES, 33, 5%, 0.1 W, 0603	0603
R15, R16, R17, R18, R27	5	10k	CRCW060310K0JNEA	Vishay-Dale	RES, 10 k, 5%, 0.1 W, 0603	0603
R19	1	120	RC0603FR-07120RL	Yageo America	RES, 120, 1%, 0.1 W, 0603	0603
R20, R36	2	1.0Meg	CRCW06031M00JNEA	Vishay-Dale	RES, 1.0 M, 5%, 0.1 W, 0603	0603
R28, R29, R30, R31	4	49.9	CRCW040249R9FKED	Vishay-Dale	RES, 49.9, 1%, 0.063 W, 0402	0402
R34, R44	2	1.0Meg	CRCW12061M00JNEA	Vishay-Dale	RES, 1.0 M, 5%, 0.25 W, 1206	1206
R35, R39	2	10.0k	RCG060310K0FKEA	Vishay Draloric	RES, 10.0 k, 1%, 0.1 W, 0603	0603
R37	1	820	RC0603FR-07820RL	Yageo America	RES, 820, 1%, 0.1 W, 0603	0603
R38	1	12.0k	RC0603FR-0712KL	Yageo America	RES, 12.0 k, 1%, 0.1 W, 0603	0603
R40, R41, R42, R43	4	10k	RC0603JR-0710KL	Yageo America	RES, 10 k, 5%, 0.1 W, 0603	0603
S1, S2, S3	3		SKRKAEE010	Alps	Switch, Push Button, SMD	2.9x2x3.9mm SMD
S4	1		1825115-1	TE Connectivity	Switch, SPDT, On-On, 2 Pos, TH	433x220mil
TP1, TP2, TP3, TP4	4		TMS-101-02-T-S	Samtec	Header, 1x1, Tin, TH	Header, 1x1, 50mil, TH
U1	1		TM4C129ENCPDTI3R	Texas Instruments	Tiva C Series Microcontroller, PDT0128A	PDT0128A
U2	1		TPS73733DCQR	Texas Instruments	Single Output LDO, 1 A, Fixed 3.3 V Output, 2.2 to 5.5 V Input, with Reverse Current Protection, 6-pin SOT-223 (DCQ), -40 to 125 degC, Green (RoHS & no Sb/Br)	DCQ0006A
U3	1		SN65HVD1050D	Texas Instruments	High-Speed EMC Optimized CAN Transceiver, 70 mA, 5 V, -40 to 125 degC, 8-pin SOIC (D), Green (RoHS & no Sb/Br)	D0008A
U4	1		MAX3232CPW	Texas Instruments	3-V to 5.5-V Multichannel RS-232 Line Driver / Receiver with ±15-kV ESD Protection, 0 to 70 degC, 16-Pin TSSOP (PW), Green (RoHS & no Sb/Br)	PW0016A
U5	1		TPD2E2U06DRLR	Texas Instruments	DUAL CHANNEL HIGH SPEED ESD PROTECTION DEVICE, DRL0005A	DRL0005A
U6	1		USB3300-EZK	Microchip	Hi-Speed USB Host, Device or OTG PHY with ULPI Low Pin Interface, QFN-32	5x5 QFN-32
U7	1		TS3USB221ERSER	Texas Instruments	High-Speed USB 2.0 (480 Mbps) 1:2 Multiplexer / Demultiplexer Switch with Single Enable, 6 ohm RON, 2.5 to 3.3V, -40 to 85 degC, 10-Pin UQFN (RSE), Green (RoHS & no Sb/Br)	RSE0010A
U8	1		TXB0106PWR	Texas Instruments	6-BIT BIDIRECTIONAL VOLTAGE-LEVEL TRANSLATOR WITH AUTO-DIRECTION SENSING AND ±15-kV ESD PROTECTION, PW0016A	PW0016A
Y1	1		NX5032GA-25.000M-STD-CSK-4	NDK	Crystal, 25MHz, SMD	5x3.2mm
Y2	1		NX5032GA-24.000M-STD-CSK-4	NDK	Crystal, 24MHz, SMD	5x3.2mm

IMPORTANT NOTICE FOR TI DESIGN INFORMATION AND RESOURCES

Texas Instruments Incorporated ("TI") technical, application or other design advice, services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using any particular TI Resource in any way, you (individually or, if you are acting on behalf of a company, your company) agree to use it solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources.

You understand and agree that you remain responsible for using your independent analysis, evaluation and judgment in designing your applications and that you have full and exclusive responsibility to assure the safety of your applications and compliance of your applications (and of all TI products used in or for your applications) with all applicable regulations, laws and other applicable requirements. You represent that, with respect to your applications, you have all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. You agree that prior to using or distributing any applications that include TI products, you will thoroughly test such applications and the functionality of such TI products as used in such applications. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

You are authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING TI RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY YOU AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

You agree to fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of your non-compliance with the terms and provisions of this Notice.

This Notice applies to TI Resources. Additional terms apply to the use and purchase of certain types of materials, TI products and services. These include; without limitation, TI's standard terms for semiconductor products (<http://www.ti.com/sc/docs/stdterms.htm>), [evaluation modules](#), and [samples](http://www.ti.com/sc/docs/sampterm.htm) (<http://www.ti.com/sc/docs/sampterm.htm>).

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2017, Texas Instruments Incorporated