

PMP30284 REV A Bill of Materials

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
C1, C9, C11, C12	4	1uF	GRM188R61C105KA93D	MuRata	CAP, CERM, 1 μ F, 16 V,+/- 10%, X5R, 0603	0603
C2	1	0.01uF	GRM188R71E103KA01D	MuRata	CAP, CERM, 0.01 μ F, 25 V,+/- 10%, X7R, 0603	0603
C3	1	180uF	16SVP180M	Panasonic	CAP, Aluminum Polymer, 180 μ F, 16 V,+/- 20%, 0.02 ohm	8x10 SMD
C4, C5	2	22uF	GRM32ER71E226KE15L	MuRata	CAP, CERM, 22 μ F, 25 V,+/- 10%, X7R, 1210	1210
C6	1	470pF	GRM188R71H471KA01D	MuRata	CAP, CERM, 470 pF, 50 V,+/- 10%, X7R, 0603	0603
C7, C8, C14	3	100uF	GRM32ER60J107ME20L	MuRata	CAP, CERM, 100 μ F, 6.3 V,+/- 20%, X5R, 1210	1210
C10	1	0.068uF	GRM188R71C683KA01D	MuRata	CAP, CERM, 0.068 μ F, 16 V,+/- 10%, X7R, 0603	0603
C13	1	6800pF	GRM188R71E682KA01D	MuRata	CAP, CERM, 6800 pF, 25 V,+/- 10%, X7R, 0603	0603
D1	1	40V	B340A-13-F	Diodes Inc.	Diode, Schottky, 40 V, 3 A, SMA	SMA
D2	1	30V	BAT54-7-F	Diodes Inc.	Diode, Schottky, 30 V, 0.2 A, SOT-23	SOT-23
D3	1	3.6V	MMSZ5227B-7-F	Diodes Inc.	Diode, Zener, 3.6 V, 500 mW, SOD-123	SOD-123
J1, J2	2		ED555/2DS	On-Shore Technology	Terminal Block, 3.5mm Pitch, 2x1, TH	7.0x8.2x6.5mm
J3, J4	2		PEC03SAAN	Sullins Connector Solutions	Header, 100mil, 3x1, Tin, THT	Header, 3 PIN, 100mil, Tin
L1	1	10uH	MSD1260-103MLB	Coilcraft	Coupled inductor, 10 μ H, 3.7 A, 0.06 ohm, SMD	MSD1260
Q1	1	-20V	CSD25404Q3	Texas Instruments	MOSFET, P-CH, -20 V, -60 A, DQG0008A (VSON-CLIP-8)	DQG0008A
Q2	1	25V	CSD16340Q3	Texas Instruments	MOSFET, N-CH, 25 V, 60 A, DQG0008A (VSON-CLIP-8)	DQG0008A
R1	1	0.05	LVK12R050FER	Ohmite	RES, 0.05, 1%, 0.5 W, 1206 sense	1206 sense
R2, R4, R7	3	1.00k	CRCW06031K00FKEA	Vishay-Dale	RES, 1.00 k, 1%, 0.1 W, 0603	0603
R3	1	20.0k	CRCW060320K0FKEA	Vishay-Dale	RES, 20.0 k, 1%, 0.1 W, 0603	0603
R6	1	124k	CRCW0603124KFKEA	Vishay-Dale	RES, 124 k, 1%, 0.1 W, 0603	0603
R8	1	33.2k	CRCW060333K2FKEA	Vishay-Dale	RES, 33.2 k, 1%, 0.1 W, 0603	0603
R9	1	49.9	CRCW060349R9FKEA	Vishay-Dale	RES, 49.9, 1%, 0.1 W, 0603	0603
R10, R11	2	10.0	CRCW060310R0FKEA	Vishay-Dale	RES, 10.0, 1%, 0.1 W, 0603	0603
TP1, TP3, TP10	3		5000	Keystone	Test Point, Miniature, Red, TH	Red Miniature Testpoint
TP2, TP4, TP6, TP9	4		5001	Keystone	Test Point, Miniature, Black, TH	Black Miniature Testpoint
TP5	1		5004	Keystone	Test Point, Miniature, Yellow, TH	Yellow Miniature Testpoint
TP7, TP8	2		5002	Keystone	Test Point, Miniature, White, TH	White Miniature Testpoint
U1	1		TLV6001UIDBVR	Texas Instruments	1-MHz, Low-Power Operational Amplifier for Cost-Sensitive Systems, DBV0005A (SOT-23-5)	DBV0005A
U2	1		TPS43000PW	Texas Instruments	Multi-Topology (buck, boost, sepic) High Frequency DC/DC Controller, PW0016A (TSSOP-16)	PW0016A

IMPORTANT NOTICE FOR TI DESIGN INFORMATION AND RESOURCES

Texas Instruments Incorporated ("TI") technical, application or other design advice, services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using any particular TI Resource in any way, you (individually or, if you are acting on behalf of a company, your company) agree to use it solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources.

You understand and agree that you remain responsible for using your independent analysis, evaluation and judgment in designing your applications and that you have full and exclusive responsibility to assure the safety of your applications and compliance of your applications (and of all TI products used in or for your applications) with all applicable regulations, laws and other applicable requirements. You represent that, with respect to your applications, you have all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. You agree that prior to using or distributing any applications that include TI products, you will thoroughly test such applications and the functionality of such TI products as used in such applications. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

You are authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING TI RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY YOU AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

You agree to fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of your non-compliance with the terms and provisions of this Notice.

This Notice applies to TI Resources. Additional terms apply to the use and purchase of certain types of materials, TI products and services. These include; without limitation, TI's standard terms for semiconductor products (<http://www.ti.com/sc/docs/stdterms.htm>), [evaluation modules](#), and [samples](http://www.ti.com/sc/docs/sampterm.htm) (<http://www.ti.com/sc/docs/sampterm.htm>).

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2017, Texas Instruments Incorporated