

**PMP20852 REV A Bill of Materials**

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
I PCB1	1		PMP20852	Any	Printed Circuit Board	
C1	1	470uF	UUD1E471MNL1GS	Nichicon	CAP, AL, 470 µF, 25 V, +/- 20%, 0.09 ohm, SMD	10x10
C2, C3, C10	3	10uF	C3216X7R1V106K160AC	TDK	CAP, CERM, 10 µF, 35 V, +/- 10%, X7R, 1206	1206
C4	1	0.022uF	GRM188R71H223KA01D	MuRata	CAP, CERM, 0.022 µF, 50 V, +/- 10%, X7R, 0603	0603
C5, C17, C18, C19	4	0.1uF	GRM188R71H104KA93D	MuRata	CAP, CERM, 0.1 µF, 50 V, +/- 10%, X7R, 0603	0603
C7	1	1uF	GRM188R71C105KA12D	MuRata	CAP, CERM, 1 µF, 16 V, +/- 10%, X7R, 0603	0603
C8, C9	2	100pF	GRM1885C1H101JA01D	MuRata	CAP, CERM, 100 pF, 50 V, +/- 5%, C0G/NP0, 0603	0603
C11, C12, C13, C14, C15, C16, C20, C21, C22, C23, C24, C25	12	4.7uF	C2012X7R1V475K125AC	TDK	CAP, CERM, 4.7 µF, 35 V, +/- 10%, X7R, 0805	0805
Cx1	1	6800pF	GRM188R71H682KA01D	MuRata	CAP, CERM, 6800 pF, 50 V, +/- 10%, X7R, 0603	0603
Cx2, Cx3, Cx4, Cx5, Cx6, Cx7	6	1000pF	202R18W102KV4E	Johanson Technology	CAP, CERM, 1000 pF, 2000 V, +/- 10%, X7R, 1206_190	1206_190
D1	1	14VWM	SMF14A	Littlefuse	Diode, TVS, Uni, 200Wpk, 14VWM, 23.2VC, SOD-123F	SOD-123F
D2, D3	2	100V	S310FA	Fairchild/ON Semi	Diode, Schottky, 100V, 3A, SOD-123W	SOD-123W
D4, D5, D6	3	200V	SMD1200PL-TP	MicroCommercial	Diode, Schottky, 200V, 1A, SOD-123FL	SOD-123FL
H1, H3, H5, H7	4		1902C	Keystone	Standoff, Hex, 0.5"L #4-40 Nylon	Standoff
H2, H4, H6, H8	4		NY PMS 440 0025 PH	B&F Fastener Supply	Machine Screw, Round, #4-40 x 1/4, Nylon, Philips panhead	Screw
LBL1	1		THT-14-423-10	Brady	Thermal Transfer Printable Labels, 0.650" W x 0.200" H - 10,000 per roll	PCB Label 0.650"H x 0.200"W
Q1	1	40 V	MMBT3904-7-F	Diodes Inc.	Transistor, NPN, 40 V, 0.2 A, SOT-23	SOT-23
Q2	1	60V	CSD18543Q3A	Texas Instruments	MOSFET, N-CH, 60V, 8.1mOhm @ 10Vgs, SOIC-8	CSD19538Q3A
R1	1	0.1	ERJ-8RSJR10V	Panasonic	RES, 0.1, 5%, 0.25 W, 1206	1206
R2	1	4.75k	CRCW12064K75FKEA	Vishay-Dale	RES, 4.75 k, 1%, 0.25 W, 1206	1206
R3	1	49.9k	CRCW060349K9FKEA	Vishay-Dale	RES, 49.9 k, 1%, 0.1 W, 0603	0603
R4	1	8.25k	CRCW06038K25FKEA	Vishay-Dale	RES, 8.25 k, 1%, 0.1 W, 0603	0603
R5	1	2.49k	CRCW06032K49FKEA	Vishay-Dale	RES, 2.49 k, 1%, 0.1 W, 0603	0603
R6	1	36.5k	CRCW060336K5FKEA	Vishay-Dale	RES, 36.5 k, 1%, 0.1 W, 0603	0603
R7	1	10.0k	CRCW060310K0FKEA	Vishay-Dale	RES, 10.0 k, 1%, 0.1 W, 0603	0603
R8	1	0	CRCW06030000Z0EA	Vishay-Dale	RES, 0, 5%, 0.1 W, 0603	0603
R9	1	15.0k	CRCW060315K0FKEA	Vishay-Dale	RES, 15.0 k, 1%, 0.1 W, 0603	0603
R10	1	1.00k	CRCW06031K00FKEA	Vishay-Dale	RES, 1.00 k, 1%, 0.1 W, 0603	0603
R11	1	0.5	RL1210FR-070R5L	Yageo	RES, 0.5 ohm, 1%, 0.5W, 2010	2010
R12, R13, R14	3	20.0k	CRCW060320K0FKEA	Vishay-Dale	RES, 20.0 k, 1%, 0.1 W, 0603	0603
R15, R16, R17, R18, R19, R20	6	100k	CRCW0603100KJNEA	Vishay-Dale	RES, 100 k, 5%, 0.1 W, 0603	0603
R21, R23, R25	3	1.21Meg	CRCW06031M21FKEA	Vishay-Dale	RES, 1.21 M, 1%, 0.1 W, 0603	0603
R22, R24, R26	3	100k	CRCW0603100KFKEA	Vishay-Dale	RES, 100 k, 1%, 0.1 W, 0603	0603
R27, R28, R29, Rx3, Rx4, Rx5	6	4.02	CRCW12064R02FKEA	Vishay-Dale	RES, 4.02, 1%, 0.25 W, 1206	1206
R30	1	150	CRCW0603150RFKEA	Vishay-Dale	RES, 150, 1%, 0.1 W, 0603	0603
R33	1	49.9	CRCW060349R9FKEA	Vishay-Dale	RES, 49.9, 1%, 0.1 W, 0603	0603
Rx1	1	3.65k	CRCW06033K65FKEA	Vishay-Dale	RES, 3.65 k, 1%, 0.1 W, 0603	0603
Rx2	1	22.1	CRCW060322R1FKEA	Vishay-Dale	RES, 22.1, 1%, 0.1 W, 0603	0603
T1	1		750316914	Würth Elektronik	Transformer, Pri:Sec = 1:3, Pri:Aux = 1:1.5, TH	
TP1, TP2	2		1503-2	Keystone	Terminal, Turret, TH, Double	Keystone1503-2

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
TP3, TP4, TP8, TP9, TP10, TP17, TP18, TP19, TP20	9		5012	Keystone	Test Point, Multipurpose, White, TH	White Multipurpose Testpoint
TP5, TP6, TP7	3		5014	Keystone	Test Point, Multipurpose, Yellow, TH	Yellow Multipurpose Testpoint
TP11, TP13, TP15	3		5010	Keystone	Test Point, Multipurpose, Red, TH	Red Multipurpose Testpoint
TP12, TP14, TP16, TP21	4		5011	Keystone	Test Point, Multipurpose, Black, TH	Black Multipurpose Testpoint
U1	1		UCC2805PW	Texas Instruments		
U2, U3, U4	3		LP2951-33DRGR	Texas Instruments	Adjustable Micropower Voltage Regulators with Shutdown, DRG0008A	DRG0008A
C6	0	100pF	GRM1885C1H101JA01D	MuRata	CAP, CERM, 100 pF, 50 V, +/- 5%, C0G/NP0, 0603	0603
C26	0	100pF	GRM2165C2A101JA01D	MuRata	CAP, CERM, 100 pF, 100 V, +/- 5%, C0G/NP0, 0805	0805
FID1, FID2, FID3	0		N/A	N/A	Fiducial mark. There is nothing to buy or mount.	Fiducial
R31	0	4.99k	CRCW08054K99FKEA	Vishay-Dale	RES, 4.99 k, 1%, 0.125 W, 0805	0805
R32	0	10	CRCW201010R0JNEF	Vishay-Dale	RES, 10, 5%, 0.75 W, AEC-Q200 Grade 0, 2010	2010

## IMPORTANT NOTICE FOR TI DESIGN INFORMATION AND RESOURCES

Texas Instruments Incorporated ("TI") technical, application or other design advice, services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using any particular TI Resource in any way, you (individually or, if you are acting on behalf of a company, your company) agree to use it solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources.

You understand and agree that you remain responsible for using your independent analysis, evaluation and judgment in designing your applications and that you have full and exclusive responsibility to assure the safety of your applications and compliance of your applications (and of all TI products used in or for your applications) with all applicable regulations, laws and other applicable requirements. You represent that, with respect to your applications, you have all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. You agree that prior to using or distributing any applications that include TI products, you will thoroughly test such applications and the functionality of such TI products as used in such applications. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

You are authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING TI RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY YOU AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

You agree to fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of your non-compliance with the terms and provisions of this Notice.

This Notice applies to TI Resources. Additional terms apply to the use and purchase of certain types of materials, TI products and services. These include; without limitation, TI's standard terms for semiconductor products (<http://www.ti.com/sc/docs/stdterms.htm>), [evaluation modules](#), and [samples](http://www.ti.com/sc/docs/sampterm.htm) (<http://www.ti.com/sc/docs/sampterm.htm>).

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265  
Copyright © 2017, Texas Instruments Incorporated