

Dual-Mode Bluetooth® CC2564 Module Evaluation Board

1 Introduction

TI intends the CC2564MODNEM board to evaluate of the dual-mode *Bluetooth*® CC2564 module which supports classic *Bluetooth* and *Bluetooth* low energy wireless technology. The CC2564MODNEM board works with TI's Hardware Development Kit (HDKs), such as the following:

- MSP-EXP430F5529
- MSP-EXP430F5438
- DK-TM4C123G
- DK-TM4C129X

The TI CC256x *Bluetooth* device is a complete basic rate (BR), enhanced data rate (EDR), and LE host controller interface (HCI) solution that reduces the effort of the designer and time to market for your solution. Based on TI's seventh-generation core, the device is a product-proven solution that supports *Bluetooth* 4.1 dual-mode protocols.

This document is an overview of the CC2564MODNEM board and describes the hardware and software tools for the board. This quick start guide shows basic settings for the CC2564MODNEM board. For further details, see the *Dual-Mode Bluetooth CC2564 Module Evaluation Board User's Guide* ([SWRU390](#)). See [Figure 1](#) to view the CC2564MODNEM board.




Figure 1. CC2564MODNEM Board

2 CC2564MODN Kit Contents

The contents of the kit are as follows:

- One CC2564MODNEM board with the TI dual-mode *Bluetooth* CC2564 module
- One block jumper for the MSP-EXP430F5438 board
- Four Jumpers for the MSP-EXP430F5529 Board

MSP430 is a trademark of Texas Instruments.
Bluetooth is a registered trademark of Bluetooth SIG.

3 Hardware and Software Requirements

For a complete evaluation, the CC2564MODNEM board requires the hardware (see [Figure 2](#)) and software tools from the following list:

- Hardware
 - An MSP430™ experimenter board (sold separately) or a TM4C development kit (sold separately):
 - MSP430 experimenter board options:
 - [MSP-EXP430F5529](#)
 - [MSP-EXP430F5438](#)
 - TM4C development kit options
 - [DK-TM4C123G](#)
 - [DK-TM4C129X](#)
- Software
 - TI dual-mode *Bluetooth* stack
 - On MSP430™ MCUs: [CC256XMSPBTBLESW](#)
 - On TM4C MCUs: [CC256XM4BTBLESW](#)
 - Other MCUs
 - On STM32F4 MCUs: [CC256XSTBTBLESW](#)

[Figure 2](#) shows example hardware setups for the CC2564MODNEM board using MSP-EXP430F5529 and MSP-EXP430F5438.




Figure 2. Hardware Setup

4 CC2564MODNEM Overview

The CC2564MODNEM board has the following connectors:

- EM (default): I/Os are at 3.3 V.
- COM: I/Os are at 1.8 V.

Figure 3 and Figure 4 show an overview of the front and back of the CC2564MODNEM board.




Figure 3. CC2564MODNEM Board Front Overview




Figure 4. CC2564MODNEM Board Back Connectors

5 CC2564MODNEM Board Settings

5.1 EM Connector

The EM connectors can be mounted on a wide variety of TI MCU platforms, such as the MSP430 (MSP-EXP430F5529 and MSP-EXP430F5438) and TM4C (DK-TM4C123G and DK-TM4C129X). All EM inputs and outputs are at 3.3 V. The pin assignments refer to the front side (CC2564MODN). For example, MODULE_UART_RX refers to the receiving UART RX pin on the CC2564MODN device that connects to the UART_TX pin on the MCU. For the standard pinouts for EM1 and EM2, see [Table 1](#) and [Table 2](#), respectively.

Table 1. EM1 Standard Pinout

Pin	EM Adapter Assignment ⁽¹⁾	Pin	EM Adaptor Assignments ⁽¹⁾
1	GND	2	SWRU4369603
2	MODULE_UART_CTS	4	N/C
5	SLOW_CLK	6	N/C
7	MODULE_UART_RX	8	N/C
9	MODULE_UART_TX	10	N/C
11	N/C	12	N/C
13	N/C	14	N/C
15	N/C	16	N/C
17	N/C	18	N/C
19	GND	20	N/C

⁽¹⁾ NC = not connected

Table 2. EM2 Standard Pinout

Pin	EM Adapter Assignment ⁽¹⁾	Pin	EM Adaptor Assignments ⁽¹⁾
1	N/C	2	N/C
2	N/C	4	N/C
5	N/C	6	N/C
7	3.3 V	8	MODULE_AUDIO_DATA_OUT
9	3.3 V	10	MODULE_AUDIO_DATA_IN
11	MODULE_AUDIO_FSINK	12	N/C
13	N/C	14	N/C
15	N/C	16	N/C
17	MODULE_AUDIO_CLK	18	MODULE_UART_RTS
19	nSHUTD	20	N/C

⁽¹⁾ NC = not connected

5.2 COM Connector Settings

The COM connector interfaces with TI's MPU platforms, such as the AM335x evaluation module (TMDXEVM3358). For the pinout, see [Table 3](#).

NOTE: All inputs and outputs for the COM connector are 1.8 V.

Some components must be DNI (do not install) to use the COM connector. For further details, refer to the *Dual-Mode Bluetooth CC2564 Module Evaluation Board User's Guide* ([SWRU390](#)).

Table 3. COM Connector Pinout

Pin ⁽¹⁾	Relevant COM Connector Pin Assignment
1	SLOW_CLK_EDGE
8	1V8_IN
52	AUD_CLK_1V8
54	AUD_FSYNC_1V8
56	AUD_IN_1V8
58	AUD_OUT_1V8
66	HCI_TX_1V8
68	HCI_RX_1V8
70	HCI_CTS_1V8
72	HCI_RTS_1V8
76	TX_DEBUG_1V8
89	nSHUTDOWN_1V8
3, 9, 19, 37, 47, 63, 77, 83, 87, 95, 97	GND
2, 6, 18, 22, 42, 60, 64, 92	GND

⁽¹⁾ Pins not listed are N/C.

IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products (also referred to herein as "components") are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of significant portions of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI components or services with statements different from or beyond the parameters stated by TI for that component or service voids all express and any implied warranties for the associated TI component or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards which anticipate dangerous consequences of failures, monitor failures and their consequences, lessen the likelihood of failures that might cause harm and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed a special agreement specifically governing such use.

Only those TI components which TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components which have **not** been so designated is solely at the Buyer's risk, and that Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.

Products

Audio	www.ti.com/audio
Amplifiers	amplifier.ti.com
Data Converters	dataconverter.ti.com
DLP® Products	www.dlp.com
DSP	dsp.ti.com
Clocks and Timers	www.ti.com/clocks
Interface	interface.ti.com
Logic	logic.ti.com
Power Mgmt	power.ti.com
Microcontrollers	microcontroller.ti.com
RFID	www.ti-rfid.com
OMAP Applications Processors	www.ti.com/omap
Wireless Connectivity	www.ti.com/wirelessconnectivity

Applications

Automotive and Transportation	www.ti.com/automotive
Communications and Telecom	www.ti.com/communications
Computers and Peripherals	www.ti.com/computers
Consumer Electronics	www.ti.com/consumer-apps
Energy and Lighting	www.ti.com/energy
Industrial	www.ti.com/industrial
Medical	www.ti.com/medical
Security	www.ti.com/security
Space, Avionics and Defense	www.ti.com/space-avionics-defense
Video and Imaging	www.ti.com/video

TI E2E Community

e2e.ti.com