

TIDA-01427 REV E2 Bill of Materials

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
I PCB1	1		TIDA-01427	Any	Printed Circuit Board	
C1, C7, C10, C13, C14, C18, C25	7	10uF	GRM32ER71H106KA12L	MuRata	CAP, CERM, 10 µF, 50 V, +/- 10%, X7R, 1210	1210
C2, C9, C24	3	0.1uF	GCM188R71H104KA57D	MuRata	CAP, CERM, 0.1 µF, 50 V, +/- 10%, X7R, 0603	0603
C3, C5	2	1uF	GRM188R61H105KAALD	MuRata	CAP, CERM, 1 µF, 50 V, +/- 10%, X5R, 0603	0603
C4	1	47uF	GRM32EC81C476ME15L	MuRata	CAP, CERM, 47 µF, 16 V, +/- 20%, X6S, 1210	1210
C6, C11, C12, C19, C21, C26	6	0.01uF	C0603C103J5RACTU	Kemet	CAP, CERM, 0.01 µF, 50 V, +/- 5%, X7R, 0603	0603
C8, C22, C23	3	22uF	GRM32ER71E226KE15L	MuRata	CAP, CERM, 22uF, 25V, +/-10%, X7R, 1210	1210
C15	1	4.7uF	GRM319R61E475KA12D	MuRata	CAP, CERM, 4.7 µF, 25 V, +/- 10%, X5R, 1206	1206
C16	1	0.1uF	C1608X7R1H104K	TDK	CAP, CERM, 0.1uF, 50V, +/-10%, X7R, 0603	0603
C17	1	1uF	C1608X7R1E105K080AB	TDK	CAP, CERM, 1uF, 25V, +/-10%, X7R, 0603	0603
C20	1	1000pF	GRM188R71H102JA01D	MuRata	CAP, CERM, 1000 pF, 50 V, +/- 5%, X7R, 0603	0603
C27, C28, C30, C33, C34, C43, C45, C52	8	1uF	GRM188R71E105KA12D	MuRata	CAP, CERM, 1 µF, 25 V, +/- 10%, X7R, 0603	0603
C29, C32, C35, C38, C40, C42, C56, C58, C61, C62, C73	11	10uF	C1608X5R1E106M080AC	TDK	CAP, CERM, 10 µF, 25 V, +/- 20%, X5R, 0603	0603
C31, C39, C41, C44, C57, C60, C63, C64, C74, C77	10	0.1uF	C0603C104J3RACTU	Kemet	CAP, CERM, 0.1 µF, 25 V, +/- 5%, X7R, 0603	0603
C59, C75	2	750pF	C0603C751J5GACTU	Kemet	CAP, CERM, 750 pF, 50 V, +/- 5%, C0G/NP0, 0603	0603
C65, C67	2	20pF	GQM2195C1H200JB01D	MuRata	CAP, CERM, 20 pF, 50 V, +/- 5%, C0G/NP0, 0805	0805
C66, C70	2	0.01uF	GRM188R71H103KA01D	MuRata	CAP, CERM, 0.01 µF, 50 V, +/- 10%, X7R, 0603	0603
C68	1	1500pF	08055A152JAT2A	AVX	CAP, CERM, 1500 pF, 50 V, +/- 5%, C0G/NP0, 0805	0805
C69, C76	2	10uF	0805YD106KAT2A	AVX	CAP, CERM, 10 µF, 16 V, +/- 10%, X5R, 0805	0805
C71, C72	2	150pF	06035A151JAT2A	AVX	CAP, CERM, 150 pF, 50 V, +/- 5%, C0G/NP0, 0603	0603
D1, D2, D4, D5	4	30V	DFLS130L-7	Diodes Inc.	Diode, Schottky, 30 V, 1 A, PowerDI123	PowerDI123
D3	1	60V	RB160M-60TR	Rohm	Diode, Schottky, 60 V, 1 A, SOD-123	SOD-123
GND, N13V, N15V, P5V, P13V, P15V, REF_N10V_B, REF_P10V, REF_P10V_B, VOCM	10		5007	Keystone	Test Point, Compact, White, TH	White Compact Testpoint
H1, H2, H3, H4	4		NY PMS 440 0025 PH	B&F Fastener Supply	Machine Screw, Round, #4-40 x 1/4, Nylon, Philips panhead	Screw
H5, H6, H7, H8	4		1902C	Keystone	Standoff, Hex, 0.5"L #4-40 Nylon	Standoff
J1	1		ED555/3DS	On-Shore Technology	Terminal Block, 3.5mm Pitch, 3x1, TH	10.5x8.2x6.5mm
J2	1		39357-0002	Molex	Terminal Block, 3.5 mm, 2x1, Tin, TH	Terminal Block, 3.5 mm, 2x1, TH
J3	1		61301011121	Würth Elektronik	Header, 2.54mm, 10x1, Gold, TH	Header, 2.54mm, 10x1, TH
J4, J5, J6, J7	4		901-144-8RFX	Amphenol RF	SMA Straight Jack, Gold, 50 Ohm, TH	SMA Straight Jack, TH

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
L1	1	100uH	SRF1260-101M	Bourns	Inductor, Drum Core, Ferrite, 100 µH, 1.78 A, 0.171 ohm, SMD	12.5x12.5mm
L2, L4	2	1000 ohm	MPZ2012S102AT000	TDK Corporation	FERRITE BEAD 1 KOHM 0805 1LN	0805
R1, R2, R3, R6, R11, R18, R20, R21, R22, R23, R31, R35, R37, R39, R40, R43, R45, R53, R54	19	0	CRCW06030000Z0EA	Vishay-Dale	RES, 0, 5%, 0.1 W, 0603	0603
R4	1	102k	CRCW0603102KFKEA	Vishay-Dale	RES, 102 k, 1%, 0.1 W, 0603	0603
R5	1	3.01k	CRCW06033K01FKEA	Vishay-Dale	RES, 3.01 k, 1%, 0.1 W, 0603	0603
R7	1	10.2k	RC0603FR-0710K2L	Yageo America	RES, 10.2 k, 1%, 0.1 W, 0603	0603
R8	1	768k	CRCW0603768KFKEA	Vishay-Dale	RES, 768 k, 1%, 0.1 W, 0603	0603
R9	1	49.9k	CRCW060349K9FKEA	Vishay-Dale	RES, 49.9 k, 1%, 0.1 W, 0603	0603
R10, R15	2	20.0k	CRCW060320K0FKEA	Vishay-Dale	RES, 20.0 k, 1%, 0.1 W, 0603	0603
R12	1	137k	CRCW0603137KFKEA	Vishay-Dale	RES, 137 k, 1%, 0.1 W, 0603	0603
R13	1	115k	CRCW0603115KFKEA	Vishay-Dale	RES, 115 k, 1%, 0.1 W, 0603	0603
R14	1	22.6k	CRCW060322K6FKEA	Vishay-Dale	RES, 22.6 k, 1%, 0.1 W, 0603	0603
R16	1	10.5k	RC0603FR-0710K5L	Yageo America	RES, 10.5 k, 1%, 0.1 W, 0603	0603
R17, R24, R25, R36, R41, R47, R51, R57, R58, R59	10	1.00k	RT0603DRE071KL	Yageo America	RES, 1.00 k, 0.5%, 0.1 W, 0603	0603
R19	1	1.00	CRCW06031R00FKEA	Vishay-Dale	RES, 1.00, 1%, 0.1 W, 0603	0603
R29	1	4.02k	RT0603DRE074K02L	Yageo America	RES, 4.02 k, 0.5%, 0.1 W, 0603	0603
R33	1	374	RT0603DRE07374RL	Yageo America	RES, 374, 0.5%, 0.1 W, 0603	0603
R38, R49	2	348	CRCW2010348RFKEF	Vishay-Dale	RES, 348, 1%, 0.75 W, AEC-Q200 Grade 0, 2010	2010
R42, R48	2	499	RT0603DRE07499RL	Yageo America	RES, 499, 0.5%, 0.1 W, 0603	0603
R44, R46	2	28.0	RT1206DRD0728RL	Yageo	RES, 28.0, 0.5%, 0.25 W, 1206	1206
R56	1	590	RT0603DRE07590RL	Yageo America	RES, 590, 0.5%, 0.1 W, 0603	0603
U1	1		TPS7A4700RGWR	Texas Instruments	36-V, 1-A, 4.17-uVRMS, RF LDO Voltage Regulator, RGW0020A (VQFN-20)	RGW0020A
U2	1		TPS7A3901DSC	Texas Instruments	Wide-VIN (+/-33 V), 150-mA, Spilt-Rail Output, Positive and Negative LDO Voltage Regulator with Startup Tracking, DSC0010J (WSO-10)	DSC0010J
U3	1		LM5160DNTR	Texas Instruments	Wide Input 65V, 1.5A Synchronous Step-Down DC-DC Converter, DNT0012B	DNT0012B
U4	1		REF5010AIDGKR	Texas Instruments	Low Noise, Very Low Drift, Precision Voltage Reference, -40 to 125 degC, 8-pin MSOP (DGK), Green (RoHS & no Sb/Br)	DGK0008A
U5, U8	2		OPA2209AIDGKR	Texas Instruments	2.2 nV/rtHz, 18 MHz, Precision, RRO, Operational Amplifier, 4.5 to 36 V, -40 to 125 degC, 8-pin SOP (DGK0008A), Green (RoHS & no Sb/Br)	DGK0008A
U9	1		DAC8802IPWR	Texas Instruments	Dual, Serial Input 14-Bit Multiplying Digital-to-Analog Converter, PW0016A (TSSOP-16)	PW0016A
U10	1		THS4130IDGNR	Texas Instruments	Fully Differential Input/Output Low Noise Amplifier, DGN0008D (VSSOP-8)	DGN0008D
VCNTLM, VCNTLP	2		5001	Keystone	Test Point, Miniature, Black, TH	Black Miniature Testpoint
FID1, FID2, FID3, FID4, FID5, FID6	0		N/A	N/A	Fiducial mark. There is nothing to buy or mount.	Fiducial
R34, R50	0	0	CRCW06030000Z0EA	Vishay-Dale	RES, 0, 5%, 0.1 W, 0603	0603

IMPORTANT NOTICE FOR TI DESIGN INFORMATION AND RESOURCES

Texas Instruments Incorporated ("TI") technical, application or other design advice, services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using any particular TI Resource in any way, you (individually or, if you are acting on behalf of a company, your company) agree to use it solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources.

You understand and agree that you remain responsible for using your independent analysis, evaluation and judgment in designing your applications and that you have full and exclusive responsibility to assure the safety of your applications and compliance of your applications (and of all TI products used in or for your applications) with all applicable regulations, laws and other applicable requirements. You represent that, with respect to your applications, you have all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. You agree that prior to using or distributing any applications that include TI products, you will thoroughly test such applications and the functionality of such TI products as used in such applications. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

You are authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING TI RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY YOU AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

You agree to fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of your non-compliance with the terms and provisions of this Notice.

This Notice applies to TI Resources. Additional terms apply to the use and purchase of certain types of materials, TI products and services. These include; without limitation, TI's standard terms for semiconductor products (<http://www.ti.com/sc/docs/stdterms.htm>), [evaluation modules](#), and [samples](http://www.ti.com/sc/docs/sampterm.htm) (<http://www.ti.com/sc/docs/sampterm.htm>).

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2017, Texas Instruments Incorporated