

PMP40871 REV E1 Bill of Materials

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
C1	1	4.7uF	GRM188R61C475KAAJ	MuRata	CAP, CERM, 4.7 uF, 16 V, +/- 10%, X5R, 0603	0603
C3, C4	2	0.47uF	C2012X7S2A474K125AB	TDK	CAP, CERM, 0.47 uF, 100 V,+/- 10%, X7S, 0805	0805
C8, C9	2	10uF	CGA5L1X7R1H106K160AC	TDK	CAP, CERM, 10 uF, 50 V,+/- 10%, X7R, AEC-Q200 Grade 1, 1206	1206
C10, C11	2	2.2uF	CGA5L3X7S2A225K160AB	TDK	CAP, CERM, 2.2 uF, 100 V,+/- 10%, X7S, AEC-Q200 Grade 1, 1206	1206
CBYP	1	0.01uF	C0603C103J1RACTU	Kemet	CAP, CERM, 0.01 uF, 100 V,+/- 5%, X7R, 0603	0603
D1	1	100V	BAS16D-E3-08	Vishay-Semiconductor	Diode, Switching, 100 V, 0.25 A, AEC-Q101, SOD-123	SOD-123
J1, J2, JP3	3		PEC03SAAN	Sullins Connector Solutions	Header, 100mil, 3x1, Tin, TH	Header, 3 PIN, 100mil, Tin
J5, J6	2		PEC02SAAN	Sullins Connector Solutions	Header, 100mil, 2x1, Tin, TH	Header, 2 PIN, 100mil, Tin
L1	1	4.7uH	DFE201612E-4R7M=P2	MuRata	Inductor, Shielded, Metal Composite, 4.7 uH, 1.2 A, 0.252 ohm, SMD	2x1.6mm
R1	1	392k	RT0603BRD07392KL	Yageo America	RES, 392 k, 0.1%, 0.1 W, 0603	0603
R2, R4	2	10.0k	CRCW060310K0FKEA	Vishay-Dale	RES, 10.0 k, 1%, 0.1 W, AEC-Q200 Grade 0, 0603	0603
R5	1	475k	RC0603FR-07475KL	Yageo	RES, 475 k, 1%, 0.1 W, 0603	0603
R6	1	12.0k	RC0603FR-0712KL	Yageo	RES, 12.0 k, 1%, 0.1 W, 0603	0603
U1	1		TPS61391RGT	Texas Instruments	85-VOUT Boost Converter with Current Mirror and Sample / Hold, RGT0016C (VQFN-16)	RGT0016C
U2	1		TPS7A4101DGNR	Texas Instruments	Single Output LDO, 50 mA, Adjustable 1.175 to 48 V Output, 7 to 50 V Input, 8-pin MSOP (DGN), -40 to 125 degC, Green (RoHS & no Sb/Br)	DGN0008B
C0	0	100uF	EEHZA1E101XP	Panasonic	CAP, Polymer Hybrid, 100 uF, 25 V, +/- 20%, 30 ohm, 6.3x7.7 SMD	6.3x7.7

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale (<https://www.ti.com/legal/termsofsale.html>) or other applicable terms available either on [ti.com](https://www.ti.com) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2021, Texas Instruments Incorporated